


Dual Operational Amplifier

FEATURES

- No Frequency Compensation Required
- Short-Circuit Protection
- Wide Common-Mode and Differential Voltage Ranges
- Low-Power Consumption
- No Latch Up When Input Common Mode Range is Exceeded




DESCRIPTION

The LM1458 and the LM1558 are general purpose dual operational amplifiers. The two amplifiers share a common bias network and power supply leads. Otherwise, their operation is completely independent.

The LM1458 is identical to the LM1558 except that the LM1458 has its specifications guaranteed over the temperature range from 0° C to $+70^{\circ}$ C instead of -55° C to $+125^{\circ}$ C.

Connection Diagram





Absolute Maximum Ratings

Supply Voltage	
LM1558	±22V
LM1458	±18V
Power Dissipation	
LM1558H/LM1458H	500 mW
LM1458N	400 mW
Differential Input Voltage	±30V
Input Voltage	±15V
Output Short-Circuit Duration	Continuous
Operating Temperature Range LM1558 LM1458	−55°C to +125°C 0°C to +70°C
Storage Temperature Range	−65°C to +150°C
Lead Temperature (Soldering, 10 sec.)	260°C
Soldering Information	
PDIP Package	
Soldering (10 seconds)	260°C
SOIC Package	
Vapor Phase (60 seconds)	215°C
Infrared (15 seconds)	220°C
See AN-450 "Surface Mounting Methods and Their Effect on Product Reliability"	for other methods of soldering surface mount devices.
ESD tolerance	300V

- (1) "Absolute Maximum Ratings" indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not guarantee specific performance limits.
- (2) The maximum junction temperature of the LM1558 is 150 C, while that of the LM1458 is 100 C. For operating at elevated temperatures, devices in the LMC package must be derated based on a thermal resistance of 150°C/W, junction to ambient or 20°C/W, junction to case. For the PDIP the device must be derated based on a thermal resistance of 187°C/W, junction to ambient.
- (3) For supply voltages less than ±15V, the absolute maximum input voltage is equal to the supply voltage.
- (4) Human body model, 1.5 kΩ in series with 100 pF.

Electrical Characteristics (1)

Parameter	Conditions	LM1558			LM1458			Units
		Min	Тур	Max	Min	Тур	Max	
Input Offset Voltage	$T_A = 25$ °C, $R_S \le 10 \text{ k}\Omega$		1.0	5.0		1.0	6.0	mV
Input Offset Current	T _A = 25°C		80	200		80	200	nA
Input Bias Current	T _A = 25°C		200	500		200	500	nA
Input Resistance	T _A = 25°C	0.3	1.0		0.3	1.0		ΜΩ
Supply Current Both Amplifiers	$T_A = 25^{\circ}C, V_S = \pm 15V$		3.0	5.0		3.0	5.6	mA
Large Signal Voltage Gain	$T_A = 25$ °C, $V_S = \pm 15$ V	50	160		20	160		V/mV
	$V_{OUT} = \pm 10V, R_L \ge 2 k\Omega$							
Input Offset Voltage	R _S ≤ 10 kΩ			6.0			7.5	mV
Input Offset Current				500			300	nA
Input Bias Current				1.5			0.8	μA
Large Signal Voltage Gain	$V_S = \pm 15V, V_{OUT} = \pm 10V$	25			15			V/mV
	$R_L \ge k\Omega$							
Output Voltage Swing	$V_S = \pm 15V, R_L = 10 \text{ k}\Omega$	±12	±14		±12	±14		V
	$R_L = 2 k\Omega$	±10	±13		±10	±13		V


⁽¹⁾ These specifications apply for $V_S = \pm 15V$ and $-55^{\circ}C \le T_A \le 125^{\circ}C$, unless otherwise specified. With the LM1458, however, all specifications are limited to $0^{\circ}C \le T_A \le 70^{\circ}C$ and $V_S = \pm 15V$.



Electrical Characteristics (1) (continued)

Parameter	Conditions	LM1558			LM1458			Units
		Min	Тур	Max	Min	Тур	Max	
Input Voltage Range	$V_S = \pm 15V$	±12			±12			V
Common Mode Rejection Ratio	R _S ≤ 10 kΩ	70	90		70	90		dB
Supply Voltage Rejection Ratio	$R_S \le 10 \text{ k}\Omega$	77	96		77	96		dB

SCHEMATIC DIAGRAM





Numbers in parentheses are pin numbers for amplifier B.



PACKAGE









UNIT: mm							
DIM.	MIN	TYP	MAX	DIM.	MIN	TYP	MAX
A	4.520	4.570	4.620	a	0.400	0.420	0.440
A1	0.100	ı	0.250	ь	1.260	1.270	1.280
В	4.800	4.920	5.100	Q	0°	-	8°
С	5.800	6.100	6.250				
C1	3.800	3.900	4.000	·		·	
D	0.400	_	0.950				

DIP8







UNIT: mm							
DIM.	MIN	TYP	MAX	DIM.	MIN	TYP	MAX
A	6.100	6.300	6.680	a	1.504	1.524	1.544
В	9.000	9.200	9.500	b	-	0.889	-
D	8.400	8.700	9.000	С	0.437	0.457	0.477
D1	7.42	7.62	7.82	d	2.530	2.540	2.550
Е	3.100	3. 300	3.550	L	0.500	-	0.700
				L1	3.000	3.200	3.600



Important statement:

Huaguan Semiconductor Co,Ltd. reserves the right to change the products and services provided without notice. Customers should obtain the latest relevant information before ordering, and verify the timeliness and accuracy of this information.

Customers are responsible for complying with safety standards and taking safety measures when using our products for system design and machine manufacturing to avoid potential risks that may result in personal injury or property damage.

Our products are not licensed for applications in life support, military, aerospace, etc., so we do not bear the consequences of the application of these products in these fields.

Our documentation is only permitted to be copied without any tampering with the content, so we do not accept any responsibility or liability for the altered documents.