


Multilayer Ceramic Chip Capacitor

Part Number: 0805J1K00470JKT Description: 0805 1000V 47pF ±5% C0G/NP0 (1B) to AEC-Q200

A range of C0G MLC capacitors fully tested and approved to automotive specification AEC-Q200. Available in 0603 to 3640 chip sizes with capacitance values up to 5.6uF as standard. A variety of termination options are available, including FlexiCap™, the world's

first commercially available flexible termination.



Mechanical Specification

Size Code

Length (L1) in mm (")

Width (W) in mm (")

Thickness (T) in mm (")

Minimum Termination Band (L2,L3) in mm (")

Maximum Termination Band (L2,L3) in mm (")

Termination Material

Solderability

Packaging

0805

 $2.0 \pm 0.20 (0.079 \pm 0.008)$

 $1.25 \pm 0.20 \ (0.049 \pm 0.008)$

1.37 Max (0.054 Max)

0.25 (0.010)

0.75 (0.030)

Nickel Barrier, Sn Plated Solder (RoHS compliant)

IEC-60068-2-58

7" Reel Horizontal Orientation, 3000 per reel

General Electrical Specification

Rated Voltage

Nominal Capacitance Value

Capacitance Tolerance

Tangent of Loss Angle (Tan δ)

Capacitance and Tan δ Test Conditions

Voltage Proof

(Voltage applied for 5 secs max. @ 50mA max. charge current)

Min Insulation Resistance (IR)

Dielectric Classification

Rated Temperature Range

Maximum Capacitance Change over Temperature Range

Climatic Category (IEC)
Ageing Characteristic

1000Vdc

47pF

±5%

0.00153

1.0Vrms @ 1MHz

1500Vdc

100.00GOhm @ 100Vdc

C0G/NP0 (1B) to AEC-Q200

-55°C / +125°C

No DC Voltage 0±30ppm/°C

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data

for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

Rated DC Voltage -

55/125/56

Zero

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com
Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Friday, January 18, 2019

20190118 062354584UTC



Multilayer Ceramic Chip Capacitor

Part Number: 0805J1K00470JKT Description: 0805 1000V 47pF ±5% C0G/NP0 (1B) to AEC-Q200

Environmental

RoHS Compliant to 2011/65/EC as amended by 2015/863/EU

Compliant

REACH Compliant

191 compliant

California Proposition 65

No exposure risk


Board Layout

Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.

Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.

IPC-7351 pad design


	0805	
С	1.80mm	0.071"
Υ	1.15mm	0.045"
X	1.45mm	0.057"



Packaging

Tape packaging information for tape-and-reel parts:

Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.




Soldering

Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.

Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

PdAg terminations are primarily intended for conductive epoxy attachment - they may be suitable for soldering but trials are recommended.



Application notes with mounting and handling guidance are available on request.

Compex DLI Johanson MFG Novacap Syfer Voltronics

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

© The information contained on this drawing is omissions ex

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and

omissions excepted.

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data

for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

Date: Friday, January 18, 2019