

## Multilayer Ceramic Chip Capacitor

no man	- offen - Toelhonioo			1812 250Vac 50/60Hz / 2500Vdc 470pF
Part Number:	1812YA250471K	ETSY2	Description:	±10% X7R (2R1) to AEC-Q200
Approval	IEC/EN60384-14:2013			$\rightarrow$
Specifications:	UL-60950-1, 2nd Ed			
	CSA 60950-1-07 2nd Ed			, <b>~</b> .
Certification:	Unmarked parts are unce manufactured in accorda specifications.		*	Ť
Classification:	These capacitors comply requirements of IEC/EN class X1.			
Component Marking and Certification Bodies:				L2- F
	Not Applicable			
		Mechanical	Specification	
Size Code			1812	
Length (L1) in mm (")			4.5 ± 0.30 (0.180 ± 0.012)	
Width (W) in mm (")			3.2 ± 0.30 (0.126 ± 0.012)	
Thickness (T) in mm (")	)		2.5 Max (0.1 Max)	
Minimum Termination Band (L2,L3) in mm (")			0.50 (0.020)	
Maximum Termination Band (L2,L3) in mm (")			0.80 (0.030)	
Minimum Band Gap (L4) in mm (")		3.0 (0.118)		
Termination Material			FlexiCap ™ Polyme (RoHS compliant)	er termination, Nickel barrier, Sn Plated Solder
Solderability			IEC-60068-2-58	
Packaging		7" Reel Horizontal Orientation, 500 per reel		
	Ge	eneral Electri	cal Specificat	ion
Rated Voltage			250Vac 50/60Hz / 2500Vdc 1kV impulse	
Nominal Capacitance Value			470pF	
Capacitance Tolerance			±10%	
Tangent of Loss Angle (Tan $\delta$ )			≤0.025	
Capacitance and Tan $\delta$ Test Conditions			1.0Vrms @ 1kHz	
Voltage Proof		3000Vdc/2000Vac		
(Voltage applied for 5 secs max. @ 50mA max. charge current)				
Min Insulation Resistance (IR)		100.00GOhm @ 100Vdc		
Dielectric Classification		X7R (2R1) to AEC-Q200		
Rated Temperature Range		-55°C / +125°C		
Maximum Capacitance Change over Temperature Range		No DC Voltage Rated DC Voltage	±15% -	
Climatic Category (IEC)			55/125/56	
Ageing Characteristic			<2% per decade	
Knowles Precisio				irmed valid on the date generated, the latest published dat
		nd is available at http://w	ww.knowlescapacitors.com or by contacting us.	
confidential and may not b		ained on this drawing is e copied in whole or part ir	n omissions excepted.	
		hird party without the consen comer mentioned within this		



## **Multilayer Ceramic Chip Capacitor**

ETSY2	Description:	1812 250Vac 50/60Hz / 2500Vdc 470pF ±10% X7R (2R1) to AEC-Q200					
Environmental							
RoHS Compliant to 2011/65/EC as amended by 2015/863/EU Compliant							
	191 compliant						
	No exposure risk						
Board Layout							
capacitors can accordance with c Requirements n Standards, but shown to reduce ad width to less of the chip on the bifications to the ormal coating to ote AN0043 for		IPC-7351 pad design 1812 C 4.00mm 0.157" Y 1.55mm 0.061" X 3.40mm 0.134" x 1 c					
Packaging							
-reel parts: ng chip n accordance		Product identifying label Plastic carrier tape Top tape 8 or 12mm 178mm (7") or nominal 330mm (13") dia. reel					
Soldering							
610. n in e must be l component d. l can lead to ock.	Temperature	T <sub>p</sub> T <sub>L</sub> Max Min t t t T <sub>L</sub> Preheat area Time					
component damage through thermal shock.							
hanson MFG	Novacap	Syfer Voltronics					
or this part may differ a The information contr onfidential and may not b ny form or disclosed to a th	nd is available at http://w ained on this drawing is e copied in whole or part ir hird party without the consen	t					
	Enviro by 2015/863/EU by 2015/863/EU capacitors can accordance with c Requirements o Standards, but shown to reduce ad width to less of the chip on the ifications to the ormal coating to ote AN0043 for Pack -reel parts: ng chip n accordance Contemponent can lead to ck. dling guidance a hanson MFG his datasheet is for a s or the information conten his datasheet is for a s or the information conten his datasheet is for a s or the information conten by content and may oust by content and may oust by content and to by content and to by content and to by content and the information content by converse and any cust by content and the information content by converse and any cust by converse any	Environmental         by 2015/863/EU       Compliant         191 compliant       No exposure risk         Board Layout       Capacitors can         accordance with       C Requirements         a Standards, but       Shown to reduce         ad width to less       f the chip on the         ifications to the bornal coating to ote AN0043 for       Packaging         -reel parts:					