#### LITEON LITE-ON SEMICONDUCTOR

# SURFACE MOUNT **GLASS PASSIVATED RECTIFIERS**

#### **FEATURES**


- · Glass passivated chip
- For surface mounted applications
- Low reverse leakage current
- · Low forward voltage drop
- High current capability

#### **MECHANICAL DATA**

- · Case: Molded plastic
- Case Material molding compound, UL flammability classification 94V-0, (No Br. Sb. Cl.) "Halogen-free".
- Polarity: Color band denotes cathode
- Weight : 0.246 grams ( Approximate )

### **REVERSE VOLTAGE – 50 to 1000 Volts FORWARD CURRENT – 3.0 Amperes**

S3A thru S3M



#### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

#### **ABSOLUTE RATINGS**

| PARAMETER   | SYMBOL            | S3A | S3B | S3D | S3G        | S3J | S3K | S3M  | UNIT             |
|---|-------------------|-----|-----|-----|------------|-----|-----|------|------------------|
| Maximum repetitive peak reverse voltage   | V <sub>RRM</sub>  | 50  | 100 | 200 | 400        | 600 | 800 | 1000 | V                |
| Maximum DC blocking voltage   | V <sub>DC</sub>   | 50  | 100 | 200 | 400        | 600 | 800 | 1000 | V                |
| Maximum average forward rectified current @ $T_L=75^{\circ}C$   | I <sub>(AV)</sub> |     |     |     | 3.0        |     |     |      | Α                |
| Peak forward surge current 8.3ms single half @T <sub>J</sub> =25°C<br>sine-wave superimposed on rated load @T <sub>J</sub> =125°C | I <sub>FSM</sub>  |     |     |     | 120<br>100 |     |     |      | А                |
| Peak forward surge current 1ms single half @T <sub>J</sub> =25°C<br>sine-wave superimposed on rated load @T <sub>J</sub> =125°C   | I <sub>FSM</sub>  |     |     |     | 240<br>200 |     |     |      | А                |
| $I^{2}$ t rating for fusing (t = 8.3 ms)  | l²t               |     |     |     | 59.8       |     |     |      | A <sup>2</sup> S |
| Typical junction capacitance (Note 1)   | CJ                |     |     |     | 40         |     |     |      | pF               |
| Operation and storage temperature range   | $T_J$ , $T_{STG}$ |     |     | -   | 55 to +150 | )   |     |      | °C               |

# STATIC ELECTRICAL CHARACTERISTICS

| PARAMETER       | TEST CONDITIONS       |                      | SYMBOL         | MAX.      | UNIT |
|-----------------|-----------------------|----------------------|----------------|-----------|------|
| Forward voltage | I <sub>F</sub> = 3.0A | T <sub>J</sub> =25°C | VF             | 1.15      | V    |
| Leakage current | $V_{R}$ at rated      | Tյ=25°C<br>Tյ=125°C  | I <sub>R</sub> | 10<br>250 | uA   |

#### THERMAL CHARACTERISTICS

| PARAMETER                           | SYMBOL                    | TYP. | UNIT |
|-------------------------------------|---------------------------|------|------|
| Typical thermal resistance (Note 2) | <b>R</b> thJ <sub>A</sub> | 50   | °C/W |
|                                     | RthJ∟                     | 10   | 0/11 |

#### DYNAMIC ELECTRICAL CHARACTERISTICS

| PARAMETER             | TEST CONDITIONS                                 | SYMBOL          | ТҮР. |                          |  |
|-----------------------|---|-----------------|------|--------------------------|--|
| Reverse recovery time | $I_{F}$ = 0.5A, $I_{RR}$ = 0.25A, $I_{R}$ =1.0A | T <sub>RR</sub> | 2000 |                          |  |
| Note :                |   |                 |      | REV. 10, Nov2016, KSDC01 |  |

Note :

(1) Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

(2) Thermal resistance junction to ambient and lead.

# RATING AND CHARACTERISTIC CURVES S3A thru S3M

# LITEON




FIG.2- MAXIMUM NON-REPETITIVE SURGE CURRENT 120 PEAK FORWARD SURGE CURRENT,(A) 100 80 60 40 20 8.3ms single half sine-wave 0 10 100 1 NUMBER OF CYCLES AT 60Hz

FIG.3- TYPICAL FORWORD CHARACTERISTICS





FIG.4- TYPICAL REVERSE CHARACTERISTICS



# LEGAL DISCLAIMER NOTICE



# **Important Notice and Disclaimer**

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.