

LBSS84ELT1G S-LBSS84ELT1G

Power MOSFET 60V P-Channel

1. FEATURES

- Advanced trench cell design.
- High speed switch.
- G-S ESD Protected: $\pm 1000V$
- Pb-Free Package is available.
- We declare that the material of product compliance with RoHS requirements and Halogen Free.
- S- prefix for automotive and other applications requiring unique site and control change requirements; AEC-Q101 qualified and PPAP capable.

2. APPLICATIONS

- Portable appliances.
- Load switch appliances.

3. DEVICE MARKING AND ORDERING INFORMATION

| Device | Marking | Shipping |
|-------------|---------|----------------|
| LBSS84ELT1G | PE | 3000/Tape&Reel |



4. MAXIMUM RATINGS($T_a = 25^\circ C$)

| Parameter | Symbol | Limits | Unit |
|---------------------------------|--------|----------|------|
| Drain-Source Voltage | VDSS | -60 | V |
| Gate-to-Source Voltage | VGSS | ± 20 | V |
| Drain Current | | | mA |
| - Continuous $T_A = 25^\circ C$ | ID | -130 | |
| - Pulsed ($t_p \leq 10\mu s$) | IDM | -520 | |

5. THERMAL CHARACTERISTICS

| Parameter | Symbol | Limits | Unit |
|--|---------------|----------|----------------|
| Total Device Dissipation, FR-5 Board (Note 1) @ $T_A = 25^\circ C$ Derate above $25^\circ C$ | PD | 225 | mW |
| | | 1.8 | mW/ $^\circ C$ |
| Thermal Resistance, Junction-to-Ambient(Note 1) | R θ JA | 556 | $^\circ C/W$ |
| Junction and Storage temperature | TJ, Tstg | -55~+150 | $^\circ C$ |
| Maximum Lead Temperature for Soldering Purposes, for 10 seconds | TL | 260 | $^\circ C$ |

1. FR-5 = 1.0×0.75×0.062 in.



6. ELECTRICAL CHARACTERISTICS (Ta= 25°C)
OFF CHARACTERISTICS

| Characteristic | Symbol | Min. | Typ. | Max. | Unit |
|---|--------|------|------|-------------|------|
| Drain-Source Breakdown Voltage (VGS = 0, ID = -250μA) | VBRDSS | -60 | - | - | V |
| Zero Gate Voltage Drain Current (VGS = 0, VDS = -25 V) (VGS = 0, VDS = -60 V) | IDSS | - | - | -0.1 -15 | μA |
| Gate-Body Leakage Current, Forward (VGS = 20 V) | IGSSF | - | - | 10 | μA |
| Gate-Body Leakage Current, Reverse (VGS = -20 V) | IGSSR | - | - | -10 | μA |

ON CHARACTERISTICS (Note 2)

| | | | | | |
|--|---------|------|----------|--------|----|
| Gate Threshold Voltage (VDS = VGS, ID = -250μA) | VGS(th) | -0.9 | - | -2 | V |
| Static Drain-Source On-State Resistance (VGS = -5.0 V, ID = -100 mA) (VGS = -10 V, ID = -100 mA) | RDS(on) | - | 2 1.8 | 6 5 | Ω |
| Transfer Admittance (VDS = -25 V, ID = -100 mA, f = 1.0 kHz) | yfs | 50 | - | - | mS |

DYNAMIC CHARACTERISTICS

| | | | | | | |
|---|---------------------------------------|-----|-----|-----|----|----|
| Input Capacitance (VDS = -25 V, VGS=0V, f=1MHz) | Ciss | - | 45 | - | pF | |
| Output Capacitance (VDS = -25 V, VGS=0V, f=1MHz) | Coss | - | 4 | - | pF | |
| Reverse Transfer Capacitance (VDS = -25 V, VGS=0V, f=1MHz) | Crss | - | 1.5 | - | pF | |
| Total Gate Charge | (VDS = -25V, VGS = -4.5V, ID = -0.1A) | Qg | - | 1.1 | - | nC |
| Gate-Source Charge | | Qgs | - | 0.3 | - | |
| Gate-Drain Charge | | Qgd | - | 0.2 | - | |

SWITCHING CHARACTERISTICS





| | | | | | | |
|---------------------|--|---------|---|-----|---|----|
| Turn-On Delay Time | (VDS = -25 V, VGEN = -10V, IDS = -0.1 A, RL = 250Ω, RG=6Ω) | td(on) | - | 4.8 | - | ns |
| Rise Time | | tr | - | 19 | - | |
| Turn-Off Delay Time | | td(off) | - | 52 | - | |
| Fall Time | | tf | - | 32 | - | |

SOURCE-DRAIN DIODE CHARACTERISTICS



| | | | | | |
|--------------------|-----|---|------|-------|---|
| Continuous Current | IS | - | - | -0.13 | A |
| Pulsed Current | ISM | - | - | -0.52 | A |
| Forward Voltage | VSD | - | -2.2 | - | V |

2.Pulse Test: Pulse Width ≤300 μs, Duty Cycle ≤2.0%.

7. ELECTRICAL CHARACTERISTICS CURVES




7.ELECTRICAL CHARACTERISTICS CURVES(Con.)



8. OUTLINE AND DIMENSIONS

Notes:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.



| DIM | MILLIMETERS | | | INCHES | | |
|-----|-------------|------|------|--------|-------|-------|
| | MIN | NOM | MAX | MIN | NOM | MAX |
| A | 0.89 | 1 | 1.11 | 0.035 | 0.04 | 0.044 |
| A1 | 0.01 | 0.06 | 0.1 | 0.001 | 0.002 | 0.004 |
| b | 0.37 | 0.44 | 0.5 | 0.015 | 0.018 | 0.02 |
| c | 0.09 | 0.13 | 0.18 | 0.003 | 0.005 | 0.007 |
| D | 2.80 | 2.9 | 3.04 | 0.11 | 0.114 | 0.12 |
| E | 1.20 | 1.3 | 1.4 | 0.047 | 0.051 | 0.055 |
| e | 1.78 | 1.9 | 2.04 | 0.07 | 0.075 | 0.081 |
| L | 0.10 | 0.2 | 0.3 | 0.004 | 0.008 | 0.012 |
| L1 | 0.35 | 0.54 | 0.69 | 0.014 | 0.021 | 0.029 |
| HE | 2.10 | 2.4 | 2.64 | 0.083 | 0.094 | 0.104 |
| θ | 0° | --- | 10° | 0° | --- | 10° |

9. SOLDERING FOOTPRINT

