# 規格承認書

### PECIFICATION FOR APPROVAL

客 戶							
CUSTOMER	:						
項目							
ITEM	:	贴片式电磁有源蜂鸣器	(内部含驱	(动电路)			
型號							
TYPE	:	GSD9650YB-3V2800					
描述	_						
DESCRIPTION	: _	W9.6 x L9.6 x H 5.0 mm	2800Hz	DC3.3V	≥80dB	正发音	LCP 材质
客戶料號							
CUSTOMER NO	). <b>:</b> _						
規格書號							
SPECIFICATION	NO	). <b>:</b>					
版本							
EDITION NO.	:	V1.1					
日 期	-						
DATE	:	2019-5-30					

# 客戶承認

## **CUSTOMER CONFIRM AND SIGN**

檢查	審核	承認
TESTED BY	CHECKED BY	APPROVED BY

# 東莞市赢海電子有限公司

# DONGUAN INGHAI ELECTRONICS CO.,LTD

製作	審查	確認
ISSUED BY	CHECKED BY	APPROVED BY
周明	刘承成	

地址: 廣東省東莞市虎门镇怀德社区雅瑶工业区

網址: HTTP://WWW.INGHAI.COM


# A. SCOPE

This specification applies SMD piezoelectric buzzer, GSD9605YB-3V2800

# **B. SPECIFICATION**

No.	Item	Unit	Specification	Condition
1	1 Oscillation Frequency		2700±0.3	
2	2 Operating Voltage		2~ 5	
3 Rated Voltage		VDC	3.3	
4	4 Current Consumption		MAX. 30	at Rated Voltage
5	5 Sound Pressure Level		MIN. 80	at 10cm at Rated Voltage
6	6 Tone Nature		Single	
7	7 Operating Temperature		-20~+70 可承受回流焊 260°5秒	
8	8 Storage Temperature		-30 ~ +85	
9	9 Dimension		9.6x 9.6x H5.0	See appearance drawing
10	10 Weight (MAX)		1.5	
11	11 Housing Material		PPS( Black )	
12	12 Leading Pin		Plated Brass(Au)	See appearance drawing
13	Environmental Protection Regulation		RoHS	

# C. APPEARANCE DRAWING Tol: $\pm$ 0.3 Unit: mm




### **D.TESTING METHOD**

### **Standard Measurement conditions**


Temperature:25±2℃ Humidity:45-65%

## **Acoustic Characteristics:**


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below



In the measuring test, buzzer is placed as follows:




## E. VOLTAGE / CURRENT / SOUND PRESSURE CHARACTERISTICS



# **F. Soldering Condition**

(1)Recommendable reflow soldering condition is as follows (Reflow soldering is twice)

Note:It is requested that reflow soldering should be executed after heat of product goes down to normal.



Heat resistant line

(Used when heat resistant reliability test is performed)

(2)Manual soldering

Manual soldering temperature 350 °C within 5 sec.

# **G:** Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

### 1. Ordinary Temperature Life Test

#### 2. High Temperature Test

The part shall be capable of with standing a storage temperature of +85℃ for 96 hours.

### 3. Low Temperature Test

The part shall be capable of with standing a storage temperature of -30℃ for 96 hours.

### 4. Humidity Test

Temperature:+40  $^{\circ}$ C  $\pm$ 3  $^{\circ}$ C Relative Humidity:90% $\sim$ 95% Duration: 48 hours and expose to room temperature for 6 hours

### 5. Temperature Shock Test

Temperature:  $70^{\circ}$ C /1hour  $\rightarrow$  25  $^{\circ}$ C/3hours  $\rightarrow$  -30  $^{\circ}$ C/1hour  $\rightarrow$  25  $^{\circ}$ C/3hours (1cycle) Total cycle: 10 cycles

### 6. Drop Test

Standard Packaging From 120mm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

#### 7. Vibration Test

Vibration: 1000cycles /min. Amplitude: 1.5mm, Duration: 1 hour in each 3 axes

### **Measuring condition**

Part shall be measured under a condition (Temperature:  $5 \sim 35 \,^{\circ}$ C, Humidity:  $45\% \sim 85\%$ R.H., Atmospheric pressure:  $860 \sim 1060$ hPa) unless the standard condition (Temperature:  $25\pm3\,^{\circ}$ C, Humidity:  $60\pm10\%$ R.H. Atmospheric pressure:  $860 \sim 1060$ hPa) is regulated to measure.

#### Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.

# H. PACKING STANDARD

