



SPECIFICATIONS

Rated Current: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact Plating: Au Or Sn Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PBT
 Max. Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



Ordering Information

2285 02 XX X N XX S Y X 0X

No. of Pins Per Row: 2*40
 Insulator Material Option:
 A=BK-PBT
 B=BK-PA66
 C=BK-PA6T
 D=BK-PA46
 F=BK-LCP
 Contact Plating:
 G1:1U" Gold
 G2:1.5U" Gold
 G3:2U" Gold
 G4:3U" Gold
 G5:5U" Gold
 S0:Gold Flash/Tin
 SN:Tin
 Packing:
 O=PE Bog
 A=Troy
 T=Tube
 P=Tube+Cap
 R=Reel+Cap
 M=Reel+Mylar



OPERATION		DRAW		SCALE		FIT	
X.X	±0.30	YYSsheng	12.03.28	UNIT	mm	A4	1/1
X.XX	±0.20	CHECK		SIZE	A4	SHEET	1/1
X.XXX	±0.10			ANGLE	±3°	PROJ.	◆
REV	DATE	MODIFICATION DESCRIPTION	CHANGE				
A0	2012.03.28	NEW DRAWING					
1							

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892

PART NO. 228502XXXXXXSY0X
 TITLE: 2.54PF H8.5mm 2XNpin 180° W5.0mm