





FILE NO.:E302810

SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)





Ordering Information

2343 01 XX X N XX S U X 01

No.of Pins Per Row 1*40
 Insulator Material Option
 A=BK-PBT
 B=BK-PA66
 C=BK-PA6T
 D=BK-PA46
 E=BK-PA9T
 F=BK-LCP
 Contact Plating
 G1:1U" Gold
 G2:1.5U" Gold
 G3:2U" Gold
 G4:3U" Gold
 G5:5U" Gold
 S0:Gold Flash/Tin
 SN:Tin

Packing
 0=PE Bag
 A=Troy
 T=Tube
 P=Tube+Cap
 R=Reel+Cap
 M=Reel+Mylar



OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30	YYSSheng	12.04.18	UNIT	mm	A4	1/1	234301XXXXXSUX01	
X.XX	±0.20	CHECK		SIZE	A4	SHEET	1/1	TITLE:	
X.XXX	±0.10	APPROVE		PROJ.	PROJ.	2.00PF H4.30mm 1xNpin 180°			
Angle	±3°								
DIM	TOL								

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892

1 2 3 4 5 6 7 8 9