



Micro Commercial Components 130 W Cochran St, Unit B Simi Valley, CA 93065 Tel:818-701-4933

BAW56

Features

- Low Current Leakage
- Low Cost
- Small Outline Surface Mount Package
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Marking: A1/JC
- Lead Free Finish/Rohs Compliant ("P"Suffix designates RoHS Compliant. See ordering information)
- Halogen free available upon request by adding suffix "-HF"

Maximum Ratings


- Operating Temperature: -55°C to +150°C
- Storage Temperature: -55°C to +150°C
- Maximum Thermal Resistance; 357K/W Junction To Ambient

Electrical Characteristics @ 25°C Unless Otherwise Specified

			потинос оросниса
Reverse Voltage	V_R	75V	
Forward Continuous Current	lF	250mA	
Power Dissipation	P _{TOT}	350mW	
Peak Forward Surge Current	I _{FSM}	1.0A	t=1s,Non-Repetitive
Maximum Instantaneous Forward Voltage	V_{F}	855mV	I _{FM} = 10mA; T _J = 25°C*
Maximum DC Reverse Current At Rated DC Blocking Voltage	I _R	2.5μA 50μA	V_R =75Volts T_J = 25°C T_J = 150°C
Typical Junction Capacitance	CJ	2pF	Measured at 1.0MHz, V _R =0V
Reverse Recovery Time	T _{rr}	4nS	I_F =10mA V_R = 0V R_L =500 Ω

^{*}Pulse test: Pulse width 300 µsec, Duty cycle 2%


350mW 75Volt Dual Switching Diode




DIMENSIONS						
INCHES		ММ				
MIN	MAX	MIN	MAX	NOTE		
.110	.120	2.80	3.04			
.083	.104	2.10	2.64			
.047	.055	1.20	1.40			
.035	.041	.89	1.03			
.070	.081	1.78	2.05			
.018	.024	.45	.60			
.0005	.0039	.013	.100			
.035	.044	.89	1.12			
.003	.007	.085	.180			
.015	.020	.37	.51			
	MIN .110 .083 .047 .035 .070 .018 .0005 .035	INCHES MIN MAX .110 .120 .083 .104 .047 .055 .035 .041 .070 .081 .018 .024 .0005 .0039 .035 .044 .003 .007	INCHES MM MIN .110 .120 2.80 .083 .104 2.10 .047 .055 1.20 .035 .041 .89 .070 .081 1.78 .018 .024 .45 .0005 .0039 .013 .035 .044 .89 .003 .007 .085 .0039 .003 .007 .085	NCHES		









T_j, JUNCTION TEMPERATURE (°C) Fig. 2 Leakage Current vs Junction Temperature



Ordering Information:

Device	Packing	
Part Number-TP	Tape&Reel: 3Kpcs/Reel	

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.