



# 深圳市凯越翔实业

## 石英谐振器规格书

产品名称:	石英晶振谐振器
产品型号:	3225/24.000MHZ
产品参数:	20PF/±10ppm
原厂型号:	K3A240002010
尺寸图:	P. 2 3
凯越翔实业技术部:	董宗全


## 客户确认印栏

客户确认印栏	
认证印章	负责人印章
年 月 日	年 月 日


工厂地址: 深圳市宝安区观澜人民路蔡发工业城一栋四层 TEL: 0755-89315823 89315866 FAX: 0755-89315223  
官网: [www.kaiyuexiang.com](http://www.kaiyuexiang.com)



- |  |                            |
|--|----------------------------|
| 1. Frequency:                                  | <b>24.000MHZ</b>           |
| 2. Holder Type:                                | SMD3.2*2.5                 |
| 3. Frequency Tolerance:                        | <b>±10ppm at 25°C ±3°C</b> |
| 4. Equivalent Series Resistance:               | <b>40 Ω Max</b>            |
| 5. Storage Temperature Range:                  | -40°C ~ +85°C              |
| 6. Operating Temperature Range:                | -40°C ~ +85°C              |
| 7. Frequency Characteristics Over Temperature: | ±10ppm -40°C~+85°C         |
| 8. Load Capacitance (CL):                      | 20 PF                      |
| 9. Drive Level:                                | 100 μ W Max                |
| 10. Shunt Capacitance:                         | 5PF MAX                    |
| 11. Insulation Resistance:                     | ≥500M Ω Min at 100 V       |
| 12. Mode Of Oscillation:                       | Fundamental                |
| 13. Aging:                                     | 3ppm/Year                  |
| Marking description:                           | K24.00MHZ                  |
| 14. Dimensions(mm):                            |                            |



## 16. Structure Illustration



PART NAME		MATERIAL	PART NAME		MATERIAL
1.	BASE	CERAMIC	4.	ELECTRODE	Metal
2.	LID	Co	5.	ADHESMES	SILVER GLUE
3.	BLANK	QUARTZ			


Reliability Testing 可靠性测试项目介绍

项目	验条件及要求	要求
Vibration 振动	Endurance condition by a frequency sweep shall be made. The entire frequency range from 10HZ to 50HZ and return to 10HZ, shall be transverse in 1min. Amplitude(total excursion):1.5mm this motion shall be applied for a period of 2h each of 3 mutually perpendicular axes(a total of 6h) 振动频率: 从 10HZ 到 55HZ, 再回到 10HZ 1 倍频程/min 幅度为 1.5mm 3 个相互垂直的方向各 2 小时	(1). FL: +/-5ppm (2). Rr: +/-15%
Drop 跌落	Form 70cm height 3 times on 3cm hard wooden floor 从 70cm 高处跌落到 3cm 厚的硬质木板上, 重复 3 次	
Shock 冲击	Peak acceleration:981m/s <sup>2</sup> duration of the pulse :6ms three successive shocks shall be applied in both direction of 3 mutually perpendicular axes(a total of 18 shocks) 加速度: 981m/s <sup>2</sup> 时间: 6ms 作用在 3 个相互垂直的方向	(1). FL: +/-10ppm (2). Rr: +/-80 Ω
Damp heat, constant 恒定湿热	The unit shall be stored at a temperature of 40°C±2°Cwith relative humidity of 90%to95% for 48h, then it shall be subjected to standard atmospheric conditions for 1~2h after which measurement shall be made. 在温度: 40°C±2°C、湿度: 90%to95%条件下存放 48 小时, 然后在标准大气压下放置 1~2 小时后测试	
Cold 低温存储	The unit shall be stored at a temperature of-40°C±5°C for 48h, then it shall be subjected to standard atmospheric conditions for 1~2h after which measurement shall be made. 在-40°C±5°C下存放 48 小时, 然后在标准大气压下放置 1~2 小时后测试	
Dry heat 高温存储	The unit shall be stored at a temperature of 100°C±5°C for 24h, then it shall be subjected to standard atmospheric conditions for 1~2h after which measurement shall be made. 100°C±5°C下存放 24 小时, 然后在标准大气压下放置 1~2 小时后测试	
Aging 老化	The unit shall be stored at a temperature of 85°C±5°C for 7d then it shall be subjected to standard atmospheric conditions for 1~2h after which measurement shall be made. 85°C±5°C下放置 7 天, 然后在标准大气压下放置 1~2 小时后测试	
Temperature cycling 温度循环	The unit shall be subjected to 5 successive change of temperature cycles, each as show in table below, then it shall be subjected to standard atmospheric conditions for 1~2h after which measurement shall be made 在下表给定温度和时间参数的条件下循环 5 次, 标准大气压下放置 1~2 小时后测试	

凯越翔实业


	Temperature 温度	Duration 放置时间
1	-40°C ± 3°C	30min (30分钟)
2	Standard atmospheric conditions 标准大气压	Within 30s 30秒内
3	100°C ± 3°C	30min (30分钟)
4	Standard atmospheric conditions 标准大气压	Within 30s 30秒内

Resistance to  
soldering heat  
耐焊接热




■ PACKING

1. CARRIER TYPE



2. REEL : 3000 PCS



拟制	成望生	审核	董宗全	批准	赵庸桓
----	-----	----	-----	----	-----