

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------------------|
| GJ431CC81E105KA01 | 1uF | 25 | X6S | | 3216M/1206 | 1.8 | +/-10% | Audio signal low distortion |
| GJ821BR71H105KA12 | 1uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | Acoustic noise reduction |
| GJ8319R61H225KA12 | 2.2uF | 50 | X5R | | 3216M/1206 | 0.95 | +/-10% | Acoustic noise reduction |
| GJ831CC81E105KA01 | 1uF | 25 | X6S | | 3216M/1206 | 1.8 | +/-10% | Acoustic noise reduction |
| GJ831CR61E106KE83 | 10uF | 25 | X5R | | 3216M/1206 | 1.9 | +/-10% | Acoustic noise reduction |
| GJ831CR71H475KA12 | 4.7uF | 50 | X7R | | 3216M/1206 | 1.8 | +/-10% | Acoustic noise reduction |
| GJ832ER7YA106KA12 | 10uF | 35 | X7R | | 3225M/1210 | 2.7 | +/-10% | Acoustic noise reduction |
| GRJ155R60J106ME11 | 10uF | 6.3 | X5R | | 1005M/0402 | 0.7 | +/-20% | Resin external electrode |
| GRJ188C70J475KE11 | 4.7uF | 6.3 | X7S | | 1608M/0603 | 1 | +/-10% | Resin external electrode |
| GRJ188C70J475ME11 | 4.7uF | 6.3 | X7S | | 1608M/0603 | 1 | +/-20% | Resin external electrode |
| GRJ188R60J106ME11 | 10uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R60J475KE11 | 4.7uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R60J475ME11 | 4.7uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R61A106ME11 | 10uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R61A475KE11 | 4.7uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R61A475ME11 | 4.7uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R61C105KE11 | 1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R61C105ME11 | 1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R6YA105KE11 | 1uF | 35 | X5R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R70J225KE11 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R70J225ME11 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71C474KE11 | 0.47uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71C474ME11 | 0.47uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71E105KE11 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71E105ME11 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71E224KE11 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71E224ME11 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71E473KE11 | 47000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71E473ME11 | 47000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H102KE11 | 1000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H102ME11 | 1000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H103KE11 | 10000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H103ME11 | 10000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H104KE11 | 0.1uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H104ME11 | 0.1uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H222KE11 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H222ME11 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H223KE11 | 22000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H223ME11 | 22000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H224KE11 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H224ME11 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H472KE11 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H472ME11 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R71H473KE11 | 47000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R71H473ME11 | 47000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R72A102KE11 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R72A102ME11 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R72A103KE11 | 10000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R72A103ME11 | 10000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R72A104KE11 | 0.1uF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R72A104ME11 | 0.1uF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R72A222KE11 | 2200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R72A222ME11 | 2200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R72A223KE11 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R72A223ME11 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ188R72A472KE11 | 4700pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Resin external electrode |
| GRJ188R72A472ME11 | 4700pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | Resin external electrode |
| GRJ216R71H102KE01 | 1000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R71H102ME01 | 1000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R71H103KE01 | 10000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R71H103ME01 | 10000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R71H222KE01 | 2200pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R71H222ME01 | 2200pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R71H223KE01 | 22000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R71H223ME01 | 22000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R71H471KE01 | 470pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R71H471ME01 | 470pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R71H472KE01 | 4700pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R71H472ME01 | 4700pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R72A102KE01 | 1000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R72A102ME01 | 1000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R72A103KE01 | 10000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R72A103ME01 | 10000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R72A222KE01 | 2200pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|--------------------------|
| GRJ216R72A222ME01 | 2200pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R72A223KE01 | 22000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R72A223ME01 | 22000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ216R72A472KE01 | 4700pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Resin external electrode |
| GRJ216R72A472ME01 | 4700pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Resin external electrode |
| GRJ219R72A221KE01 | 220pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Resin external electrode |
| GRJ219R72A221ME01 | 220pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | Resin external electrode |
| GRJ219R72A471KE01 | 470pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Resin external electrode |
| GRJ219R72A471ME01 | 470pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | Resin external electrode |
| GRJ21BC72A105KE11 | 1uF | 100 | X7S | | 2012M/0805 | 1.5 | +/-10% | Resin external electrode |
| GRJ21BC72A105ME11 | 1uF | 100 | X7S | | 2012M/0805 | 1.5 | +/-20% | Resin external electrode |
| GRJ21BR61E106KE01 | 10uF | 25 | X5R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71A106KE01 | 10uF | 10 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71A106ME01 | 10uF | 10 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71C475KE01 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71C475ME01 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71E105KE11 | 1uF | 25 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71E105ME11 | 1uF | 25 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71E225KE01 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71E225ME01 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71H104KE01 | 0.1uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71H104ME01 | 0.1uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71H105KE01 | 1uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71H105ME01 | 1uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71H224KE01 | 0.22uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71H224ME01 | 0.22uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71H473KE01 | 47000pF | 50 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71H473ME01 | 47000pF | 50 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR71H474KE01 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR71H474ME01 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR72A104KE01 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR72A104ME01 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ21BR72A473KE01 | 47000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Resin external electrode |
| GRJ21BR72A473ME01 | 47000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Resin external electrode |
| GRJ319R71H104KE11 | 0.1uF | 50 | X7R | | 3216M/1206 | 0.95 | +/-10% | Resin external electrode |
| GRJ319R71H104ME11 | 0.1uF | 50 | X7R | | 3216M/1206 | 0.95 | +/-20% | Resin external electrode |
| GRJ319R72A104KE11 | 0.1uF | 100 | X7R | | 3216M/1206 | 0.95 | +/-10% | Resin external electrode |
| GRJ319R72A104ME11 | 0.1uF | 100 | X7R | | 3216M/1206 | 0.95 | +/-20% | Resin external electrode |
| GRJ31CC71E106KE11 | 10uF | 25 | X7S | | 3216M/1206 | 2 | +/-10% | Resin external electrode |
| GRJ31CC71E106ME11 | 10uF | 25 | X7S | | 3216M/1206 | 2 | +/-20% | Resin external electrode |
| GRJ31CC72A475KE01 | 4.7uF | 100 | X7S | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CC72A475ME01 | 4.7uF | 100 | X7S | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CC8YA106KE01 | 10uF | 35 | X6S | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CC8YA106ME01 | 10uF | 35 | X6S | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR61E106KE11 | 10uF | 25 | X5R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR70J226KE12 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR70J226ME12 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71A106KE11 | 10uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71A106ME11 | 10uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71A226KE12 | 22uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71A226ME12 | 22uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71C106KE11 | 10uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71C106ME11 | 10uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71C475KE11 | 4.7uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71C475ME11 | 4.7uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71E106KE11 | 10uF | 25 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71E106ME11 | 10uF | 25 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71H105KE11 | 1uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71H105ME11 | 1uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71H225KE11 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71H225ME11 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR71H475KE11 | 4.7uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR71H475ME11 | 4.7uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CR72A105KE11 | 1uF | 100 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CR72A105ME11 | 1uF | 100 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31CZ72A475KE01 | 4.7uF | 100 | X7R | | 3216M/1206 | 1.9 | +/-10% | Resin external electrode |
| GRJ31CZ72A475ME01 | 4.7uF | 100 | X7R | | 3216M/1206 | 1.9 | +/-20% | Resin external electrode |
| GRJ31MR71C225KE11 | 2.2uF | 16 | X7R | | 3216M/1206 | 1.35 | +/-10% | Resin external electrode |
| GRJ31MR71C225ME11 | 2.2uF | 16 | X7R | | 3216M/1206 | 1.35 | +/-20% | Resin external electrode |
| GRJ31MR71E225KE11 | 2.2uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Resin external electrode |
| GRJ31MR71E225ME11 | 2.2uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-20% | Resin external electrode |
| GRJ31MR71H104KE01 | 0.1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Resin external electrode |
| GRJ31MR71H104ME01 | 0.1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Resin external electrode |
| GRJ31MR71H105KE01 | 1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Resin external electrode |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|--------------------------|
| GRJ31MR71H105ME01 | 1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Resin external electrode |
| GRJ31MR71H224KE01 | 0.22uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Resin external electrode |
| GRJ31MR71H224ME01 | 0.22uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Resin external electrode |
| GRJ31MR71H474KE01 | 0.47uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Resin external electrode |
| GRJ31MR71H474ME01 | 0.47uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Resin external electrode |
| GRJ31MR72A224KE01 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.35 | +/-10% | Resin external electrode |
| GRJ31MR72A224ME01 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.35 | +/-20% | Resin external electrode |
| GRJ32DC72A475KE11 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.3 | +/-10% | Resin external electrode |
| GRJ32DC72A475ME11 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.3 | +/-20% | Resin external electrode |
| GRJ32DR72A225KE11 | 2.2uF | 100 | X7R | | 3225M/1210 | 2.3 | +/-10% | Resin external electrode |
| GRJ32DR72A225ME11 | 2.2uF | 100 | X7R | | 3225M/1210 | 2.3 | +/-20% | Resin external electrode |
| GRJ32EC71E226KE11 | 22uF | 25 | X7S | | 3225M/1210 | 2.85 | +/-10% | Resin external electrode |
| GRJ32EC71H106KE11 | 10uF | 50 | X7S | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32EC71H106ME11 | 10uF | 50 | X7S | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER70J476KE11 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER70J476ME11 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER71A226KE11 | 22uF | 10 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER71A226ME11 | 22uF | 10 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER71A476KE11 | 47uF | 10 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER71A476ME11 | 47uF | 10 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER71C226KE11 | 22uF | 16 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER71C226ME11 | 22uF | 16 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER71E106KE11 | 10uF | 25 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER71E106ME11 | 10uF | 25 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER71H106KE11 | 10uF | 50 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER71H106ME11 | 10uF | 50 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER71H475KE11 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER71H475ME11 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRJ32ER71K475KE11 | 4.7uF | 80 | X7R | | 3225M/1210 | 2.8 | +/-10% | Resin external electrode |
| GRJ32ER71K475ME11 | 4.7uF | 80 | X7R | | 3225M/1210 | 2.8 | +/-20% | Resin external electrode |
| GRM011R60G103KE01 | 10000pF | 4 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60G332KE01 | 3300pF | 4 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60G472KE01 | 4700pF | 4 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60G682KE01 | 6800pF | 4 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J102KE01 | 1000pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J102ME01 | 1000pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R60J103KE01 | 10000pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J103ME01 | 10000pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R60J152KE01 | 1500pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J152ME01 | 1500pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R60J222KE01 | 2200pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J222ME01 | 2200pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R60J332KE01 | 3300pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J332ME01 | 3300pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R60J472KE01 | 4700pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J472ME01 | 4700pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R60J682KE01 | 6800pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R60J682ME01 | 6800pF | 6.3 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R61A101KE01 | 100pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R61A101ME01 | 100pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R61A151KE01 | 150pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R61A151ME01 | 150pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R61A221KE01 | 220pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R61A221ME01 | 220pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R61A331KE01 | 330pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R61A331ME01 | 330pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R61A471KE01 | 470pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R61A471ME01 | 470pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM011R61A681KE01 | 680pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-10% | Ultra-small |
| GRM011R61A681ME01 | 680pF | 10 | X5R | | 0201M/008004 | 0.138 | +/-20% | Ultra-small |
| GRM022D80E104ME15 | 0.1uF | 2.5 | X6T | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022D80E224ME14 | 0.22uF | 2.5 | X6T | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022D80G104ME15 | 0.1uF | 4 | X6T | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60G104ME15 | 0.1uF | 4 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60G153KE15 | 15000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60G153ME15 | 15000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60G223KE15 | 22000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60G223ME15 | 22000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60G224ME14 | 0.22uF | 4 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60G333KE15 | 33000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60G333ME15 | 33000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60G473KE15 | 47000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60G473ME15 | 47000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60G474ME15 | 0.47uF | 4 | X5R | | 0402M/01005 | 0.25 | +/-20% | Ultra-small |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM022R60G683ME15 | 68000pF | 4 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J102KE19 | 1000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J102ME19 | 1000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J103KE19 | 10000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J103ME19 | 10000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J104KE15 | 0.1uF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J104ME15 | 0.1uF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J152KE19 | 1500pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J152ME19 | 1500pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J153ME15 | 15000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J182KE19 | 1800pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J222KE19 | 2200pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J222ME19 | 2200pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J223KE15 | 22000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J223ME15 | 22000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J224KE14 | 0.22uF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J224ME14 | 0.22uF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J332KE19 | 3300pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J332ME19 | 3300pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J333ME15 | 33000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J392KE19 | 3900pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J472KE19 | 4700pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J472ME19 | 4700pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J473ME15 | 47000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J474ME05 | 0.47uF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | General Purpose |
| GRM022R60J474ME15 | 0.47uF | 6.3 | X5R | | 0402M/01005 | 0.25 | +/-20% | Ultra-small |
| GRM022R60J681KE19 | 680pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J681ME19 | 680pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J682KE19 | 6800pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R60J682ME19 | 6800pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R60J683ME15 | 68000pF | 6.3 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A101KA01 | 100pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A101MA01 | 100pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A102KE19 | 1000pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A102ME19 | 1000pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A103KE19 | 10000pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A103ME19 | 10000pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A104ME01 | 0.1uF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A151KA01 | 150pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A151MA01 | 150pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A152KE19 | 1500pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A152ME19 | 1500pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A221KA01 | 220pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A221MA01 | 220pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A222KE19 | 2200pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A222ME19 | 2200pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A331KA01 | 330pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A331MA01 | 330pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A332KE19 | 3300pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A332ME19 | 3300pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A471KA01 | 470pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A471MA01 | 470pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A472KE19 | 4700pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A472ME19 | 4700pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A562KE19 | 5600pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A680KA01 | 68pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A680MA01 | 68pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A681KE19 | 680pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A681ME19 | 680pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A682KE19 | 6800pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R61A682ME19 | 6800pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R61A821KE19 | 820pF | 10 | X5R | | 0402M/01005 | 0.22 | +/-10% | General Purpose |
| GRM022R71A101KA01 | 100pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A101MA01 | 100pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71A102KA12 | 1000pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A102MA12 | 1000pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71A121KA01 | 120pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A151KA01 | 150pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A151MA01 | 150pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71A181KA01 | 180pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A221KA01 | 220pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A221MA01 | 220pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71A331KA01 | 330pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A331MA01 | 330pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-------------|
| GRM022R71A471KA01 | 470pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A471MA01 | 470pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71A680KA01 | 68pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A680MA01 | 68pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71A681KA12 | 680pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A681MA12 | 680pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71A821KA12 | 820pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71A821MA12 | 820pF | 10 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71C101KE14 | 100pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71C101ME14 | 100pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71C102KE14 | 1000pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71C102ME14 | 1000pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71C151KE14 | 150pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71C151ME14 | 150pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71C221KE14 | 220pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71C221ME14 | 220pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71C271KE14 | 270pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71C331KE14 | 330pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71C331ME14 | 330pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71C471KE14 | 470pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022R71C471ME14 | 470pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022R71C681KE14 | 680pF | 16 | X7R | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM032R60G105ME05 | 1uF | 4 | X5R | | 0603M/0201 | 0.22 | +/-20% | Ultra-small |
| GRM032R60J104KE15 | 0.1uF | 6.3 | X5R | | 0603M/0201 | 0.22 | +/-10% | Ultra-small |
| GRM032R60J105ME05 | 1uF | 6.3 | X5R | | 0603M/0201 | 0.22 | +/-20% | Ultra-small |
| GRM033C71A104KE14 | 0.1uF | 10 | X7S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C71A104ME14 | 0.1uF | 10 | X7S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C71C104KE14 | 0.1uF | 16 | X7S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C71C104ME14 | 0.1uF | 16 | X7S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80E224ME15 | 0.22uF | 2.5 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80G104KE19 | 0.1uF | 4 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80G153KE01 | 15000pF | 4 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80G223KE01 | 22000pF | 4 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80G224ME15 | 0.22uF | 4 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80G224ME90 | 0.22uF | 4 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80G333KE01 | 33000pF | 4 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80G473KE01 | 47000pF | 4 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J104KE15 | 0.1uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J104KE84 | 0.1uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J104ME84 | 0.1uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80J105ME05 | 1uF | 6.3 | X6S | | 0603M/0201 | 0.39 | +/-20% | Ultra-small |
| GRM033C80J153KE01 | 15000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J153ME01 | 15000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80J223KE01 | 22000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J223ME01 | 22000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80J224KE90 | 0.22uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J224ME90 | 0.22uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80J333KE01 | 33000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J333ME01 | 33000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80J473KE19 | 47000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J473ME19 | 47000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C80J683KE84 | 68000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C80J683ME84 | 68000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C81A104KE14 | 0.1uF | 10 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C81A105ME05 | 1uF | 10 | X6S | | 0603M/0201 | 0.39 | +/-20% | Ultra-small |
| GRM033C81A473KE05 | 47000pF | 10 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C81C104KE14 | 0.1uF | 16 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C81C104ME14 | 0.1uF | 16 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C81E103KE14 | 10000pF | 25 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C81E103ME14 | 10000pF | 25 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033C81E104KE14 | 0.1uF | 25 | X6S | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033C81E104ME14 | 0.1uF | 25 | X6S | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R60G105MEA2 | 1uF | 4 | X5R | | 0603M/0201 | 0.35 | +/-20% | Ultra-small |
| GRM033R60G155ME14 | 1.5uF | 4 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R60G224ME15 | 0.22uF | 4 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R60G225ME44 | 2.2uF | 4 | X5R | | 0603M/0201 | 0.35 | +/-20% | Ultra-small |
| GRM033R60G225ME47 | 2.2uF | 4 | X5R | | 0603M/0201 | 0.39 | +/-20% | Ultra-small |
| GRM033R60G474ME90 | 0.47uF | 4 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R60J103KA01 | 10000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J104KE19 | 0.1uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J104KE84 | 0.1uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J105MEA2 | 1uF | 6.3 | X5R | | 0603M/0201 | 0.35 | +/-20% | Ultra-small |
| GRM033R60J153KE01 | 15000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J155ME14 | 1.5uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM033R60J223KE01 | 22000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J224KE15 | 0.22uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J224ME15 | 0.22uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R60J224ME90 | 0.22uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R60J225ME05 | 2.2uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-20% | General Purpose |
| GRM033R60J225ME15 | 2.2uF | 6.3 | X5R | | 0603M/0201 | 0.35 | +/-20% | Ultra-small |
| GRM033R60J225ME47 | 2.2uF | 6.3 | X5R | | 0603M/0201 | 0.39 | +/-20% | Ultra-small |
| GRM033R60J273KE01 | 27000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J333KE01 | 33000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J473KE19 | 47000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R60J474KE90 | 0.47uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A103KA01 | 10000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A103MA01 | 10000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A104KE15 | 0.1uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A104KE84 | 0.1uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A104ME84 | 0.1uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A105ME15 | 1uF | 10 | X5R | | 0603M/0201 | 0.39 | +/-20% | Ultra-small |
| GRM033R61A105ME44 | 1uF | 10 | X5R | | 0603M/0201 | 0.35 | +/-20% | Ultra-small |
| GRM033R61A123KE84 | 12000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A123ME84 | 12000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A152KA01 | 1500pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A153KE84 | 15000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A153ME84 | 15000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A182KA01 | 1800pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A183KE84 | 18000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A183ME84 | 18000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A222KA01 | 2200pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A223KE84 | 22000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A223ME84 | 22000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A224KE90 | 0.22uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A224ME90 | 0.22uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A225KE47 | 2.2uF | 10 | X5R | | 0603M/0201 | 0.39 | +/-10% | Ultra-small |
| GRM033R61A225ME47 | 2.2uF | 10 | X5R | | 0603M/0201 | 0.39 | +/-20% | Ultra-small |
| GRM033R61A273KE84 | 27000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A273ME84 | 27000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A332KA01 | 3300pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A333KE84 | 33000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A333ME84 | 33000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A393KE84 | 39000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A393ME84 | 39000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A472KA01 | 4700pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A472MA01 | 4700pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A473KE84 | 47000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A473ME84 | 47000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A682KA01 | 6800pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A682MA01 | 6800pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61A683KE84 | 68000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61A683ME84 | 68000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C103KA12 | 10000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C103MA12 | 10000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C104KE14 | 0.1uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C104KE18 | 0.1uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C104KE84 | 0.1uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C104ME14 | 0.1uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C104ME18 | 0.1uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C104ME84 | 0.1uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C105ME15 | 1uF | 16 | X5R | | 0603M/0201 | 0.39 | +/-20% | Ultra-small |
| GRM033R61C153KE84 | 15000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C153ME84 | 15000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C223KE84 | 22000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C223ME84 | 22000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C224KE14 | 0.22uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C224ME14 | 0.22uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C333KE84 | 33000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C333ME84 | 33000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C473KE84 | 47000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C473ME84 | 47000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61C683KE84 | 68000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61C683ME84 | 68000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61E101KA01 | 100pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E102KA01 | 1000pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E103KA12 | 10000pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E103MA12 | 10000pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61E104KE14 | 0.1uF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-------------|
| GRM033R61E104ME14 | 0.1uF | 25 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61E151KA01 | 150pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E221KA01 | 220pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E331KA01 | 330pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E471KA01 | 470pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E472KA12 | 4700pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E472MA12 | 4700pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61E681KA01 | 680pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E682KA12 | 6800pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R61E682MA12 | 6800pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R61H471KA12 | 470pF | 50 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R6YA104KE14 | 0.1uF | 35 | X5R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R6YA104ME14 | 0.1uF | 35 | X5R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R70J103KA01 | 10000pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R70J152KA01 | 1500pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R70J222KA01 | 2200pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R70J332KA01 | 3300pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R70J472KA01 | 4700pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R70J682KA01 | 6800pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A103KA01 | 10000pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A103MA01 | 10000pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71A122KA01 | 1200pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A152KA01 | 1500pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A222KA01 | 2200pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A272KA01 | 2700pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A332KA01 | 3300pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A472KA01 | 4700pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A472MA01 | 4700pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71A562KA01 | 5600pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A682KA01 | 6800pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71A682MA01 | 6800pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71A822KA01 | 8200pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C101KA01 | 100pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C102KA01 | 1000pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C103KE14 | 10000pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C103ME14 | 10000pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71C151KA01 | 150pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C152KA01 | 1500pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C182KA88 | 1800pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C221KA01 | 220pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C222KA88 | 2200pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C271JA01 | 270pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-5% | Ultra-small |
| GRM033R71C271KA01 | 270pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C331KA01 | 330pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C332KA88 | 3300pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C471KA01 | 470pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C472KE14 | 4700pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C472ME14 | 4700pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71C681KA01 | 680pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C682KE14 | 6800pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71C682ME14 | 6800pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71E101KA01 | 100pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E102KA01 | 1000pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E103KE14 | 10000pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E103ME14 | 10000pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71E121KA01 | 120pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E151KA01 | 150pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E152KA01 | 1500pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E182KA12 | 1800pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E221KA01 | 220pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E222KA12 | 2200pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E222MA12 | 2200pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71E331KA01 | 330pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E332KA12 | 3300pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E332MA12 | 3300pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71E471KA01 | 470pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E472KE14 | 4700pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E472ME14 | 4700pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71E681KA01 | 680pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E682KE14 | 6800pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71E682ME14 | 6800pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71E821KA01 | 820pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H101KA12 | 100pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H101MA12 | 100pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM033R71H102KA12 | 1000pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H102MA12 | 1000pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71H151KA12 | 150pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H151MA12 | 150pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71H152KA12 | 1500pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H152MA12 | 1500pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71H221KA12 | 220pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H221MA12 | 220pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71H331KA12 | 330pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H331MA12 | 330pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71H471KA12 | 470pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H471MA12 | 470pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R71H561KA12 | 560pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H681KA12 | 680pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R71H681MA12 | 680pF | 50 | X7R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM035R60G475ME15 | 4.7uF | 4 | X5R | | 0603M/0201 | 0.55 | +/-20% | Ultra-small |
| GRM035R60J475ME15 | 4.7uF | 6.3 | X5R | | 0603M/0201 | 0.55 | +/-20% | Ultra-small |
| GRM152C80G104KE19 | 0.1uF | 4 | X6S | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152C80G104ME19 | 0.1uF | 4 | X6S | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152C80G224KE19 | 0.22uF | 4 | X6S | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152C80G224ME19 | 0.22uF | 4 | X6S | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152C80J104KE19 | 0.1uF | 6.3 | X6S | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152C80J104ME19 | 0.1uF | 6.3 | X6S | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152C80J224KE19 | 0.22uF | 6.3 | X6S | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152C80J224ME19 | 0.22uF | 6.3 | X6S | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152D70E104KE19 | 0.1uF | 2.5 | X7T | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152D70E104ME19 | 0.1uF | 2.5 | X7T | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152D70E224KE19 | 0.22uF | 2.5 | X7T | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152D70E224ME19 | 0.22uF | 2.5 | X7T | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152D70G104KE15 | 0.1uF | 4 | X7T | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152D70G104ME15 | 0.1uF | 4 | X7T | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152D70G224KE15 | 0.22uF | 4 | X7T | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152D70G224ME15 | 0.22uF | 4 | X7T | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152D80G105ME15 | 1uF | 4 | X6T | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152D80G474ME15 | 0.47uF | 4 | X6T | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R60G105ME15 | 1uF | 4 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R60J104KE19 | 0.1uF | 6.3 | X5R | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152R60J104ME19 | 0.1uF | 6.3 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R60J105ME15 | 1uF | 6.3 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R60J224KE19 | 0.22uF | 6.3 | X5R | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152R60J224ME19 | 0.22uF | 6.3 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R60J225ME05 | 2.2uF | 6.3 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R60J474ME15 | 0.47uF | 6.3 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R61A104KE19 | 0.1uF | 10 | X5R | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152R61A104ME19 | 0.1uF | 10 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152R61A224KE19 | 0.22uF | 10 | X5R | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152R61A224ME19 | 0.22uF | 10 | X5R | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM153D80G105ME95 | 1uF | 4 | X6T | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153D80J105ME95 | 1uF | 6.3 | X6T | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153R60G105ME95 | 1uF | 4 | X5R | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153R60G225ME95 | 2.2uF | 4 | X5R | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153R60G475ME15 | 4.7uF | 4 | X5R | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153R60J105ME95 | 1uF | 6.3 | X5R | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153R60J225ME95 | 2.2uF | 6.3 | X5R | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153R60J475ME15 | 4.7uF | 6.3 | X5R | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153R61A105ME95 | 1uF | 10 | X5R | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM155C70J225KE11 | 2.2uF | 6.3 | X7S | | 1005M/0402 | 0.7 | +/-10% | General Purpose |
| GRM155C70J225ME11 | 2.2uF | 6.3 | X7S | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155C71A105KE11 | 1uF | 10 | X7S | | 1005M/0402 | 0.6 | +/-10% | General Purpose |
| GRM155C71A225KE11 | 2.2uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | General Purpose |
| GRM155C71A225ME11 | 2.2uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155C71H104KE19 | 0.1uF | 50 | X7S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C71H333KE19 | 33000pF | 50 | X7S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C71H333ME19 | 33000pF | 50 | X7S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C71H473KE19 | 47000pF | 50 | X7S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C71H473ME19 | 47000pF | 50 | X7S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C71H683KE19 | 68000pF | 50 | X7S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C71H683ME19 | 68000pF | 50 | X7S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80E106ME44 | 10uF | 2.5 | X6S | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155C80G105KE19 | 1uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80G154KE01 | 0.15uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80G154ME01 | 0.15uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80G224KE01 | 0.22uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80G224ME01 | 0.22uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM155C80G334KE01 | 0.33uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80G334ME01 | 0.33uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80G474KE01 | 0.47uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80G474ME01 | 0.47uF | 4 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80J105KE15 | 1uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80J106ME11 | 10uF | 6.3 | X6S | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155C80J154KE01 | 0.15uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80J154ME01 | 0.15uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80J224KE01 | 0.22uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80J224ME01 | 0.22uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80J225KE95 | 2.2uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80J225ME95 | 2.2uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80J334KE01 | 0.33uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80J334ME01 | 0.33uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80J474KE19 | 0.47uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C80J474ME19 | 0.47uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C80J475MEAA | 4.7uF | 6.3 | X6S | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155C81A105KA12 | 1uF | 10 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81A105MA12 | 1uF | 10 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C81A225KE11 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.7 | +/-10% | General Purpose |
| GRM155C81A225ME11 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155C81A225ME44 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155C81C105KE11 | 1uF | 16 | X6S | | 1005M/0402 | 0.6 | +/-10% | General Purpose |
| GRM155C81C105KE15 | 1uF | 16 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81C105ME11 | 1uF | 16 | X6S | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155C81C225KE11 | 2.2uF | 16 | X6S | | 1005M/0402 | 0.7 | +/-10% | General Purpose |
| GRM155C81C225ME11 | 2.2uF | 16 | X6S | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155C81C474KE01 | 0.47uF | 16 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81C474ME01 | 0.47uF | 16 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C81E104KA12 | 0.1uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81E104MA12 | 0.1uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C81E105KE11 | 1uF | 25 | X6S | | 1005M/0402 | 0.6 | +/-10% | General Purpose |
| GRM155C81E105ME11 | 1uF | 25 | X6S | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155C81E224KE01 | 0.22uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81E224ME01 | 0.22uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C81E225KE11 | 2.2uF | 25 | X6S | | 1005M/0402 | 0.7 | +/-10% | General Purpose |
| GRM155C81E225ME11 | 2.2uF | 25 | X6S | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155C81E683KA12 | 68000pF | 25 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81H104KE14 | 0.1uF | 50 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81H104KE19 | 0.1uF | 50 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81H104ME14 | 0.1uF | 50 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C81H333KE14 | 33000pF | 50 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81H333ME14 | 33000pF | 50 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C81H473KE14 | 47000pF | 50 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81H473KE19 | 47000pF | 50 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81H473ME14 | 47000pF | 50 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C81H683KE14 | 68000pF | 50 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C81H683ME14 | 68000pF | 50 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155C8YA224KE01 | 0.22uF | 35 | X6S | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155C8YA224ME01 | 0.22uF | 35 | X6S | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155D71A225ME11 | 2.2uF | 10 | X7T | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155D71C225ME11 | 2.2uF | 16 | X7T | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155D80E475ME47 | 4.7uF | 2.5 | X6T | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155D80G225KE95 | 2.2uF | 4 | X6T | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155D80G225ME95 | 2.2uF | 4 | X6T | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155D80J225KE95 | 2.2uF | 6.3 | X6T | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155D80J225ME95 | 2.2uF | 6.3 | X6T | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155D81C225ME11 | 2.2uF | 16 | X6T | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155D81E225ME11 | 2.2uF | 25 | X6T | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155R60E106ME16 | 10uF | 2.5 | X5R | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155R60G105ME01 | 1uF | 4 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60G106ME15 | 10uF | 4 | X5R | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155R60G106ME44 | 10uF | 4 | X5R | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155R60G106ME47 | 10uF | 4 | X5R | | 1005M/0402 | 0.5 | +/-20% | General Purpose |
| GRM155R60G475ME47 | 4.7uF | 4 | X5R | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155R60J104KA01 | 0.1uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R60J104MA01 | 0.1uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60J105KE19 | 1uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R60J105ME19 | 1uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60J106ME15 | 10uF | 6.3 | X5R | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155R60J106ME47 | 10uF | 6.3 | X5R | | 1005M/0402 | 0.5 | +/-20% | General Purpose |
| GRM155R60J154KE01 | 0.15uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R60J154ME01 | 0.15uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60J224KE01 | 0.22uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM155R60J224ME01 | 0.22uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60J334KE01 | 0.33uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R60J334ME01 | 0.33uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60J474KE19 | 0.47uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R60J474ME19 | 0.47uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60J475ME47 | 4.7uF | 6.3 | X5R | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155R60J684KE19 | 0.68uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R60J684ME19 | 0.68uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R60J824KE19 | 0.82uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A104KA01 | 0.1uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A104MA01 | 0.1uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61A105KE01 | 1uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A105KE15 | 1uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A105ME01 | 1uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61A124KE19 | 0.12uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A154KE19 | 0.15uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A154ME19 | 0.15uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61A184KE19 | 0.18uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A224KE19 | 0.22uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A224ME19 | 0.22uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61A333KA01 | 33000pF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A334KE15 | 0.33uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A334ME15 | 0.33uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61A393KA01 | 39000pF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A473KA01 | 47000pF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A474KE15 | 0.47uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A474ME15 | 0.47uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61A475MEAA | 4.7uF | 10 | X5R | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155R61A683KA01 | 68000pF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A684KE15 | 0.68uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61A684ME15 | 0.68uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61C103KA01 | 10000pF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C104KA88 | 0.1uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C105KA12 | 1uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C105MA12 | 1uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61C223KA01 | 22000pF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C224KA12 | 0.22uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C224MA12 | 0.22uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61C225KE11 | 2.2uF | 16 | X5R | | 1005M/0402 | 0.7 | +/-10% | General Purpose |
| GRM155R61C225KE44 | 2.2uF | 16 | X5R | | 1005M/0402 | 0.6 | +/-10% | General Purpose |
| GRM155R61C225ME11 | 2.2uF | 16 | X5R | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155R61C333KA01 | 33000pF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C473KA01 | 47000pF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C474KE01 | 0.47uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61C474ME01 | 0.47uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61C683KA88 | 68000pF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E102KA01 | 1000pF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E104KA87 | 0.1uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E104MA87 | 0.1uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61E105KA12 | 1uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E105MA12 | 1uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61E222KA01 | 2200pF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E224KE01 | 0.22uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E224ME01 | 0.22uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61E225KE11 | 2.2uF | 25 | X5R | | 1005M/0402 | 0.7 | +/-10% | General Purpose |
| GRM155R61E225ME11 | 2.2uF | 25 | X5R | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155R61E225ME15 | 2.2uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61E472KA01 | 4700pF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E474KE01 | 0.47uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E474ME01 | 0.47uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61E683KA87 | 68000pF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61E683MA87 | 68000pF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61H102KA01 | 1000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H104KE14 | 0.1uF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H104KE19 | 0.1uF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H104ME14 | 0.1uF | 50 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61H105ME05 | 1uF | 50 | X5R | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155R61H222KA01 | 2200pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H333KE14 | 33000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H333KE19 | 33000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H333ME14 | 33000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61H333ME19 | 33000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61H472KA01 | 4700pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H473KE14 | 47000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM155R61H473KE19 | 47000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H473ME14 | 47000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61H473ME19 | 47000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61H474KE11 | 0.47uF | 50 | X5R | | 1005M/0402 | 0.6 | +/-10% | General Purpose |
| GRM155R61H474ME11 | 0.47uF | 50 | X5R | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155R61H683KE14 | 68000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H683KE19 | 68000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R61H683ME14 | 68000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R61H683ME19 | 68000pF | 50 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R62A104KE14 | 0.1uF | 100 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R6YA105KE11 | 1uF | 35 | X5R | | 1005M/0402 | 0.6 | +/-10% | General Purpose |
| GRM155R6YA105ME11 | 1uF | 35 | X5R | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155R6YA224KE01 | 0.22uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R6YA224ME01 | 0.22uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R6YA225ME11 | 2.2uF | 35 | X5R | | 1005M/0402 | 0.7 | +/-20% | General Purpose |
| GRM155R6YA474KE01 | 0.47uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R6YA474ME01 | 0.47uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R70G105KA12 | 1uF | 4 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R70G105MA12 | 1uF | 4 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R70J104KA01 | 0.1uF | 6.3 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R70J105KA12 | 1uF | 6.3 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R70J105MA12 | 1uF | 6.3 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R70J223KA01 | 22000pF | 6.3 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71A104KA01 | 0.1uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71A104MA01 | 0.1uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71A224KE01 | 0.22uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71A224ME01 | 0.22uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71A333MA01 | 33000pF | 10 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71A474KE01 | 0.47uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71A474ME01 | 0.47uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71A683KA01 | 68000pF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71A683MA01 | 68000pF | 10 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71C102KA01 | 1000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C103KA01 | 10000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C103MA01 | 10000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71C104KA88 | 0.1uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C153KA01 | 15000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C154KA12 | 0.15uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C183KA01 | 18000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C223KA01 | 22000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C223MA01 | 22000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71C224KA12 | 0.22uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C333KA01 | 33000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C472KA01 | 4700pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C473KA01 | 47000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C563KA88 | 56000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C683KA88 | 68000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71C823KA88 | 82000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E103KA01 | 10000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E104KE14 | 0.1uF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E104ME14 | 0.1uF | 25 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71E123KA61 | 12000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E153KA61 | 15000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E222KA01 | 2200pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E223KA61 | 22000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E273KA88 | 27000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E333KA88 | 33000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E472KA01 | 4700pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E473KA88 | 47000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E562KA01 | 5600pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E682KA01 | 6800pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E683KE14 | 68000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71E683ME14 | 68000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71E822KA01 | 8200pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H102KA01 | 1000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H102MA01 | 1000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71H103KA88 | 10000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H104KE14 | 0.1uF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H104ME14 | 0.1uF | 50 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71H122KA01 | 1200pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H152KA01 | 1500pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H153KA12 | 15000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H182KA01 | 1800pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H221KA01 | 220pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM155R71H222KA01 | 2200pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H223KA12 | 22000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H271KA01 | 270pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H272KA01 | 2700pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H331KA01 | 330pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H332KA01 | 3300pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H333KE14 | 33000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H333ME14 | 33000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71H391KA01 | 390pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H392KA01 | 3900pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H393KE14 | 39000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H471KA01 | 470pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H472KA01 | 4700pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H473KE14 | 47000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H473ME14 | 47000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71H561KA01 | 560pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H562KA88 | 5600pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H681KA01 | 680pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H682KA88 | 6800pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H683KE14 | 68000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H683ME14 | 68000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R71H821KA01 | 820pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R71H823KE14 | 82000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A102KA01 | 1000pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A152KA01 | 1500pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A221KA01 | 220pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A222KA01 | 2200pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A331KA01 | 330pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A332KA01 | 3300pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A471KA01 | 470pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A472KA01 | 4700pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R72A681KA01 | 680pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM15XR61A153KA86 | 15000pF | 10 | X5R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR61A153MA86 | 15000pF | 10 | X5R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR61A223KA86 | 22000pF | 10 | X5R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR61A223MA86 | 22000pF | 10 | X5R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR61A333KA86 | 33000pF | 10 | X5R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR61A333MA86 | 33000pF | 10 | X5R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR71C103KA86 | 10000pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71C103MA86 | 10000pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR71C332KA86 | 3300pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71C332MA86 | 3300pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR71C472KA86 | 4700pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71C472MA86 | 4700pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR71C682KA86 | 6800pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71C682MA86 | 6800pF | 16 | X7R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR71E222KA86 | 2200pF | 25 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71E222MA86 | 2200pF | 25 | X7R | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR71H102KA86 | 1000pF | 50 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71H152KA86 | 1500pF | 50 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71H221KA86 | 220pF | 50 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71H331KA86 | 330pF | 50 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71H471KA86 | 470pF | 50 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR71H681KA86 | 680pF | 50 | X7R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM185C80J105KE26 | 1uF | 6.3 | X6S | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185C80J475ME11 | 4.7uF | 6.3 | X6S | | 1608M/0603 | 0.55 | +/-20% | General Purpose |
| GRM185C81A105KE36 | 1uF | 10 | X6S | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185C81A475KE11 | 4.7uF | 10 | X6S | | 1608M/0603 | 0.55 | +/-10% | General Purpose |
| GRM185C81A475ME11 | 4.7uF | 10 | X6S | | 1608M/0603 | 0.55 | +/-20% | General Purpose |
| GRM185D70J475ME11 | 4.7uF | 6.3 | X7T | | 1608M/0603 | 0.55 | +/-20% | General Purpose |
| GRM185D71A105KE36 | 1uF | 10 | X7T | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185R60G106ME15 | 10uF | 4 | X5R | | 1608M/0603 | 0.5 | +/-20% | General Purpose |
| GRM185R60J105KE26 | 1uF | 6.3 | X5R | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185R60J106ME15 | 10uF | 6.3 | X5R | | 1608M/0603 | 0.5 | +/-20% | General Purpose |
| GRM185R60J225KE26 | 2.2uF | 6.3 | X5R | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185R61A475KE11 | 4.7uF | 10 | X5R | | 1608M/0603 | 0.55 | +/-10% | General Purpose |
| GRM185R61A475ME11 | 4.7uF | 10 | X5R | | 1608M/0603 | 0.55 | +/-20% | General Purpose |
| GRM185R61C105KE44 | 1uF | 16 | X5R | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185R61C105ME44 | 1uF | 16 | X5R | | 1608M/0603 | 0.5 | +/-20% | General Purpose |
| GRM185R61C475KE11 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.55 | +/-10% | General Purpose |
| GRM185R61C475ME11 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.55 | +/-20% | General Purpose |
| GRM185R61E105KA12 | 1uF | 25 | X5R | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185R61E105MA12 | 1uF | 25 | X5R | | 1608M/0603 | 0.5 | +/-20% | General Purpose |
| GRM186R60G226ME15 | 22uF | 4 | X5R | | 1608M/0603 | 0.6 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|-----------------|
| GRM186R60J226ME15 | 22uF | 6.3 | X5R | | 1608M/0603 | 0.6 | +/-20% | General Purpose |
| GRM187R60J226ME15 | 22uF | 6.3 | X5R | | 1608M/0603 | 0.8 | +/-20% | General Purpose |
| GRM187R61A226ME15 | 22uF | 10 | X5R | | 1608M/0603 | 0.8 | +/-20% | General Purpose |
| GRM188C60J226MEA0 | 22uF | 6.3 | X5S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C70G225KE20 | 2.2uF | 4 | X7S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C70G225ME20 | 2.2uF | 4 | X7S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C70J225KE20 | 2.2uF | 6.3 | X7S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C70J225ME20 | 2.2uF | 6.3 | X7S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C71A475KE11 | 4.7uF | 10 | X7S | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188C71A475ME11 | 4.7uF | 10 | X7S | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188C71C225KE11 | 2.2uF | 16 | X7S | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188C71C225ME11 | 2.2uF | 16 | X7S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C71C475KE21 | 4.7uF | 16 | X7S | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188C71C475ME21 | 4.7uF | 16 | X7S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C71C684MA12 | 0.68uF | 16 | X7S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C71E225KE11 | 2.2uF | 25 | X7S | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188C71E225ME11 | 2.2uF | 25 | X7S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C80E106ME47 | 10uF | 2.5 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C80E476ME05 | 47uF | 2.5 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C80G105MA01 | 1uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C80G106KE47 | 10uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C80G106ME47 | 10uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C80G226ME15 | 22uF | 4 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C80G226MEA0 | 22uF | 4 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C80G475KE19 | 4.7uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C80G475ME19 | 4.7uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C80J225KE19 | 2.2uF | 6.3 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C80J225ME19 | 2.2uF | 6.3 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C80J475KE15 | 4.7uF | 6.3 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C80J475ME15 | 4.7uF | 6.3 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C81A105KA12 | 1uF | 10 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C81A106MA73 | 10uF | 10 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C81A225KAAD | 2.2uF | 10 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C81A225KE34 | 2.2uF | 10 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C81A225ME34 | 2.2uF | 10 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C81C105KA12 | 1uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C81C105MA12 | 1uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C81C106MA73 | 10uF | 16 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C81C225KA12 | 2.2uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C81C225MA12 | 2.2uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C81C475KE11 | 4.7uF | 16 | X6S | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188C81C475ME11 | 4.7uF | 16 | X6S | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188C81E105KA12 | 1uF | 25 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C81E105KAAD | 1uF | 25 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C81E105MAAD | 1uF | 25 | X6S | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188C81E225KE11 | 2.2uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188C81E225ME11 | 2.2uF | 25 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C81E475KE11 | 4.7uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188C81E475ME11 | 4.7uF | 25 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188C8YA105KAAL | 1uF | 35 | X6S | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188C8YA225KE11 | 2.2uF | 35 | X6S | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188C8YA225ME11 | 2.2uF | 35 | X6S | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188D70J106MA73 | 10uF | 6.3 | X7T | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188D71A106MA73 | 10uF | 10 | X7T | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R60E476ME15 | 47uF | 2.5 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R60G106ME47 | 10uF | 4 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R60G226MEA0 | 22uF | 4 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R60G476ME15 | 47uF | 4 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R60J105KA01 | 1uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R60J105MA01 | 1uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R60J106ME47 | 10uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R60J106ME84 | 10uF | 6.3 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188R60J225KE19 | 2.2uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R60J226MEA0 | 22uF | 6.3 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R60J474KA01 | 0.47uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R60J475KE19 | 4.7uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R60J475ME19 | 4.7uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R60J475ME84 | 4.7uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R60J476ME15 | 47uF | 6.3 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R61A105KA61 | 1uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A105MA61 | 1uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61A106KAAL | 10uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188R61A106KE69 | 10uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188R61A106MAAL | 10uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM188R61A106ME69 | 10uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188R61A224KA01 | 0.22uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A225KE34 | 2.2uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A225ME34 | 2.2uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61A226ME15 | 22uF | 10 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R61A334KA61 | 0.33uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A334MA61 | 0.33uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61A335KE15 | 3.3uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A474KA61 | 0.47uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A475KAAJ | 4.7uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188R61A475KE15 | 4.7uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A475MAAJ | 4.7uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188R61A475ME15 | 4.7uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61A684KA61 | 0.68uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61A684MA61 | 0.68uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61C104KA01 | 0.1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C105KA12 | 1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C105KA93 | 1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C105MA12 | 1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61C105MA93 | 1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61C106KAAL | 10uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188R61C106MA73 | 10uF | 16 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R61C106MAAL | 10uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188R61C224KA88 | 0.22uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C225KAAD | 2.2uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C225KE15 | 2.2uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C474KA12 | 0.47uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C474KA93 | 0.47uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C474MA12 | 0.47uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61C474MA93 | 0.47uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61C475KAAJ | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188R61C475KE11 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188R61C475MAAJ | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188R61C475ME11 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188R61C684KA75 | 0.68uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61C684MA75 | 0.68uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61E104KA01 | 0.1uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61E105KA12 | 1uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61E105KAAD | 1uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61E105MA12 | 1uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61E106MA73 | 10uF | 25 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R61E224KA88 | 0.22uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61E225KA12 | 2.2uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61E225MA12 | 2.2uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61E474KA12 | 0.47uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61E474MA12 | 0.47uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61E475KE11 | 4.7uF | 25 | X5R | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188R61E475KE15 | 4.7uF | 25 | X5R | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188R61E475ME11 | 4.7uF | 25 | X5R | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188R61E475ME15 | 4.7uF | 25 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R61E684KA75 | 0.68uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61E684MA75 | 0.68uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61H102KA01 | 1000pF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H103KA01 | 10000pF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H105KAAL | 1uF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H105MAAL | 1uF | 50 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61H222KA01 | 2200pF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H223KA01 | 22000pF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H224KAC4 | 0.22uF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H225KE11 | 2.2uF | 50 | X5R | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188R61H225ME11 | 2.2uF | 50 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R61H472KA01 | 4700pF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H474KA12 | 0.47uF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R61H474MA12 | 0.47uF | 50 | X5R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R61H684KA75 | 0.68uF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R6YA105KA12 | 1uF | 35 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R6YA105KAAL | 1uF | 35 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R6YA106MA73 | 10uF | 35 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R6YA225KA12 | 2.2uF | 35 | X5R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R6YA475KE15 | 4.7uF | 35 | X5R | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188R6YA475ME15 | 4.7uF | 35 | X5R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188R70J104KA01 | 0.1uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R70J105KA01 | 1uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R70J105MA01 | 1uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|--------------------------------|------------------------------|---------------------|-------------------|-----------------|
| GRM188R70J224KA88 | 0.22uF | 6.3 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R70J225KE15 | 2.2uF | 6.3 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R70J474KA01 | 0.47uF | 6.3 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A105KA61 | 1uF | 10 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A154KA01 | 0.15uF | 10 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A224JA01 | 0.22uF | 10 | X7R | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71A224KA01 | 0.22uF | 10 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A225KE15 | 2.2uF | 10 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A225ME15 | 2.2uF | 10 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71A334KA61 | 0.33uF | 10 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A334MA61 | 0.33uF | 10 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71A474KA61 | 0.47uF | 10 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A474MA61 | 0.47uF | 10 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71A684KA61 | 0.68uF | 10 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71A684MA61 | 0.68uF | 10 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71C104KA01 | 0.1uF | 16 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71C104MA01 | 0.1uF | 16 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71C105KA12 | 1uF | 16 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71C105KE15 | 1uF | 16 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71C105MA12 | 1uF | 16 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71C105ME15 | 1uF | 16 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71C154KA01 | 0.15uF | 16 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71C224KA01 | 0.22uF | 16 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71C224MA01 | 0.22uF | 16 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71C334KA01 | 0.33uF | 16 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71C473JA01 | 47000pF | 16 | X7R | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71C474KA88 | 0.47uF | 16 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71C474MA88 | 0.47uF | 16 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E102KA01 | 1000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E103KA01 | 10000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E103MA01 | 10000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E104KA01 | 0.1uF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E104MA01 | 0.1uF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E105KA12 | 1uF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E105MA12 | 1uF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E152KA01 | 1500pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E153KA01 | 15000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E154KA01 | 0.15uF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E222KA01 | 2200pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E222MA01 | 2200pF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E223KA01 | 22000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E223MA01 | 22000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E224KA88 | 0.22uF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E224MA88 | 0.22uF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E272KA01 | 2700pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E332KA01 | 3300pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E333KA01 | 33000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E472KA01 | 4700pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E472MA01 | 4700pF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E473KA01 | 47000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E473MA01 | 47000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E474KA12 | 0.47uF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E474MA12 | 0.47uF | 25 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71E682KA01 | 6800pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E683KA01 | 68000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71E823KA01 | 82000pF | 25 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H102KA01 | 1000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H102MA01 | 1000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H103JA01 | 10000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71H103KA01 | 10000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H103MA01 | 10000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H104KA93 | 0.1uF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H104MA93 | 0.1uF | 50 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H123JA01 | 12000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71H123KA01 | 12000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H152KA01 | 1500pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H153JA01 | 15000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71H153KA01 | 15000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H154KAC4 | 0.15uF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H154MAC4 | 0.15uF | 50 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H182KA01 | 1800pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H183KA01 | 18000pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H221KA01 | 220pF | 50 | X7R | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H221MA01 | 220pF | 50 | X7R | 1608M/0603 | 0.9 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM188R71H222JA01 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71H222KA01 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H222MA01 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H223KA01 | 22000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H223MA01 | 22000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H224KAC4 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H224MAC4 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H273KA61 | 27000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H331KA01 | 330pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H332KA01 | 3300pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H333KA61 | 33000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H392KA01 | 3900pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H393KA61 | 39000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H471JA01 | 470pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71H471KA01 | 470pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H471MA01 | 470pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H472JA01 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-5% | General Purpose |
| GRM188R71H472KA01 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H472MA01 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H473KA61 | 47000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H473MA61 | 47000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R71H562KA01 | 5600pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H681KA01 | 680pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H682KA01 | 6800pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H683KA93 | 68000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R71H822KA01 | 8200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A102KA01 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A102MA01 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R72A104KA35 | 0.1uF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A104MA35 | 0.1uF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R72A152KA01 | 1500pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A153KAC4 | 15000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A153MAC4 | 15000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R72A221KA01 | 220pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A221MA01 | 220pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R72A222KA01 | 2200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A222MA01 | 2200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R72A223KAC4 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A223MAC4 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R72A331KA01 | 330pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A332KA01 | 3300pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A471KA01 | 470pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R72A471MA01 | 470pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R72A681KA01 | 680pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R7YA105KA12 | 1uF | 35 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R7YA105MA12 | 1uF | 35 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R7YA474KE05 | 0.47uF | 35 | X7R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R7YA474ME05 | 0.47uF | 35 | X7R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188Z71A106KA73 | 10uF | 10 | X7R | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188Z71C225KE43 | 2.2uF | 16 | X7R | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188Z71C475KE21 | 4.7uF | 16 | X7R | | 1608M/0603 | 1 | +/-10% | General Purpose |
| GRM188Z71C475ME21 | 4.7uF | 16 | X7R | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM216C81C105KA12 | 1uF | 16 | X6S | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216D71C105KA12 | 1uF | 16 | X7T | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216D71C105MA12 | 1uF | 16 | X7T | | 2012M/0805 | 0.7 | +/-20% | General Purpose |
| GRM216R61C105KA88 | 1uF | 16 | X5R | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216R61E105KA12 | 1uF | 25 | X5R | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216R71H103KA01 | 10000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216R71H123KA01 | 12000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216R71H223KA01 | 22000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216R71H223MA01 | 22000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | General Purpose |
| GRM216R71H472KA01 | 4700pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM216R71H682KA01 | 6800pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM219C71C475KE21 | 4.7uF | 16 | X7S | | 2012M/0805 | 1 | +/-10% | General Purpose |
| GRM219C71C475ME21 | 4.7uF | 16 | X7S | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM219C71E475KE21 | 4.7uF | 25 | X7S | | 2012M/0805 | 1 | +/-10% | General Purpose |
| GRM219C71E475ME21 | 4.7uF | 25 | X7S | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM219C80G106KE19 | 10uF | 4 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C80G106ME19 | 10uF | 4 | X6S | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219C80J106KE39 | 10uF | 6.3 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C80J106ME39 | 10uF | 6.3 | X6S | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219C80J475KE19 | 4.7uF | 6.3 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C81A475KE34 | 4.7uF | 10 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C81A475ME34 | 4.7uF | 10 | X6S | | 2012M/0805 | 0.95 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM219C81C225KA12 | 2.2uF | 16 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C81C475KA73 | 4.7uF | 16 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C81C475MA73 | 4.7uF | 16 | X6S | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219C81E225KE15 | 2.2uF | 25 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C81E225ME15 | 2.2uF | 25 | X6S | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219C81E475KE21 | 4.7uF | 25 | X6S | | 2012M/0805 | 1 | +/-10% | General Purpose |
| GRM219C81E475ME21 | 4.7uF | 25 | X6S | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM219C8YA225KE15 | 2.2uF | 35 | X6S | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219C8YA225ME15 | 2.2uF | 35 | X6S | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219C8YA475KE21 | 4.7uF | 35 | X6S | | 2012M/0805 | 1 | +/-10% | General Purpose |
| GRM219C8YA475ME21 | 4.7uF | 35 | X6S | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM219D71A475KE15 | 4.7uF | 10 | X7T | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219D71A475ME15 | 4.7uF | 10 | X7T | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219D71C225KA12 | 2.2uF | 16 | X7T | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219D71C225MA12 | 2.2uF | 16 | X7T | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219D80E476ME44 | 47uF | 2.5 | X6T | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R60G226ME66 | 22uF | 4 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R60G476ME44 | 47uF | 4 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R60J106KE19 | 10uF | 6.3 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R60J106ME19 | 10uF | 6.3 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R60J226ME47 | 22uF | 6.3 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R60J226MEA0 | 22uF | 6.3 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R60J475KE19 | 4.7uF | 6.3 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R60J476ME44 | 47uF | 6.3 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61A105KA01 | 1uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61A106KE44 | 10uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61A106ME44 | 10uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61A106ME47 | 10uF | 10 | X5R | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM219R61A225KA01 | 2.2uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61A226MEA0 | 22uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61A335KE19 | 3.3uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61A475KE34 | 4.7uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61A475ME34 | 4.7uF | 10 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61C106KA73 | 10uF | 16 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61C106MA73 | 10uF | 16 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61C225KA88 | 2.2uF | 16 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61C226ME15 | 22uF | 16 | X5R | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM219R61C475KE15 | 4.7uF | 16 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61E106KA12 | 10uF | 25 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61E106MA12 | 10uF | 25 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61E225KA12 | 2.2uF | 25 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61E225MA12 | 2.2uF | 25 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61E475KA73 | 4.7uF | 25 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61E475MA73 | 4.7uF | 25 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61H105KA73 | 1uF | 50 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61H105MA73 | 1uF | 50 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R61H225KE15 | 2.2uF | 50 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R61H225ME15 | 2.2uF | 50 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R6YA475KA73 | 4.7uF | 35 | X5R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R6YA475MA73 | 4.7uF | 35 | X5R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71A225KE15 | 2.2uF | 10 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71A225ME15 | 2.2uF | 10 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71C225KE15 | 2.2uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71C225ME15 | 2.2uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71C334KA88 | 0.33uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71C474KA01 | 0.47uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71C684KA01 | 0.68uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71E104KA01 | 0.1uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71E104MA01 | 0.1uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71E105KA88 | 1uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71E224MA01 | 0.22uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71E474KA88 | 0.47uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71E474MA88 | 0.47uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71E683KA01 | 68000pF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71E684KA88 | 0.68uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71H103KA01 | 10000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71H103MA01 | 10000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71H153KA01 | 15000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71H153MA01 | 15000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R71H223KA17 | 22000pF | 50 | X7R | | 2012M/0805 | 1 | +/-10% | General Purpose |
| GRM219R71H223MA17 | 22000pF | 50 | X7R | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM219R71H333KA01 | 33000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R71H334KA88 | 0.33uF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R72A103KA01 | 10000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM219R72A103MA01 | 10000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R72A682KA01 | 6800pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R7YA105KA12 | 1uF | 35 | X7R | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM21AR72A224KAC5 | 0.22uF | 100 | X7R | | 2012M/0805 | 1 | +/-10% | General Purpose |
| GRM21AR72A224MAC5 | 0.22uF | 100 | X7R | | 2012M/0805 | 1 | +/-20% | General Purpose |
| GRM21AR72A334KAC5 | 0.33uF | 100 | X7R | | 2012M/0805 | 1 | +/-10% | General Purpose |
| GRM21BC70G106KE45 | 10uF | 4 | X7S | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BC71C106KE11 | 10uF | 16 | X7S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC71C106ME11 | 10uF | 16 | X7S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC71E106KE11 | 10uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC71E106ME11 | 10uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC71E475KE11 | 4.7uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC71E475ME11 | 4.7uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC71H475KE11 | 4.7uF | 50 | X7S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC71H475ME11 | 4.7uF | 50 | X7S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC72A105KE01 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC7YA475KE11 | 4.7uF | 35 | X7S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC7YA475ME11 | 4.7uF | 35 | X7S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC80E107ME15 | 100uF | 2.5 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC80G106KE01 | 10uF | 4 | X6S | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BC80G106ME19 | 10uF | 4 | X6S | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BC80G107ME15 | 100uF | 4 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC80G226ME39 | 22uF | 4 | X6S | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BC80G476ME15 | 47uF | 4 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC80J106KE19 | 10uF | 6.3 | X6S | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BC80J106ME19 | 10uF | 6.3 | X6S | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BC80J226ME51 | 22uF | 6.3 | X6S | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BC81A106KE18 | 10uF | 10 | X6S | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BC81A106ME18 | 10uF | 10 | X6S | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BC81A226ME44 | 22uF | 10 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC81C106KA73 | 10uF | 16 | X6S | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BC81C106KE15 | 10uF | 16 | X6S | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BC81C106MA73 | 10uF | 16 | X6S | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BC81C106ME15 | 10uF | 16 | X6S | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BC81C226ME44 | 22uF | 16 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC81C475KA88 | 4.7uF | 16 | X6S | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BC81E106KE11 | 10uF | 25 | X6S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC81E106ME11 | 10uF | 25 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC81E225KA12 | 2.2uF | 25 | X6S | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BC81E475KA12 | 4.7uF | 25 | X6S | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BC81E475MA12 | 4.7uF | 25 | X6S | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BC81H475KE11 | 4.7uF | 50 | X6S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC81H475ME11 | 4.7uF | 50 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC8YA106KE11 | 10uF | 35 | X6S | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BC8YA106ME11 | 10uF | 35 | X6S | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BC8YA225KA73 | 2.2uF | 35 | X6S | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BC8YA225MA73 | 2.2uF | 35 | X6S | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BC8YA475KE51 | 4.7uF | 35 | X6S | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BD70J226ME44 | 22uF | 6.3 | X7T | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BD71A226ME44 | 22uF | 10 | X7T | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BD71C475KA12 | 4.7uF | 16 | X7T | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BD71C475MA12 | 4.7uF | 16 | X7T | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BE70G226ME51 | 22uF | 4 | X7U | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BE71C475KA12 | 4.7uF | 16 | X7U | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BE71C475MA12 | 4.7uF | 16 | X7U | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR60G107ME11 | 100uF | 4 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR60G476ME01 | 47uF | 4 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR60J106KE19 | 10uF | 6.3 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR60J106ME19 | 10uF | 6.3 | X5R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR60J107ME15 | 100uF | 6.3 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR60J225KA01 | 2.2uF | 6.3 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR60J226ME39 | 22uF | 6.3 | X5R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR60J475KA11 | 4.7uF | 6.3 | X5R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR60J475MA11 | 4.7uF | 6.3 | X5R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR60J476ME01 | 47uF | 6.3 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR61A105KA01 | 1uF | 10 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61A106KE19 | 10uF | 10 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61A106ME19 | 10uF | 10 | X5R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR61A225KA01 | 2.2uF | 10 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61A225MA01 | 2.2uF | 10 | X5R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR61A226ME44 | 22uF | 10 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR61A226ME51 | 22uF | 10 | X5R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR61A475KA73 | 4.7uF | 10 | X5R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR61A475MA73 | 4.7uF | 10 | X5R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM21BR61A476ME15 | 47uF | 10 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR61C105KA01 | 1uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61C106KE15 | 10uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61C106ME15 | 10uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR61C225KA88 | 2.2uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61C226ME44 | 22uF | 16 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR61C475KA88 | 4.7uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61D106KE15 | 10uF | 20 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61D106ME15 | 10uF | 20 | X5R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR61E106KA73 | 10uF | 25 | X5R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR61E106MA73 | 10uF | 25 | X5R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR61E225KA12 | 2.2uF | 25 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61E226ME44 | 22uF | 25 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR61E475KA12 | 4.7uF | 25 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61E475MA12 | 4.7uF | 25 | X5R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR61H105KA12 | 1uF | 50 | X5R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR61H225KA73 | 2.2uF | 50 | X5R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR61H225MA73 | 2.2uF | 50 | X5R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR61H475KE51 | 4.7uF | 50 | X5R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR61H475ME51 | 4.7uF | 50 | X5R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR6YA106KE43 | 10uF | 35 | X5R | | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM21BR6YA106ME43 | 10uF | 35 | X5R | | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BR70J106KA73 | 10uF | 6.3 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR70J106KE76 | 10uF | 6.3 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR70J106ME76 | 10uF | 6.3 | X7R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR70J225KA01 | 2.2uF | 6.3 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71A105KA01 | 1uF | 10 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71A106KA73 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71A106KE51 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71A106MA73 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR71A106ME51 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR71A225KA01 | 2.2uF | 10 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71A225MA01 | 2.2uF | 10 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71A475KA73 | 4.7uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71A475MA73 | 4.7uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR71C105KA01 | 1uF | 16 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71C224KA01 | 0.22uF | 16 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71C224MA01 | 0.22uF | 16 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71C225KA12 | 2.2uF | 16 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71C225MA12 | 2.2uF | 16 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71C474MA01 | 0.47uF | 16 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71C475KA73 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71C475KE51 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71C475MA73 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR71E104JA01 | 0.1uF | 25 | X7R | | 2012M/0805 | 1.35 | +/-5% | General Purpose |
| GRM21BR71E104KA01 | 0.1uF | 25 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71E104MA01 | 0.1uF | 25 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71E105KA99 | 1uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71E154KA01 | 0.15uF | 25 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71E224KA01 | 0.22uF | 25 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71E224MA01 | 0.22uF | 25 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71E225KA73 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71E225KE11 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71E225ME11 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR71E334KA01 | 0.33uF | 25 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71E475KA73 | 4.7uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR71E475MA73 | 4.7uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR71H104KA01 | 0.1uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71H104MA01 | 0.1uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71H105KA12 | 1uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71H154KA01 | 0.15uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71H224KA01 | 0.22uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71H224MA01 | 0.22uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71H473KA01 | 47000pF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71H473MA01 | 47000pF | 50 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71H474KA88 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR71H474MA88 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR71H683KA01 | 68000pF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR72A103KA01 | 10000pF | 100 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR72A103MA01 | 10000pF | 100 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR72A104KAC4 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR72A104MAC4 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR72A153KA01 | 15000pF | 100 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR72A223KA01 | 22000pF | 100 | X7R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|--------------------------------|------------------------------|---------------------|-------------------|-----------------|
| GRM21BR72A223MA01 | 22000pF | 100 | X7R | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR72A333KA01 | 33000pF | 100 | X7R | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR72A473KA01 | 47000pF | 100 | X7R | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR72A473MA01 | 47000pF | 100 | X7R | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR72A474KA73 | 0.47uF | 100 | X7R | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR72A474MA73 | 0.47uF | 100 | X7R | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BR72A683KAC4 | 68000pF | 100 | X7R | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR72A683MAC4 | 68000pF | 100 | X7R | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BZ71E106KE15 | 10uF | 25 | X7R | 2012M/0805 | 1.45 | +/-10% | General Purpose |
| GRM316C81C225KA12 | 2.2uF | 16 | X6S | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM316D71C225KA12 | 2.2uF | 16 | X7T | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM316D71C225MA12 | 2.2uF | 16 | X7T | 3216M/1206 | 0.7 | +/-20% | General Purpose |
| GRM316R61A475KE19 | 4.7uF | 10 | X5R | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM316R61C225KA88 | 2.2uF | 16 | X5R | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM316R61E225KA12 | 2.2uF | 25 | X5R | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM319C80J106KE19 | 10uF | 6.3 | X6S | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319C80J106ME19 | 10uF | 6.3 | X6S | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319C80J226ME15 | 22uF | 6.3 | X6S | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319C81A106KA12 | 10uF | 10 | X6S | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319C81A106MA12 | 10uF | 10 | X6S | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319C81C106KA12 | 10uF | 16 | X6S | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319C81C106MA12 | 10uF | 16 | X6S | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319C81C475KA12 | 4.7uF | 16 | X6S | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319C8YA225KA12 | 2.2uF | 35 | X6S | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319C8YA225MA12 | 2.2uF | 35 | X6S | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319D71C475KA12 | 4.7uF | 16 | X7T | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319D71C475MA12 | 4.7uF | 16 | X7T | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R60J106KE19 | 10uF | 6.3 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R60J226ME15 | 22uF | 6.3 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R61A105KA01 | 1uF | 10 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61A106KE19 | 10uF | 10 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61A106ME19 | 10uF | 10 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R61A225KA01 | 2.2uF | 10 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61A226ME15 | 22uF | 10 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R61A475KA01 | 4.7uF | 10 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61C105KAA3 | 1uF | 16 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61C106KE15 | 10uF | 16 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61C106ME15 | 10uF | 16 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R61C226ME15 | 22uF | 16 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R61C335KA12 | 3.3uF | 16 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61C475KA88 | 4.7uF | 16 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61E105KC36 | 1uF | 25 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61E106KA12 | 10uF | 25 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61E106MA12 | 10uF | 25 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R61E475KA12 | 4.7uF | 25 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61H225KA12 | 2.2uF | 50 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61H225MA12 | 2.2uF | 50 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R61H475KA12 | 4.7uF | 50 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R61H475MA12 | 4.7uF | 50 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R6YA106KA12 | 10uF | 35 | X5R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R6YA106MA12 | 10uF | 35 | X5R | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R71A105KA01 | 1uF | 10 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R71C105KAA3 | 1uF | 16 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R71E334KA01 | 0.33uF | 25 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R71E474KA01 | 0.47uF | 25 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R71H104JA01 | 0.1uF | 50 | X7R | 3216M/1206 | 0.95 | +/-5% | General Purpose |
| GRM319R71H153KA01 | 15000pF | 50 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R71H223KA01 | 22000pF | 50 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R71H334KA01 | 0.33uF | 50 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R71H683KA01 | 68000pF | 50 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R72A104KA01 | 0.1uF | 100 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R72A153KA01 | 15000pF | 100 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R72A222KA01 | 2200pF | 100 | X7R | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM31CC70G226ME01 | 22uF | 4 | X7S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CC70J226KE15 | 22uF | 6.3 | X7S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC71C226ME11 | 22uF | 16 | X7S | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CC72A475KE11 | 4.7uF | 100 | X7S | 3216M/1206 | 1.9 | +/-10% | General Purpose |
| GRM31CC72A475ME11 | 4.7uF | 100 | X7S | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CC80E157ME11 | 150uF | 2.5 | X6S | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CC80E227ME11 | 220uF | 2.5 | X6S | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CC80G157ME11 | 150uF | 4 | X6S | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CC80G226KE19 | 22uF | 4 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC80G226ME19 | 22uF | 4 | X6S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CC80G227ME11 | 220uF | 4 | X6S | 3216M/1206 | 1.9 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-----------------------------|------------------------|------------------|----------------|-----------------|
| GRM31CC80J226KE19 | 22uF | 6.3 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC80J226ME19 | 22uF | 6.3 | X6S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CC81A226KE19 | 22uF | 10 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC81A226ME19 | 22uF | 10 | X6S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CC81A476ME44 | 47uF | 10 | X6S | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CC81C106KA12 | 10uF | 16 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC81C106KE19 | 10uF | 16 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC81C106MA12 | 10uF | 16 | X6S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CC81C226KE15 | 22uF | 16 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC81C226ME15 | 22uF | 16 | X6S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CC81E106KE15 | 10uF | 25 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC81E106MA12 | 10uF | 25 | X6S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CC81E226ME11 | 22uF | 25 | X6S | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CC8YA106KA12 | 10uF | 35 | X6S | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CC8YA106MA12 | 10uF | 35 | X6S | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CD70J226KE19 | 22uF | 6.3 | X7T | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CD70J226ME19 | 22uF | 6.3 | X7T | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CD71A226KE15 | 22uF | 10 | X7T | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CD71A226ME15 | 22uF | 10 | X7T | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CD80G107ME39 | 100uF | 4 | X6T | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CD80G476ME19 | 47uF | 4 | X6T | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CD80J107ME39 | 100uF | 6.3 | X6T | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CE70G107ME39 | 100uF | 4 | X7U | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CE70G476ME15 | 47uF | 4 | X7U | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR60E227ME11 | 220uF | 2.5 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR60G107ME39 | 100uF | 4 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR60G157ME11 | 150uF | 4 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR60G227ME11 | 220uF | 4 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR60J106KA01 | 10uF | 6.3 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR60J106MC01 | 10uF | 6.3 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR60J107ME39 | 100uF | 6.3 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR60J157ME11 | 150uF | 6.3 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR60J226KE19 | 22uF | 6.3 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR60J226ME19 | 22uF | 6.3 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR60J227ME11 | 220uF | 6.3 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR60J475KA01 | 4.7uF | 6.3 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR60J476KE19 | 47uF | 6.3 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR60J476ME19 | 47uF | 6.3 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61A106KA01 | 10uF | 10 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61A107ME05 | 100uF | 10 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR61A226KE19 | 22uF | 10 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61A226ME19 | 22uF | 10 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61A475KA01 | 4.7uF | 10 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61A476KE15 | 47uF | 10 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61A476ME15 | 47uF | 10 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61C106KA88 | 10uF | 16 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61C106KC31 | 10uF | 16 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61C226KE15 | 22uF | 16 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61C226ME15 | 22uF | 16 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61C475KA01 | 4.7uF | 16 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61C475MA01 | 4.7uF | 16 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61C476ME44 | 47uF | 16 | X5R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CR61E106KA12 | 10uF | 25 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61E106MA12 | 10uF | 25 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61E226KE15 | 22uF | 25 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61E226ME15 | 22uF | 25 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61E335KA88 | 3.3uF | 25 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61E475KA88 | 4.7uF | 25 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61H106KA12 | 10uF | 50 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR61H106MA12 | 10uF | 50 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR61H225KA88 | 2.2uF | 50 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR6YA106KA12 | 10uF | 35 | X5R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR6YA106MA12 | 10uF | 35 | X5R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR70J106KA01 | 10uF | 6.3 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR70J226KE19 | 22uF | 6.3 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR70J226ME19 | 22uF | 6.3 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR71A106KA01 | 10uF | 10 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71A106MA01 | 10uF | 10 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR71A226KE15 | 22uF | 10 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71A226ME15 | 22uF | 10 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR71A475KA01 | 4.7uF | 10 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71C106KA12 | 10uF | 16 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71C106KAC7 | 10uF | 16 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71C106MA12 | 10uF | 16 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-----------------------------|------------------------|------------------|----------------|-----------------|
| GRM31CR71C106MAC7 | 10uF | 16 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR71C475KA01 | 4.7uF | 16 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71C475MA01 | 4.7uF | 16 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR71E106KA12 | 10uF | 25 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71E106MA12 | 10uF | 25 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR71E475KA88 | 4.7uF | 25 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71H225KA88 | 2.2uF | 50 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71H475KA12 | 4.7uF | 50 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR71H475MA12 | 4.7uF | 50 | X7R | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR72A105KA01 | 1uF | 100 | X7R | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR72A225KA73 | 2.2uF | 100 | X7R | 3216M/1206 | 1.9 | +/-10% | General Purpose |
| GRM31CR72A225MA73 | 2.2uF | 100 | X7R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31CZ72A475KE11 | 4.7uF | 100 | X7R | 3216M/1206 | 1.9 | +/-10% | General Purpose |
| GRM31CZ72A475ME11 | 4.7uF | 100 | X7R | 3216M/1206 | 1.9 | +/-20% | General Purpose |
| GRM31MC81A106KE19 | 10uF | 10 | X6S | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MC81A106ME19 | 10uF | 10 | X6S | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MC81C106KA12 | 10uF | 16 | X6S | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MC81C685KA12 | 6.8uF | 16 | X6S | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MC81C685MA12 | 6.8uF | 16 | X6S | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MC81E106KA12 | 10uF | 25 | X6S | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MC81E106MA12 | 10uF | 25 | X6S | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR61A106KE19 | 10uF | 10 | X5R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR61A225KA01 | 2.2uF | 10 | X5R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR61C105KA01 | 1uF | 16 | X5R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR61C106KA12 | 10uF | 16 | X5R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR61C225KA35 | 2.2uF | 16 | X5R | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MR61E106KA12 | 10uF | 25 | X5R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR61E106MA12 | 10uF | 25 | X5R | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR71A225KA01 | 2.2uF | 10 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71C105KA01 | 1uF | 16 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71C105MA01 | 1uF | 16 | X7R | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR71C225KA35 | 2.2uF | 16 | X7R | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MR71C225MA35 | 2.2uF | 16 | X7R | 3216M/1206 | 1.3 | +/-20% | General Purpose |
| GRM31MR71E105KA01 | 1uF | 25 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71E105MC01 | 1uF | 25 | X7R | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR71E225KA93 | 2.2uF | 25 | X7R | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MR71E474KA01 | 0.47uF | 25 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71H105KA88 | 1uF | 50 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71H154KA01 | 0.15uF | 50 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71H224KA01 | 0.22uF | 50 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71H224MA01 | 0.22uF | 50 | X7R | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR71H474JA01 | 0.47uF | 50 | X7R | 3216M/1206 | 1.25 | +/-5% | General Purpose |
| GRM31MR71H474KA01 | 0.47uF | 50 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR71H474MA01 | 0.47uF | 50 | X7R | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR71H684KA88 | 0.68uF | 50 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR72A154KA01 | 0.15uF | 100 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR72A223KA01 | 22000pF | 100 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR72A223MA01 | 22000pF | 100 | X7R | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR72A224KA01 | 0.22uF | 100 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR72A333KA01 | 33000pF | 100 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR72A473KA01 | 47000pF | 100 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR72A473MA01 | 47000pF | 100 | X7R | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MR72A474KA35 | 0.47uF | 100 | X7R | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MR72A474MA35 | 0.47uF | 100 | X7R | 3216M/1206 | 1.3 | +/-20% | General Purpose |
| GRM31MR72A683KA01 | 68000pF | 100 | X7R | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR72A684KA35 | 0.68uF | 100 | X7R | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM32AR61C106KAB7 | 10uF | 16 | X5R | 3225M/1210 | 1 | +/-10% | General Purpose |
| GRM32CR72A105KA35 | 1uF | 100 | X7R | 3225M/1210 | 1.8 | +/-10% | General Purpose |
| GRM32CR72A105MA35 | 1uF | 100 | X7R | 3225M/1210 | 1.8 | +/-20% | General Purpose |
| GRM32CR72A684KA01 | 0.68uF | 100 | X7R | 3225M/1210 | 1.8 | +/-10% | General Purpose |
| GRM32DC72A475KE01 | 4.7uF | 100 | X7S | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DC72A475ME01 | 4.7uF | 100 | X7S | 3225M/1210 | 2.2 | +/-20% | General Purpose |
| GRM32DC81E106KA12 | 10uF | 25 | X6S | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR60J226MA01 | 22uF | 6.3 | X5R | 3225M/1210 | 2.2 | +/-20% | General Purpose |
| GRM32DR60J336ME19 | 33uF | 6.3 | X5R | 3225M/1210 | 2.2 | +/-20% | General Purpose |
| GRM32DR61C106KA01 | 10uF | 16 | X5R | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR61E106KA12 | 10uF | 25 | X5R | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR61E106MA12 | 10uF | 25 | X5R | 3225M/1210 | 2.2 | +/-20% | General Purpose |
| GRM32DR71A106KA01 | 10uF | 10 | X7R | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR71C106KA01 | 10uF | 16 | X7R | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR71E106KA12 | 10uF | 25 | X7R | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR71E475KA61 | 4.7uF | 25 | X7R | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32EC70G107ME15 | 100uF | 4 | X7S | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EC70J107ME15 | 100uF | 6.3 | X7S | 3225M/1210 | 2.7 | +/-20% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-----------------------------|------------------------|------------------|----------------|-----------------|
| GRM32EC80E227ME05 | 220uF | 2.5 | X6S | 3225M/1210 | 2.8 | +/-20% | General Purpose |
| GRM32EC80E337ME05 | 330uF | 2.5 | X6S | 3225M/1210 | 2.8 | +/-20% | General Purpose |
| GRM32EC80G107KE20 | 100uF | 4 | X6S | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EC80G107ME20 | 100uF | 4 | X6S | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EC80G227ME05 | 220uF | 4 | X6S | 3225M/1210 | 2.8 | +/-20% | General Purpose |
| GRM32EC80J107ME20 | 100uF | 6.3 | X6S | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EC80J476KE64 | 47uF | 6.3 | X6S | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EC80J476ME64 | 47uF | 6.3 | X6S | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EC81A476KE19 | 47uF | 10 | X6S | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EC81A476ME19 | 47uF | 10 | X6S | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EC81C476KE15 | 47uF | 16 | X6S | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EC81C476ME15 | 47uF | 16 | X6S | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EC81E226KE15 | 22uF | 25 | X6S | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EC81E226ME15 | 22uF | 25 | X6S | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ED70J476KE20 | 47uF | 6.3 | X7T | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ED70J476ME20 | 47uF | 6.3 | X7T | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ED71A476KE15 | 47uF | 10 | X7T | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ED71A476ME15 | 47uF | 10 | X7T | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EE70G107ME19 | 100uF | 4 | X7U | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EE70J107ME15 | 100uF | 6.3 | X7U | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EE70J476KE20 | 47uF | 6.3 | X7U | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EE70J476ME20 | 47uF | 6.3 | X7U | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER60E337ME05 | 330uF | 2.5 | X5R | 3225M/1210 | 2.8 | +/-20% | General Purpose |
| GRM32ER60G227ME05 | 220uF | 4 | X5R | 3225M/1210 | 2.8 | +/-20% | General Purpose |
| GRM32ER60G337ME05 | 330uF | 4 | X5R | 3225M/1210 | 2.8 | +/-20% | General Purpose |
| GRM32ER60J107ME20 | 100uF | 6.3 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER60J227ME05 | 220uF | 6.3 | X5R | 3225M/1210 | 2.8 | +/-20% | General Purpose |
| GRM32ER60J476KE64 | 47uF | 6.3 | X5R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER60J476ME20 | 47uF | 6.3 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER60J476ME64 | 47uF | 6.3 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER61A106KA01 | 10uF | 10 | X5R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER61A107ME20 | 100uF | 10 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER61A476KE20 | 47uF | 10 | X5R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER61A476ME20 | 47uF | 10 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER61C226ME20 | 22uF | 16 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER61C476KE15 | 47uF | 16 | X5R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER61C476ME15 | 47uF | 16 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER61E226KE15 | 22uF | 25 | X5R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER61E226ME15 | 22uF | 25 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER61H106KA12 | 10uF | 50 | X5R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER61H106MA12 | 10uF | 50 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER6YA106KA12 | 10uF | 35 | X5R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER6YA106MA12 | 10uF | 35 | X5R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER70J476KE20 | 47uF | 6.3 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER70J476ME20 | 47uF | 6.3 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER71A226ME20 | 22uF | 10 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER71A476KE15 | 47uF | 10 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER71A476ME15 | 47uF | 10 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER71C226KEA8 | 22uF | 16 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER71C226MEA8 | 22uF | 16 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER71E226ME15 | 22uF | 25 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER71H475KA88 | 4.7uF | 50 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER71J106KA12 | 10uF | 63 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER71J106MA12 | 10uF | 63 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER71K475KE14 | 4.7uF | 80 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER71K475ME14 | 4.7uF | 80 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER72A225KA35 | 2.2uF | 100 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER72A225MA35 | 2.2uF | 100 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER7YA106KA12 | 10uF | 35 | X7R | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32ER7YA106MA12 | 10uF | 35 | X7R | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32MR71C225KA01 | 2.2uF | 16 | X7R | 3225M/1210 | 1.25 | +/-10% | General Purpose |
| GRM32MR71H104KA01 | 0.1uF | 50 | X7R | 3225M/1210 | 1.25 | +/-10% | General Purpose |
| GRM32NC81A226ME19 | 22uF | 10 | X6S | 3225M/1210 | 1.5 | +/-20% | General Purpose |
| GRM32NC81C226KE15 | 22uF | 16 | X6S | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32NC81C226ME15 | 22uF | 16 | X6S | 3225M/1210 | 1.5 | +/-20% | General Purpose |
| GRM32ND70J226ME19 | 22uF | 6.3 | X7T | 3225M/1210 | 1.5 | +/-20% | General Purpose |
| GRM32ND71A226KE15 | 22uF | 10 | X7T | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32ND71A226ME15 | 22uF | 10 | X7T | 3225M/1210 | 1.5 | +/-20% | General Purpose |
| GRM32NR61A226KE19 | 22uF | 10 | X5R | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32NR61A226ME19 | 22uF | 10 | X5R | 3225M/1210 | 1.5 | +/-20% | General Purpose |
| GRM32NR71H154KA01 | 0.15uF | 50 | X7R | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32NR71H684KA01 | 0.68uF | 50 | X7R | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32NR72A104KA01 | 0.1uF | 100 | X7R | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32RR61C475KA01 | 4.7uF | 16 | X5R | 3225M/1210 | 2 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|----------------------------------|
| GRM32RR61E475KA12 | 4.7uF | 25 | X5R | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM32RR71C475KA01 | 4.7uF | 16 | X7R | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM32RR71E225KA01 | 2.2uF | 25 | X7R | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM32RR71H105KA01 | 1uF | 50 | X7R | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM43DR61E106KA12 | 10uF | 25 | X5R | | 4532M/1812 | 2.2 | +/-10% | General Purpose |
| GRM43ER61C226ME01 | 22uF | 16 | X5R | | 4532M/1812 | 2.7 | +/-20% | General Purpose |
| GRM43ER61H475KA88 | 4.7uF | 50 | X5R | | 4532M/1812 | 2.7 | +/-10% | General Purpose |
| GRM43ER71E475KA01 | 4.7uF | 25 | X7R | | 4532M/1812 | 2.7 | +/-10% | General Purpose |
| GRM43ER71H225KA01 | 2.2uF | 50 | X7R | | 4532M/1812 | 2.7 | +/-10% | General Purpose |
| GRM43ER72A225KA01 | 2.2uF | 100 | X7R | | 4532M/1812 | 2.7 | +/-10% | General Purpose |
| GRM55DR61H106KA88 | 10uF | 50 | X5R | | 5750M/2220 | 2.2 | +/-10% | General Purpose |
| GRM55DR71E106KA01 | 10uF | 25 | X7R | | 5750M/2220 | 2.1 | +/-10% | General Purpose |
| GRM55DR72A105KA01 | 1uF | 100 | X7R | | 5750M/2220 | 2.2 | +/-10% | General Purpose |
| GRM55ER61H475KA01 | 4.7uF | 50 | X5R | | 5750M/2220 | 2.7 | +/-10% | General Purpose |
| GRM55ER71H475KA01 | 4.7uF | 50 | X7R | | 5750M/2220 | 2.7 | +/-10% | General Purpose |
| GRM55ER72A475KA01 | 4.7uF | 100 | X7R | | 5750M/2220 | 2.7 | +/-10% | General Purpose |
| GRM55RR71H105KA01 | 1uF | 50 | X7R | | 5750M/2220 | 2 | +/-10% | General Purpose |
| GRMMDXR60J105ME05 | 1uF | 6.3 | X5R | | 05025M/015008 | 0.275 | +/-20% | Ultra-small |
| GXM155C70J225KE11 | 2.2uF | 6.3 | X7S | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ General Purpose |
| GXM155C71A225KE11 | 2.2uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ General Purpose |
| GXM155C81A225KE11 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ General Purpose |
| GXM155C81C105KE11 | 1uF | 16 | X6S | | 1005M/0402 | 0.6 | +/-10% | Water repellent/ General Purpose |
| GXM155C81C225KE11 | 2.2uF | 16 | X6S | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ General Purpose |
| GXM155C81E105KE11 | 1uF | 25 | X6S | | 1005M/0402 | 0.6 | +/-10% | Water repellent/ General Purpose |
| GXM155R61C105KA10 | 1uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ General Purpose |
| GXM155R61C225KE11 | 2.2uF | 16 | X5R | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ General Purpose |
| GXM155R61E105KA10 | 1uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ General Purpose |
| GXM155R61E225KE11 | 2.2uF | 25 | X5R | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ General Purpose |
| GXM155R6YA105KE11 | 1uF | 35 | X5R | | 1005M/0402 | 0.6 | +/-10% | Water repellent/ General Purpose |
| GXM155R70G105KA10 | 1uF | 4 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ General Purpose |
| GXM155R70J105KA10 | 1uF | 6.3 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ General Purpose |
| GXM188C71A475KE11 | 4.7uF | 10 | X7S | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ General Purpose |
| GXM188C71C225KE11 | 2.2uF | 16 | X7S | | 1608M/0603 | 1 | +/-10% | Water repellent/ General Purpose |
| GXM188C71E225KE11 | 2.2uF | 25 | X7S | | 1608M/0603 | 1 | +/-10% | Water repellent/ General Purpose |
| GXM188C81C106MA73 | 10uF | 16 | X6S | | 1608M/0603 | 1 | +/-20% | Water repellent/ General Purpose |
| GXM188C81C225KA10 | 2.2uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ General Purpose |
| GXM188C81C475KE11 | 4.7uF | 16 | X6S | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ General Purpose |
| GXM188C81E225KE11 | 2.2uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | Water repellent/ General Purpose |
| GXM188C81E475KE11 | 4.7uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | Water repellent/ General Purpose |
| GXM188C8YA225KE11 | 2.2uF | 35 | X6S | | 1608M/0603 | 1 | +/-10% | Water repellent/ General Purpose |
| GXM188D70J106MA73 | 10uF | 6.3 | X7T | | 1608M/0603 | 1 | +/-20% | Water repellent/ General Purpose |
| GXM188R60G106ME47 | 10uF | 4 | X5R | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ General Purpose |
| GXM188R61A106KAAL | 10uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ General Purpose |
| GXM188R61C106KAAL | 10uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ General Purpose |
| GXM188R61C475KE11 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ General Purpose |
| GXM188R61E106MA73 | 10uF | 25 | X5R | | 1608M/0603 | 1 | +/-20% | Water repellent/ General Purpose |
| GXM188R61E225KA10 | 2.2uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ General Purpose |
| GXM188R61E475KE11 | 4.7uF | 25 | X5R | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ General Purpose |
| GXM188R61H225KE11 | 2.2uF | 50 | X5R | | 1608M/0603 | 1 | +/-10% | Water repellent/ General Purpose |
| GXM188R6YA475KE10 | 4.7uF | 35 | X5R | | 1608M/0603 | 1 | +/-10% | Water repellent/ General Purpose |
| GXM188R71A225KE10 | 2.2uF | 10 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ General Purpose |
| GXM219R61C226ME10 | 22uF | 16 | X5R | | 2012M/0805 | 1 | +/-20% | Water repellent/ General Purpose |
| GXM21BC71C106KE11 | 10uF | 16 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BC71E106KE11 | 10uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BC71E475KE11 | 4.7uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BC71H475KE11 | 4.7uF | 50 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BC72A105KE01 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BC7YA475KE11 | 4.7uF | 35 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BC81A226ME44 | 22uF | 10 | X6S | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ General Purpose |
| GXM21BC81C106KA73 | 10uF | 16 | X6S | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ General Purpose |
| GXM21BC81C226ME44 | 22uF | 16 | X6S | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ General Purpose |
| GXM21BC81E106KE11 | 10uF | 25 | X6S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BC8YA106KE11 | 10uF | 35 | X6S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM21BD70J226ME44 | 22uF | 6.3 | X7T | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ General Purpose |
| GXM21BD71A226ME44 | 22uF | 10 | X7T | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ General Purpose |
| GXM21BR61C106KE10 | 10uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | Water repellent/ General Purpose |
| GXM21BR61C106ME10 | 10uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-20% | Water repellent/ General Purpose |
| GXM21BR61C226ME44 | 22uF | 16 | X5R | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ General Purpose |
| GXM21BR61E106KA73 | 10uF | 25 | X5R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ General Purpose |
| GXM21BR61E226ME44 | 22uF | 25 | X5R | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ General Purpose |
| GXM21BR6YA106KE43 | 10uF | 35 | X5R | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ General Purpose |
| GXM31CC71C226ME11 | 22uF | 16 | X7S | | 3216M/1206 | 1.9 | +/-20% | Water repellent/ General Purpose |
| GXM31CR71H475KA10 | 4.7uF | 50 | X7R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ General Purpose |
| LLL153C70E105ME21 | 1uF | 2.5 | X7S | | 1005M/0402 | 0.35 | +/-20% | Low ESL |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|---------|
| LLL153C70G474ME17 | 0.47uF | 4 | X7S | | 1005M/0402 | 0.35 | +/-20% | Low ESL |
| LLL153C80G105ME21 | 1uF | 4 | X6S | | 1005M/0402 | 0.35 | +/-20% | Low ESL |
| LLL153C80J104ME01 | 0.1uF | 6.3 | X6S | | 1005M/0402 | 0.35 | +/-20% | Low ESL |
| LLL153C80J224ME14 | 0.22uF | 6.3 | X6S | | 1005M/0402 | 0.35 | +/-20% | Low ESL |
| LLL153R61A104ME01 | 0.1uF | 10 | X5R | | 1005M/0402 | 0.35 | +/-20% | Low ESL |
| LLL185C70G105ME01 | 1uF | 4 | X7S | | 1608M/0603 | 0.55 | +/-20% | Low ESL |
| LLL185C70G224MA11 | 0.22uF | 4 | X7S | | 1608M/0603 | 0.5 | +/-20% | Low ESL |
| LLL185C70G225ME01 | 2.2uF | 4 | X7S | | 1608M/0603 | 0.55 | +/-20% | Low ESL |
| LLL185C70G474MA01 | 0.47uF | 4 | X7S | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185C70J105ME14 | 1uF | 6.3 | X7S | | 1608M/0603 | 0.55 | +/-20% | Low ESL |
| LLL185R71A104MA01 | 0.1uF | 10 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71A104MA11 | 0.1uF | 10 | X7R | | 1608M/0603 | 0.5 | +/-20% | Low ESL |
| LLL185R71A224MA01 | 0.22uF | 10 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71C103MA01 | 10000pF | 16 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71C223MA01 | 22000pF | 16 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71C223MA11 | 22000pF | 16 | X7R | | 1608M/0603 | 0.5 | +/-20% | Low ESL |
| LLL185R71C473MA01 | 47000pF | 16 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71C473MA11 | 47000pF | 16 | X7R | | 1608M/0603 | 0.5 | +/-20% | Low ESL |
| LLL185R71E103MA01 | 10000pF | 25 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71E103MA11 | 10000pF | 25 | X7R | | 1608M/0603 | 0.5 | +/-20% | Low ESL |
| LLL185R71E223MA01 | 22000pF | 25 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71H222MA01 | 2200pF | 50 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL185R71H472MA01 | 4700pF | 50 | X7R | | 1608M/0603 | 0.6 | +/-20% | Low ESL |
| LLL1U4R60G435ME22 | 4.3uF | 4 | X5R | | 0610M/02404 | 0.45 | +/-20% | Low ESL |
| LLL215C70G105MA11 | 1uF | 4 | X7S | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R70J474MA11 | 0.47uF | 6.3 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R71A224MA11 | 0.22uF | 10 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R71C104MA11 | 0.1uF | 16 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R71C223MA11 | 22000pF | 16 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R71C473MA11 | 47000pF | 16 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R71E103MA11 | 10000pF | 25 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R71E223MA11 | 22000pF | 25 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL215R71H103MA11 | 10000pF | 50 | X7R | | 2012M/0805 | 0.5 | +/-20% | Low ESL |
| LLL216R71A224MA01 | 0.22uF | 10 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL216R71C104MA01 | 0.1uF | 16 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL216R71C473MA01 | 47000pF | 16 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL216R71E104MA01 | 0.1uF | 25 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL216R71E223MA01 | 22000pF | 25 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL216R71E473MA01 | 47000pF | 25 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL216R71H103MA01 | 10000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL216R71H223MA01 | 22000pF | 50 | X7R | | 2012M/0805 | 0.7 | +/-20% | Low ESL |
| LLL219C70G225MA01 | 2.2uF | 4 | X7S | | 2012M/0805 | 0.95 | +/-20% | Low ESL |
| LLL219R70J105MA01 | 1uF | 6.3 | X7R | | 2012M/0805 | 0.95 | +/-20% | Low ESL |
| LLL219R71A105MA01 | 1uF | 10 | X7R | | 2012M/0805 | 0.95 | +/-20% | Low ESL |
| LLL219R71A474MA01 | 0.47uF | 10 | X7R | | 2012M/0805 | 0.95 | +/-20% | Low ESL |
| LLL219R71C224MA01 | 0.22uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-20% | Low ESL |
| LLL315R71A474MA11 | 0.47uF | 10 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71C104MA11 | 0.1uF | 16 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71C223MA11 | 22000pF | 16 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71C224MA11 | 0.22uF | 16 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71C473MA11 | 47000pF | 16 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71E104MA11 | 0.1uF | 25 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71E223MA11 | 22000pF | 25 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71E473MA11 | 47000pF | 25 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71H103MA11 | 10000pF | 50 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL315R71H223MA11 | 22000pF | 50 | X7R | | 3216M/1206 | 0.5 | +/-20% | Low ESL |
| LLL317R70J225MA01 | 2.2uF | 6.3 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71A105MA01 | 1uF | 10 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71A474MA01 | 0.47uF | 10 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71C104MA01 | 0.1uF | 16 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71C224MA01 | 0.22uF | 16 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71C474MA01 | 0.47uF | 16 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71E104MA01 | 0.1uF | 25 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71E223MA01 | 22000pF | 25 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71E473MA01 | 47000pF | 25 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71H103MA01 | 10000pF | 50 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71H223MA01 | 22000pF | 50 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL317R71H473MA01 | 47000pF | 50 | X7R | | 3216M/1206 | 0.8 | +/-20% | Low ESL |
| LLL31MR60J106ME01 | 10uF | 6.3 | X5R | | 3216M/1206 | 1.25 | +/-20% | Low ESL |
| LLL31MR70J475MA01 | 4.7uF | 6.3 | X7R | | 3216M/1206 | 1.25 | +/-20% | Low ESL |
| LLL31MR71A225MA01 | 2.2uF | 10 | X7R | | 3216M/1206 | 1.25 | +/-20% | Low ESL |
| LLL31MR71C105MA01 | 1uF | 16 | X7R | | 3216M/1206 | 1.25 | +/-20% | Low ESL |
| LLL31MR71E224MA01 | 0.22uF | 25 | X7R | | 3216M/1206 | 1.25 | +/-20% | Low ESL |
| LLL31MR71E474MA01 | 0.47uF | 25 | X7R | | 3216M/1206 | 1.25 | +/-20% | Low ESL |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|--------------------------------|------------------------------|---------------------|-------------------|---------------------------------------|
| LLL31MR71H104MA01 | 0.1uF | 50 | X7R | 3216M/1206 | 1.25 | +/-20% | Low ESL |
| LLR185C70G105ME01 | 1uF | 4 | X7S | 1608M/0603 | 0.55 | +/-20% | Low ESL |
| LLR185C70G105ME03 | 1uF | 4 | X7S | 1608M/0603 | 0.55 | +/-20% | Low ESL |
| LLR185C70G105ME05 | 1uF | 4 | X7S | 1608M/0603 | 0.55 | +/-20% | Low ESL |
| LLR185C70G105ME07 | 1uF | 4 | X7S | 1608M/0603 | 0.55 | +/-20% | Low ESL |
| ZRA21CR61E226ME01 | 22uF | 25 | X5R | 2012M/0805 | 1.65 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB155R61E225ME01 | 2.2uF | 25 | X5R | 1005M/0402 | 0.65 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB15XC80J106ME05 | 10uF | 6.3 | X6S | 1005M/0402 | 0.85 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB15XR60J106ME12 | 10uF | 6.3 | X5R | 1005M/0402 | 0.8 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB186R60G226ME11 | 22uF | 4 | X5R | 1608M/0603 | 0.8 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB186R60J226ME11 | 22uF | 6.3 | X5R | 1608M/0603 | 0.8 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB186R61E475ME05 | 4.7uF | 25 | X5R | 1608M/0603 | 0.65 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB188R61A226ME05 | 22uF | 10 | X5R | 1608M/0603 | 0.95 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB18AR60J476ME01 | 47uF | 6.3 | X5R | 1608M/0603 | 1.2 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB18AR61E106ME01 | 10uF | 25 | X5R | 1608M/0603 | 1.2 | +/-20% | Acoustic noise reduction (interposer) |
| ZRB18AR6YA475KE05 | 4.7uF | 35 | X5R | 1608M/0603 | 1.2 | +/-10% | Acoustic noise reduction (interposer) |
| ZRB18AR6YA475ME05 | 4.7uF | 35 | X5R | 1608M/0603 | 1.2 | +/-20% | Acoustic noise reduction (interposer) |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCE21BR72A123KA01 | 12000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A123MA01 | 12000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A153KA01 | 15000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A153MA01 | 15000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A183KA01 | 18000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A183MA01 | 18000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A223KA01 | 22000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A223MA01 | 22000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A273KA01 | 27000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A273MA01 | 27000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A333KA01 | 33000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A333MA01 | 33000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A393KA01 | 39000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A393MA01 | 39000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A473KA01 | 47000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A473MA01 | 47000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A563KA01 | 56000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A563MA01 | 56000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A683KA01 | 68000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A683MA01 | 68000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A822KA01 | 8200pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A822MA01 | 8200pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A823KA01 | 82000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCE21BR72A823MA01 | 82000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCH155C71A105KE11 | 1uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Implantable medical device |
| GCH155R71A104KE01 | 0.1uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71C104KE01 | 0.1uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71C224KE01 | 0.22uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71C473KE01 | 47000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71E103KE01 | 10000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71E223KE01 | 22000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71E473KE01 | 47000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H102KE01 | 1000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H103KE01 | 10000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H104KE01 | 0.1uF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H221KE01 | 220pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H222KE01 | 2200pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H223KE01 | 22000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H471KE01 | 470pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H472KE01 | 4700pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R71H473KE01 | 47000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R72A102KE01 | 1000pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R72A221KE01 | 220pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R72A222KE01 | 2200pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R72A331KE01 | 330pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R72A471KE01 | 470pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH155R72A472KE01 | 4700pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Implantable medical device |
| GCH188C71A225KE01 | 2.2uF | 10 | X7S | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R70J225KE01 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71C104KE01 | 0.1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71C105KE01 | 1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71C474KE01 | 0.47uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71E104KE01 | 0.1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71E105KE01 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71E224KE01 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71E473KE01 | 47000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71E474KE01 | 0.47uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H102KE01 | 1000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H103KE01 | 10000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H104KE01 | 0.1uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H222KE01 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H223KE01 | 22000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H224KE01 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H472KE01 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R71H473KE01 | 47000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R72A102KE01 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R72A103KE01 | 10000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R72A104KE01 | 0.1uF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R72A222KE01 | 2200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R72A223KE01 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH188R72A472KE01 | 4700pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Implantable medical device |
| GCH219R71C105KE01 | 1uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | Implantable medical device |
| GCH219R71E474KE01 | 0.47uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | Implantable medical device |
| GCH21BC71A475KE01 | 4.7uF | 10 | X7S | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BC71E475KE11 | 4.7uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Implantable medical device |
| GCH21BC72A105KE11 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-10% | Implantable medical device |
| GCH21BC7YA475KE11 | 4.7uF | 35 | X7S | | 2012M/0805 | 1.45 | +/-10% | Implantable medical device |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCH21BR70J106KE01 | 10uF | 6.3 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71A106KE01 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71A225KE01 | 2.2uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71C225KE01 | 2.2uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71C475KE01 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71E105KE01 | 1uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71E224KE01 | 0.22uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71E225KE01 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71H104KE01 | 0.1uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71H105KE01 | 1uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71H224KE01 | 0.22uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71H473KE01 | 47000pF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR71H474KE01 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR72A103KE01 | 10000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR72A104KE01 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR72A223KE01 | 22000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR72A473KE01 | 47000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH21BR7YA105KE01 | 1uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Implantable medical device |
| GCH319R72A104KE01 | 0.1uF | 100 | X7R | | 3216M/1206 | 0.95 | +/-10% | Implantable medical device |
| GCH31CR71A106KE01 | 10uF | 10 | X7R | | 3216M/1206 | 1.8 | +/-10% | Implantable medical device |
| GCH31CR71C106KE01 | 10uF | 16 | X7R | | 3216M/1206 | 1.8 | +/-10% | Implantable medical device |
| GCH31CR71C475KE01 | 4.7uF | 16 | X7R | | 3216M/1206 | 1.8 | +/-10% | Implantable medical device |
| GCH31CR71E475KE01 | 4.7uF | 25 | X7R | | 3216M/1206 | 1.8 | +/-10% | Implantable medical device |
| GCH31CR71H225KE01 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.8 | +/-10% | Implantable medical device |
| GCH31CR72A105KE01 | 1uF | 100 | X7R | | 3216M/1206 | 1.8 | +/-10% | Implantable medical device |
| GCH31MR71E225KE01 | 2.2uF | 25 | X7R | | 3216M/1206 | 1.3 | +/-10% | Implantable medical device |
| GCH31MR71H105KE01 | 1uF | 50 | X7R | | 3216M/1206 | 1.25 | +/-10% | Implantable medical device |
| GCH31MR71H474KE01 | 0.47uF | 50 | X7R | | 3216M/1206 | 1.25 | +/-10% | Implantable medical device |
| GCH31MR72A224KE01 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.25 | +/-10% | Implantable medical device |
| GCH32DR71C106KE01 | 10uF | 16 | X7R | | 3225M/1210 | 2.2 | +/-10% | Implantable medical device |
| GCH32DR71E475KE01 | 4.7uF | 25 | X7R | | 3225M/1210 | 2.2 | +/-10% | Implantable medical device |
| GCH32DR72A225KE01 | 2.2uF | 100 | X7R | | 3225M/1210 | 2.2 | +/-10% | Implantable medical device |
| GCH32ER70J476KE01 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.7 | +/-10% | Implantable medical device |
| GCH32ER71A226KE01 | 22uF | 10 | X7R | | 3225M/1210 | 2.7 | +/-10% | Implantable medical device |
| GCH32ER71H105KE01 | 1uF | 50 | X7R | | 3225M/1210 | 2.7 | +/-10% | Implantable medical device |
| GCH32ER71H475KE01 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.7 | +/-10% | Implantable medical device |
| GCJ188C70J335KE02 | 3.3uF | 6.3 | X7S | | 1608M/0603 | 1 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188C70J335ME02 | 3.3uF | 6.3 | X7S | | 1608M/0603 | 1 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188C70J475KE02 | 4.7uF | 6.3 | X7S | | 1608M/0603 | 1 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188C70J475ME02 | 4.7uF | 6.3 | X7S | | 1608M/0603 | 1 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C104KA01 | 0.1uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C104MA01 | 0.1uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C124KA01 | 0.12uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C154KA01 | 0.15uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C154MA01 | 0.15uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C224KA01 | 0.22uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C224MA01 | 0.22uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C393KA01 | 39000pF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C473KA01 | 47000pF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C473MA01 | 47000pF | 16 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C683KA01 | 68000pF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81C683MA01 | 68000pF | 16 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E154KA01 | 0.15uF | 25 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E154MA01 | 0.15uF | 25 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E184KA01 | 0.18uF | 25 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E224KA01 | 0.22uF | 25 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E224MA01 | 0.22uF | 25 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E393KA01 | 39000pF | 25 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E563KA01 | 56000pF | 25 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E683KA01 | 68000pF | 25 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81E683MA01 | 68000pF | 25 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H102KA01 | 1000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H102MA01 | 1000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H103KA01 | 10000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H103MA01 | 10000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H123KA01 | 12000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H152KA01 | 1500pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H152MA01 | 1500pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H153KA01 | 15000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H153MA01 | 15000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H182KA01 | 1800pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H222KA01 | 2200pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H222MA01 | 2200pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H223KA01 | 22000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H223MA01 | 22000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H272KA01 | 2700pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H332KA01 | 3300pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCJ188L81H392KA01 | 3900pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H472KA01 | 4700pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H472MA01 | 4700pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H562KA01 | 5600pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H682KA01 | 6800pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L81H822KA01 | 8200pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8EC335KE08 | 3.3uF | 6.3 | X8L | | 1608M/0603 | 1 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8EH154KA07 | 0.15uF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8EH224KA07 | 0.22uF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8EL104KA07 | 0.1uF | 100 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8YA393KA01 | 39000pF | 35 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8YA563KA01 | 56000pF | 35 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8YA683KA01 | 68000pF | 35 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188L8YA683MA01 | 68000pF | 35 | X8L | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188M8EC475KE08 | 4.7uF | 6.3 | X8M | | 1608M/0603 | 1 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R70J225KE01 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R70J225ME01 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71A124KA01 | 0.12uF | 10 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71A154KA01 | 0.15uF | 10 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71A154MA01 | 0.15uF | 10 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71A224KA01 | 0.22uF | 10 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71A224MA01 | 0.22uF | 10 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C103KA01 | 10000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C103MA01 | 10000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C124KA01 | 0.12uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C154KA01 | 0.15uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C154MA01 | 0.15uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C184KA01 | 0.18uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C224KA01 | 0.22uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C224MA01 | 0.22uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C273KA01 | 27000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C273MA01 | 27000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C274KA01 | 0.27uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C333KA01 | 33000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C333MA01 | 33000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C334KA01 | 0.33uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C334MA01 | 0.33uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C393KA01 | 39000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C393MA01 | 39000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C473KA01 | 47000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C473MA01 | 47000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C474KA12 | 0.47uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C474MA12 | 0.47uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C563KA01 | 56000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71C823KA01 | 82000pF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E102KA01 | 1000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E102MA01 | 1000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E103KA01 | 10000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E103MA01 | 10000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E104KA12 | 0.1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E104MA12 | 0.1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E123KA01 | 12000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E124KA01 | 0.12uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E152KA01 | 1500pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E152MA01 | 1500pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E153KA01 | 15000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E153MA01 | 15000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E154KA01 | 0.15uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E154MA01 | 0.15uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E182KA01 | 1800pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E184KA12 | 0.18uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E222KA01 | 2200pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E222MA01 | 2200pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E223KA01 | 22000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E223MA01 | 22000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E224KA12 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E224MA12 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E272KA01 | 2700pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E273KA01 | 27000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E273MA01 | 27000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E332KA01 | 3300pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E333KA01 | 33000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E333MA01 | 33000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E392KA01 | 3900pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E393KA01 | 39000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E393MA01 | 39000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ188R71E472KA01 | 4700pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCJ216R72A123KA01 | 12000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A152KA01 | 1500pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive |
| GCJ216R72A153KA01 | 15000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A153MA01 | 15000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A182KA01 | 1800pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A183KA01 | 18000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A222KA01 | 2200pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A222MA01 | 2200pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A223KA01 | 22000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A223MA01 | 22000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A272KA01 | 2700pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A332KA01 | 3300pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A332MA01 | 3300pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A392KA01 | 3900pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A472KA01 | 4700pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A472MA01 | 4700pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A562KA01 | 5600pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A682KA01 | 6800pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A682MA01 | 6800pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ216R72A822KA01 | 8200pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71C105KA01 | 1uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71C105MA01 | 1uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71E223KA01 | 22000pF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71E223MA01 | 22000pF | 25 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71E474KA12 | 0.47uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71E474MA12 | 0.47uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71H273KA01 | 27000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71H273MA01 | 27000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71H333KA01 | 33000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71H333MA01 | 33000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71H334KA12 | 0.33uF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71H334MA12 | 0.33uF | 50 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R71H393KA01 | 39000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A221KA01 | 220pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A221MA01 | 220pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A271KA01 | 270pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A273KA01 | 27000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A273MA01 | 27000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A331KA01 | 330pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A333KA01 | 33000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A333MA01 | 33000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A391KA01 | 390pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A393KA01 | 39000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A471KA01 | 470pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A471MA01 | 470pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A561KA01 | 560pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A681KA01 | 680pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A681MA01 | 680pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ219R72A821KA01 | 820pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BC72A105KE02 | 1uF | 100 | X7S | | 2012M/0805 | 1.5 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BC72A105ME02 | 1uF | 100 | X7S | | 2012M/0805 | 1.5 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81C105KA01 | 1uF | 16 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81C105MA01 | 1uF | 16 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81C564KA01 | 0.56uF | 16 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81C684KA01 | 0.68uF | 16 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81C684MA01 | 0.68uF | 16 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81C824KA01 | 0.82uF | 16 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive |
| GCJ21BL81E105KA01 | 1uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E105MA01 | 1uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E124KA01 | 0.12uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E154KA01 | 0.15uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E154MA01 | 0.15uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E184KA01 | 0.18uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E184MA01 | 0.18uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E224KA01 | 0.22uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E224MA01 | 0.22uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E274KA01 | 0.27uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E334KA01 | 0.33uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E334MA01 | 0.33uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E394KA01 | 0.39uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E684KA01 | 0.68uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E684MA01 | 0.68uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81E824KA01 | 0.82uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive |
| GCJ21BL81H104KA01 | 0.1uF | 50 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81H104MA01 | 0.1uF | 50 | X8L | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81H273KA01 | 27000pF | 50 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BL81H393KA01 | 39000pF | 50 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCJ21BR72A683MA01 | 68000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ21BR72A823KA01 | 82000pF | 100 | X7R | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ319R71H104KA01 | 0.1uF | 50 | X7R | | 3216M/1206 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ319R71H104MA01 | 0.1uF | 50 | X7R | | 3216M/1206 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ319R72A104KA01 | 0.1uF | 100 | X7R | | 3216M/1206 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ319R72A104MA01 | 0.1uF | 100 | X7R | | 3216M/1206 | 0.95 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CC71E106KA15 | 10uF | 25 | X7S | | 3216M/1206 | 2 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CC71E106MA15 | 10uF | 25 | X7S | | 3216M/1206 | 2 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CC71H475KA01 | 4.7uF | 50 | X7S | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CC71H475MA01 | 4.7uF | 50 | X7S | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CC72A225KE01 | 2.2uF | 100 | X7S | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81C475KA01 | 4.7uF | 16 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81C475MA01 | 4.7uF | 16 | X8L | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81E105KA01 | 1uF | 25 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81E105MA01 | 1uF | 25 | X8L | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81E564KA01 | 0.56uF | 25 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81E684KA01 | 0.68uF | 25 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81E684MA01 | 0.68uF | 25 | X8L | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL81E824KA01 | 0.82uF | 25 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8ED226KE07 | 22uF | 10 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8EF106KA08 | 10uF | 25 | X8L | | 3216M/1206 | 2 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8EL105KA07 | 1uF | 100 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8YA105KA01 | 1uF | 35 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8YA105MA01 | 1uF | 35 | X8L | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8YA564KA01 | 0.56uF | 35 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8YA684KA01 | 0.68uF | 35 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8YA684MA01 | 0.68uF | 35 | X8L | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CL8YA824KA01 | 0.82uF | 35 | X8L | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR70J226KE01 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR70J226ME01 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71A106KA13 | 10uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71A106MA13 | 10uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71A226KE01 | 22uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71A226ME01 | 22uF | 10 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71C106KA15 | 10uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71C106MA15 | 10uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71C475KA01 | 4.7uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71C475MA01 | 4.7uF | 16 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71E475KA12 | 4.7uF | 25 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71E475MA12 | 4.7uF | 25 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H105KA12 | 1uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H105MA12 | 1uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H155KA12 | 1.5uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H155MA12 | 1.5uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H225KA12 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H225MA12 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H684KA01 | 0.68uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR71H684MA01 | 0.68uF | 50 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR72A105KA01 | 1uF | 100 | X7R | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31CR72A105MA01 | 1uF | 100 | X7R | | 3216M/1206 | 1.9 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81C105KA01 | 1uF | 16 | X8L | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81C105MA01 | 1uF | 16 | X8L | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81C225KA01 | 2.2uF | 16 | X8L | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81C225MA01 | 2.2uF | 16 | X8L | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81E394KA01 | 0.39uF | 25 | X8L | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81E394MA01 | 0.39uF | 25 | X8L | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81E474KA01 | 0.47uF | 25 | X8L | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML81E474MA01 | 0.47uF | 25 | X8L | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML8YA394KA01 | 0.39uF | 35 | X8L | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML8YA394MA01 | 0.39uF | 35 | X8L | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML8YA474KA01 | 0.47uF | 35 | X8L | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31ML8YA474MA01 | 0.47uF | 35 | X8L | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71C105KA01 | 1uF | 16 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71C105MA01 | 1uF | 16 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71C225KA01 | 2.2uF | 16 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71C225MA01 | 2.2uF | 16 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E104KA01 | 0.1uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E104MA01 | 0.1uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E105KA01 | 1uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E105MA01 | 1uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E124KA01 | 0.12uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E154KA01 | 0.15uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E184KA01 | 0.18uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E224KA01 | 0.22uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E224MA01 | 0.22uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E225KA12 | 2.2uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E225MA12 | 2.2uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCJ31MR71E335KA12 | 3.3uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71E335MA12 | 3.3uF | 25 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H104KA01 | 0.1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H104MA01 | 0.1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H105KA12 | 1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H105MA12 | 1uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H224KA01 | 0.22uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H224MA01 | 0.22uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H274KA01 | 0.27uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H394KA01 | 0.39uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H394MA01 | 0.39uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H474KA01 | 0.47uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H474MA01 | 0.47uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H564KA12 | 0.56uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR71H564MA12 | 0.56uF | 50 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR72A154KA01 | 0.15uF | 100 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR72A184KA01 | 0.18uF | 100 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR72A224KA01 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.35 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ31MR72A224MA01 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.35 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32DC72A475KE01 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.3 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32DL8EL225KA07 | 2.2uF | 100 | X8L | | 3225M/1210 | 2.3 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32DR72A225KA01 | 2.2uF | 100 | X7R | | 3225M/1210 | 2.3 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32DR72A225MA01 | 2.2uF | 100 | X7R | | 3225M/1210 | 2.3 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32EC71E226KE02 | 22uF | 25 | X7S | | 3225M/1210 | 2.85 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32EC71H106KA01 | 10uF | 50 | X7S | | 3225M/1210 | 2.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32EC71H106MA01 | 10uF | 50 | X7S | | 3225M/1210 | 2.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32EL81E475KA01 | 4.7uF | 25 | X8L | | 3225M/1210 | 2.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32EL81E475MA01 | 4.7uF | 25 | X8L | | 3225M/1210 | 2.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32EL8EF226KE08 | 22uF | 25 | X8L | | 3225M/1210 | 2.85 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER70J476KE01 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER70J476ME01 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER71C226KE01 | 22uF | 16 | X7R | | 3225M/1210 | 2.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER71C226ME01 | 22uF | 16 | X7R | | 3225M/1210 | 2.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER71H475KA12 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER71H475MA12 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER91C106KE01 | 10uF | 16 | X8R | | 3225M/1210 | 2.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER91C106ME01 | 10uF | 16 | X8R | | 3225M/1210 | 2.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCJ32ER91C685KE01 | 6.8uF | 16 | X8R | | 3225M/1210 | 2.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71A103KA03 | 10000pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71A152KA03 | 1500pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71A222KA03 | 2200pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71A332KA03 | 3300pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71A472KA03 | 4700pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71A682KA03 | 6800pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71C222KA55 | 2200pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71C331KA03 | 330pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71C332KA55 | 3300pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71C681KA03 | 680pF | 16 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E101KA03 | 100pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E102KA03 | 1000pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E151KA03 | 150pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E152KA03 | 1500pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E221KA03 | 220pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E222KE01 | 2200pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R71E222KE02 | 2200pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E331KA03 | 330pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E332KE01 | 3300pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R71E332KE02 | 3300pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E471KA03 | 470pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM033R71E681KA03 | 680pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155C71A105KE38 | 1uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155C71A105KE39 | 1uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM155C71A474KE35 | 0.47uF | 10 | X7S | | 1005M/0402 | 0.6 | +/-10% | Powertrain/Safety for Automotive |
| GCM155C71A474KE36 | 0.47uF | 10 | X7S | | 1005M/0402 | 0.6 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155C71A474ME35 | 0.47uF | 10 | X7S | | 1005M/0402 | 0.6 | +/-20% | Powertrain/Safety for Automotive |
| GCM155C71A474ME36 | 0.47uF | 10 | X7S | | 1005M/0402 | 0.6 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155C71A684KE38 | 0.68uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155C71A684KE39 | 0.68uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM155C71A684ME38 | 0.68uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155C71A684ME39 | 0.68uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-20% | Powertrain/Safety for Automotive |
| GCM155L81C223KA01 | 22000pF | 16 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81C223KA37 | 22000pF | 16 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81C473KA01 | 47000pF | 16 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81C473KA37 | 47000pF | 16 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81E103KA01 | 10000pF | 25 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81E103KA37 | 10000pF | 25 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81E104KE01 | 0.1uF | 25 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCM155L81E104KE02 | 0.1uF | 25 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81H102KA01 | 1000pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81H102KA37 | 1000pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81H221KA01 | 220pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81H221KA37 | 220pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81H222KA01 | 2200pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81H222KA37 | 2200pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81H471KA01 | 470pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81H471KA37 | 470pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L81H472KA01 | 4700pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155L81H472KA37 | 4700pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L8EH333KE07 | 33000pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155L8EH473KE07 | 47000pF | 50 | X8L | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71A104KA01 | 0.1uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71C104KA55 | 0.1uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71C154KE02 | 0.15uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71C224KE01 | 0.22uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71C224KE02 | 0.22uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71C333KA37 | 33000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71C473KA37 | 47000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71C683KA55 | 68000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71E103KA37 | 10000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71E153KA55 | 15000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71E223KA55 | 22000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71E333KA55 | 33000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71E473KA55 | 47000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71E682KA37 | 6800pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H102KA37 | 1000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H103KA55 | 10000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H104KE02 | 0.1uF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H104KE37 | 0.1uF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71H152KA37 | 1500pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H153KA40 | 15000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71H153KA55 | 15000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H221KA37 | 220pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H222KA37 | 2200pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H223KA40 | 22000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71H223KA55 | 22000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H331KA37 | 330pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H332KA37 | 3300pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H333KE01 | 33000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71H333KE02 | 33000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H471KA37 | 470pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H472KA37 | 4700pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H473KE01 | 47000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71H473KE02 | 47000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H681KA37 | 680pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H682KA55 | 6800pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R71H683KE01 | 68000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R71H683KE02 | 68000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A102KA01 | 1000pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A102KA37 | 1000pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A152KA01 | 1500pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A152KA37 | 1500pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A221KA01 | 220pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A221KA37 | 220pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A222KA01 | 2200pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A222KA37 | 2200pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A331KA01 | 330pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A331KA37 | 330pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A332KA01 | 3300pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A332KA37 | 3300pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A471KA01 | 470pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A471KA37 | 470pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A472KA01 | 4700pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A472KA37 | 4700pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM155R72A681KA01 | 680pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R72A681KA37 | 680pF | 100 | X7R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188C71A225KE01 | 2.2uF | 10 | X7S | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188C71A225ME01 | 2.2uF | 10 | X7S | | 1608M/0603 | 0.9 | +/-20% | Powertrain/Safety for Automotive |
| GCM188D70G106ME35 | 10uF | 4 | X7T | | 1608M/0603 | 1 | +/-20% | Powertrain/Safety for Automotive |
| GCM188D70G106ME36 | 10uF | 4 | X7T | | 1608M/0603 | 1 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188L81C224KA01 | 0.22uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188L81C224KA37 | 0.22uF | 16 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188L81H104KA57 | 0.1uF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188L81H223KA37 | 22000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188L81H473KA40 | 47000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|---|
| GCM188L81H473KA55 | 47000pF | 50 | X8L | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R70J225KE21 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R70J225KE22 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71C104KA37 | 0.1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71C105KA49 | 1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R71C105KA64 | 1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71C334KA37 | 0.33uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71C474KA55 | 0.47uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E102KA37 | 1000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E103KA37 | 10000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E104KA57 | 0.1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E105KA49 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R71E105KA64 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E152KA37 | 1500pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E153KA37 | 15000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E154KA37 | 0.15uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E222KA37 | 2200pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E223KA37 | 22000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E224KA55 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E332KA37 | 3300pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E333KA37 | 33000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E472KA37 | 4700pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E473KA37 | 47000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E474KA49 | 0.47uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R71E474KA64 | 0.47uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E682KA37 | 6800pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71E683KA57 | 68000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H102KA37 | 1000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H103KA37 | 10000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H104KA57 | 0.1uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H152KA37 | 1500pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H153KA37 | 15000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H154KA49 | 0.15uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R71H154KA64 | 0.15uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H222KA37 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H223KA37 | 22000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H224KA49 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R71H224KA64 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H332KA37 | 3300pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H333KA55 | 33000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H472KA37 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H473KA55 | 47000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H682KA37 | 6800pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R71H683KA57 | 68000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A102KA01 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A102KA37 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A103KA01 | 10000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A103KA37 | 10000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A152KA01 | 1500pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A152KA37 | 1500pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A153KA01 | 15000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A153KA37 | 15000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A222KA01 | 2200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A222KA37 | 2200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A223KA01 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A223KA37 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A332KA01 | 3300pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A332KA37 | 3300pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A472KA01 | 4700pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A472KA37 | 4700pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM188R72A682KA01 | 6800pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R72A682KA37 | 6800pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM216R72A103KA37 | 10000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM216R72A153KA37 | 15000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM216R72A223KA37 | 22000pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM216R72A682KA37 | 6800pF | 100 | X7R | | 2012M/0805 | 0.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R71C105KA37 | 1uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R71C224KA37 | 0.22uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R71C684KA37 | 0.68uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R71E474KA55 | 0.47uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R71H333KA37 | 33000pF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R71H334KA40 | 0.33uF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM219R71H334KA55 | 0.33uF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R72A333KA37 | 33000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM219R72A682KA01 | 6800pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BC71A475KA67 | 4.7uF | 10 | X7S | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BC71A475KA73 | 4.7uF | 10 | X7S | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|---|
| GCM21BC71C106KE35 | 10uF | 16 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BC71C106KE36 | 10uF | 16 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BC71E475KE35 | 4.7uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BC71E475KE36 | 4.7uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BC72A105KE35 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BC72A105KE36 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BC72A105ME35 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive |
| GCM21BC72A105ME36 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BC7YA225KE01 | 2.2uF | 35 | X7S | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BC7YA225KE02 | 2.2uF | 35 | X7S | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BC7YA475KE35 | 4.7uF | 35 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BC7YA475KE36 | 4.7uF | 35 | X7S | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BL8EF155KA07 | 1.5uF | 25 | X8L | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BL8EF475KE08 | 4.7uF | 25 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BL8EG225KE07 | 2.2uF | 350 | X8L | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BL8EG475KE08 | 4.7uF | 350 | X8L | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BM8EE106KE08 | 10uF | 16 | X8M | | 2012M/0805 | 1.45 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR70J106KE21 | 10uF | 6.3 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR70J106KE22 | 10uF | 6.3 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71A106KE21 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71A106KE22 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71A225KA01 | 2.2uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71A225KA37 | 2.2uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71C225KA49 | 2.2uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71C225KA64 | 2.2uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71C474KA37 | 0.47uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71C475KA67 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71C475KA73 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E104KA37 | 0.1uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E105KA56 | 1uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E154KA37 | 0.15uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E155KA36 | 1.5uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71E155KA54 | 1.5uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E155MA36 | 1.5uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-20% | Powertrain/Safety for Automotive |
| GCM21BR71E155MA54 | 1.5uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E224KA37 | 0.22uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E225KA67 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71E225KA73 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E334KA37 | 0.33uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71E684KA55 | 0.68uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71H104KA37 | 0.1uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71H105KA01 | 1uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71H105KA03 | 1uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71H154KA37 | 0.15uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71H224KA37 | 0.22uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71H473KA37 | 47000pF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71H474KA40 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR71H474KA55 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR71H683KA37 | 68000pF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR72A103KA01 | 10000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR72A104KA01 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR72A104KA37 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR72A153KA01 | 15000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR72A223KA01 | 22000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR72A333KA01 | 33000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR72A473KA01 | 47000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR72A473KA37 | 47000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR72A683KA01 | 68000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR72A683KA37 | 68000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR7YA105KA40 | 1uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR7YA105KA55 | 1uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR7YA155KA36 | 1.5uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR7YA155KA54 | 1.5uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM21BR7YA684KA40 | 0.68uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR7YA684KA55 | 0.68uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM319R72A104KA01 | 0.1uF | 100 | X7R | | 3216M/1206 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM319R72A104KA37 | 0.1uF | 100 | X7R | | 3216M/1206 | 0.95 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CC71E106KA01 | 10uF | 25 | X7S | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CC71E106KA03 | 10uF | 25 | X7S | | 3216M/1206 | 1.9 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CC71H475KA03 | 4.7uF | 50 | X7S | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CC71H475KA49 | 4.7uF | 50 | X7S | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CC72A225KE01 | 2.2uF | 100 | X7S | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CC72A225KE02 | 2.2uF | 100 | X7S | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CC72A225ME01 | 2.2uF | 100 | X7S | | 3216M/1206 | 1.8 | +/-20% | Powertrain/Safety for Automotive |
| GCM31CC72A225ME02 | 2.2uF | 100 | X7S | | 3216M/1206 | 1.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CL8EL225KE07 | 2.2uF | 100 | X8L | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CR70J226ME23 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.8 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|--|
| GCM31CR70J226ME26 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.8 | +/-20% | Powertrain/Safety for Automotive |
| GCM31CR71A106KA64 | 10uF | 10 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CR71A226KE01 | 22uF | 10 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR71A226KE02 | 22uF | 10 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CR71C106KA49 | 10uF | 16 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR71C106KA64 | 10uF | 16 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CR71C475KA37 | 4.7uF | 16 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CR71E475KA40 | 4.7uF | 25 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR71E475KA55 | 4.7uF | 25 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CR71H225KA40 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR71H225KA55 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31CR72A105KA01 | 1uF | 100 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR72A105KA03 | 1uF | 100 | X7R | | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR71E105KA37 | 1uF | 25 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR71E225KA57 | 2.2uF | 25 | X7R | | 3216M/1206 | 1.3 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR71H105KA40 | 1uF | 50 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR71H105KA55 | 1uF | 50 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR71H334KA37 | 0.33uF | 50 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR71H474KA37 | 0.47uF | 50 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR71H684KA55 | 0.68uF | 50 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR72A154KA01 | 0.15uF | 100 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR72A154KA37 | 0.15uF | 100 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM31MR72A224KA01 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR72A224KA37 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32DC72A475KE01 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.2 | +/-10% | Powertrain/Safety for Automotive |
| GCM32DC72A475KE02 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.2 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32DC72A475ME01 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.2 | +/-20% | Powertrain/Safety for Automotive |
| GCM32DC72A475ME02 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.2 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32DL8EL475KE07 | 4.7uF | 100 | X8L | | 3225M/1210 | 2.2 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32DR71C106KA37 | 10uF | 16 | X7R | | 3225M/1210 | 2.2 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32DR71E475KA55 | 4.7uF | 25 | X7R | | 3225M/1210 | 2.2 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32EC71A476KE01 | 47uF | 10 | X7S | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32EC71A476KE02 | 47uF | 10 | X7S | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32EC71E226KE35 | 22uF | 25 | X7S | | 3225M/1210 | 2.85 | +/-10% | Powertrain/Safety for Automotive |
| GCM32EC71E226KE36 | 22uF | 25 | X7S | | 3225M/1210 | 2.85 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32EC71H106KA01 | 10uF | 50 | X7S | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32EC71H106KA03 | 10uF | 50 | X7S | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32EC7YA106KA01 | 10uF | 35 | X7S | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32EC7YA106KA03 | 10uF | 35 | X7S | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32EL8EF226KE08 | 22uF | 25 | X8L | | 3225M/1210 | 2.85 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32EL8EH106KA07 | 10uF | 50 | X8L | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32ER70J476KE16 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32ER70J476ME16 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.7 | +/-20% | Powertrain/Safety for Automotive |
| GCM32ER70J476ME19 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32ER71A226KE12 | 22uF | 10 | X7R | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32ER71A226ME12 | 22uF | 10 | X7R | | 3225M/1210 | 2.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32ER71C226ME15 | 22uF | 16 | X7R | | 3225M/1210 | 2.7 | +/-20% | Powertrain/Safety for Automotive |
| GCM32ER71C226ME19 | 22uF | 16 | X7R | | 3225M/1210 | 2.7 | +/-20% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32ER71E106KA42 | 10uF | 25 | X7R | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32ER71E106KA57 | 10uF | 25 | X7R | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32ER71H105KA37 | 1uF | 50 | X7R | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GCM32ER71H475KA40 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32ER71H475KA55 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive [AEC-Q200] |
| GGD188R71E273KA02 | 27000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71E333KA02 | 33000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71E393KA02 | 39000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71E473KA02 | 47000pF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H102KA02 | 1000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H103KA02 | 10000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H122KA02 | 1200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H123KA02 | 12000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H152KA02 | 1500pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H153KA02 | 15000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H182KA02 | 1800pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H183KA02 | 18000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H222KA02 | 2200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H223KA02 | 22000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H272KA02 | 2700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H332KA02 | 3300pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H392KA02 | 3900pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H472KA02 | 4700pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H562KA02 | 5600pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H682KA02 | 6800pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R71H822KA02 | 8200pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R72A102KA02 | 1000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R72A103KA02 | 10000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |
| GGD188R72A122KA02 | 1200pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent(MLSC)/ Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|--|
| GGM188R70J225KE22 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R71C105KA64 | 1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R71C334KA37 | 0.33uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R71C474KA55 | 0.47uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R71E105KA64 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R71E224KA55 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R71E474KA64 | 0.47uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R71H224KA64 | 0.22uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R72A103KA37 | 10000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R72A153KA37 | 15000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R72A223KA37 | 22000pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM188R72A682KA37 | 6800pF | 100 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM219R71C105KA37 | 1uF | 16 | X7R | | 2012M/0805 | 0.95 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM219R71E474KA55 | 0.47uF | 25 | X7R | | 2012M/0805 | 0.95 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM219R71H334KA55 | 0.33uF | 50 | X7R | | 2012M/0805 | 0.95 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM219R72A333KA37 | 33000pF | 100 | X7R | | 2012M/0805 | 0.95 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BC71E475KE36 | 4.7uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BC72A105KE36 | 1uF | 100 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BC7YA225KE02 | 2.2uF | 35 | X7S | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BC7YA475KE36 | 4.7uF | 35 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71A106KE22 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71A225KA37 | 2.2uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71C225KA64 | 2.2uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71E105KA56 | 1uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71E155KA54 | 1.5uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71E334KA37 | 0.33uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71E684KA55 | 0.68uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71H105KA03 | 1uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71H224KA37 | 0.22uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR71H474KA55 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR72A104KA37 | 0.1uF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR72A473KA37 | 47000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR72A683KA37 | 68000pF | 100 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR7YA105KA55 | 1uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR7YA155KA54 | 1.5uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM21BR7YA684KA55 | 0.68uF | 35 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31CC71E106KA03 | 10uF | 25 | X7S | | 3216M/1206 | 1.9 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31CC71H475KA03 | 4.7uF | 50 | X7S | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31CC72A225KE02 | 2.2uF | 100 | X7S | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31CR71A226KE02 | 22uF | 10 | X7R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31CR71C475KA37 | 4.7uF | 16 | X7R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31CR71E475KA55 | 4.7uF | 25 | X7R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31CR71H225KA55 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM31MR72A224KA37 | 0.22uF | 100 | X7R | | 3216M/1206 | 1.25 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM32DC72A475KE02 | 4.7uF | 100 | X7S | | 3225M/1210 | 2.2 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM32EC71H106KA03 | 10uF | 50 | X7S | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM32EC7YA106KA03 | 10uF | 35 | X7S | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM32ER71A226KE12 | 22uF | 10 | X7R | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GGM32ER71E106KA57 | 10uF | 25 | X7R | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Automotive [AEC-Q200] |
| GRT033C80G104KE01 | 0.1uF | 4 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80G224ME01 | 0.22uF | 4 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J103KE01 | 10000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J104KE01 | 0.1uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J153KE01 | 15000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J153ME01 | 15000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J222KE01 | 2200pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J223KE01 | 22000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J223ME01 | 22000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J224KE01 | 0.22uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J224ME01 | 0.22uF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J333KE01 | 33000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J333ME01 | 33000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J472KE01 | 4700pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J473KE01 | 47000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C80J473ME01 | 47000pF | 6.3 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C81A104KE01 | 0.1uF | 10 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C81C104KE01 | 0.1uF | 16 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C81C104ME01 | 0.1uF | 16 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C81E102KE01 | 1000pF | 25 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C81E104KE01 | 0.1uF | 25 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033C81E104ME01 | 0.1uF | 25 | X6S | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033C81E471KE01 | 470pF | 25 | X6S | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60G105ME13 | 1uF | 4 | X5R | | 0603M/0201 | 0.35 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J103KE01 | 10000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J104KE01 | 0.1uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J105ME13 | 1uF | 6.3 | X5R | | 0603M/0201 | 0.35 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J153KE01 | 15000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|--|
| GRT033R60J223KE01 | 22000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J224KE01 | 0.22uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J333KE01 | 33000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J473KE01 | 47000pF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R60J474KE01 | 0.47uF | 6.3 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A103KE01 | 10000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A104KE01 | 0.1uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A222KE01 | 2200pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A223KE01 | 22000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A224KE01 | 0.22uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A224ME01 | 0.22uF | 10 | X5R | | 0603M/0201 | 0.33 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A472KE01 | 4700pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61A473KE01 | 47000pF | 10 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61C103KE01 | 10000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61C104KE01 | 0.1uF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61C223KE01 | 22000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61C473KE01 | 47000pF | 16 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61E101KE01 | 100pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61E102KE01 | 1000pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61E103KE01 | 10000pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61E104KE01 | 0.1uF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61E221KE01 | 220pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61E471KE01 | 470pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R61E472KE01 | 4700pF | 25 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R6YA104KE01 | 0.1uF | 35 | X5R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R70J103KE01 | 10000pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R70J222KE01 | 2200pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R70J472KE01 | 4700pF | 6.3 | X7R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R71A103KE01 | 10000pF | 10 | X7R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R71E102KE01 | 1000pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT033R71E471KE01 | 470pF | 25 | X7R | | 0603M/0201 | 0.33 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C71A105KE13 | 1uF | 10 | X7S | | 1005M/0402 | 0.6 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C71A225KE13 | 2.2uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80E106ME13 | 10uF | 2.5 | X6S | | 1005M/0402 | 0.7 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J105KE01 | 1uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J224KE01 | 0.22uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J224ME01 | 0.22uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J225KE01 | 2.2uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J225ME01 | 2.2uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J334KE01 | 0.33uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J334ME01 | 0.33uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J474KE01 | 0.47uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J474ME01 | 0.47uF | 6.3 | X6S | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C80J475ME13 | 4.7uF | 6.3 | X6S | | 1005M/0402 | 0.65 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81A105KE01 | 1uF | 10 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81A225KE13 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81A225ME13 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.7 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81C105KE13 | 1uF | 16 | X6S | | 1005M/0402 | 0.6 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81C105ME13 | 1uF | 16 | X6S | | 1005M/0402 | 0.6 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81C225KE13 | 2.2uF | 16 | X6S | | 1005M/0402 | 0.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81C225ME13 | 2.2uF | 16 | X6S | | 1005M/0402 | 0.7 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81C474KE01 | 0.47uF | 16 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81C474ME01 | 0.47uF | 16 | X6S | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81E105KE13 | 1uF | 25 | X6S | | 1005M/0402 | 0.6 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81E105ME13 | 1uF | 25 | X6S | | 1005M/0402 | 0.6 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81E224KE01 | 0.22uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C81E224ME01 | 0.22uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155C8YA224KE01 | 0.22uF | 35 | X6S | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155C8YA224ME01 | 0.22uF | 35 | X6S | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60G475ME13 | 4.7uF | 4 | X5R | | 1005M/0402 | 0.6 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J105KE01 | 1uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J224KE01 | 0.22uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J224ME01 | 0.22uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J225KE01 | 2.2uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J225ME01 | 2.2uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J334KE01 | 0.33uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J334ME01 | 0.33uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J474KE01 | 0.47uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J474ME01 | 0.47uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J475ME13 | 4.7uF | 6.3 | X5R | | 1005M/0402 | 0.6 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J684KE01 | 0.68uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R60J684ME01 | 0.68uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A105KE01 | 1uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A224KE01 | 0.22uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A224ME01 | 0.22uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A225KE01 | 2.2uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A225ME01 | 2.2uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|--|
| GRT155R61A334KE01 | 0.33uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A334ME01 | 0.33uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A474KE01 | 0.47uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A474ME01 | 0.47uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A475ME13 | 4.7uF | 10 | X5R | | 1005M/0402 | 0.65 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A684KE01 | 0.68uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61A684ME01 | 0.68uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61C105KE01 | 1uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61C224KE01 | 0.22uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61C225KE13 | 2.2uF | 16 | X5R | | 1005M/0402 | 0.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61C474KE01 | 0.47uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61C474ME01 | 0.47uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61E105KE01 | 1uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61E224KE01 | 0.22uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61E224ME01 | 0.22uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61E225KE13 | 2.2uF | 25 | X5R | | 1005M/0402 | 0.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61E474KE01 | 0.47uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R61E474ME01 | 0.47uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R6YA105KE13 | 1uF | 35 | X5R | | 1005M/0402 | 0.6 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R6YA105ME13 | 1uF | 35 | X5R | | 1005M/0402 | 0.6 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R6YA224KE01 | 0.22uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R6YA224ME01 | 0.22uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R6YA474KE01 | 0.47uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R6YA474ME01 | 0.47uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT155R70J223KE01 | 22000pF | 6.3 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71A224KE01 | 0.22uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71A474KE01 | 0.47uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71C103KE01 | 10000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71C104KE01 | 0.1uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71C223KE01 | 22000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71C224KE01 | 0.22uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71C473KE01 | 47000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71E103KE01 | 10000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71E104KE01 | 0.1uF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71E223KE01 | 22000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71E473KE01 | 47000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H102KE01 | 1000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H103KE01 | 10000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H104KE01 | 0.1uF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H221KE01 | 220pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H222KE01 | 2200pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H223KE01 | 22000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H471KE01 | 470pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H472KE01 | 4700pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT155R71H473KE01 | 47000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80G105ME01 | 1uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80G106ME13 | 10uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80G226ME13 | 22uF | 4 | X6S | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80G475KE01 | 4.7uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80G475ME01 | 4.7uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80J226ME13 | 22uF | 6.3 | X6S | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80J475KE01 | 4.7uF | 6.3 | X6S | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C80J475ME01 | 4.7uF | 6.3 | X6S | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81A105KE13 | 1uF | 10 | X6S | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81A106ME13 | 10uF | 10 | X6S | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81C105KE13 | 1uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81C106ME13 | 10uF | 16 | X6S | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81C225KE13 | 2.2uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81C475KE13 | 4.7uF | 16 | X6S | | 1608M/0603 | 0.95 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81C475ME13 | 4.7uF | 16 | X6S | | 1608M/0603 | 0.95 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81E105KE13 | 1uF | 25 | X6S | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81E225KE13 | 2.2uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81E225ME13 | 2.2uF | 25 | X6S | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81E475KE13 | 4.7uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C81E475ME13 | 4.7uF | 25 | X6S | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188C8YA105KE13 | 1uF | 35 | X6S | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188C8YA225KE13 | 2.2uF | 35 | X6S | | 1608M/0603 | 1 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R60G106ME13 | 10uF | 4 | X5R | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R60J105KE01 | 1uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R60J105ME01 | 1uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R60J106ME13 | 10uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R60J225KE13 | 2.2uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R60J226ME13 | 22uF | 6.3 | X5R | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R60J475KE01 | 4.7uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61A105KE01 | 1uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61A105ME01 | 1uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61A106KE13 | 10uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-10% | Infotainment for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|----------------------|-------------|-----------------|------------------------------|---------------------|-------------------|--|
| GRT188R61A106ME13 | 10uF | 10 | X5R | | 1608M/0603 | 0.95 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61A225KE13 | 2.2uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61A226ME13 | 22uF | 10 | X5R | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61C105KE13 | 1uF | 16 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61C106KE13 | 10uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61C106ME13 | 10uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61C475KE13 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61C475ME13 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61E105KE13 | 1uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61E106ME13 | 10uF | 25 | X5R | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61E225KE13 | 2.2uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61E475KE13 | 4.7uF | 25 | X5R | | 1608M/0603 | 0.95 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61E475ME13 | 4.7uF | 25 | X5R | | 1608M/0603 | 0.95 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61H105KE13 | 1uF | 50 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61H225KE13 | 2.2uF | 50 | X5R | | 1608M/0603 | 1 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R61H225ME13 | 2.2uF | 50 | X5R | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R6YA105KE13 | 1uF | 35 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R6YA225KE13 | 2.2uF | 35 | X5R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R6YA475KE13 | 4.7uF | 35 | X5R | | 1608M/0603 | 1 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R6YA475ME13 | 4.7uF | 35 | X5R | | 1608M/0603 | 1 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT188R70J225KE13 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R71C105KE13 | 1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R71E105KE13 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R71E224KE01 | 0.22uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R71H104KE13 | 0.1uF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT188R71H473KE01 | 47000pF | 50 | X7R | | 1608M/0603 | 0.9 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC71E106KE13 | 10uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC80G476ME13 | 47uF | 4 | X6S | | 2012M/0805 | 1.45 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81A106KE01 | 10uF | 10 | X6S | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81A226ME13 | 22uF | 10 | X6S | | 2012M/0805 | 1.45 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81C106KE01 | 10uF | 16 | X6S | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81C225KA02 | 2.2uF | 16 | X6S | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81C475KA02 | 4.7uF | 16 | X6S | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81E105KE13 | 1uF | 25 | X6S | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81E225KA02 | 2.2uF | 25 | X6S | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC81E475KA02 | 4.7uF | 25 | X6S | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC8YA225KE13 | 2.2uF | 35 | X6S | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BC8YA475KE13 | 4.7uF | 35 | X6S | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR60J106KE01 | 10uF | 6.3 | X5R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR60J226ME13 | 22uF | 6.3 | X5R | | 2012M/0805 | 1.4 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR60J475KE13 | 4.7uF | 6.3 | X5R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61A106KE01 | 10uF | 10 | X5R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61A226ME13 | 22uF | 10 | X5R | | 2012M/0805 | 1.4 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61A475KE13 | 4.7uF | 10 | X5R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61C106KE01 | 10uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61C225KA02 | 2.2uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61C226ME13 | 22uF | 16 | X5R | | 2012M/0805 | 1.45 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61C475KA02 | 4.7uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61E106KE13 | 10uF | 25 | X5R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61E225KA02 | 2.2uF | 25 | X5R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61E226ME13 | 22uF | 25 | X5R | | 2012M/0805 | 1.45 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61E475KA02 | 4.7uF | 25 | X5R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61H225KE13 | 2.2uF | 50 | X5R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR61H475KE13 | 4.7uF | 50 | X5R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR70J106KE13 | 10uF | 6.3 | X7R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71A106KE13 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71A475KE13 | 4.7uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71C225KE01 | 2.2uF | 16 | X7R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71C475KE13 | 4.7uF | 16 | X7R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71E105KE13 | 1uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71E225KE13 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71H105KE01 | 1uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT21BR71H474KE01 | 0.47uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC80G226KE01 | 22uF | 4 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC80G476ME01 | 47uF | 4 | X6S | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC80J226KE01 | 22uF | 6.3 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC80J476KE13 | 47uF | 6.3 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81A106KE01 | 10uF | 10 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81A106ME01 | 10uF | 10 | X6S | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81A226KE01 | 22uF | 10 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81C106KE01 | 10uF | 16 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81C106ME01 | 10uF | 16 | X6S | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81C226KE01 | 22uF | 16 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81C475KE01 | 4.7uF | 16 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81C475ME01 | 4.7uF | 16 | X6S | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81E106KE01 | 10uF | 25 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC81E475KE01 | 4.7uF | 25 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|--|
| GRT31CC81H225KE01 | 2.2uF | 50 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC8YA106KE01 | 10uF | 35 | X6S | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CC8YA106ME01 | 10uF | 35 | X6S | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR60J226KE01 | 22uF | 6.3 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR60J476KE13 | 47uF | 6.3 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61A106KE01 | 10uF | 10 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61A226KE01 | 22uF | 10 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61A476KE13 | 47uF | 10 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61C106KE01 | 10uF | 16 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61C226KE01 | 22uF | 16 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61C475KE01 | 4.7uF | 16 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61C475ME01 | 4.7uF | 16 | X5R | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61E106KE01 | 10uF | 25 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61E106ME01 | 10uF | 25 | X5R | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61E226KE01 | 22uF | 25 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61E335KE01 | 3.3uF | 25 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61E475KE01 | 4.7uF | 25 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61H106KE01 | 10uF | 50 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR61H225KE01 | 2.2uF | 50 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR6YA106KE01 | 10uF | 35 | X5R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR6YA106ME01 | 10uF | 35 | X5R | | 3216M/1206 | 1.8 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR70J226KE13 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR71E106KE13 | 10uF | 25 | X7R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT31CR71H225KE13 | 2.2uF | 50 | X7R | | 3216M/1206 | 1.8 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32DC81A106KE01 | 10uF | 10 | X6S | | 3225M/1210 | 2.2 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32DC81C106KE01 | 10uF | 16 | X6S | | 3225M/1210 | 2.2 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32DC81E106KE01 | 10uF | 25 | X6S | | 3225M/1210 | 2.2 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32DR60J336ME01 | 33uF | 6.3 | X5R | | 3225M/1210 | 2.2 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT32DR61C106KE01 | 10uF | 16 | X5R | | 3225M/1210 | 2.2 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32DR61E106KE01 | 10uF | 25 | X5R | | 3225M/1210 | 2.2 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32DR61E106ME01 | 10uF | 25 | X5R | | 3225M/1210 | 2.2 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT32EC80J476KE13 | 47uF | 6.3 | X6S | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32EC81A226ME13 | 22uF | 10 | X6S | | 3225M/1210 | 2.7 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT32EC81A476KE13 | 47uF | 10 | X6S | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32EC81C476KE13 | 47uF | 16 | X6S | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32EC81H475KE01 | 4.7uF | 50 | X6S | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32ER60J107ME13 | 100uF | 6.3 | X5R | | 3225M/1210 | 2.7 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT32ER61C226ME13 | 22uF | 16 | X5R | | 3225M/1210 | 2.7 | +/-20% | Infotainment for Automotive [AEC-Q200] |
| GRT32ER61E226KE13 | 22uF | 25 | X5R | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32ER61H475KE01 | 4.7uF | 50 | X5R | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32ER70J476KE13 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GRT32ER71H475KE01 | 4.7uF | 50 | X7R | | 3225M/1210 | 2.7 | +/-10% | Infotainment for Automotive [AEC-Q200] |
| GXT155C71A105KE13 | 1uF | 10 | X7S | | 1005M/0402 | 0.6 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C71A225KE13 | 2.2uF | 10 | X7S | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81A105KE01 | 1uF | 10 | X6S | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81A225KE13 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81A225ME13 | 2.2uF | 10 | X6S | | 1005M/0402 | 0.7 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81C105ME13 | 1uF | 16 | X6S | | 1005M/0402 | 0.6 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81C225KE13 | 2.2uF | 16 | X6S | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81C225ME13 | 2.2uF | 16 | X6S | | 1005M/0402 | 0.7 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81C474KE01 | 0.47uF | 16 | X6S | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81C474ME01 | 0.47uF | 16 | X6S | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81E105KE13 | 1uF | 25 | X6S | | 1005M/0402 | 0.6 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81E105ME13 | 1uF | 25 | X6S | | 1005M/0402 | 0.6 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81E224KE01 | 0.22uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C81E224ME01 | 0.22uF | 25 | X6S | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C8YA224KE01 | 0.22uF | 35 | X6S | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155C8YA224ME01 | 0.22uF | 35 | X6S | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R60J105KE01 | 1uF | 6.3 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61A105KE01 | 1uF | 10 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61C105KE01 | 1uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61C224KE01 | 0.22uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61C225KE13 | 2.2uF | 16 | X5R | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61C474KE01 | 0.47uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61C474ME01 | 0.47uF | 16 | X5R | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61E105KE01 | 1uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61E224KE01 | 0.22uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61E224ME01 | 0.22uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61E225KE13 | 2.2uF | 25 | X5R | | 1005M/0402 | 0.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61E474KE01 | 0.47uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R61E474ME01 | 0.47uF | 25 | X5R | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R6YA105KE13 | 1uF | 35 | X5R | | 1005M/0402 | 0.6 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R6YA105ME13 | 1uF | 35 | X5R | | 1005M/0402 | 0.6 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R6YA224KE01 | 0.22uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R6YA224ME01 | 0.22uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R6YA474KE01 | 0.47uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R6YA474ME01 | 0.47uF | 35 | X5R | | 1005M/0402 | 0.55 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|--|
| GXT155R71A224KE01 | 0.22uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71A474KE01 | 0.47uF | 10 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71C224KE01 | 0.22uF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71C473KE01 | 47000pF | 16 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71E104KE01 | 0.1uF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71E473KE01 | 47000pF | 25 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H102KE01 | 1000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H103KE01 | 10000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H104KE01 | 0.1uF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H221KE01 | 220pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H222KE01 | 2200pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H223KE01 | 22000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H471KE01 | 470pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H472KE01 | 4700pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT155R71H473KE01 | 47000pF | 50 | X7R | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C80G105ME01 | 1uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C80G106ME13 | 10uF | 4 | X6S | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81A106ME13 | 10uF | 10 | X6S | | 1608M/0603 | 1 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81C106ME13 | 10uF | 16 | X6S | | 1608M/0603 | 1 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81C225KE13 | 2.2uF | 16 | X6S | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81C475KE13 | 4.7uF | 16 | X6S | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81C475ME13 | 4.7uF | 16 | X6S | | 1608M/0603 | 0.95 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81E225KE13 | 2.2uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81E225ME13 | 2.2uF | 25 | X6S | | 1608M/0603 | 1 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81E475KE13 | 4.7uF | 25 | X6S | | 1608M/0603 | 1 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C81E475ME13 | 4.7uF | 25 | X6S | | 1608M/0603 | 1 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188C8YA225KE13 | 2.2uF | 35 | X6S | | 1608M/0603 | 1 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R60G106ME13 | 10uF | 4 | X5R | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R60J105KE01 | 1uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R60J105ME01 | 1uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R60J106ME13 | 10uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R60J225KE13 | 2.2uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R60J475KE01 | 4.7uF | 6.3 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61A105KE01 | 1uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61A105ME01 | 1uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61A225KE13 | 2.2uF | 10 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61C106ME13 | 10uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61C475KE13 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61C475ME13 | 4.7uF | 16 | X5R | | 1608M/0603 | 0.95 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61E106ME13 | 10uF | 25 | X5R | | 1608M/0603 | 1 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61E225KE13 | 2.2uF | 25 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61E475KE13 | 4.7uF | 25 | X5R | | 1608M/0603 | 0.95 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61E475ME13 | 4.7uF | 25 | X5R | | 1608M/0603 | 0.95 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61H225KE13 | 2.2uF | 50 | X5R | | 1608M/0603 | 1 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R61H225ME13 | 2.2uF | 50 | X5R | | 1608M/0603 | 1 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R6YA225KE13 | 2.2uF | 35 | X5R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R6YA475KE13 | 4.7uF | 35 | X5R | | 1608M/0603 | 1 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R6YA475ME13 | 4.7uF | 35 | X5R | | 1608M/0603 | 1 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R70J225KE13 | 2.2uF | 6.3 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R71C105KE13 | 1uF | 16 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT188R71E105KE13 | 1uF | 25 | X7R | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BC71E106KE13 | 10uF | 25 | X7S | | 2012M/0805 | 1.45 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BC81A226ME13 | 22uF | 10 | X6S | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR60J106KE01 | 10uF | 6.3 | X5R | | 2012M/0805 | 1.35 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR61A106KE01 | 10uF | 10 | X5R | | 2012M/0805 | 1.35 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR61C106KE01 | 10uF | 16 | X5R | | 2012M/0805 | 1.35 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR61C226ME13 | 22uF | 16 | X5R | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR61E226ME13 | 22uF | 25 | X5R | | 2012M/0805 | 1.45 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR71A106KE13 | 10uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR71A475KE13 | 4.7uF | 10 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR71E225KE13 | 2.2uF | 25 | X7R | | 2012M/0805 | 1.4 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT21BR71H105KE01 | 1uF | 50 | X7R | | 2012M/0805 | 1.35 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CC81E106KE01 | 10uF | 25 | X6S | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CC8YA106KE01 | 10uF | 35 | X6S | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CC8YA106ME01 | 10uF | 35 | X6S | | 3216M/1206 | 1.8 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CR61E106KE01 | 10uF | 25 | X5R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CR61E106ME01 | 10uF | 25 | X5R | | 3216M/1206 | 1.8 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CR6YA106KE01 | 10uF | 35 | X5R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CR6YA106ME01 | 10uF | 35 | X5R | | 3216M/1206 | 1.8 | +/-20% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CR70J226KE13 | 22uF | 6.3 | X7R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT31CR71E106KE13 | 10uF | 25 | X7R | | 3216M/1206 | 1.8 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT32DC81E106KE01 | 10uF | 25 | X6S | | 3225M/1210 | 2.2 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT32EC80J476KE13 | 47uF | 6.3 | X6S | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT32EC81A476KE13 | 47uF | 10 | X6S | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT32EC81C476KE13 | 47uF | 16 | X6S | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |
| GXT32ER70J476KE13 | 47uF | 6.3 | X7R | | 3225M/1210 | 2.7 | +/-10% | Water repellent/ Infotainment [AEC-Q200] |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|--------------------------|
| GJ821BB31H105KA12 | 1uF | 50 | B | | 2012M/0805 | 1.35 | +/-10% | Acoustic noise reduction |
| GRM022B11A101KA01 | 100pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B11A101MA01 | 100pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B11A151KA01 | 150pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B11A151MA01 | 150pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B11A221KA01 | 220pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B11A221MA01 | 220pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B11A331KA01 | 330pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B11A331MA01 | 330pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B11A471KA01 | 470pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B11A471MA01 | 470pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B11A680KA01 | 68pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B11A680MA01 | 68pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J102KE19 | 1000pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J102ME19 | 1000pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J103KE19 | 10000pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J103ME19 | 10000pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J152KE19 | 1500pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J152ME19 | 1500pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J222KE19 | 2200pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J222ME19 | 2200pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J332KE19 | 3300pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J332ME19 | 3300pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J472KE19 | 4700pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J472ME19 | 4700pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J681KE19 | 680pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J681ME19 | 680pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B30J682KE19 | 6800pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B30J682ME19 | 6800pF | 6.3 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A102KE19 | 1000pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A102ME19 | 1000pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A103KE19 | 10000pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A103ME19 | 10000pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A152KE19 | 1500pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A152ME19 | 1500pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A222KE19 | 2200pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A222ME19 | 2200pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A332KE19 | 3300pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A332ME19 | 3300pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A472KE19 | 4700pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A472ME19 | 4700pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A681KE19 | 680pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A681ME19 | 680pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM022B31A682KE19 | 6800pF | 10 | B | | 0402M/01005 | 0.22 | +/-10% | Ultra-small |
| GRM022B31A682ME19 | 6800pF | 10 | B | | 0402M/01005 | 0.22 | +/-20% | Ultra-small |
| GRM033B10J103KA01 | 10000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J152KA01 | 1500pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J153KE01 | 15000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J153ME01 | 15000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B10J222KA01 | 2200pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J223KE01 | 22000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J223ME01 | 22000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B10J332KA01 | 3300pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J333KE01 | 33000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J333ME01 | 33000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B10J472KA01 | 4700pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B10J682KA01 | 6800pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11A103KA01 | 10000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11A103MA01 | 10000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B11A152KA01 | 1500pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11A222KA01 | 2200pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11A332KA01 | 3300pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11A472KA01 | 4700pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11A472MA01 | 4700pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B11A682KA01 | 6800pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11A682MA01 | 6800pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B11C101KA01 | 100pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11C102KA01 | 1000pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11C151KA01 | 150pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11C152KA01 | 1500pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11C221KA01 | 220pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11C331KA01 | 330pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11C471KA01 | 470pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11C681KA01 | 680pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E101KA01 | 100pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E102KA01 | 1000pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E102MA01 | 1000pF | 25 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-------------|
| GRM033B11E151KA01 | 150pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E152KA01 | 1500pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E152MA01 | 1500pF | 25 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B11E221KA01 | 220pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E331KA01 | 330pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E471KA01 | 470pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B11E681KA01 | 680pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B30G224ME15 | 0.22uF | 4 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B30J224ME15 | 0.22uF | 6.3 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B30J473KE18 | 47000pF | 6.3 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A104KE84 | 0.1uF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A104ME84 | 0.1uF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A123KE84 | 12000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A123ME84 | 12000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A153KE84 | 15000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A153ME84 | 15000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A183KE84 | 18000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A183ME84 | 18000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A223KE84 | 22000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A223ME84 | 22000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A273KE84 | 27000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A273ME84 | 27000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A333KE84 | 33000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A333ME84 | 33000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A393KE84 | 39000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A393ME84 | 39000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A473KE84 | 47000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A473ME84 | 47000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31A683KE84 | 68000pF | 10 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31A683ME84 | 68000pF | 10 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C103KA12 | 10000pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C103MA12 | 10000pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C104KE84 | 0.1uF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C104ME84 | 0.1uF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C153KE84 | 15000pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C153ME84 | 15000pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C222KA87 | 2200pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C222MA87 | 2200pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C223KE84 | 22000pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C223ME84 | 22000pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C332KA87 | 3300pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C332MA87 | 3300pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C333KE84 | 33000pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C333ME84 | 33000pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C473KE84 | 47000pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C473ME84 | 47000pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31C683KE84 | 68000pF | 16 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31C683ME84 | 68000pF | 16 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31E103KA12 | 10000pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31E103MA12 | 10000pF | 25 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31E222KA12 | 2200pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31E222MA12 | 2200pF | 25 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31E332KA12 | 3300pF | 25 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31E332MA12 | 3300pF | 25 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H101KA12 | 100pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H101MA12 | 100pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H102KA12 | 1000pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H102MA12 | 1000pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H151KA12 | 150pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H151MA12 | 150pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H152KA12 | 1500pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H152MA12 | 1500pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H221KA12 | 220pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H221MA12 | 220pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H331KA12 | 330pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H331MA12 | 330pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H471KA12 | 470pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H471MA12 | 470pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033B31H681KA12 | 680pF | 50 | B | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033B31H681MA12 | 680pF | 50 | B | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R10J103KA01 | 10000pF | 6.3 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R10J152KA01 | 1500pF | 6.3 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R10J222KA01 | 2200pF | 6.3 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R10J332KA01 | 3300pF | 6.3 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R10J472KA01 | 4700pF | 6.3 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R10J682KA01 | 6800pF | 6.3 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11A103KA01 | 10000pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM033R11A103MA01 | 1000pF | 10 | R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R11A152KA01 | 1500pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11A222KA01 | 2200pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11A332KA01 | 3300pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11A472KA01 | 4700pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11A472MA01 | 4700pF | 10 | R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R11A682KA01 | 6800pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11A682MA01 | 6800pF | 10 | R | | 0603M/0201 | 0.33 | +/-20% | Ultra-small |
| GRM033R11C101KA01 | 100pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C102KA01 | 1000pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C151KA01 | 150pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C152KA01 | 1500pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C221KA01 | 220pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C222KA88 | 2200pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C331KA01 | 330pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C332KA88 | 3300pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C471KA01 | 470pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11C681KA01 | 680pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E101KA01 | 100pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E102KA01 | 1000pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E151KA01 | 150pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E152KA01 | 1500pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E221KA01 | 220pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E331KA01 | 330pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E471KA01 | 470pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM033R11E681KA01 | 680pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Ultra-small |
| GRM152B30J104KE19 | 0.1uF | 6.3 | B | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152B30J104ME19 | 0.1uF | 6.3 | B | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152B30J224KE19 | 0.22uF | 6.3 | B | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152B30J224ME19 | 0.22uF | 6.3 | B | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152B30J474ME15 | 0.47uF | 6.3 | B | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152B31A104KE19 | 0.1uF | 10 | B | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152B31A104ME19 | 0.1uF | 10 | B | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM152B31A224KE19 | 0.22uF | 10 | B | | 1005M/0402 | 0.22 | +/-10% | General Purpose |
| GRM152B31A224ME19 | 0.22uF | 10 | B | | 1005M/0402 | 0.22 | +/-20% | General Purpose |
| GRM153B30G225ME95 | 2.2uF | 4 | B | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153B30J105ME95 | 1uF | 6.3 | B | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153B30J225ME95 | 2.2uF | 6.3 | B | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM153B31A105ME95 | 1uF | 10 | B | | 1005M/0402 | 0.33 | +/-20% | General Purpose |
| GRM155B10J104KA01 | 0.1uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B10J154KE01 | 0.15uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B10J154ME01 | 0.15uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B10J224KE01 | 0.22uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B10J224ME01 | 0.22uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B10J334KE01 | 0.33uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B10J334ME01 | 0.33uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11A104KA01 | 0.1uF | 10 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11C103KA01 | 1000pF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11C103MA01 | 1000pF | 16 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11C223KA01 | 2200pF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11C333KA01 | 3300pF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11C473KA01 | 4700pF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11E102KA01 | 1000pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11E103KA01 | 1000pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11E103MA01 | 1000pF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11E153KA61 | 1500pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11E153MA61 | 1500pF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11E222KA01 | 2200pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11E223KA61 | 2200pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11E223MA61 | 2200pF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11E472KA01 | 4700pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11E682KA01 | 6800pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H102KA01 | 1000pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H102MA01 | 1000pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H152KA01 | 1500pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H152MA01 | 1500pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H221KA01 | 220pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H221MA01 | 220pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H222KA01 | 2200pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H222MA01 | 2200pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H331KA01 | 330pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H331MA01 | 330pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H332KA01 | 3300pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H332MA01 | 3300pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H471KA01 | 470pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H471MA01 | 470pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H472KA01 | 4700pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM155B11H472MA01 | 4700pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B11H681KA01 | 680pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B11H681MA01 | 680pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B30G475ME47 | 4.7uF | 4 | B | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155B30J105KE18 | 1uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B30J105ME18 | 1uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B30J225KE95 | 2.2uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B30J225ME95 | 2.2uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B30J474KE18 | 0.47uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B30J474ME18 | 0.47uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B30J475ME47 | 4.7uF | 6.3 | B | | 1005M/0402 | 0.6 | +/-20% | General Purpose |
| GRM155B30J475ME87 | 4.7uF | 6.3 | B | | 1005M/0402 | 0.65 | +/-20% | General Purpose |
| GRM155B30J684KE18 | 0.68uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B30J684ME18 | 0.68uF | 6.3 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31A105ME01 | 1uF | 10 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31A154KE18 | 0.15uF | 10 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31A154ME18 | 0.15uF | 10 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31A224KE18 | 0.22uF | 10 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31A224ME18 | 0.22uF | 10 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31A225KE95 | 2.2uF | 10 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31A225ME95 | 2.2uF | 10 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31A334KE14 | 0.33uF | 10 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31A334ME14 | 0.33uF | 10 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31A474KE14 | 0.47uF | 10 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31A474ME14 | 0.47uF | 10 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31A684KE15 | 0.68uF | 10 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31A684ME15 | 0.68uF | 10 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31C104KA87 | 0.1uF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31C105KA12 | 1uF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31C105MA12 | 1uF | 16 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31C683KA87 | 6800pF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31E104KA87 | 0.1uF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31E104MA87 | 0.1uF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31E105KA12 | 1uF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31E105MA12 | 1uF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31E333KA87 | 3300pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31E333MA87 | 3300pF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31E473KA87 | 4700pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31E473MA87 | 4700pF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31E683KA87 | 6800pF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31E683MA87 | 6800pF | 25 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31H103KA88 | 1000pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31H103MA88 | 1000pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31H104KE14 | 0.1uF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31H104ME14 | 0.1uF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31H153KA12 | 1500pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31H153MA12 | 1500pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31H223KA12 | 2200pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31H223MA12 | 2200pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155B31H682KA88 | 680pF | 50 | B | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155B31H682MA88 | 680pF | 50 | B | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R11A104KA01 | 0.1uF | 10 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11A683KA01 | 6800pF | 10 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11A683MA01 | 6800pF | 10 | R | | 1005M/0402 | 0.55 | +/-20% | General Purpose |
| GRM155R11C104KA88 | 0.1uF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11C223KA01 | 2200pF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11C333KA01 | 3300pF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11C473KA01 | 4700pF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11C683KA88 | 6800pF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11E103KA01 | 1000pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11E153KA61 | 1500pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11E223KA61 | 2200pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11E333KA88 | 3300pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11E472KA01 | 4700pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11E473KA88 | 4700pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11E682KA01 | 680pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H102KA01 | 1000pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H103KA88 | 1000pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H152KA01 | 1500pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H221KA01 | 220pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H222KA01 | 220pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H331KA01 | 330pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H332KA01 | 330pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H471KA01 | 470pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H472KA01 | 470pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H681KA01 | 680pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |
| GRM155R11H682KA88 | 680pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM15XB11C103KA86 | 10000pF | 16 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11C103MA86 | 10000pF | 16 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11C332KA86 | 3300pF | 16 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11C332MA86 | 3300pF | 16 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11C472KA86 | 4700pF | 16 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11C472MA86 | 4700pF | 16 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11C682KA86 | 6800pF | 16 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11C682MA86 | 6800pF | 16 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11E222KA86 | 2200pF | 25 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11E222MA86 | 2200pF | 25 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11H102KA86 | 1000pF | 50 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11H102MA86 | 1000pF | 50 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11H152KA86 | 1500pF | 50 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11H152MA86 | 1500pF | 50 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11H221KA86 | 220pF | 50 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11H221MA86 | 220pF | 50 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11H331KA86 | 330pF | 50 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11H331MA86 | 330pF | 50 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11H471KA86 | 470pF | 50 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11H471MA86 | 470pF | 50 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XB11H681KA86 | 680pF | 50 | B | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XB11H681MA86 | 680pF | 50 | B | | 1005M/0402 | 0.3 | +/-20% | General Purpose |
| GRM15XR11C103KA86 | 10000pF | 16 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11C472KA86 | 4700pF | 16 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11E222KA86 | 2200pF | 25 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11H102KA86 | 1000pF | 50 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11H152KA86 | 1500pF | 50 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11H221KA86 | 220pF | 50 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11H331KA86 | 330pF | 50 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11H471KA86 | 470pF | 50 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM15XR11H681KA86 | 680pF | 50 | R | | 1005M/0402 | 0.3 | +/-10% | General Purpose |
| GRM185B30J105KE25 | 1uF | 6.3 | B | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185B31A105KE35 | 1uF | 10 | B | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185B31C105KE43 | 1uF | 16 | B | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185B31C105ME43 | 1uF | 16 | B | | 1608M/0603 | 0.5 | +/-20% | General Purpose |
| GRM185B31E105KA12 | 1uF | 25 | B | | 1608M/0603 | 0.5 | +/-10% | General Purpose |
| GRM185B31E105MA12 | 1uF | 25 | B | | 1608M/0603 | 0.5 | +/-20% | General Purpose |
| GRM188B10J105KA01 | 1uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B10J474KA01 | 0.47uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11A105KA61 | 1uF | 10 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11A224KA01 | 0.22uF | 10 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11A334KA61 | 0.33uF | 10 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11A334MA61 | 0.33uF | 10 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11A474KA61 | 0.47uF | 10 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11A684KA61 | 0.68uF | 10 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11A684MA61 | 0.68uF | 10 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11C104KA01 | 0.1uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11C104MA01 | 0.1uF | 16 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11C154KA01 | 0.15uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11C224KA01 | 0.22uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11C224MA01 | 0.22uF | 16 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11C334KA01 | 0.33uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11C334MA01 | 0.33uF | 16 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E102KA01 | 1000pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E103KA01 | 10000pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E103MA01 | 10000pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E104KA01 | 0.1uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E104MA01 | 0.1uF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E152KA01 | 1500pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E153KA01 | 15000pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E153MA01 | 15000pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E154KA01 | 0.15uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E222KA01 | 2200pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E222MA01 | 2200pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E223KA01 | 22000pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E223MA01 | 22000pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E332KA01 | 3300pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E333KA01 | 33000pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E333MA01 | 33000pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E472KA01 | 4700pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E472MA01 | 4700pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E473KA01 | 47000pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E473MA01 | 47000pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11E682KA01 | 6800pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E683KA01 | 68000pF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11E683MA01 | 68000pF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H102KA01 | 1000pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|-----------------|
| GRM188B11H102MA01 | 1000pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H103KA01 | 10000pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H103MA01 | 10000pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H152KA01 | 1500pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H152MA01 | 1500pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H153KA01 | 15000pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H153MA01 | 15000pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H221KA01 | 220pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H221MA01 | 220pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H222KA01 | 2200pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H222MA01 | 2200pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H223KA01 | 22000pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H223MA01 | 22000pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H331KA01 | 330pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H331MA01 | 330pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H332KA01 | 3300pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H332MA01 | 3300pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H333KA61 | 33000pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H333MA61 | 33000pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H471KA01 | 470pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H471MA01 | 470pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H472KA01 | 4700pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H472MA01 | 4700pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H473KA61 | 47000pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H473MA61 | 47000pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H681KA01 | 680pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H681MA01 | 680pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B11H682KA01 | 6800pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B11H682MA01 | 6800pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B30G106ME46 | 10uF | 4 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B30G226MEA0 | 22uF | 4 | B | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188B30J106ME47 | 10uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B30J106ME84 | 10uF | 6.3 | B | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188B30J225KE18 | 2.2uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B30J226MEA0 | 22uF | 6.3 | B | | 1608M/0603 | 1 | +/-20% | General Purpose |
| GRM188B30J475KE18 | 4.7uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B30J475ME18 | 4.7uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B30J475ME84 | 4.7uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31A106KE69 | 10uF | 10 | B | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188B31A106ME69 | 10uF | 10 | B | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188B31A225KE33 | 2.2uF | 10 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31A225ME33 | 2.2uF | 10 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31A475KE15 | 4.7uF | 10 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31A475ME15 | 4.7uF | 10 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31C105KA92 | 1uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31C105MA92 | 1uF | 16 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31C225KE14 | 2.2uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31C474KA75 | 0.47uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31C474KA87 | 0.47uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31C474MA75 | 0.47uF | 16 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31C474MA87 | 0.47uF | 16 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31C475KAAJ | 4.7uF | 16 | B | | 1608M/0603 | 0.95 | +/-10% | General Purpose |
| GRM188B31C475MAAJ | 4.7uF | 16 | B | | 1608M/0603 | 0.95 | +/-20% | General Purpose |
| GRM188B31C684KA75 | 0.68uF | 16 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31C684MA75 | 0.68uF | 16 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31E105KA75 | 1uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31E105MA75 | 1uF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31E224KA87 | 0.22uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31E224MA87 | 0.22uF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31E225KA12 | 2.2uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31E225MA12 | 2.2uF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31E474KA75 | 0.47uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31E474MA75 | 0.47uF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31E684KA75 | 0.68uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31E684MA75 | 0.68uF | 25 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31H104KA92 | 0.1uF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31H104MA92 | 0.1uF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31H105KAAL | 1uF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31H105MAAL | 1uF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31H154KAC4 | 0.15uF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31H154MAC4 | 0.15uF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31H224KAC4 | 0.22uF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31H224MAC4 | 0.22uF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188B31H683KA92 | 68000pF | 50 | B | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188B31H683MA92 | 68000pF | 50 | B | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11A224KA01 | 0.22uF | 10 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11C104KA01 | 0.1uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM188R11C154KA01 | 0.15uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11C224KA01 | 0.22uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11C224MA01 | 0.22uF | 16 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11C334KA01 | 0.33uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11C474KA88 | 0.47uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11C474MA88 | 0.47uF | 16 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E102KA01 | 1000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E103KA01 | 1000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E103MA01 | 1000pF | 25 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E104KA01 | 0.1uF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E104MA01 | 0.1uF | 25 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E152KA01 | 1500pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E153KA01 | 1500pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E154KA01 | 0.15uF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E222KA01 | 2200pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E222MA01 | 2200pF | 25 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E223KA01 | 2200pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E223MA01 | 2200pF | 25 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E224KA88 | 0.22uF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E224MA88 | 0.22uF | 25 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E332KA01 | 3300pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E333KA01 | 3300pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E472KA01 | 4700pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E472MA01 | 4700pF | 25 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E473KA01 | 4700pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E473MA01 | 4700pF | 25 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11E682KA01 | 6800pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11E683KA01 | 6800pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H102KA01 | 1000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H102MA01 | 1000pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H103KA01 | 1000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H103MA01 | 1000pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H104KA93 | 0.1uF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H104MA93 | 0.1uF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H152KA01 | 1500pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H153KA01 | 1500pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H221KA01 | 220pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H221MA01 | 220pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H222KA01 | 2200pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H222MA01 | 2200pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H223KA01 | 2200pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H223MA01 | 2200pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H331KA01 | 330pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H332KA01 | 3300pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H333KA61 | 3300pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H471KA01 | 470pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H471MA01 | 470pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H472KA01 | 4700pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H472MA01 | 4700pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H473KA61 | 4700pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H473MA61 | 4700pF | 50 | R | | 1608M/0603 | 0.9 | +/-20% | General Purpose |
| GRM188R11H681KA01 | 680pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H682KA01 | 6800pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM188R11H683KA93 | 6800pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | General Purpose |
| GRM219B31C105KA87 | 1uF | 16 | B | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM219B31E105KA75 | 1uF | 25 | B | | 2012M/0805 | 0.7 | +/-10% | General Purpose |
| GRM219B11A105KA01 | 1uF | 10 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B11A225KA01 | 2.2uF | 10 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B11C684KA01 | 0.68uF | 16 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B11H333KA01 | 3300pF | 50 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B30G226ME66 | 22uF | 4 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B30J106KE18 | 10uF | 6.3 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B30J106ME18 | 10uF | 6.3 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B30J226ME47 | 22uF | 6.3 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B30J226MEA0 | 22uF | 6.3 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B30J475KE18 | 4.7uF | 6.3 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31A106KE44 | 10uF | 10 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31A106ME44 | 10uF | 10 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31A226MEA0 | 22uF | 10 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31A475KE33 | 4.7uF | 10 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31A475ME33 | 4.7uF | 10 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31C106KA73 | 10uF | 16 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31C106MA73 | 10uF | 16 | B | | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31C225KA87 | 2.2uF | 16 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31C475KE15 | 4.7uF | 16 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31E105KA88 | 1uF | 25 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31E106KA12 | 10uF | 25 | B | | 2012M/0805 | 0.95 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-----------------------------|------------------------|------------------|----------------|-----------------|
| GRM219B31E106MA12 | 10uF | 25 | B | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31E225KA75 | 2.2uF | 25 | B | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31E225MA75 | 2.2uF | 25 | B | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31E474KA88 | 0.47uF | 25 | B | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31E474MA88 | 0.47uF | 25 | B | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31E684KA88 | 0.68uF | 25 | B | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31H105KA73 | 1uF | 50 | B | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31H105MA73 | 1uF | 50 | B | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31H225KE15 | 2.2uF | 50 | B | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31H225ME15 | 2.2uF | 50 | B | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219B31H334KA87 | 0.33uF | 50 | B | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219B31H334MA87 | 0.33uF | 50 | B | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R11C684KA01 | 0.68uF | 16 | R | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R11E474KA88 | 0.47uF | 25 | R | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R11E474MA88 | 0.47uF | 25 | R | 2012M/0805 | 0.95 | +/-20% | General Purpose |
| GRM219R11E683KA01 | 68000pF | 25 | R | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM219R11H333KA01 | 33000pF | 50 | R | 2012M/0805 | 0.95 | +/-10% | General Purpose |
| GRM21BB10J105KC01 | 1uF | 6.3 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB10J225KA01 | 2.2uF | 6.3 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB10J475KA11 | 4.7uF | 6.3 | B | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BB10J475MA11 | 4.7uF | 6.3 | B | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BB11A105KA01 | 1uF | 10 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11A225KA01 | 2.2uF | 10 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11A225MA01 | 2.2uF | 10 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB11C105KA01 | 1uF | 16 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11C224KA01 | 0.22uF | 16 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11C224MA01 | 0.22uF | 16 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB11E154KA01 | 0.15uF | 25 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11E224KA01 | 0.22uF | 25 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11E224MA01 | 0.22uF | 25 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB11E334KA01 | 0.33uF | 25 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11H104KA01 | 0.1uF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11H104MA01 | 0.1uF | 50 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB11H473KA01 | 47000pF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB11H473MA01 | 47000pF | 50 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB11H683KA01 | 68000pF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB30G476ME15 | 47uF | 4 | B | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BB30J106KE18 | 10uF | 6.3 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB30J106ME18 | 10uF | 6.3 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB30J226ME38 | 22uF | 6.3 | B | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BB30J476ME15 | 47uF | 6.3 | B | 2012M/0805 | 1.45 | +/-20% | General Purpose |
| GRM21BB31A106KE18 | 10uF | 10 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31A106ME18 | 10uF | 10 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31A226ME51 | 22uF | 10 | B | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BB31A475KA74 | 4.7uF | 10 | B | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BB31A475MA74 | 4.7uF | 10 | B | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BB31C106KE15 | 10uF | 16 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31C106ME15 | 10uF | 16 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31C225KA87 | 2.2uF | 16 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31C475KA87 | 4.7uF | 16 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31D106KE15 | 10uF | 20 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31D106ME15 | 10uF | 20 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31E105KA98 | 1uF | 25 | B | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BB31E106KA73 | 10uF | 25 | B | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BB31E106MA73 | 10uF | 25 | B | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BB31E225KA75 | 2.2uF | 25 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31E225MA75 | 2.2uF | 25 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31E475KA75 | 4.7uF | 25 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31E475MA75 | 4.7uF | 25 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31H105KA12 | 1uF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31H105MA12 | 1uF | 50 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31H154KA88 | 0.15uF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31H154MA88 | 0.15uF | 50 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31H224KA88 | 0.22uF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31H224MA88 | 0.22uF | 50 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31H225KA73 | 2.2uF | 50 | B | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BB31H225MA73 | 2.2uF | 50 | B | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BB31H474KA87 | 0.47uF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31H474MA87 | 0.47uF | 50 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BB31H475KE51 | 4.7uF | 50 | B | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BB31H475ME51 | 4.7uF | 50 | B | 2012M/0805 | 1.4 | +/-20% | General Purpose |
| GRM21BB31H684KAC4 | 0.68uF | 50 | B | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BB31H684MAC4 | 0.68uF | 50 | B | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR10J105KC01 | 1uF | 6.3 | R | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11A105KA01 | 1uF | 10 | R | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11C105KA01 | 1uF | 16 | R | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11C224KA01 | 0.22uF | 16 | R | 2012M/0805 | 1.35 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|-------------|-----------------|------------------------------|---------------------|-------------------|-----------------|
| GRM21BR11C224MA01 | 0.22uF | 16 | R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR11E104KA01 | 0.1uF | 25 | R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11E104MA01 | 0.1uF | 25 | R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR11E105KA99 | 1uF | 25 | R | | 2012M/0805 | 1.4 | +/-10% | General Purpose |
| GRM21BR11E154KA01 | 0.15uF | 25 | R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11E154MA01 | 0.15uF | 25 | R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR11E224KA01 | 0.22uF | 25 | R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11E224MA01 | 0.22uF | 25 | R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR11E684KA88 | 0.68uF | 25 | R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11H104KA01 | 0.1uF | 50 | R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11H104MA01 | 0.1uF | 50 | R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR11H473KA01 | 47000pF | 50 | R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM21BR11H473MA01 | 47000pF | 50 | R | | 2012M/0805 | 1.35 | +/-20% | General Purpose |
| GRM21BR11H683KA01 | 68000pF | 50 | R | | 2012M/0805 | 1.35 | +/-10% | General Purpose |
| GRM316B31A475KE18 | 4.7uF | 10 | B | | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM316B31C225KA87 | 2.2uF | 16 | B | | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM316B31E225KA75 | 2.2uF | 25 | B | | 3216M/1206 | 0.7 | +/-10% | General Purpose |
| GRM319B11A105KA01 | 1uF | 10 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B11A225KA01 | 2.2uF | 10 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B11A475KA01 | 4.7uF | 10 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B11C105KAA3 | 1uF | 16 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B11C474KA01 | 0.47uF | 16 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B11C474MA01 | 0.47uF | 16 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B11E334KA01 | 0.33uF | 25 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B11E474KA01 | 0.47uF | 25 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B11E474MA01 | 0.47uF | 25 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B11E684KA01 | 0.68uF | 25 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B30J106KE18 | 10uF | 6.3 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B30J226ME15 | 22uF | 6.3 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B31A106KE18 | 10uF | 10 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31A106ME18 | 10uF | 10 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B31A226ME15 | 22uF | 10 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B31C106KE15 | 10uF | 16 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31C106ME15 | 10uF | 16 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B31C226ME15 | 22uF | 16 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B31C335KA75 | 3.3uF | 16 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31C475KA87 | 4.7uF | 16 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31E105KC45 | 1uF | 25 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31E475KA75 | 4.7uF | 25 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31H225KA12 | 2.2uF | 50 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31H225MA12 | 2.2uF | 50 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319B31H475KA12 | 4.7uF | 50 | B | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319B31H475MA12 | 4.7uF | 50 | B | | 3216M/1206 | 0.95 | +/-20% | General Purpose |
| GRM319R11A105KA01 | 1uF | 10 | R | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R11C105KAA3 | 1uF | 16 | R | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R11E334KA01 | 0.33uF | 25 | R | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM319R11E474KA01 | 0.47uF | 25 | R | | 3216M/1206 | 0.95 | +/-10% | General Purpose |
| GRM31CB10J475KA01 | 4.7uF | 6.3 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB11A475KA01 | 4.7uF | 10 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB11C475KA01 | 4.7uF | 16 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB30J226KE18 | 22uF | 6.3 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB30J226ME18 | 22uF | 6.3 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB30J476KE18 | 47uF | 6.3 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB30J476ME18 | 47uF | 6.3 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31A226KE19 | 22uF | 10 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31A226ME19 | 22uF | 10 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31A476KE15 | 47uF | 10 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31A476ME15 | 47uF | 10 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31C106KA88 | 10uF | 16 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31C226KE15 | 22uF | 16 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31C226ME15 | 22uF | 16 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31E106KA75 | 10uF | 25 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31E106MA75 | 10uF | 25 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31E226KE15 | 22uF | 25 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31E226ME15 | 22uF | 25 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31E475KA87 | 4.7uF | 25 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31H106KA12 | 10uF | 50 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31H106MA12 | 10uF | 50 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31H225KA87 | 2.2uF | 50 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31H225MA87 | 2.2uF | 50 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB31H475KA12 | 4.7uF | 50 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB31H475MA12 | 4.7uF | 50 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CB3YA106KA12 | 10uF | 35 | B | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CB3YA106MA12 | 10uF | 35 | B | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR11A106KA01 | 10uF | 10 | R | | 3216M/1206 | 1.8 | +/-10% | General Purpose |
| GRM31CR11A106MA01 | 10uF | 10 | R | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31CR11C475KA01 | 4.7uF | 16 | R | | 3216M/1206 | 1.8 | +/-10% | General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|----------------------------------|
| GRM31CR11C475MA01 | 4.7uF | 16 | R | | 3216M/1206 | 1.8 | +/-20% | General Purpose |
| GRM31MB11A225KA01 | 2.2uF | 10 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB11C105KA01 | 1uF | 16 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB11C225KA35 | 2.2uF | 16 | B | | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MB11C225MA35 | 2.2uF | 16 | B | | 3216M/1206 | 1.3 | +/-20% | General Purpose |
| GRM31MB11C684KA01 | 0.68uF | 16 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB11E105KA01 | 1uF | 25 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB11E224KA01 | 0.22uF | 25 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB11E224MA01 | 0.22uF | 25 | B | | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MB11H154KA01 | 0.15uF | 50 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB11H224KA01 | 0.22uF | 50 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB11H224MA01 | 0.22uF | 50 | B | | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MB30J106KE18 | 10uF | 6.3 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB31A106KE18 | 10uF | 10 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MB31A106ME18 | 10uF | 10 | B | | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM31MB31E225KA92 | 2.2uF | 25 | B | | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MB31H105KA87 | 1uF | 50 | B | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR11A225KA01 | 2.2uF | 10 | R | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR11C105KA01 | 1uF | 16 | R | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR11C225KA35 | 2.2uF | 16 | R | | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MR11C225MA35 | 2.2uF | 16 | R | | 3216M/1206 | 1.3 | +/-20% | General Purpose |
| GRM31MR11E105KA01 | 1uF | 25 | R | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR11E225KA93 | 2.2uF | 25 | R | | 3216M/1206 | 1.3 | +/-10% | General Purpose |
| GRM31MR11H154KA01 | 0.15uF | 50 | R | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR11H224KA01 | 0.22uF | 50 | R | | 3216M/1206 | 1.25 | +/-10% | General Purpose |
| GRM31MR11H224MA01 | 0.22uF | 50 | R | | 3216M/1206 | 1.25 | +/-20% | General Purpose |
| GRM32AB31C106KAB6 | 10uF | 16 | B | | 3225M/1210 | 1 | +/-10% | General Purpose |
| GRM32DB11C106KA01 | 10uF | 16 | B | | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DB11E475KA61 | 4.7uF | 25 | B | | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DB31E106KA75 | 10uF | 25 | B | | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR11C106KA01 | 10uF | 16 | R | | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32DR11E475KA61 | 4.7uF | 25 | R | | 3225M/1210 | 2.2 | +/-10% | General Purpose |
| GRM32EB11A106KA01 | 10uF | 10 | B | | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EB30J107ME16 | 100uF | 6.3 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EB30J476ME16 | 47uF | 6.3 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EB31A476KE20 | 47uF | 10 | B | | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EB31A476ME20 | 47uF | 10 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EB31C226ME16 | 22uF | 16 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EB31C476KE15 | 47uF | 16 | B | | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EB31C476ME15 | 47uF | 16 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EB31E226KE15 | 22uF | 25 | B | | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EB31E226ME15 | 22uF | 25 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EB31H106KA12 | 10uF | 50 | B | | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EB31H106MA12 | 10uF | 50 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32EB31H475KA87 | 4.7uF | 50 | B | | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EB3YA106KA12 | 10uF | 35 | B | | 3225M/1210 | 2.7 | +/-10% | General Purpose |
| GRM32EB3YA106MA12 | 10uF | 35 | B | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32ER11A226ME20 | 22uF | 10 | R | | 3225M/1210 | 2.7 | +/-20% | General Purpose |
| GRM32MB11C225KA01 | 2.2uF | 16 | B | | 3225M/1210 | 1.25 | +/-10% | General Purpose |
| GRM32MB11H474KA01 | 0.47uF | 50 | B | | 3225M/1210 | 1.25 | +/-10% | General Purpose |
| GRM32MB11H474MA01 | 0.47uF | 50 | B | | 3225M/1210 | 1.25 | +/-20% | General Purpose |
| GRM32MR11C225KA01 | 2.2uF | 16 | R | | 3225M/1210 | 1.25 | +/-10% | General Purpose |
| GRM32NB11H684KA01 | 0.68uF | 50 | B | | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32NB31A226KE19 | 22uF | 10 | B | | 3225M/1210 | 1.5 | +/-10% | General Purpose |
| GRM32NB31A226ME19 | 22uF | 10 | B | | 3225M/1210 | 1.5 | +/-20% | General Purpose |
| GRM32RB11C475KA01 | 4.7uF | 16 | B | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM32RB11E225KA01 | 2.2uF | 25 | B | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM32RB11H105KA01 | 1uF | 50 | B | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM32RR11C475KA01 | 4.7uF | 16 | R | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM32RR11H105KA01 | 1uF | 50 | R | | 3225M/1210 | 2 | +/-10% | General Purpose |
| GRM43EB11C226ME01 | 22uF | 16 | B | | 4532M/1812 | 2.7 | +/-20% | General Purpose |
| GRM43EB31H475KA88 | 4.7uF | 50 | B | | 4532M/1812 | 2.7 | +/-10% | General Purpose |
| GRM43ER11E475KA01 | 4.7uF | 25 | R | | 4532M/1812 | 2.7 | +/-10% | General Purpose |
| GRM43ER11H225KA01 | 2.2uF | 50 | R | | 4532M/1812 | 2.7 | +/-10% | General Purpose |
| GRM55DB11E106KA01 | 10uF | 25 | B | | 5750M/2220 | 2.1 | +/-10% | General Purpose |
| GRM55DB31H106KA87 | 10uF | 50 | B | | 5750M/2220 | 2.2 | +/-10% | General Purpose |
| GRM55DR11E106KA01 | 10uF | 25 | R | | 5750M/2220 | 2.1 | +/-10% | General Purpose |
| GRM55EB11H475KA01 | 4.7uF | 50 | B | | 5750M/2220 | 2.7 | +/-10% | General Purpose |
| GRM55ER11H475KA01 | 4.7uF | 50 | R | | 5750M/2220 | 2.7 | +/-10% | General Purpose |
| GRM55RB11H105KA01 | 1uF | 50 | B | | 5750M/2220 | 2 | +/-10% | General Purpose |
| GRM55RR11H105KA01 | 1uF | 50 | R | | 5750M/2220 | 2 | +/-10% | General Purpose |
| GXM155B31C105KA10 | 1uF | 16 | B | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ General Purpose |
| GXM155B31E105KA10 | 1uF | 25 | B | | 1005M/0402 | 0.55 | +/-10% | Water repellent/ General Purpose |
| GXM188B30J106ME47 | 10uF | 6.3 | B | | 1608M/0603 | 0.9 | +/-20% | Water repellent/ General Purpose |
| GXM188B31E225KA10 | 2.2uF | 25 | B | | 1608M/0603 | 0.9 | +/-10% | Water repellent/ General Purpose |
| GXM21BB31C106KE10 | 10uF | 16 | B | | 2012M/0805 | 1.35 | +/-10% | Water repellent/ General Purpose |
| GXM21BB31C106ME10 | 10uF | 16 | B | | 2012M/0805 | 1.35 | +/-20% | Water repellent/ General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|--------------------------|-------------------------|--------------------------------|------------------------------|---------------------|-------------------|----------------------------------|
| GXM21BB31E106KA73 | 10uF | 25 | B | 2012M/0805 | 1.4 | +/-10% | Water repellent/ General Purpose |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature | Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-------------|-----------------|------------------------|------------------|----------------|----------------------------------|
| GCM033R11A103KA01 | 10000pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11A152KA01 | 1500pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11A222KA01 | 2200pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11A332KA01 | 3300pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11A472KA01 | 4700pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11A682KA01 | 6800pF | 10 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11C222KA40 | 2200pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11C332KA40 | 3300pF | 16 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E101KA01 | 100pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E102KA01 | 1000pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E151KA01 | 150pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E152KA01 | 1500pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E221KA01 | 220pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E331KA01 | 330pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E471KA01 | 470pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM033R11E681KA01 | 680pF | 25 | R | | 0603M/0201 | 0.33 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11A104KA01 | 0.1uF | 10 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11C104KA40 | 0.1uF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11C333KA01 | 33000pF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11C473KA01 | 47000pF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11C683KA40 | 68000pF | 16 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11E103KA01 | 10000pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11E153KA40 | 15000pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11E223KA40 | 22000pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11E333KA40 | 33000pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11E473KA40 | 47000pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11E682KA01 | 6800pF | 25 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H102KA01 | 1000pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H103KA40 | 10000pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H152KA01 | 1500pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H221KA01 | 220pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H222KA01 | 2200pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H331KA01 | 330pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H332KA01 | 3300pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H471KA01 | 470pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H472KA01 | 4700pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H681KA01 | 680pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM155R11H682KA40 | 6800pF | 50 | R | | 1005M/0402 | 0.55 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11A224KA01 | 0.22uF | 10 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11C104KA01 | 0.1uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11C224KA01 | 0.22uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11C334KA01 | 0.33uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11C474KA40 | 0.47uF | 16 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E102KA01 | 1000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E103KA01 | 10000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E104KA42 | 0.1uF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E152KA01 | 1500pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E153KA01 | 15000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E154KA01 | 0.15uF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E222KA01 | 2200pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E223KA01 | 22000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E224KA40 | 0.22uF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E332KA01 | 3300pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E333KA01 | 33000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E472KA01 | 4700pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E473KA01 | 47000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E682KA01 | 6800pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11E683KA42 | 68000pF | 25 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H102KA01 | 1000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H103KA01 | 10000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H104KA42 | 0.1uF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H152KA01 | 1500pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H153KA01 | 15000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H222KA01 | 2200pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H223KA01 | 22000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H332KA01 | 3300pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H333KA40 | 33000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H472KA01 | 4700pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H473KA40 | 47000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H682KA01 | 6800pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM188R11H683KA42 | 68000pF | 50 | R | | 1608M/0603 | 0.9 | +/-10% | Powertrain/Safety for Automotive |
| GCM219R11A474KA01 | 0.47uF | 10 | R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM219R11C105KA01 | 1uF | 16 | R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM219R11C224KA01 | 0.22uF | 16 | R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM219R11C684KA01 | 0.68uF | 16 | R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM219R11E334KA01 | 0.33uF | 25 | R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |
| GCM219R11E474KA40 | 0.47uF | 25 | R | | 2012M/0805 | 0.95 | +/-10% | Powertrain/Safety for Automotive |

| Part Number | Capacitance (Nominal) | Rated Voltage (V) | Temperature Characteristics | Size Code (mm)/ (inch) | T size (mm Max.) | Cap. Tolerance | Type |
|-------------------|-----------------------|-------------------|-----------------------------|------------------------|------------------|----------------|----------------------------------|
| GCM21BR11A105KA01 | 1uF | 10 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11C474KA01 | 0.47uF | 16 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11E104KA01 | 0.1uF | 25 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11E105KA42 | 1uF | 25 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11E154KA01 | 0.15uF | 25 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11E224KA01 | 0.22uF | 25 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11E684KA40 | 0.68uF | 25 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11H104KA01 | 0.1uF | 50 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11H154KA01 | 0.15uF | 50 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11H224KA01 | 0.22uF | 50 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11H333KA01 | 33000pF | 50 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11H473KA01 | 47000pF | 50 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM21BR11H683KA01 | 68000pF | 50 | R | 2012M/0805 | 1.4 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR11A106KA49 | 10uF | 10 | R | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR11C475KA01 | 4.7uF | 16 | R | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31CR11H684KA01 | 0.68uF | 50 | R | 3216M/1206 | 1.8 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR11A225KA36 | 2.2uF | 10 | R | 3216M/1206 | 1.3 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR11C105KA01 | 1uF | 16 | R | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR11C225KA36 | 2.2uF | 16 | R | 3216M/1206 | 1.3 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR11E105KA01 | 1uF | 25 | R | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR11E225KA42 | 2.2uF | 25 | R | 3216M/1206 | 1.3 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR11H334KA01 | 0.33uF | 50 | R | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive |
| GCM31MR11H474KA01 | 0.47uF | 50 | R | 3216M/1206 | 1.25 | +/-10% | Powertrain/Safety for Automotive |
| GCM32DR11C106KA01 | 10uF | 16 | R | 3225M/1210 | 2.2 | +/-10% | Powertrain/Safety for Automotive |
| GCM32DR11E475KA40 | 4.7uF | 25 | R | 3225M/1210 | 2.2 | +/-10% | Powertrain/Safety for Automotive |
| GCM32ER11A226KE11 | 22uF | 10 | R | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32ER11A226ME11 | 22uF | 10 | R | 3225M/1210 | 2.7 | +/-20% | Powertrain/Safety for Automotive |
| GCM32ER11H105KA01 | 1uF | 50 | R | 3225M/1210 | 2.7 | +/-10% | Powertrain/Safety for Automotive |
| GCM32RR11E105KA01 | 1uF | 25 | R | 3225M/1210 | 2 | +/-10% | Powertrain/Safety for Automotive |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|-------------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------|
| 1239AS-H-100M | 10 | 1008/2520 | 1.2 | 850 | 1000 | 0.4 | 0.46 | General |
| 1239AS-H-1R0M | 1 | 1008/2520 | 1.2 | 3000 | 3000 | 0.045 | 0.059 | General |
| 1239AS-H-1R5M | 1.5 | 1008/2520 | 1.2 | 2400 | 2600 | 0.06 | 0.072 | General |
| 1239AS-H-2R2M | 2.2 | 1008/2520 | 1.2 | 2000 | 2200 | 0.09 | 0.108 | General |
| 1239AS-H-3R3M | 3.3 | 1008/2520 | 1.2 | 1500 | 1800 | 0.12 | 0.144 | General |
| 1239AS-H-4R7M | 4.7 | 1008/2520 | 1.2 | 1300 | 1500 | 0.2 | 0.24 | General |
| 1239AS-H-6R0M | 6 | 1008/2520 | 1.2 | 1100 | 1400 | 0.24 | 0.275 | General |
| 1239AS-H-6R8M | 6.8 | 1008/2520 | 1.2 | 1000 | 1300 | 0.31 | 0.375 | General |
| 1239AS-H-R47M | 0.47 | 1008/2520 | 1.2 | 3700 | 3800 | 0.029 | 0.039 | General |
| 1269AS-H-100N | 10 | 1008/2520 | 1 | 680 | 1000 | 0.53 | 0.689 | General |
| 1269AS-H-1R0M | 1 | 1008/2520 | 1 | 2500 | 2700 | 0.06 | 0.078 | General |
| 1269AS-H-1R5M | 1.5 | 1008/2520 | 1 | 1900 | 2100 | 0.09 | 0.108 | General |
| 1269AS-H-2R2M | 2.2 | 1008/2520 | 1 | 1500 | 1900 | 0.13 | 0.156 | General |
| 1269AS-H-3R3M | 3.3 | 1008/2520 | 1 | 1200 | 1500 | 0.19 | 0.228 | General |
| 1269AS-H-4R7M | 4.7 | 1008/2520 | 1 | 1000 | 1300 | 0.25 | 0.3 | General |
| 1269AS-H-6R8M | 6.8 | 1008/2520 | 1 | 760 | 1100 | 0.43 | 0.516 | General |
| 1269AS-H-R47M | 0.47 | 1008/2520 | 1 | 3100 | 3500 | 0.035 | 0.046 | General |
| 1276AS-H-100M | 10 | 1210/3225 | 1 | 800 | 1000 | 0.49 | 0.588 | General |
| 1276AS-H-1R0M | 1 | 1210/3225 | 1 | 2600 | 3100 | 0.048 | 0.062 | General |
| 1276AS-H-1R5M | 1.5 | 1210/3225 | 1 | 2100 | 2600 | 0.072 | 0.087 | General |
| 1276AS-H-2R2M | 2.2 | 1210/3225 | 1 | 1600 | 2200 | 0.098 | 0.118 | General |
| 1276AS-H-3R3M | 3.3 | 1210/3225 | 1 | 1400 | 1800 | 0.158 | 0.19 | General |
| 1276AS-H-4R7M | 4.7 | 1210/3225 | 1 | 1200 | 1600 | 0.22 | 0.264 | General |
| 1276AS-H-6R8M | 6.8 | 1210/3225 | 1 | 1000 | 1300 | 0.315 | 0.378 | General |
| 1276AS-H-R47M | 0.47 | 1210/3225 | 1 | 3300 | 3800 | 0.028 | 0.038 | General |
| 1276AS-H-R68M | 0.68 | 1210/3225 | 1 | 2900 | 3500 | 0.035 | 0.045 | General |
| 1285AS-H-1R0M | 1 | 0806/2016 | 1 | 2000 | 2200 | 0.08 | 0.096 | General |
| 1285AS-H-1R5M | 1.5 | 0806/2016 | 1 | 1600 | 1800 | 0.12 | 0.144 | General |
| 1285AS-H-2R2M | 2.2 | 0806/2016 | 1 | 1200 | 1500 | 0.17 | 0.204 | General |
| 1285AS-H-R56M | 0.56 | 0806/2016 | 1 | 2800 | 2800 | 0.044 | 0.059 | General |
| 1285AS-H-R68M | 0.68 | 0806/2016 | 1 | 2500 | 2600 | 0.055 | 0.072 | General |
| 1286AS-H-1R0M | 1 | 0806/2016 | 1.2 | 2300 | 2500 | 0.068 | 0.082 | General |
| 1286AS-H-1R5M | 1.5 | 0806/2016 | 1.2 | 1800 | 2000 | 0.095 | 0.114 | General |
| 1286AS-H-2R2M | 2.2 | 0806/2016 | 1.2 | 1300 | 1600 | 0.16 | 0.192 | General |
| 1286AS-H-R47M | 0.47 | 0806/2016 | 1.2 | 3200 | 3400 | 0.04 | 0.052 | General |
| DFE18SAN1R0ME0 | 1 | 0603/1608 | 0.8 | 1600 | 2000 | 0.12 | 0.144 | General |
| DFE18SANR24ME0 | 0.24 | 0603/1608 | 0.8 | 3200 | 4200 | 0.03 | 0.036 | General |
| DFE18SANR47ME0 | 0.47 | 0603/1608 | 0.8 | 2400 | 3100 | 0.053 | 0.064 | General |
| DFE18SANR56ME0 | 0.56 | 0603/1608 | 0.8 | 2200 | 2600 | 0.067 | 0.07 | General |
| DFE18SBN1R0ME0 | 1 | 0603/1608 | 0.8 | 1800 | 1900 | 0.1 | 0.12 | General |
| DFE18SBNR47ME0 | 0.47 | 0603/1608 | 0.8 | 2400 | 3100 | 0.051 | 0.06 | General |
| DFE201610E-100M | 10 | 0806/2016 | 1 | 650 | 1000 | 0.65 | 0.78 | General |
| DFE201610E-1R0M | 1 | 0806/2016 | 1 | 2700 | 3600 | 0.048 | 0.057 | General |
| DFE201610E-1R5M | 1.5 | 0806/2016 | 1 | 2100 | 2900 | 0.076 | 0.091 | General |
| DFE201610E-2R2M | 2.2 | 0806/2016 | 1 | 1700 | 2400 | 0.117 | 0.14 | General |
| DFE201610E-4R7M | 4.7 | 0806/2016 | 1 | 1100 | 1600 | 0.24 | 0.288 | General |
| DFE201610E-R24M | 0.24 | 0806/2016 | 1 | 4700 | 6300 | 0.016 | 0.02 | General |
| DFE201610E-R33M | 0.33 | 0806/2016 | 1 | 4000 | 5500 | 0.021 | 0.026 | General |
| DFE201610E-R47M | 0.47 | 0806/2016 | 1 | 3600 | 4800 | 0.026 | 0.032 | General |
| DFE201610E-R68M | 0.68 | 0806/2016 | 1 | 3100 | 4300 | 0.036 | 0.043 | General |
| DFE201610P-1R0M | 1 | 0806/2016 | 1 | 2200 | 3100 | 0.058 | 0.07 | General |
| DFE201610P-1R5M | 1.5 | 0806/2016 | 1 | 1800 | 2500 | 0.092 | 0.11 | General |
| DFE201610P-2R2M | 2.2 | 0806/2016 | 1 | 1400 | 2000 | 0.14 | 0.168 | General |
| DFE201610P-R24M | 0.24 | 0806/2016 | 1 | 3800 | 5400 | 0.02 | 0.026 | General |
| DFE201610P-R33M | 0.33 | 0806/2016 | 1 | 3500 | 4700 | 0.026 | 0.034 | General |
| DFE201610P-R47M | 0.47 | 0806/2016 | 1 | 3100 | 4000 | 0.032 | 0.04 | General |
| DFE201610P-R68M | 0.68 | 0806/2016 | 1 | 2700 | 3600 | 0.04 | 0.048 | General |
| DFE201610R-H-1R0M | 1 | 0806/2016 | 1 | 2100 | 2200 | 0.066 | 0.079 | General |
| DFE201610R-H-1R5M | 1.5 | 0806/2016 | 1 | 1800 | 1800 | 0.098 | 0.118 | General |
| DFE201610R-H-2R2M | 2.2 | 0806/2016 | 1 | 1400 | 1600 | 0.14 | 0.168 | General |
| DFE201610R-H-R47M | 0.47 | 0806/2016 | 1 | 2800 | 3000 | 0.037 | 0.048 | General |
| DFE201612E-1R0M | 1 | 0806/2016 | 1.2 | 2900 | 4000 | 0.04 | 0.048 | General |
| DFE201612E-1R5M | 1.5 | 0806/2016 | 1.2 | 2300 | 3200 | 0.06 | 0.072 | General |
| DFE201612E-2R2M | 2.2 | 0806/2016 | 1.2 | 1800 | 2400 | 0.097 | 0.116 | General |
| DFE201612E-4R7M | 4.7 | 0806/2016 | 1.2 | 1200 | 1800 | 0.21 | 0.252 | General |
| DFE201612E-R24M | 0.24 | 0806/2016 | 1.2 | 5000 | 6600 | 0.013 | 0.019 | General |
| DFE201612E-R33M | 0.33 | 0806/2016 | 1.2 | 4800 | 6300 | 0.015 | 0.021 | General |
| DFE201612E-R47M | 0.47 | 0806/2016 | 1.2 | 4500 | 5500 | 0.02 | 0.026 | General |
| DFE201612E-R68M | 0.68 | 0806/2016 | 1.2 | 3500 | 4300 | 0.027 | 0.033 | General |
| DFE201612P-1R0M | 1 | 0806/2016 | 1.2 | 2700 | 3300 | 0.045 | 0.054 | General |
| DFE201612P-1R5M | 1.5 | 0806/2016 | 1.2 | 2000 | 2700 | 0.078 | 0.095 | General |
| DFE201612P-2R2M | 2.2 | 0806/2016 | 1.2 | 1500 | 2100 | 0.12 | 0.144 | General |
| DFE201612P-R24M | 0.24 | 0806/2016 | 1.2 | 4400 | 6500 | 0.015 | 0.023 | General |
| DFE201612P-R33M | 0.33 | 0806/2016 | 1.2 | 3900 | 5600 | 0.021 | 0.028 | General |
| DFE201612P-R47M | 0.47 | 0806/2016 | 1.2 | 3700 | 4800 | 0.025 | 0.033 | General |
| DFE201612R-H-1R0M | 1 | 0806/2016 | 1.2 | 2600 | 2600 | 0.054 | 0.07 | General |
| DFE201612R-H-1R5M | 1.5 | 0806/2016 | 1.2 | 2000 | 2100 | 0.078 | 0.094 | General |
| DFE201612R-H-2R2M | 2.2 | 0806/2016 | 1.2 | 1400 | 1700 | 0.128 | 0.154 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturatio} n (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Applicatio |
|-------------------|-----------------|---------------------|------------------|-------------------------|-------------------------------|----------------|----------------|------------|
| DFE201612R-H-R47M | 0.47 | 0806/2016 | 1.2 | 3200 | 3500 | 0.029 | 0.04 | General |
| DFE252008C-1R0M | 1 | 1008/2520 | 0.8 | 1400 | 2300 | 0.07 | 0.084 | General |
| DFE252008C-1R5M | 1.5 | 1008/2520 | 0.8 | 1200 | 2000 | 0.105 | 0.126 | General |
| DFE252008C-2R2M | 2.2 | 1008/2520 | 0.8 | 950 | 1600 | 0.15 | 0.18 | General |
| DFE252008C-3R3M | 3.3 | 1008/2520 | 0.8 | 850 | 1300 | 0.21 | 0.252 | General |
| DFE252008C-4R7M | 4.7 | 1008/2520 | 0.8 | 650 | 1100 | 0.365 | 0.438 | General |
| DFE252008C-R47M | 0.47 | 1008/2520 | 0.8 | 2000 | 3000 | 0.046 | 0.06 | General |
| DFE252010F-100M | 10 | 1008/2520 | 1 | 900 | 1300 | 0.5 | 0.6 | General |
| DFE252010F-1R0M | 1 | 1008/2520 | 1 | 3100 | 4100 | 0.04 | 0.048 | General |
| DFE252010F-1R5M | 1.5 | 1008/2520 | 1 | 2500 | 3400 | 0.06 | 0.072 | General |
| DFE252010F-2R2M | 2.2 | 1008/2520 | 1 | 2300 | 3100 | 0.085 | 0.097 | General |
| DFE252010F-3R3M | 3.3 | 1008/2520 | 1 | 1600 | 2200 | 0.14 | 0.17 | General |
| DFE252010F-4R7M | 4.7 | 1008/2520 | 1 | 1400 | 1900 | 0.2 | 0.24 | General |
| DFE252010F-6R8M | 6.8 | 1008/2520 | 1 | 1100 | 1400 | 0.35 | 0.42 | General |
| DFE252010F-8R2M | 8.2 | 1008/2520 | 1 | 1000 | 1350 | 0.43 | 0.52 | General |
| DFE252010F-R33M | 0.33 | 1008/2520 | 1 | 4800 | 6800 | 0.016 | 0.021 | General |
| DFE252010F-R47M | 0.47 | 1008/2520 | 1 | 4400 | 6000 | 0.02 | 0.027 | General |
| DFE252010F-R68M | 0.68 | 1008/2520 | 1 | 3500 | 5000 | 0.031 | 0.037 | General |
| DFE252010F-R82M | 0.82 | 1008/2520 | 1 | 3300 | 4500 | 0.033 | 0.04 | General |
| DFE252010P-1R0M | 1 | 1008/2520 | 1 | 2700 | 3800 | 0.045 | 0.054 | General |
| DFE252010P-1R2M | 1.2 | 1008/2520 | 1 | 2400 | 3200 | 0.057 | 0.068 | General |
| DFE252010P-1R5M | 1.5 | 1008/2520 | 1 | 2100 | 3000 | 0.068 | 0.082 | General |
| DFE252010P-2R2M | 2.2 | 1008/2520 | 1 | 1700 | 2600 | 0.096 | 0.115 | General |
| DFE252010P-3R3M | 3.3 | 1008/2520 | 1 | 1400 | 2100 | 0.16 | 0.195 | General |
| DFE252010P-4R7M | 4.7 | 1008/2520 | 1 | 1100 | 1700 | 0.22 | 0.27 | General |
| DFE252010P-R33M | 0.33 | 1008/2520 | 1 | 3800 | 5700 | 0.022 | 0.029 | General |
| DFE252010P-R47M | 0.47 | 1008/2520 | 1 | 3500 | 5000 | 0.027 | 0.035 | General |
| DFE252010P-R68M | 0.68 | 1008/2520 | 1 | 3000 | 4100 | 0.04 | 0.048 | General |
| DFE252010R-H-1R0M | 1 | 1008/2520 | 1 | 2700 | 3000 | 0.052 | 0.068 | General |
| DFE252010R-H-1R5M | 1.5 | 1008/2520 | 1 | 2100 | 2300 | 0.075 | 0.09 | General |
| DFE252010R-H-2R2M | 2.2 | 1008/2520 | 1 | 1700 | 2100 | 0.105 | 0.126 | General |
| DFE252010R-H-4R7M | 4.7 | 1008/2520 | 1 | 1100 | 1400 | 0.23 | 0.276 | General |
| DFE252012F-100M | 10 | 1008/2520 | 1.2 | 950 | 1400 | 0.4 | 0.48 | General |
| DFE252012F-1R0M | 1 | 1008/2520 | 1.2 | 3300 | 4700 | 0.033 | 0.04 | General |
| DFE252012F-1R5M | 1.5 | 1008/2520 | 1.2 | 2700 | 3800 | 0.048 | 0.058 | General |
| DFE252012F-2R2M | 2.2 | 1008/2520 | 1.2 | 2300 | 3300 | 0.068 | 0.082 | General |
| DFE252012F-3R3M | 3.3 | 1008/2520 | 1.2 | 1800 | 2500 | 0.11 | 0.135 | General |
| DFE252012F-4R7M | 4.7 | 1008/2520 | 1.2 | 1500 | 2100 | 0.16 | 0.19 | General |
| DFE252012F-6R8M | 6.8 | 1008/2520 | 1.2 | 1200 | 1700 | 0.27 | 0.33 | General |
| DFE252012F-8R2M | 8.2 | 1008/2520 | 1.2 | 1100 | 1500 | 0.34 | 0.41 | General |
| DFE252012F-R33M | 0.33 | 1008/2520 | 1.2 | 5100 | 7600 | 0.014 | 0.019 | General |
| DFE252012F-R47M | 0.47 | 1008/2520 | 1.2 | 4900 | 6700 | 0.017 | 0.023 | General |
| DFE252012F-R68M | 0.68 | 1008/2520 | 1.2 | 3900 | 5400 | 0.025 | 0.031 | General |
| DFE252012F-R82M | 0.82 | 1008/2520 | 1.2 | 3600 | 4900 | 0.029 | 0.035 | General |
| DFE252012P-1R0M | 1 | 1008/2520 | 1.2 | 3200 | 4300 | 0.035 | 0.042 | General |
| DFE252012P-1R5M | 1.5 | 1008/2520 | 1.2 | 2600 | 3500 | 0.05 | 0.06 | General |
| DFE252012P-2R2M | 2.2 | 1008/2520 | 1.2 | 2200 | 3000 | 0.07 | 0.084 | General |
| DFE252012P-3R3M | 3.3 | 1008/2520 | 1.2 | 1700 | 2300 | 0.115 | 0.14 | General |
| DFE252012P-4R7M | 4.7 | 1008/2520 | 1.2 | 1400 | 2000 | 0.165 | 0.2 | General |
| DFE252012P-R33M | 0.33 | 1008/2520 | 1.2 | 4600 | 6600 | 0.017 | 0.023 | General |
| DFE252012P-R47M | 0.47 | 1008/2520 | 1.2 | 4000 | 5700 | 0.021 | 0.027 | General |
| DFE252012P-R68M | 0.68 | 1008/2520 | 1.2 | 3500 | 4800 | 0.03 | 0.037 | General |
| DFE252012R-H-1R0M | 1 | 1008/2520 | 1.2 | 3100 | 3400 | 0.038 | 0.049 | General |
| DFE252012R-H-1R5M | 1.5 | 1008/2520 | 1.2 | 2500 | 2800 | 0.053 | 0.065 | General |
| DFE252012R-H-2R2M | 2.2 | 1008/2520 | 1.2 | 2000 | 2400 | 0.075 | 0.09 | General |
| DFE252012R-H-4R7M | 4.7 | 1008/2520 | 1.2 | 1400 | 1700 | 0.18 | 0.216 | General |
| DFE322512F-100M | 10 | 1210/3225 | 1.2 | 1100 | 1700 | 0.27 | 0.324 | General |
| DFE322512F-1R0M | 1 | 1210/3225 | 1.2 | 3800 | 4800 | 0.026 | 0.032 | General |
| DFE322512F-1R5M | 1.5 | 1210/3225 | 1.2 | 3000 | 3900 | 0.04 | 0.048 | General |
| DFE322512F-2R2M | 2.2 | 1210/3225 | 1.2 | 2600 | 3400 | 0.055 | 0.066 | General |
| DFE322512F-3R3M | 3.3 | 1210/3225 | 1.2 | 2000 | 2600 | 0.09 | 0.108 | General |
| DFE322512F-4R7M | 4.7 | 1210/3225 | 1.2 | 1600 | 2300 | 0.131 | 0.157 | General |
| DFE322512F-6R8M | 6.8 | 1210/3225 | 1.2 | 1200 | 2000 | 0.183 | 0.22 | General |
| DFE322512F-R47M | 0.47 | 1210/3225 | 1.2 | 4800 | 6700 | 0.017 | 0.023 | General |
| DFE322512F-R68M | 0.68 | 1210/3225 | 1.2 | 4400 | 6100 | 0.02 | 0.026 | General |
| FDSD0412-H-1R0M | 1 | 1515/4040 | 1.2 | 4300 | 4700 | 0.037 | 0.044 | General |
| FDSD0412-H-1R2M | 1.2 | 1515/4040 | 1.2 | 3700 | 4500 | 0.04 | 0.048 | General |
| FDSD0412-H-1R5M | 1.5 | 1515/4040 | 1.2 | 3300 | 4100 | 0.053 | 0.064 | General |
| FDSD0412-H-2R2M | 2.2 | 1515/4040 | 1.2 | 2800 | 3500 | 0.07 | 0.084 | General |
| FDSD0412-H-3R3M | 3.3 | 1515/4040 | 1.2 | 2200 | 2800 | 0.102 | 0.122 | General |
| FDSD0412-H-4R7M | 4.7 | 1515/4040 | 1.2 | 1900 | 2500 | 0.136 | 0.161 | General |
| FDSD0412-H-R33M | 0.33 | 1515/4040 | 1.2 | 6400 | 7500 | 0.016 | 0.019 | General |
| FDSD0412-H-R47M | 0.47 | 1515/4040 | 1.2 | 6000 | 6500 | 0.019 | 0.023 | General |
| FDSD0415-H-1R0M | 1 | 1515/4040 | 1.5 | 4500 | 5300 | 0.034 | 0.041 | General |
| FDSD0415-H-1R5M | 1.5 | 1515/4040 | 1.5 | 3700 | 5000 | 0.039 | 0.047 | General |
| FDSD0415-H-2R2M | 2.2 | 1515/4040 | 1.5 | 3100 | 4100 | 0.054 | 0.065 | General |
| FDSD0415-H-3R3M | 3.3 | 1515/4040 | 1.5 | 2600 | 3400 | 0.079 | 0.095 | General |
| FDSD0415-H-4R7M | 4.7 | 1515/4040 | 1.5 | 2100 | 2900 | 0.1 | 0.12 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|-----------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------|
| FDSD0415-H-R22M | 0.22 | 1515/4040 | 1.5 | 7700 | 12000 | 0.011 | 0.014 | General |
| FDSD0415-H-R47M | 0.47 | 1515/4040 | 1.5 | 6100 | 9000 | 0.015 | 0.018 | General |
| FDSD0420D-1R0M | 1 | 1515/4040 | 2 | 5100 | 6800 | 0.024 | 0.029 | General |
| FDSD0420D-1R5M | 1.5 | 1515/4040 | 2 | 4300 | 5700 | 0.03 | 0.036 | General |
| FDSD0420D-2R2M | 2.2 | 1515/4040 | 2 | 3600 | 4100 | 0.039 | 0.047 | General |
| FDSD0420D-3R3M | 3.3 | 1515/4040 | 2 | 2900 | 3700 | 0.059 | 0.071 | General |
| FDSD0420D-4R7M | 4.7 | 1515/4040 | 2 | 2700 | 3600 | 0.0047 | 0.083 | General |
| FDSD0420D-R33M | 0.33 | 1515/4040 | 2 | 770 | 11000 | 0.012 | 0.014 | General |
| FDSD0420D-R47M | 0.47 | 1515/4040 | 2 | 6800 | 9400 | 0.015 | 0.018 | General |
| FDSD0420D-R68M | 0.68 | 1515/4040 | 2 | 6500 | 8300 | 0.018 | 0.022 | General |
| FDSD0420-H-1R0M | 1 | 1515/4040 | 2 | 5100 | 6800 | 0.024 | 0.029 | General |
| FDSD0420-H-1R5M | 1.5 | 1515/4040 | 2 | 4300 | 5700 | 0.03 | 0.036 | General |
| FDSD0420-H-2R2M | 2.2 | 1515/4040 | 2 | 3600 | 4100 | 0.039 | 0.047 | General |
| FDSD0420-H-3R3M | 3.3 | 1515/4040 | 2 | 2900 | 3700 | 0.059 | 0.071 | General |
| FDSD0420-H-4R7M | 4.7 | 1515/4040 | 2 | 2700 | 3600 | 0.069 | 0.083 | General |
| FDSD0420-H-R33M | 0.33 | 1515/4040 | 2 | 7700 | 11000 | 0.012 | 0.014 | General |
| FDSD0420-H-R47M | 0.47 | 1515/4040 | 2 | 6800 | 9400 | 0.015 | 0.018 | General |
| FDSD0420-H-R68M | 0.68 | 1515/4040 | 2 | 6500 | 8300 | 0.018 | 0.022 | General |
| FDSD0518-H-100M | 10 | 2019/5249 | 1.8 | 2400 | 2700 | 0.128 | 0.15 | General |
| FDSD0518-H-1R0M | 1 | 2019/5249 | 1.8 | 6100 | 8700 | 0.018 | 0.021 | General |
| FDSD0518-H-1R5M | 1.5 | 2019/5249 | 1.8 | 5300 | 6700 | 0.024 | 0.029 | General |
| FDSD0518-H-2R2M | 2.2 | 2019/5249 | 1.8 | 4300 | 5400 | 0.033 | 0.04 | General |
| FDSD0518-H-3R3M | 3.3 | 2019/5249 | 1.8 | 3400 | 4600 | 0.051 | 0.058 | General |
| FDSD0518-H-4R7M | 4.7 | 2019/5249 | 1.8 | 3000 | 3900 | 0.064 | 0.073 | General |
| FDSD0518-H-6R8M | 6.8 | 2019/5249 | 1.8 | 2600 | 2900 | 0.088 | 0.106 | General |
| FDSD0518-H-R68M | 0.68 | 2019/5249 | 1.8 | 6800 | 9000 | 0.016 | 0.019 | General |
| FDSD0630-H-100M | 10 | 2726/7066 | 3 | 3200 | 5400 | 0.062 | 0.074 | General |
| FDSD0630-H-1R0M | 1 | 2726/7066 | 3 | 9400 | 15000 | 0.009 | 0.011 | General |
| FDSD0630-H-1R5M | 1.5 | 2726/7066 | 3 | 8500 | 13000 | 0.011 | 0.013 | General |
| FDSD0630-H-2R2M | 2.2 | 2726/7066 | 3 | 7100 | 12000 | 0.014 | 0.017 | General |
| FDSD0630-H-3R3M | 3.3 | 2726/7066 | 3 | 5600 | 8000 | 0.023 | 0.028 | General |
| FDSD0630-H-4R7M | 4.7 | 2726/7066 | 3 | 4700 | 7600 | 0.033 | 0.04 | General |
| FDSD0630-H-5R6M | 5.6 | 2726/7066 | 3 | 4100 | 7000 | 0.038 | 0.046 | General |
| FDSD0630-H-6R8M | 6.8 | 2726/7066 | 3 | 3700 | 5900 | 0.051 | 0.061 | General |
| FDSD0630-H-8R2M | 8.2 | 2726/7066 | 3 | 3400 | 5500 | 0.058 | 0.07 | General |
| FDUE0630-H-R12M | 0.12 | 3026/7667 | 3 | 36000 | 33000 | 0.00058 | 0.0006206 | General |
| FDUE0630-H-R24M | 0.24 | 3026/7667 | 3 | 27000 | 23000 | 0.00112 | 0.0011984 | General |
| FDV0530S-H-1R0M | 1 | 2020/5050 | 3 | 5700 | 6200 | 0.015 | 0.017 | General |
| FDV0530S-H-1R5M | 1.5 | 2020/5050 | 3 | 4900 | 5400 | 0.021 | 0.024 | General |
| FDV0530S-H-2R2M | 2.2 | 2020/5050 | 3 | 4300 | 4500 | 0.03 | 0.034 | General |
| FDV0530S-H-R12M | 0.12 | 2020/5050 | 3 | 13000 | 18000 | 0.0034 | 0.0039 | General |
| FDV0530S-H-R24M | 0.24 | 2020/5050 | 3 | 11000 | 13000 | 0.0049 | 0.0056 | General |
| FDV0530S-H-R42M | 0.42 | 2020/5050 | 3 | 8200 | 9000 | 0.0085 | 0.0098 | General |
| FDV0530S-H-R60M | 0.6 | 2020/5050 | 3 | 7200 | 7900 | 0.01 | 0.012 | General |
| FDV0530S-H-R78M | 0.78 | 2020/5050 | 3 | 6900 | 7100 | 0.012 | 0.014 | General |
| FDVE0640-H-1R5M | 1.5 | 2926/7467 | 4 | 8200 | 8000 | 0.0088 | 0.0103 | General |
| FDVE0640-H-2R2M | 2.2 | 2926/7467 | 4 | 6500 | 7600 | 0.0139 | 0.0163 | General |
| FDVE0640-H-3R3M | 3.3 | 2926/7467 | 4 | 5600 | 6000 | 0.0167 | 0.0192 | General |
| FDVE0640-H-4R7M | 4.7 | 2926/7467 | 4 | 5000 | 4600 | 0.0254 | 0.0292 | General |
| LQH2HPN100MDR | 10 | 1008/2520 | 0.6 | 430 | 420 | 1.2 | 1.44 | General |
| LQH2HPN100MG0 | 10 | 1008/2520 | 1 | 490 | 700 | 0.73 | 0.876 | General |
| LQH2HPN100MGR | 10 | 1008/2520 | 1 | 710 | 700 | 0.56 | 0.672 | General |
| LQH2HPN100MJ0 | 10 | 1008/2520 | 1.2 | 550 | 820 | 0.641 | 0.77 | General |
| LQH2HPN100MJR | 10 | 1008/2520 | 1.2 | 830 | 830 | 0.38 | 0.456 | General |
| LQH2HPN101MG0 | 100 | 1008/2520 | 1 | 130 | 210 | 10 | 12 | General |
| LQH2HPN101MGR | 100 | 1008/2520 | 1 | 150 | 210 | 5.9 | 7.08 | General |
| LQH2HPN150MDR | 15 | 1008/2520 | 0.6 | 290 | 340 | 2.5 | 3 | General |
| LQH2HPN150MGR | 15 | 1008/2520 | 1 | 560 | 570 | 0.925 | 1.11 | General |
| LQH2HPN150MJR | 15 | 1008/2520 | 1.2 | 710 | 690 | 0.55 | 0.66 | General |
| LQH2HPN1R0MDR | 1 | 1008/2520 | 0.6 | 960 | 1370 | 0.24 | 0.288 | General |
| LQH2HPN1R0MGR | 1 | 1008/2520 | 1 | 2100 | 2130 | 0.068 | 0.0816 | General |
| LQH2HPN1R0NJR | 1 | 1008/2520 | 1.2 | 2400 | 2600 | 0.048 | 0.0576 | General |
| LQH2HPN1R2NJR | 1.2 | 1008/2520 | 1.2 | 2070 | 2450 | 0.055 | 0.066 | General |
| LQH2HPN1R5MDR | 1.5 | 1008/2520 | 0.6 | 900 | 1120 | 0.29 | 0.348 | General |
| LQH2HPN1R5MGR | 1.5 | 1008/2520 | 1 | 1850 | 1700 | 0.087 | 0.1044 | General |
| LQH2HPN1R5NJ0 | 1.5 | 1008/2520 | 1.2 | 1500 | 2400 | 0.096 | 0.116 | General |
| LQH2HPN1R5NJR | 1.5 | 1008/2520 | 1.2 | 1810 | 2200 | 0.075 | 0.09 | General |
| LQH2HPN220MDR | 22 | 1008/2520 | 0.6 | 270 | 260 | 3 | 3.6 | General |
| LQH2HPN220MG0 | 22 | 1008/2520 | 1 | 340 | 490 | 1.6 | 1.92 | General |
| LQH2HPN220MGR | 22 | 1008/2520 | 1 | 430 | 460 | 1.36 | 1.632 | General |
| LQH2HPN220MJR | 22 | 1008/2520 | 1.2 | 540 | 530 | 0.84 | 1.008 | General |
| LQH2HPN2R2MDR | 2.2 | 1008/2520 | 0.6 | 820 | 850 | 0.34 | 0.408 | General |
| LQH2HPN2R2MG0 | 2.2 | 1008/2520 | 1 | 1000 | 1640 | 0.17 | 0.204 | General |
| LQH2HPN2R2MGR | 2.2 | 1008/2520 | 1 | 1470 | 1550 | 0.134 | 0.1608 | General |
| LQH2HPN2R2MJ0 | 2.2 | 1008/2520 | 1.2 | 1300 | 1800 | 0.132 | 0.159 | General |
| LQH2HPN2R2MJR | 2.2 | 1008/2520 | 1.2 | 1650 | 1700 | 0.092 | 0.1104 | General |
| LQH2HPN2R2MM0 | 2.2 | 1008/2520 | 1.5 | 1250 | 1700 | 0.146 | 0.176 | General |
| LQH2HPN3R3MDR | 3.3 | 1008/2520 | 0.6 | 730 | 750 | 0.45 | 0.54 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------|
| LQH2HPN3R3MG0 | 3.3 | 1008/2520 | 1 | 810 | 1290 | 0.27 | 0.324 | General |
| LQH2HPN3R3MGR | 3.3 | 1008/2520 | 1 | 1100 | 1230 | 0.225 | 0.27 | General |
| LQH2HPN3R3MJ0 | 3.3 | 1008/2520 | 1.2 | 950 | 1500 | 0.23 | 0.276 | General |
| LQH2HPN3R3MJR | 3.3 | 1008/2520 | 1.2 | 1420 | 1450 | 0.13 | 0.156 | General |
| LQH2HPN4R7MDR | 4.7 | 1008/2520 | 0.6 | 650 | 650 | 0.56 | 0.672 | General |
| LQH2HPN4R7MG0 | 4.7 | 1008/2520 | 1 | 700 | 1000 | 0.36 | 0.432 | General |
| LQH2HPN4R7MGR | 4.7 | 1008/2520 | 1 | 1000 | 1090 | 0.3 | 0.36 | General |
| LQH2HPN4R7MJ0 | 4.7 | 1008/2520 | 1.2 | 700 | 1250 | 0.33 | 0.396 | General |
| LQH2HPN4R7MJR | 4.7 | 1008/2520 | 1.2 | 1290 | 1230 | 0.17 | 0.204 | General |
| LQH2HPN4R7NM0 | 4.7 | 1008/2520 | 1.5 | 800 | 1200 | 0.342 | 0.411 | General |
| LQH2HPN6R8MDR | 6.8 | 1008/2520 | 0.6 | 490 | 550 | 1 | 1.2 | General |
| LQH2HPN6R8MG0 | 6.8 | 1008/2520 | 1 | 590 | 800 | 0.5 | 0.6 | General |
| LQH2HPN6R8MGR | 6.8 | 1008/2520 | 1 | 860 | 830 | 0.395 | 0.474 | General |
| LQH2HPN6R8MJ0 | 6.8 | 1008/2520 | 1.2 | 600 | 1100 | 0.448 | 0.538 | General |
| LQH2HPN6R8MJR | 6.8 | 1008/2520 | 1.2 | 1000 | 1050 | 0.26 | 0.312 | General |
| LQH2HPNR47MDR | 0.47 | 1008/2520 | 0.6 | 1250 | 1670 | 0.14 | 0.168 | General |
| LQH2HPNR47MGR | 0.47 | 1008/2520 | 1 | 2520 | 2900 | 0.045 | 0.054 | General |
| LQH2HPNR47NJR | 0.47 | 1008/2520 | 1.2 | 2750 | 3500 | 0.031 | 0.0372 | General |
| LQH2HPNR68MGR | 0.68 | 1008/2520 | 1 | 2330 | 2430 | 0.055 | 0.066 | General |
| LQH2MCN100K02 | 10 | 0806/2016 | 0.95 | 225 | | 1.2 | 1.56 | General |
| LQH2MCN100M52 | 10 | 0806/2016 | 0.7 | 200 | | 2.27 | 2.96 | General |
| LQH2MCN120K02 | 12 | 0806/2016 | 0.95 | 210 | | 1.4 | 1.82 | General |
| LQH2MCN120M52 | 12 | 0806/2016 | 0.7 | 170 | | 2.4 | 3.12 | General |
| LQH2MCN150K02 | 15 | 0806/2016 | 0.95 | 200 | | 1.6 | 2.08 | General |
| LQH2MCN150M52 | 15 | 0806/2016 | 0.7 | 150 | | 3.5 | 4.55 | General |
| LQH2MCN180K02 | 18 | 0806/2016 | 0.95 | 190 | | 1.8 | 2.34 | General |
| LQH2MCN180M52 | 18 | 0806/2016 | 0.7 | 140 | | 4 | 5.2 | General |
| LQH2MCN1R0M02 | 1 | 0806/2016 | 0.95 | 485 | | 0.3 | 0.39 | General |
| LQH2MCN1R0M52 | 1 | 0806/2016 | 0.7 | 595 | | 0.25 | 0.325 | General |
| LQH2MCN1R5M02 | 1.5 | 0806/2016 | 0.95 | 445 | | 0.4 | 0.52 | General |
| LQH2MCN1R5M52 | 1.5 | 0806/2016 | 0.7 | 540 | | 0.33 | 0.429 | General |
| LQH2MCN220K02 | 22 | 0806/2016 | 0.95 | 185 | | 2.1 | 2.73 | General |
| LQH2MCN220M52 | 22 | 0806/2016 | 0.7 | 130 | | 5.5 | 7.15 | General |
| LQH2MCN270K02 | 27 | 0806/2016 | 0.95 | 180 | | 2.5 | 3.25 | General |
| LQH2MCN2R2M02 | 2.2 | 0806/2016 | 0.95 | 425 | | 0.48 | 0.624 | General |
| LQH2MCN2R2M52 | 2.2 | 0806/2016 | 0.7 | 500 | | 0.42 | 0.546 | General |
| LQH2MCN330K02 | 33 | 0806/2016 | 0.95 | 160 | | 2.8 | 3.64 | General |
| LQH2MCN390K02 | 39 | 0806/2016 | 0.95 | 125 | | 4.4 | 5.72 | General |
| LQH2MCN3R3M02 | 3.3 | 0806/2016 | 0.95 | 375 | | 0.6 | 0.78 | General |
| LQH2MCN3R3M52 | 3.3 | 0806/2016 | 0.7 | 360 | | 0.74 | 0.962 | General |
| LQH2MCN470K02 | 47 | 0806/2016 | 0.95 | 120 | | 5.1 | 6.63 | General |
| LQH2MCN4R7M02 | 4.7 | 0806/2016 | 0.95 | 300 | | 0.8 | 1.04 | General |
| LQH2MCN4R7M52 | 4.7 | 0806/2016 | 0.7 | 335 | | 0.91 | 1.19 | General |
| LQH2MCN560K02 | 56 | 0806/2016 | 0.95 | 110 | | 5.7 | 7.41 | General |
| LQH2MCN5R6M02 | 5.6 | 0806/2016 | 0.95 | 280 | | 0.9 | 1.17 | General |
| LQH2MCN680K02 | 68 | 0806/2016 | 0.95 | 100 | | 6.6 | 8.58 | General |
| LQH2MCN6R8M02 | 6.8 | 0806/2016 | 0.95 | 255 | | 1 | 1.3 | General |
| LQH2MCN6R8M52 | 6.8 | 0806/2016 | 0.7 | 285 | | 1.23 | 1.6 | General |
| LQH2MCN820K02 | 82 | 0806/2016 | 0.95 | 90 | | 7.5 | 9.75 | General |
| LQH2MCN8R2M02 | 8.2 | 0806/2016 | 0.95 | 235 | | 1.1 | 1.43 | General |
| LQH2MPN100MGR | 10 | 0806/2016 | 0.95 | 480 | 610 | 0.88 | 1.056 | General |
| LQH2MPN150MGR | 15 | 0806/2016 | 0.95 | 340 | 490 | 1.7 | 2.04 | General |
| LQH2MPN1R0NGR | 1 | 0806/2016 | 0.95 | 900 | 1550 | 0.25 | 0.3 | General |
| LQH2MPN1R5NGR | 1.5 | 0806/2016 | 0.95 | 790 | 1330 | 0.32 | 0.384 | General |
| LQH2MPN220MGR | 22 | 0806/2016 | 0.95 | 290 | 410 | 2.1 | 2.52 | General |
| LQH2MPN2R2MGR | 2.2 | 0806/2016 | 0.95 | 680 | 1180 | 0.39 | 0.468 | General |
| LQH2MPN330MGR | 33 | 0806/2016 | 0.95 | 200 | 310 | 4.3 | 5.16 | General |
| LQH2MPN3R3MGR | 3.3 | 0806/2016 | 0.95 | 640 | 1020 | 0.47 | 0.564 | General |
| LQH2MPN470MGR | 47 | 0806/2016 | 0.95 | 180 | 270 | 5.3 | 6.36 | General |
| LQH2MPN4R7MGR | 4.7 | 0806/2016 | 0.95 | 580 | 870 | 0.6 | 0.72 | General |
| LQH2MPN680MGR | 68 | 0806/2016 | 0.95 | 160 | 230 | 6.7 | 8.04 | General |
| LQH2MPN6R8MGR | 6.8 | 0806/2016 | 0.95 | 530 | 730 | 0.72 | 0.864 | General |
| LQH2MPN820MGR | 82 | 0806/2016 | 0.95 | 150 | 210 | 7.3 | 8.76 | General |
| LQH2MPNR33NGR | 0.33 | 0806/2016 | 0.95 | 1130 | 2200 | 0.15 | 0.18 | General |
| LQH2MPNR47NGR | 0.47 | 0806/2016 | 0.95 | 1060 | 1950 | 0.18 | 0.216 | General |
| LQH32PB100MN0 | 10 | 1210/3225 | 1.7 | 700 | 750 | 0.38 | 0.456 | General |
| LQH32PB100MNC | 10 | 1210/3225 | 1.7 | 900 | 1000 | 0.295 | 0.354 | General |
| LQH32PB101MN0 | 100 | 1210/3225 | 1.7 | 250 | 180 | 2.7 | 3.24 | General |
| LQH32PB121MN0 | 120 | 1210/3225 | 1.7 | 200 | 170 | 4.38 | 5.26 | General |
| LQH32PB150MN0 | 15 | 1210/3225 | 1.7 | 520 | 600 | 0.57 | 0.684 | General |
| LQH32PB150MNC | 15 | 1210/3225 | 1.7 | 700 | 800 | 0.475 | 0.57 | General |
| LQH32PB1R0NN0 | 1 | 1210/3225 | 1.7 | 2050 | 2300 | 0.045 | 0.054 | General |
| LQH32PB1R0NNC | 1 | 1210/3225 | 1.7 | 2500 | 3000 | 0.036 | 0.0432 | General |
| LQH32PB1R5NN0 | 1.5 | 1210/3225 | 1.7 | 1750 | 1750 | 0.057 | 0.0684 | General |
| LQH32PB1R5NNC | 1.5 | 1210/3225 | 1.7 | 2100 | 2600 | 0.053 | 0.0636 | General |
| LQH32PB220MN0 | 22 | 1210/3225 | 1.7 | 450 | 500 | 0.81 | 0.972 | General |
| LQH32PB220MNC | 22 | 1210/3225 | 1.7 | 550 | 650 | 0.685 | 0.822 | General |
| LQH32PB2R2NN0 | 2.2 | 1210/3225 | 1.7 | 1600 | 1550 | 0.076 | 0.0912 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|------------------------|------------------------------|----------------|----------------|-------------|
| LQH32PB2R2NNC | 2.2 | 1210/3225 | 1.7 | 1850 | 2000 | 0.064 | 0.0768 | General |
| LQH32PB330MN0 | 33 | 1210/3225 | 1.7 | 390 | 380 | 1.15 | 1.38 | General |
| LQH32PB3R3NN0 | 3.3 | 1210/3225 | 1.7 | 1200 | 1250 | 0.12 | 0.144 | General |
| LQH32PB3R3NNC | 3.3 | 1210/3225 | 1.7 | 1550 | 1900 | 0.1 | 0.12 | General |
| LQH32PB470MN0 | 47 | 1210/3225 | 1.7 | 310 | 330 | 1.78 | 2.14 | General |
| LQH32PB4R7NN0 | 4.7 | 1210/3225 | 1.7 | 1000 | 1000 | 0.18 | 0.216 | General |
| LQH32PB4R7NNC | 4.7 | 1210/3225 | 1.7 | 1200 | 1600 | 0.155 | 0.186 | General |
| LQH32PB680MN0 | 68 | 1210/3225 | 1.7 | 275 | 280 | 2.28 | 2.74 | General |
| LQH32PB6R8NN0 | 6.8 | 1210/3225 | 1.7 | 850 | 850 | 0.24 | 0.288 | General |
| LQH32PB6R8NNC | 6.8 | 1210/3225 | 1.7 | 1100 | 1300 | 0.22 | 0.264 | General |
| LQH32PBR47NN0 | 0.47 | 1210/3225 | 1.7 | 2550 | 3400 | 0.03 | 0.036 | General |
| LQH32PBR47NNC | 0.47 | 1210/3225 | 1.7 | 2900 | 4400 | 0.024 | 0.0288 | General |
| LQH32PN100MN0 | 10 | 1210/3225 | 1.7 | 700 | 750 | 0.38 | 0.456 | General |
| LQH32PN100MNC | 10 | 1210/3225 | 1.7 | 900 | 1000 | 0.295 | 0.354 | General |
| LQH32PN101MN0 | 100 | 1210/3225 | 1.7 | 250 | 180 | 2.7 | 3.24 | General |
| LQH32PN121MN0 | 120 | 1210/3225 | 1.7 | 200 | 170 | 4.38 | 5.26 | General |
| LQH32PN150MN0 | 15 | 1210/3225 | 1.7 | 520 | 600 | 0.57 | 0.684 | General |
| LQH32PN150MNC | 15 | 1210/3225 | 1.7 | 700 | 800 | 0.475 | 0.57 | General |
| LQH32PN1R0NN0 | 1 | 1210/3225 | 1.7 | 2050 | 2300 | 0.045 | 0.054 | General |
| LQH32PN1R0NNC | 1 | 1210/3225 | 1.7 | 2500 | 3000 | 0.036 | 0.0432 | General |
| LQH32PN1R5NN0 | 1.5 | 1210/3225 | 1.7 | 1750 | 1750 | 0.057 | 0.0684 | General |
| LQH32PN1R5NNC | 1.5 | 1210/3225 | 1.7 | 2100 | 2600 | 0.053 | 0.0636 | General |
| LQH32PN220MN0 | 22 | 1210/3225 | 1.7 | 450 | 500 | 0.81 | 0.972 | General |
| LQH32PN220MNC | 22 | 1210/3225 | 1.7 | 550 | 650 | 0.685 | 0.822 | General |
| LQH32PN2R2NN0 | 2.2 | 1210/3225 | 1.7 | 1600 | 1550 | 0.076 | 0.0912 | General |
| LQH32PN2R2NNC | 2.2 | 1210/3225 | 1.7 | 1850 | 2000 | 0.064 | 0.0768 | General |
| LQH32PN330MN0 | 33 | 1210/3225 | 1.7 | 390 | 380 | 1.15 | 1.38 | General |
| LQH32PN3R3NN0 | 3.3 | 1210/3225 | 1.7 | 1200 | 1250 | 0.12 | 0.144 | General |
| LQH32PN3R3NNC | 3.3 | 1210/3225 | 1.7 | 1550 | 1900 | 0.1 | 0.12 | General |
| LQH32PN470MN0 | 47 | 1210/3225 | 1.7 | 310 | 330 | 1.78 | 2.14 | General |
| LQH32PN4R7NN0 | 4.7 | 1210/3225 | 1.7 | 1000 | 1000 | 0.18 | 0.216 | General |
| LQH32PN4R7NNC | 4.7 | 1210/3225 | 1.7 | 1200 | 1600 | 0.155 | 0.186 | General |
| LQH32PN680MN0 | 68 | 1210/3225 | 1.7 | 275 | 280 | 2.28 | 2.74 | General |
| LQH32PN6R8NN0 | 6.8 | 1210/3225 | 1.7 | 850 | 850 | 0.24 | 0.288 | General |
| LQH32PN6R8NNC | 6.8 | 1210/3225 | 1.7 | 1100 | 1300 | 0.22 | 0.264 | General |
| LQH32PNR47NN0 | 0.47 | 1210/3225 | 1.7 | 2550 | 3400 | 0.03 | 0.036 | General |
| LQH32PNR47NNC | 0.47 | 1210/3225 | 1.7 | 2900 | 4400 | 0.024 | 0.0288 | General |
| LQH3NPN100MG0 | 10 | 1212/3030 | 1 | 630 | 500 | 0.57 | 0.684 | General |
| LQH3NPN100MGR | 10 | 1212/3030 | 1 | 1120 | 570 | 0.28 | 0.336 | General |
| LQH3NPN100MJ0 | 10 | 1212/3030 | 1.2 | 710 | 560 | 0.3 | 0.36 | General |
| LQH3NPN100MJR | 10 | 1212/3030 | 1.2 | 1200 | 810 | 0.24 | 0.288 | General |
| LQH3NPN100MM0 | 10 | 1212/3030 | 1.5 | 870 | 550 | 0.26 | 0.312 | General |
| LQH3NPN100MME | 10 | 1212/3030 | 1.5 | 1280 | 810 | 0.19 | 0.228 | General |
| LQH3NPN100MMR | 10 | 1212/3030 | 1.5 | 1150 | 590 | 0.21 | 0.252 | General |
| LQH3NPN100NG0 | 10 | 1212/3030 | 1 | 630 | 500 | 0.57 | 0.684 | General |
| LQH3NPN100NJ0 | 10 | 1212/3030 | 1.2 | 710 | 560 | 0.3 | 0.36 | General |
| LQH3NPN100NM0 | 10 | 1212/3030 | 1.5 | 870 | 550 | 0.26 | 0.312 | General |
| LQH3NPN101MG0 | 100 | 1212/3030 | 1 | 165 | 140 | 8 | 9.6 | General |
| LQH3NPN101MGR | 100 | 1212/3030 | 1 | 220 | 190 | 3.2 | 3.84 | General |
| LQH3NPN101MM0 | 100 | 1212/3030 | 1.5 | 240 | 200 | 3.5 | 4.2 | General |
| LQH3NPN101MME | 100 | 1212/3030 | 1.5 | 430 | 260 | 1.59 | 1.908 | General |
| LQH3NPN101NG0 | 100 | 1212/3030 | 1 | 165 | 140 | 8 | 9.6 | General |
| LQH3NPN150MGR | 15 | 1212/3030 | 1 | 900 | 480 | 0.39 | 0.468 | General |
| LQH3NPN150MJ0 | 15 | 1212/3030 | 1.2 | 590 | 440 | 0.44 | 0.528 | General |
| LQH3NPN150MJR | 15 | 1212/3030 | 1.2 | 870 | 650 | 0.38 | 0.456 | General |
| LQH3NPN150MM0 | 15 | 1212/3030 | 1.5 | 730 | 520 | 0.36 | 0.432 | General |
| LQH3NPN150MME | 15 | 1212/3030 | 1.5 | 1020 | 660 | 0.29 | 0.348 | General |
| LQH3NPN150NG0 | 15 | 1212/3030 | 1 | 475 | 370 | 0.91 | 1.1 | General |
| LQH3NPN150NJ0 | 15 | 1212/3030 | 1.2 | 590 | 440 | 0.44 | 0.528 | General |
| LQH3NPN150NM0 | 15 | 1212/3030 | 1.5 | 730 | 520 | 0.36 | 0.432 | General |
| LQH3NPN151MG0 | 150 | 1212/3030 | 1 | 145 | 110 | 11 | 13.2 | General |
| LQH3NPN151MGR | 150 | 1212/3030 | 1 | 180 | 160 | 4.9 | 5.88 | General |
| LQH3NPN151NG0 | 150 | 1212/3030 | 1 | 145 | 110 | 11 | 13.2 | General |
| LQH3NPN181MGR | 180 | 1212/3030 | 1 | 160 | 130 | 6.4 | 7.68 | General |
| LQH3NPN1R0MGR | 1 | 1212/3030 | 1 | 2080 | 1700 | 0.062 | 0.0744 | General |
| LQH3NPN1R0MJR | 1 | 1212/3030 | 1.2 | 2780 | 2250 | 0.04 | 0.048 | General |
| LQH3NPN1R0MM0 | 1 | 1212/3030 | 1.5 | 2050 | 1400 | 0.044 | 0.0528 | General |
| LQH3NPN1R0MME | 1 | 1212/3030 | 1.5 | 3000 | 2350 | 0.025 | 0.03 | General |
| LQH3NPN1R0MMR | 1 | 1212/3030 | 1.5 | 2150 | 1600 | 0.042 | 0.0504 | General |
| LQH3NPN1R0NG0 | 1 | 1212/3030 | 1 | 1525 | 1650 | 0.08 | 0.096 | General |
| LQH3NPN1R0NJ0 | 1 | 1212/3030 | 1.2 | 1620 | 1650 | 0.04 | 0.048 | General |
| LQH3NPN1R0NM0 | 1 | 1212/3030 | 1.5 | 2050 | 1400 | 0.044 | 0.0528 | General |
| LQH3NPN1R5MGR | 1.5 | 1212/3030 | 1 | 2040 | 1400 | 0.074 | 0.0888 | General |
| LQH3NPN1R5MJR | 1.5 | 1212/3030 | 1.2 | 2510 | 1950 | 0.049 | 0.0588 | General |
| LQH3NPN1R5NG0 | 1.5 | 1212/3030 | 1 | 1470 | 1300 | 0.1 | 0.12 | General |
| LQH3NPN1R5NJ0 | 1.5 | 1212/3030 | 1.2 | 1500 | 1200 | 0.055 | 0.066 | General |
| LQH3NPN220MG0 | 22 | 1212/3030 | 1 | 430 | 340 | 1.1 | 1.32 | General |
| LQH3NPN220MGR | 22 | 1212/3030 | 1 | 750 | 390 | 0.53 | 0.636 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------|
| LQH3NPN220MJ0 | 22 | 1212/3030 | 1.2 | 510 | 350 | 0.6 | 0.72 | General |
| LQH3NPN220MJR | 22 | 1212/3030 | 1.2 | 800 | 520 | 0.5 | 0.6 | General |
| LQH3NPN220MM0 | 22 | 1212/3030 | 1.5 | 650 | 410 | 0.51 | 0.612 | General |
| LQH3NPN220MME | 22 | 1212/3030 | 1.5 | 860 | 570 | 0.4 | 0.48 | General |
| LQH3NPN220MMR | 22 | 1212/3030 | 1.5 | 750 | 430 | 0.48 | 0.576 | General |
| LQH3NPN220NG0 | 22 | 1212/3030 | 1 | 430 | 340 | 1.1 | 1.32 | General |
| LQH3NPN220NJ0 | 22 | 1212/3030 | 1.2 | 510 | 350 | 0.6 | 0.72 | General |
| LQH3NPN221MG0 | 220 | 1212/3030 | 1 | 130 | 100 | 14 | 16.8 | General |
| LQH3NPN221MGR | 220 | 1212/3030 | 1 | 150 | 120 | 7.5 | 9 | General |
| LQH3NPN221NG0 | 220 | 1212/3030 | 1 | 130 | 100 | 14 | 16.8 | General |
| LQH3NPN251MG0 | 250 | 1212/3030 | 1 | 130 | 80 | 15 | 18 | General |
| LQH3NPN251MGR | 250 | 1212/3030 | 1 | 140 | 110 | 8 | 9.6 | General |
| LQH3NPN251NG0 | 250 | 1212/3030 | 1 | 130 | 80 | 15 | 18 | General |
| LQH3NPN2R2MGR | 2.2 | 1212/3030 | 1 | 1730 | 1180 | 0.087 | 0.1044 | General |
| LQH3NPN2R2MJ0 | 2.2 | 1212/3030 | 1.2 | 1460 | 1150 | 0.069 | 0.0828 | General |
| LQH3NPN2R2MJR | 2.2 | 1212/3030 | 1.2 | 2200 | 1800 | 0.068 | 0.0816 | General |
| LQH3NPN2R2MM0 | 2.2 | 1212/3030 | 1.5 | 1600 | 1250 | 0.073 | 0.0876 | General |
| LQH3NPN2R2MME | 2.2 | 1212/3030 | 1.5 | 2100 | 1800 | 0.065 | 0.078 | General |
| LQH3NPN2R2MMR | 2.2 | 1212/3030 | 1.5 | 1750 | 1380 | 0.068 | 0.0816 | General |
| LQH3NPN2R2NG0 | 2.2 | 1212/3030 | 1 | 1270 | 1250 | 0.14 | 0.168 | General |
| LQH3NPN2R2NJ0 | 2.2 | 1212/3030 | 1.2 | 1460 | 1150 | 0.069 | 0.0828 | General |
| LQH3NPN2R2NM0 | 2.2 | 1212/3030 | 1.5 | 1600 | 1250 | 0.073 | 0.0876 | General |
| LQH3NPN330MG0 | 33 | 1212/3030 | 1 | 345 | 250 | 2.1 | 2.52 | General |
| LQH3NPN330MGR | 33 | 1212/3030 | 1 | 600 | 320 | 0.86 | 1.032 | General |
| LQH3NPN330MJ0 | 33 | 1212/3030 | 1.2 | 410 | 280 | 0.9 | 1.08 | General |
| LQH3NPN330MJR | 33 | 1212/3030 | 1.2 | 630 | 420 | 0.79 | 0.948 | General |
| LQH3NPN330MM0 | 33 | 1212/3030 | 1.5 | 500 | 370 | 0.85 | 1.02 | General |
| LQH3NPN330MME | 33 | 1212/3030 | 1.5 | 760 | 440 | 0.55 | 0.66 | General |
| LQH3NPN330MMR | 33 | 1212/3030 | 1.5 | 600 | 380 | 0.79 | 0.948 | General |
| LQH3NPN330NG0 | 33 | 1212/3030 | 1 | 345 | 250 | 2.1 | 2.52 | General |
| LQH3NPN330NJ0 | 33 | 1212/3030 | 1.2 | 410 | 280 | 0.9 | 1.08 | General |
| LQH3NPN3R3MGR | 3.3 | 1212/3030 | 1 | 1580 | 1050 | 0.12 | 0.144 | General |
| LQH3NPN3R3MJ0 | 3.3 | 1212/3030 | 1.2 | 1270 | 950 | 0.105 | 0.126 | General |
| LQH3NPN3R3MJR | 3.3 | 1212/3030 | 1.2 | 1700 | 1350 | 0.095 | 0.114 | General |
| LQH3NPN3R3MM0 | 3.3 | 1212/3030 | 1.5 | 1450 | 1000 | 0.092 | 0.111 | General |
| LQH3NPN3R3MME | 3.3 | 1212/3030 | 1.5 | 1900 | 1520 | 0.084 | 0.1008 | General |
| LQH3NPN3R3MMR | 3.3 | 1212/3030 | 1.5 | 1550 | 1200 | 0.088 | 0.106 | General |
| LQH3NPN3R3NG0 | 3.3 | 1212/3030 | 1 | 1130 | 850 | 0.18 | 0.216 | General |
| LQH3NPN3R3NJ0 | 3.3 | 1212/3030 | 1.2 | 1270 | 950 | 0.105 | 0.126 | General |
| LQH3NPN3R3NM0 | 3.3 | 1212/3030 | 1.5 | 1450 | 1000 | 0.092 | 0.111 | General |
| LQH3NPN470MG0 | 47 | 1212/3030 | 1 | 270 | 170 | 3 | 3.6 | General |
| LQH3NPN470MGR | 47 | 1212/3030 | 1 | 460 | 260 | 1.4 | 1.68 | General |
| LQH3NPN470MJ0 | 47 | 1212/3030 | 1.2 | 350 | 200 | 1.3 | 1.56 | General |
| LQH3NPN470MJR | 47 | 1212/3030 | 1.2 | 570 | 360 | 1 | 1.2 | General |
| LQH3NPN470MM0 | 47 | 1212/3030 | 1.5 | 410 | 310 | 1.25 | 1.5 | General |
| LQH3NPN470MME | 47 | 1212/3030 | 1.5 | 610 | 380 | 0.82 | 0.984 | General |
| LQH3NPN470MMR | 47 | 1212/3030 | 1.5 | 460 | 320 | 1.14 | 1.368 | General |
| LQH3NPN470NG0 | 47 | 1212/3030 | 1 | 270 | 170 | 3 | 3.6 | General |
| LQH3NPN470NJ0 | 47 | 1212/3030 | 1.2 | 350 | 200 | 1.3 | 1.56 | General |
| LQH3NPN4R7MGR | 4.7 | 1212/3030 | 1 | 1520 | 850 | 0.14 | 0.168 | General |
| LQH3NPN4R7MJ0 | 4.7 | 1212/3030 | 1.2 | 1120 | 780 | 0.13 | 0.156 | General |
| LQH3NPN4R7MJR | 4.7 | 1212/3030 | 1.2 | 1580 | 1180 | 0.12 | 0.144 | General |
| LQH3NPN4R7MM0 | 4.7 | 1212/3030 | 1.5 | 1250 | 880 | 0.13 | 0.156 | General |
| LQH3NPN4R7MME | 4.7 | 1212/3030 | 1.5 | 1700 | 1300 | 0.1 | 0.12 | General |
| LQH3NPN4R7MMR | 4.7 | 1212/3030 | 1.5 | 1400 | 950 | 0.105 | 0.126 | General |
| LQH3NPN4R7NG0 | 4.7 | 1212/3030 | 1 | 925 | 800 | 0.26 | 0.312 | General |
| LQH3NPN4R7NJ0 | 4.7 | 1212/3030 | 1.2 | 1120 | 780 | 0.13 | 0.156 | General |
| LQH3NPN4R7NM0 | 4.7 | 1212/3030 | 1.5 | 1250 | 880 | 0.13 | 0.156 | General |
| LQH3NPN560MME | 56 | 1212/3030 | 1.5 | 500 | 350 | 1 | 1.2 | General |
| LQH3NPN680MG0 | 68 | 1212/3030 | 1 | 235 | 150 | 4.2 | 5.04 | General |
| LQH3NPN680MGR | 68 | 1212/3030 | 1 | 280 | 220 | 2.1 | 2.52 | General |
| LQH3NPN680MME | 68 | 1212/3030 | 1.5 | 470 | 310 | 1.15 | 1.38 | General |
| LQH3NPN680NG0 | 68 | 1212/3030 | 1 | 235 | 150 | 4.2 | 5.04 | General |
| LQH3NPN6R8MGR | 6.8 | 1212/3030 | 1 | 1140 | 720 | 0.23 | 0.276 | General |
| LQH3NPN6R8MJ0 | 6.8 | 1212/3030 | 1.2 | 850 | 700 | 0.21 | 0.252 | General |
| LQH3NPN6R8MJR | 6.8 | 1212/3030 | 1.2 | 1360 | 970 | 0.18 | 0.216 | General |
| LQH3NPN6R8MM0 | 6.8 | 1212/3030 | 1.5 | 1000 | 820 | 0.2 | 0.24 | General |
| LQH3NPN6R8MME | 6.8 | 1212/3030 | 1.5 | 1450 | 1040 | 0.14 | 0.168 | General |
| LQH3NPN6R8MMR | 6.8 | 1212/3030 | 1.5 | 1250 | 830 | 0.155 | 0.186 | General |
| LQH3NPN6R8NG0 | 6.8 | 1212/3030 | 1 | 710 | 650 | 0.45 | 0.54 | General |
| LQH3NPN6R8NJ0 | 6.8 | 1212/3030 | 1.2 | 850 | 700 | 0.21 | 0.252 | General |
| LQH3NPN6R8NM0 | 6.8 | 1212/3030 | 1.5 | 1000 | 820 | 0.2 | 0.24 | General |
| LQH3NPNR47NGR | 0.47 | 1212/3030 | 1 | 2540 | 2820 | 0.047 | 0.0564 | General |
| LQH3NPNR68NJR | 0.68 | 1212/3030 | 1.2 | 2860 | 2700 | 0.032 | 0.0384 | General |
| LQH43PB100M26 | 10 | 1812/4532 | 2.8 | 1170 | 1050 | 0.147 | 0.1764 | General |
| LQH43PB101M26 | 100 | 1812/4532 | 2.8 | 320 | 320 | 1.538 | 1.8456 | General |
| LQH43PB151M26 | 150 | 1812/4532 | 2.8 | 260 | 280 | 2.362 | 2.8344 | General |
| LQH43PB1R0N26 | 1 | 1812/4532 | 2.8 | 3300 | 3400 | 0.026 | 0.0312 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------|
| LQH43PB220M26 | 22 | 1812/4532 | 2.8 | 780 | 700 | 0.327 | 0.3924 | General |
| LQH43PB221M26 | 220 | 1812/4532 | 2.8 | 240 | 220 | 2.9 | 3.48 | General |
| LQH43PB2R2M26 | 2.2 | 1812/4532 | 2.8 | 2500 | 2300 | 0.042 | 0.0504 | General |
| LQH43PB3R3M26 | 3.3 | 1812/4532 | 2.8 | 2100 | 1800 | 0.052 | 0.0624 | General |
| LQH43PB470M26 | 47 | 1812/4532 | 2.8 | 520 | 470 | 0.718 | 0.8616 | General |
| LQH43PB4R7M26 | 4.7 | 1812/4532 | 2.8 | 1600 | 1400 | 0.075 | 0.09 | General |
| LQH43PB6R8M26 | 6.8 | 1812/4532 | 2.8 | 1400 | 1200 | 0.098 | 0.1176 | General |
| LQH43PB8R2M26 | 8.2 | 1812/4532 | 2.8 | 1300 | 1100 | 0.128 | 0.1536 | General |
| LQH43PN100M26 | 10 | 1812/4532 | 2.8 | 1170 | 1050 | 0.147 | 0.1764 | General |
| LQH43PN101M26 | 100 | 1812/4532 | 2.8 | 320 | 320 | 1.538 | 1.8456 | General |
| LQH43PN151M26 | 150 | 1812/4532 | 2.8 | 260 | 280 | 2.362 | 2.8344 | General |
| LQH43PN1R0N26 | 1 | 1812/4532 | 2.8 | 3300 | 3400 | 0.026 | 0.0312 | General |
| LQH43PN220M26 | 22 | 1812/4532 | 2.8 | 780 | 700 | 0.327 | 0.3924 | General |
| LQH43PN221M26 | 220 | 1812/4532 | 2.8 | 240 | 220 | 2.9 | 3.48 | General |
| LQH43PN2R2M26 | 2.2 | 1812/4532 | 2.8 | 2500 | 2300 | 0.042 | 0.0504 | General |
| LQH43PN3R3M26 | 3.3 | 1812/4532 | 2.8 | 2100 | 1800 | 0.052 | 0.0624 | General |
| LQH43PN470M26 | 47 | 1812/4532 | 2.8 | 520 | 470 | 0.718 | 0.8616 | General |
| LQH43PN4R7M26 | 4.7 | 1812/4532 | 2.8 | 1600 | 1400 | 0.075 | 0.09 | General |
| LQH43PN6R8M26 | 6.8 | 1812/4532 | 2.8 | 1400 | 1200 | 0.098 | 0.1176 | General |
| LQH43PN8R2M26 | 8.2 | 1812/4532 | 2.8 | 1300 | 1100 | 0.128 | 0.1536 | General |
| LQH44PN100MGR | 10 | 1515/4040 | 1 | 1100 | 800 | 0.27 | 0.324 | General |
| LQH44PN100MJ0 | 10 | 1515/4040 | 1.2 | 790 | 560 | 0.207 | 0.249 | General |
| LQH44PN100MP0 | 10 | 1515/4040 | 1.8 | 1170 | 1150 | 0.16 | 0.192 | General |
| LQH44PN150MGR | 15 | 1515/4040 | 1 | 900 | 640 | 0.42 | 0.504 | General |
| LQH44PN150MJ0 | 15 | 1515/4040 | 1.2 | 610 | 430 | 0.385 | 0.462 | General |
| LQH44PN1R0NJ0 | 1 | 1515/4040 | 1.2 | 1530 | 2000 | 0.048 | 0.0576 | General |
| LQH44PN1R0NP0 | 1 | 1515/4040 | 1.8 | 2450 | 2950 | 0.03 | 0.036 | General |
| LQH44PN1R5MJ0 | 1.5 | 1515/4040 | 1.2 | 1380 | 1600 | 0.061 | 0.0732 | General |
| LQH44PN220MGR | 22 | 1515/4040 | 1 | 750 | 500 | 0.57 | 0.684 | General |
| LQH44PN220MJ0 | 22 | 1515/4040 | 1.2 | 550 | 400 | 0.48 | 0.576 | General |
| LQH44PN220MP0 | 22 | 1515/4040 | 1.8 | 790 | 800 | 0.37 | 0.444 | General |
| LQH44PN2R2MJ0 | 2.2 | 1515/4040 | 1.2 | 1230 | 1320 | 0.074 | 0.0888 | General |
| LQH44PN2R2MP0 | 2.2 | 1515/4040 | 1.8 | 1800 | 2500 | 0.049 | 0.0588 | General |
| LQH44PN2R2NGR | 2.2 | 1515/4040 | 1 | 2000 | 1600 | 0.074 | 0.0888 | General |
| LQH44PN330MGR | 33 | 1515/4040 | 1 | 480 | 400 | 1.4 | 1.68 | General |
| LQH44PN330MJ0 | 33 | 1515/4040 | 1.2 | 430 | 360 | 0.74 | 0.888 | General |
| LQH44PN3R3MJ0 | 3.3 | 1515/4040 | 1.2 | 1000 | 900 | 0.088 | 0.106 | General |
| LQH44PN3R3MP0 | 3.3 | 1515/4040 | 1.8 | 1770 | 2100 | 0.065 | 0.078 | General |
| LQH44PN3R3NGR | 3.3 | 1515/4040 | 1 | 1700 | 1500 | 0.11 | 0.132 | General |
| LQH44PN470MGR | 47 | 1515/4040 | 1 | 410 | 360 | 1.7 | 2.04 | General |
| LQH44PN470MJ0 | 47 | 1515/4040 | 1.2 | 380 | 300 | 1.014 | 1.22 | General |
| LQH44PN4R7MGR | 4.7 | 1515/4040 | 1 | 1600 | 1200 | 0.13 | 0.156 | General |
| LQH44PN4R7MJ0 | 4.7 | 1515/4040 | 1.2 | 980 | 840 | 0.117 | 0.14 | General |
| LQH44PN4R7MP0 | 4.7 | 1515/4040 | 1.8 | 1700 | 1700 | 0.08 | 0.096 | General |
| LQH44PN6R8MGR | 6.8 | 1515/4040 | 1 | 1400 | 850 | 0.17 | 0.204 | General |
| LQH44PN6R8MJ0 | 6.8 | 1515/4040 | 1.2 | 860 | 720 | 0.143 | 0.172 | General |
| LQH44PN6R8MP0 | 6.8 | 1515/4040 | 1.8 | 1340 | 1400 | 0.12 | 0.144 | General |
| LQH44PNR68NGR | 0.68 | 1515/4040 | 1 | 2500 | 2400 | 0.043 | 0.0516 | General |
| LQH5BPB100MT0 | 10 | 2020/5050 | 2.2 | 1600 | 2000 | 0.106 | 0.1272 | General |
| LQH5BPB150MT0 | 15 | 2020/5050 | 2.2 | 1200 | 1600 | 0.187 | 0.2244 | General |
| LQH5BPB1R0NT0 | 1 | 2020/5050 | 2.2 | 3100 | 5800 | 0.019 | 0.0228 | General |
| LQH5BPB1R2NT0 | 1.2 | 2020/5050 | 2.2 | 3100 | 5400 | 0.019 | 0.0228 | General |
| LQH5BPB1R5NT0 | 1.5 | 2020/5050 | 2.2 | 3000 | 5000 | 0.024 | 0.0288 | General |
| LQH5BPB220MT0 | 22 | 2020/5050 | 2.2 | 1050 | 1400 | 0.259 | 0.3108 | General |
| LQH5BPB2R2NT0 | 2.2 | 2020/5050 | 2.2 | 2600 | 4000 | 0.03 | 0.036 | General |
| LQH5BPB2R7NT0 | 2.7 | 2020/5050 | 2.2 | 2500 | 3800 | 0.035 | 0.042 | General |
| LQH5BPB3R3NT0 | 3.3 | 2020/5050 | 2.2 | 2300 | 3500 | 0.044 | 0.0528 | General |
| LQH5BPB4R7NT0 | 4.7 | 2020/5050 | 2.2 | 2000 | 3000 | 0.058 | 0.0696 | General |
| LQH5BPB6R8NT0 | 6.8 | 2020/5050 | 2.2 | 1650 | 2500 | 0.083 | 0.0996 | General |
| LQH5BPBR47NT0 | 0.47 | 2020/5050 | 2.2 | 4000 | 7700 | 0.012 | 0.0144 | General |
| LQH5BPN100M38 | 10 | 2020/5050 | 4 | 2200 | 2600 | 0.056 | 0.0672 | General |
| LQH5BPN100MT0 | 10 | 2020/5050 | 2.2 | 1600 | 2000 | 0.106 | 0.1272 | General |
| LQH5BPN101M38 | 100 | 2020/5050 | 4 | 740 | 750 | 0.48 | 0.576 | General |
| LQH5BPN150M38 | 15 | 2020/5050 | 4 | 1900 | 1800 | 0.08 | 0.096 | General |
| LQH5BPN150MT0 | 15 | 2020/5050 | 2.2 | 1200 | 1600 | 0.187 | 0.2244 | General |
| LQH5BPN151M38 | 150 | 2020/5050 | 4 | 630 | 650 | 0.68 | 0.816 | General |
| LQH5BPN1R0N38 | 1 | 2020/5050 | 4 | 4600 | 7000 | 0.012 | 0.0144 | General |
| LQH5BPN1R0NT0 | 1 | 2020/5050 | 2.2 | 3100 | 5800 | 0.019 | 0.0228 | General |
| LQH5BPN1R2NT0 | 1.2 | 2020/5050 | 2.2 | 3100 | 5400 | 0.019 | 0.0228 | General |
| LQH5BPN1R5N38 | 1.5 | 2020/5050 | 4 | 4500 | 6500 | 0.014 | 0.0168 | General |
| LQH5BPN1R5NT0 | 1.5 | 2020/5050 | 2.2 | 3000 | 5000 | 0.024 | 0.0288 | General |
| LQH5BPN220M38 | 22 | 2020/5050 | 4 | 1500 | 1600 | 0.11 | 0.132 | General |
| LQH5BPN220MT0 | 22 | 2020/5050 | 2.2 | 1050 | 1400 | 0.259 | 0.3108 | General |
| LQH5BPN2R2N38 | 2.2 | 2020/5050 | 4 | 4300 | 5000 | 0.016 | 0.0192 | General |
| LQH5BPN2R2NT0 | 2.2 | 2020/5050 | 2.2 | 2600 | 4000 | 0.03 | 0.036 | General |
| LQH5BPN2R7NT0 | 2.7 | 2020/5050 | 2.2 | 2500 | 3800 | 0.035 | 0.042 | General |
| LQH5BPN330M38 | 33 | 2020/5050 | 4 | 1300 | 1300 | 0.15 | 0.18 | General |
| LQH5BPN3R3N38 | 3.3 | 2020/5050 | 4 | 4000 | 4000 | 0.021 | 0.0252 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------|
| LQH5BPN3R3NT0 | 3.3 | 2020/5050 | 2.2 | 2300 | 3500 | 0.044 | 0.0528 | General |
| LQH5BPN470M38 | 47 | 2020/5050 | 4 | 1100 | 1100 | 0.22 | 0.264 | General |
| LQH5BPN4R7N38 | 4.7 | 2020/5050 | 4 | 3800 | 3500 | 0.026 | 0.0312 | General |
| LQH5BPN4R7NT0 | 4.7 | 2020/5050 | 2.2 | 2000 | 3000 | 0.058 | 0.0696 | General |
| LQH5BPN680M38 | 68 | 2020/5050 | 4 | 930 | 900 | 0.33 | 0.396 | General |
| LQH5BPN6R8M38 | 6.8 | 2020/5050 | 4 | 3000 | 3000 | 0.039 | 0.0468 | General |
| LQH5BPN6R8NT0 | 6.8 | 2020/5050 | 2.2 | 1650 | 2500 | 0.083 | 0.0996 | General |
| LQH5BPNR47NT0 | 0.47 | 2020/5050 | 2.2 | 4000 | 7700 | 0.012 | 0.0144 | General |
| LQM18PN1R0MFH | 1 | 0603/1608 | 0.95 | 1300 | 550 | 0.13 | 0.163 | General |
| LQM18PN1R0MFR | 1 | 0603/1608 | 0.95 | 950 | | 0.2 | 0.25 | General |
| LQM18PN1R0MGH | 1 | 0603/1608 | 1 | 1050 | 800 | 0.2 | 0.25 | General |
| LQM18PN1R0NC0 | 1 | 0603/1608 | 0.55 | 750 | | 0.2 | 0.25 | General |
| LQM18PN1R0NF0 | 1 | 0603/1608 | 0.95 | 600 | | 0.28 | 0.35 | General |
| LQM18PN1R5MFH | 1.5 | 0603/1608 | 0.95 | 1100 | 400 | 0.17 | 0.213 | General |
| LQM18PN1R5MFR | 1.5 | 0603/1608 | 0.95 | 800 | | 0.23 | 0.288 | General |
| LQM18PN1R5NB0 | 1.5 | 0603/1608 | 0.4 | 600 | | 0.35 | 0.438 | General |
| LQM18PN1R5NC0 | 1.5 | 0603/1608 | 0.55 | 720 | | 0.22 | 0.275 | General |
| LQM18PN1R8NC0 | 1.8 | 0603/1608 | 0.55 | 700 | | 0.24 | 0.3 | General |
| LQM18PN2R2MDH | 2.2 | 0603/1608 | 0.75 | 650 | 250 | 0.38 | 0.475 | General |
| LQM18PN2R2MFH | 2.2 | 0603/1608 | 0.95 | 700 | 300 | 0.38 | 0.475 | General |
| LQM18PN2R2MFR | 2.2 | 0603/1608 | 0.95 | 750 | | 0.3 | 0.375 | General |
| LQM18PN2R2MGH | 2.2 | 0603/1608 | 1 | 1050 | 250 | 0.2 | 0.25 | General |
| LQM18PN2R2NC0 | 2.2 | 0603/1608 | 0.55 | 700 | | 0.24 | 0.3 | General |
| LQM18PN2R5ND0 | 2.5 | 0603/1608 | 0.75 | 700 | | 0.24 | 0.3 | General |
| LQM18PN3R3MFR | 3.3 | 0603/1608 | 0.95 | 700 | | 0.35 | 0.438 | General |
| LQM18PN3R3MGH | 3.3 | 0603/1608 | 1 | 1050 | 150 | 0.2 | 0.25 | General |
| LQM18PN4R7MFR | 4.7 | 0603/1608 | 0.95 | 620 | | 0.44 | 0.55 | General |
| LQM18PNR22NFR | 0.22 | 0603/1608 | 0.95 | 1250 | | 0.11 | 0.138 | General |
| LQM18PNR47MFH | 0.47 | 0603/1608 | 0.95 | 1400 | 1300 | 0.1 | 0.125 | General |
| LQM18PNR47NC0 | 0.47 | 0603/1608 | 0.55 | 850 | | 0.15 | 0.1875 | General |
| LQM18PNR47NFR | 0.47 | 0603/1608 | 0.95 | 1100 | | 0.15 | 0.188 | General |
| LQM18PW1R0MCH | 1 | 0603/1608 | 0.65 | 950 | 600 | 0.23 | 0.288 | General |
| LQM18PW2R2MCH | 2.2 | 0603/1608 | 0.65 | 750 | 200 | 0.38 | 0.475 | General |
| LQM18PW2R5NCH | 2.5 | 0603/1608 | 0.6 | 900 | 100 | 0.24 | 0.3 | General |
| LQM21PN1R0MC0 | 1 | 0805/2012 | 0.55 | 800 | | 0.19 | 0.238 | General |
| LQM21PN1R0MCH | 1 | 0805/2012 | 0.55 | 1200 | 350 | 0.15 | 0.188 | General |
| LQM21PN1R0MEH | 1 | 0805/2012 | 0.8 | 1600 | 800 | 0.085 | 0.107 | General |
| LQM21PN1R0MGH | 1 | 0805/2012 | 1 | 1700 | 1100 | 0.08 | 0.1 | General |
| LQM21PN1R0NGC | 1 | 0805/2012 | 1 | 900 | | 0.1 | 0.125 | General |
| LQM21PN1R0NGR | 1 | 0805/2012 | 1 | 1300 | | 0.066 | 0.0825 | General |
| LQM21PN1R5MC0 | 1.5 | 0805/2012 | 0.55 | 700 | | 0.26 | 0.325 | General |
| LQM21PN1R5MCH | 1.5 | 0805/2012 | 0.55 | 1100 | 250 | 0.17 | 0.213 | General |
| LQM21PN1R5MEH | 1.5 | 0805/2012 | 0.8 | 1500 | 400 | 0.1 | 0.125 | General |
| LQM21PN1R5MGH | 1.5 | 0805/2012 | 1 | 1400 | 640 | 0.11 | 0.137 | General |
| LQM21PN2R2MC0 | 2.2 | 0805/2012 | 0.55 | 600 | | 0.34 | 0.425 | General |
| LQM21PN2R2MCA | 2.2 | 0805/2012 | 0.65 | 1050 | 280 | 0.2 | 0.25 | General |
| LQM21PN2R2MCH | 2.2 | 0805/2012 | 0.55 | 1050 | 180 | 0.2 | 0.25 | General |
| LQM21PN2R2MEH | 2.2 | 0805/2012 | 0.8 | 1100 | 300 | 0.175 | 0.219 | General |
| LQM21PN2R2MGH | 2.2 | 0805/2012 | 1 | 1300 | 450 | 0.125 | 0.156 | General |
| LQM21PN2R2MGS | 2.2 | 0805/2012 | 1 | 950 | | 0.18 | 0.225 | General |
| LQM21PN2R2NGC | 2.2 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | General |
| LQM21PN3R3MG0 | 3.3 | 0805/2012 | 1 | 800 | | 0.165 | 0.207 | General |
| LQM21PN3R3MGR | 3.3 | 0805/2012 | 1 | 1000 | | 0.15 | 0.188 | General |
| LQM21PN3R3NG0 | 3.3 | 0805/2012 | 1 | 800 | | 0.165 | 0.207 | General |
| LQM21PN3R3NGR | 3.3 | 0805/2012 | 1 | 1000 | | 0.15 | 0.188 | General |
| LQM21PN4R7MGH | 4.7 | 0805/2012 | 1 | 1000 | 250 | 0.22 | 0.275 | General |
| LQM21PN4R7MGR | 4.7 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | General |
| LQM21PN4R7MGS | 4.7 | 0805/2012 | 1 | 750 | | 0.29 | 0.363 | General |
| LQM21PN4R7NGR | 4.7 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | General |
| LQM21PNR24MEH | 0.24 | 0805/2012 | 0.8 | 2400 | 2800 | 0.04 | 0.05 | General |
| LQM21PNR47MC0 | 0.47 | 0805/2012 | 0.55 | 1100 | | 0.12 | 0.15 | General |
| LQM21PNR47MCH | 0.47 | 0805/2012 | 0.55 | 1400 | 1600 | 0.11 | 0.138 | General |
| LQM21PNR47MEH | 0.47 | 0805/2012 | 0.8 | 1900 | 1500 | 0.06 | 0.075 | General |
| LQM21PNR47MG0 | 0.47 | 0805/2012 | 1 | 1300 | | 0.075 | 0.094 | General |
| LQM21PNR47MGH | 0.47 | 0805/2012 | 1 | 2400 | 1800 | 0.04 | 0.05 | General |
| LQM21PNR54MG0 | 0.54 | 0805/2012 | 1 | 1300 | | 0.075 | 0.094 | General |
| LQM21PNR82MCH | 0.82 | 0805/2012 | 0.55 | 1300 | 700 | 0.13 | 0.163 | General |
| LQM2HPN1R0MCH | 1 | 1008/2520 | 0.55 | 1700 | 600 | 0.08 | 0.1 | General |
| LQM2HPN1R0MEH | 1 | 1008/2520 | 0.8 | 1650 | 1900 | 0.095 | 0.119 | General |
| LQM2HPN1R0MG0 | 1 | 1008/2520 | 1 | 1600 | | 0.055 | 0.069 | General |
| LQM2HPN1R0MGC | 1 | 1008/2520 | 1 | 1500 | | 0.08 | 0.1 | General |
| LQM2HPN1R0MGH | 1 | 1008/2520 | 1 | 2300 | 2000 | 0.05 | 0.063 | General |
| LQM2HPN1R0MJ0 | 1 | 1008/2520 | 1.2 | 1500 | | 0.09 | 0.113 | General |
| LQM2HPN1R0MJC | 1 | 1008/2520 | 1.2 | 1500 | | 0.086 | 0.108 | General |
| LQM2HPN1R0MJH | 1 | 1008/2520 | 1.2 | 2300 | 2100 | 0.05 | 0.063 | General |
| LQM2HPN1R5MCH | 1.5 | 1008/2520 | 0.55 | 950 | 600 | 0.285 | 0.36 | General |
| LQM2HPN1R5MEH | 1.5 | 1008/2520 | 0.8 | 1450 | 1200 | 0.12 | 0.15 | General |
| LQM2HPN1R5MG0 | 1.5 | 1008/2520 | 1 | 1500 | | 0.07 | 0.088 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------|
| LQM2HPN1R5MGH | 1.5 | 1008/2520 | 1 | 2000 | 1500 | 0.065 | 0.081 | General |
| LQM2HPN2R2MCH | 2.2 | 1008/2520 | 0.55 | 850 | 430 | 0.355 | 0.44 | General |
| LQM2HPN2R2MEH | 2.2 | 1008/2520 | 0.8 | 1300 | 800 | 0.15 | 0.188 | General |
| LQM2HPN2R2MG0 | 2.2 | 1008/2520 | 1 | 1300 | | 0.08 | 0.1 | General |
| LQM2HPN2R2MGH | 2.2 | 1008/2520 | 1 | 1500 | 1500 | 0.11 | 0.138 | General |
| LQM2HPN2R2MGS | 2.2 | 1008/2520 | 1 | 1100 | | 0.18 | 0.225 | General |
| LQM2HPN2R2MJ0 | 2.2 | 1008/2520 | 1.2 | 1000 | | 0.12 | 0.15 | General |
| LQM2HPN2R2MJH | 2.2 | 1008/2520 | 1.2 | 1500 | 1400 | 0.11 | 0.138 | General |
| LQM2HPN2R2NJC | 2.2 | 1008/2520 | 1.2 | 1000 | | 0.175 | 0.219 | General |
| LQM2HPN3R3MG0 | 3.3 | 1008/2520 | 1 | 1200 | | 0.1 | 0.125 | General |
| LQM2HPN3R3MGC | 3.3 | 1008/2520 | 1 | 1000 | | 0.16 | 0.2 | General |
| LQM2HPN3R3MGS | 3.3 | 1008/2520 | 1 | 1050 | | 0.21 | 0.263 | General |
| LQM2HPN3R3MJ0 | 3.3 | 1008/2520 | 1.2 | 1000 | | 0.12 | 0.15 | General |
| LQM2HPN4R7MG0 | 4.7 | 1008/2520 | 1 | 1100 | | 0.11 | 0.138 | General |
| LQM2HPN4R7MGC | 4.7 | 1008/2520 | 1 | 800 | | 0.18 | 0.225 | General |
| LQM2HPN4R7MGS | 4.7 | 1008/2520 | 1 | 1000 | | 0.25 | 0.313 | General |
| LQM2HPNR24MCH | 0.24 | 1008/2520 | 0.55 | 2200 | 2550 | 0.055 | 0.07 | General |
| LQM2HPNR24MEH | 0.24 | 1008/2520 | 0.8 | 3000 | 4500 | 0.027 | 0.034 | General |
| LQM2HPNR24MGH | 0.24 | 1008/2520 | 1 | 3300 | 4500 | 0.024 | 0.03 | General |
| LQM2HPNR33MGH | 0.33 | 1008/2520 | 1 | 3000 | 5000 | 0.03 | 0.038 | General |
| LQM2HPNR47MCH | 0.47 | 1008/2520 | 0.55 | 1500 | 1660 | 0.115 | 0.145 | General |
| LQM2HPNR47MEH | 0.47 | 1008/2520 | 0.8 | 2200 | 4000 | 0.055 | 0.069 | General |
| LQM2HPNR47MG0 | 0.47 | 1008/2520 | 1 | 1800 | | 0.04 | 0.05 | General |
| LQM2HPNR47MGH | 0.47 | 1008/2520 | 1 | 2600 | 4500 | 0.04 | 0.05 | General |
| LQM2HPNR47MJH | 0.47 | 1008/2520 | 1.2 | 2700 | 3200 | 0.037 | 0.046 | General |
| LQM2HPNR56ME0 | 0.56 | 1008/2520 | 0.8 | 1500 | | 0.06 | 0.075 | General |
| LQM2HPNR68MCH | 0.68 | 1008/2520 | 0.55 | 1500 | 1100 | 0.12 | 0.15 | General |
| LQM2HPNR68MEH | 0.68 | 1008/2520 | 0.8 | 1850 | 2100 | 0.075 | 0.094 | General |
| LQM2HPNR68MGH | 0.68 | 1008/2520 | 1 | 2300 | 3800 | 0.05 | 0.063 | General |
| LQM2MPN1R0MEH | 1 | 0806/2016 | 0.8 | 1500 | 1800 | 0.1 | 0.125 | General |
| LQM2MPN1R0MGH | 1 | 0806/2016 | 1 | 1900 | 2000 | 0.064 | 0.08 | General |
| LQM2MPN1R0NG0 | 1 | 0806/2016 | 1 | 1400 | | 0.085 | 0.107 | General |
| LQM2MPN1R5MEH | 1.5 | 0806/2016 | 0.8 | 1600 | 750 | 0.09 | 0.113 | General |
| LQM2MPN1R5MG0 | 1.5 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | General |
| LQM2MPN1R5MGH | 1.5 | 0806/2016 | 1 | 1500 | 1800 | 0.104 | 0.13 | General |
| LQM2MPN1R5NG0 | 1.5 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | General |
| LQM2MPN2R2MDH | 2.2 | 0806/2016 | 0.7 | 1270 | 630 | 0.2 | 0.25 | General |
| LQM2MPN2R2MEH | 2.2 | 0806/2016 | 0.8 | 1100 | 700 | 0.18 | 0.225 | General |
| LQM2MPN2R2MG0 | 2.2 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | General |
| LQM2MPN2R2MGH | 2.2 | 0806/2016 | 1 | 1000 | 1300 | 0.21 | 0.263 | General |
| LQM2MPN2R2NG0 | 2.2 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | General |
| LQM2MPN3R3NG0 | 3.3 | 0806/2016 | 1 | 1200 | | 0.12 | 0.15 | General |
| LQM2MPN4R7MG0 | 4.7 | 0806/2016 | 1 | 1100 | | 0.14 | 0.175 | General |
| LQM2MPN4R7NG0 | 4.7 | 0806/2016 | 1 | 1100 | | 0.14 | 0.175 | General |
| LQM2MPNR16MGH | 0.16 | 0806/2016 | 1 | 4000 | 5000 | 0.014 | 0.018 | General |
| LQM2MPNR24MEH | 0.24 | 0806/2016 | 0.8 | 2600 | 4100 | 0.035 | 0.044 | General |
| LQM2MPNR24MGH | 0.24 | 0806/2016 | 1 | 3400 | 4800 | 0.02 | 0.025 | General |
| LQM2MPNR33MGH | 0.33 | 0806/2016 | 1 | 3100 | 3700 | 0.024 | 0.03 | General |
| LQM2MPNR47MEH | 0.47 | 0806/2016 | 0.8 | 2150 | 2300 | 0.05 | 0.063 | General |
| LQM2MPNR47MG0 | 0.47 | 0806/2016 | 1 | 1600 | | 0.06 | 0.075 | General |
| LQM2MPNR47MGH | 0.47 | 0806/2016 | 1 | 2500 | 3400 | 0.037 | 0.046 | General |
| LQM2MPNR47NG0 | 0.47 | 0806/2016 | 1 | 1600 | | 0.06 | 0.075 | General |
| LQM2MPNR68MEH | 0.68 | 0806/2016 | 0.8 | 1750 | 2000 | 0.075 | 0.094 | General |
| LQM2MPNR68MGH | 0.68 | 0806/2016 | 1 | 1900 | 3100 | 0.055 | 0.069 | General |
| LQM31PN1R0M00 | 1 | 1206/3216 | 0.95 | 1200 | | 0.12 | 0.15 | General |
| LQM31PN1R0MC0 | 1 | 1206/3216 | 0.55 | 1100 | | 0.14 | 0.175 | General |
| LQM31PN1R5M00 | 1.5 | 1206/3216 | 0.95 | 1000 | | 0.14 | 0.175 | General |
| LQM31PN1R5MC0 | 1.5 | 1206/3216 | 0.55 | 1000 | | 0.17 | 0.213 | General |
| LQM31PN2R2M00 | 2.2 | 1206/3216 | 0.95 | 900 | | 0.19 | 0.238 | General |
| LQM31PN2R2MC0 | 2.2 | 1206/3216 | 0.55 | 900 | | 0.25 | 0.313 | General |
| LQM31PN3R3M00 | 3.3 | 1206/3216 | 0.95 | 800 | | 0.24 | 0.3 | General |
| LQM31PN4R7M00 | 4.7 | 1206/3216 | 0.95 | 700 | | 0.3 | 0.375 | General |
| LQM31PNR47M00 | 0.47 | 1206/3216 | 0.95 | 1400 | | 0.07 | 0.0875 | General |
| LQM31PNR47MC0 | 0.47 | 1206/3216 | 0.55 | 1300 | | 0.085 | 0.107 | General |
| LQM32PN1R0MG0 | 1 | 1210/3225 | 1 | 1800 | | 0.048 | 0.06 | General |
| LQM32PN1R0MGC | 1 | 1210/3225 | 1 | 1800 | 2200 | 0.043 | 0.054 | General |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I_temp. (mA) | I_saturation (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|------------------|-----------------|---------------------|------------------|--------------|-------------------|----------------|----------------|-------------------|
| DFE201612PD-1R0M | 1 | 0806/2016 | 1.2 | 2200 | 2700 | 0.05 | 0.06 | Infotainment |
| DFE201612PD-1R5M | 1.5 | 0806/2016 | 1.2 | 1700 | 2000 | 0.082 | 0.098 | Infotainment |
| DFE201612PD-2R2M | 2.2 | 0806/2016 | 1.2 | 1200 | 1700 | 0.143 | 0.172 | Infotainment |
| DFE201612PD-R15M | 0.15 | 0806/2016 | 1.2 | 5200 | 6200 | 0.012 | 0.018 | Infotainment |
| DFE201612PD-R24M | 0.24 | 0806/2016 | 1.2 | 4000 | 5000 | 0.016 | 0.022 | Infotainment |
| DFE201612PD-R33M | 0.33 | 0806/2016 | 1.2 | 3800 | 4500 | 0.02 | 0.026 | Infotainment |
| DFE201612PD-R47M | 0.47 | 0806/2016 | 1.2 | 3200 | 3800 | 0.026 | 0.032 | Infotainment |
| DFE201612PD-R68M | 0.68 | 0806/2016 | 1.2 | 2500 | 3100 | 0.036 | 0.046 | Infotainment |
| DFE252012PD-1R0M | 1 | 1008/2520 | 1.2 | 3200 | 3800 | 0.035 | 0.042 | Infotainment |
| DFE252012PD-1R5M | 1.5 | 1008/2520 | 1.2 | 2600 | 3300 | 0.05 | 0.06 | Infotainment |
| DFE252012PD-2R2M | 2.2 | 1008/2520 | 1.2 | 2200 | 2800 | 0.07 | 0.084 | Infotainment |
| DFE252012PD-3R3M | 3.3 | 1008/2520 | 1.2 | 1700 | 2100 | 0.115 | 0.14 | Infotainment |
| DFE252012PD-4R7M | 4.7 | 1008/2520 | 1.2 | 1400 | 1900 | 0.165 | 0.2 | Infotainment |
| DFE252012PD-R33M | 0.33 | 1008/2520 | 1.2 | 4600 | 6000 | 0.017 | 0.023 | Infotainment |
| DFE252012PD-R47M | 0.47 | 1008/2520 | 1.2 | 4000 | 5200 | 0.021 | 0.027 | Infotainment |
| DFE252012PD-R68M | 0.68 | 1008/2520 | 1.2 | 3500 | 4300 | 0.03 | 0.037 | Infotainment |
| DFEG10040D-100M | 10 | 4339/109100 | 4 | 5700 | 5500 | 0.027 | 0.033 | Powertrain/Safety |
| DFEG10040D-150M | 15 | 4339/109100 | 4 | 5200 | 4400 | 0.039 | 0.047 | Powertrain/Safety |
| DFEG10040D-1R0M | 1 | 4339/109100 | 4 | 17000 | 18000 | 0.0029 | 0.0035 | Powertrain/Safety |
| DFEG10040D-1R5M | 1.5 | 4339/109100 | 4 | 14000 | 14000 | 0.0041 | 0.005 | Powertrain/Safety |
| DFEG10040D-220M | 22 | 4339/109100 | 4 | 3800 | 4000 | 0.058 | 0.07 | Powertrain/Safety |
| DFEG10040D-2R2M | 2.2 | 4339/109100 | 4 | 12000 | 11000 | 0.0062 | 0.0075 | Powertrain/Safety |
| DFEG10040D-330M | 33 | 4339/109100 | 4 | 3300 | 3000 | 0.089 | 0.107 | Powertrain/Safety |
| DFEG10040D-3R3M | 3.3 | 4339/109100 | 4 | 10000 | 10000 | 0.0092 | 0.012 | Powertrain/Safety |
| DFEG10040D-470M | 47 | 4339/109100 | 4 | 2500 | 2900 | 0.137 | 0.164 | Powertrain/Safety |
| DFEG10040D-4R7M | 4.7 | 4339/109100 | 4 | 8800 | 7300 | 0.013 | 0.016 | Powertrain/Safety |
| DFEG10040D-5R6M | 5.6 | 4339/109100 | 4 | 8000 | 6900 | 0.015 | 0.018 | Powertrain/Safety |
| DFEG10040D-6R8M | 6.8 | 4339/109100 | 4 | 6400 | 6500 | 0.019 | 0.023 | Powertrain/Safety |
| DFEG10040D-8R2M | 8.2 | 4339/109100 | 4 | 5900 | 5600 | 0.024 | 0.029 | Powertrain/Safety |
| DFEG12060D-100M | 10 | 5150/130126 | 6 | 7900 | 6600 | 0.016 | 0.02 | Powertrain/Safety |
| DFEG12060D-150M | 15 | 5150/130126 | 6 | 6600 | 5600 | 0.023 | 0.028 | Powertrain/Safety |
| DFEG12060D-1R0M | 1 | 5150/130126 | 6 | 20000 | 19000 | 0.0024 | 0.0029 | Powertrain/Safety |
| DFEG12060D-1R5M | 1.5 | 5150/130126 | 6 | 17000 | 17000 | 0.003 | 0.0036 | Powertrain/Safety |
| DFEG12060D-220M | 22 | 5150/130126 | 6 | 6000 | 4900 | 0.029 | 0.035 | Powertrain/Safety |
| DFEG12060D-2R2M | 2.2 | 5150/130126 | 6 | 16000 | 16000 | 0.0036 | 0.0044 | Powertrain/Safety |
| DFEG12060D-330M | 33 | 5150/130126 | 6 | 4200 | 3400 | 0.045 | 0.054 | Powertrain/Safety |
| DFEG12060D-3R3M | 3.3 | 5150/130126 | 6 | 13000 | 14000 | 0.0052 | 0.0063 | Powertrain/Safety |
| DFEG12060D-470M | 47 | 5150/130126 | 6 | 3600 | 3000 | 0.066 | 0.079 | Powertrain/Safety |
| DFEG12060D-4R7M | 4.7 | 5150/130126 | 6 | 10000 | 11000 | 0.0086 | 0.011 | Powertrain/Safety |
| DFEG12060D-5R6M | 5.6 | 5150/130126 | 6 | 10000 | 10000 | 0.0089 | 0.011 | Powertrain/Safety |
| DFEG12060D-6R8M | 6.8 | 5150/130126 | 6 | 9000 | 8300 | 0.011 | 0.014 | Powertrain/Safety |
| DFEG12060D-8R2M | 8.2 | 5150/130126 | 6 | 8000 | 8300 | 0.014 | 0.017 | Powertrain/Safety |
| DFEG7030D-100M | 10 | 2726/7066 | 3 | 3000 | 3200 | 0.068 | 0.082 | Powertrain/Safety |
| DFEG7030D-150M | 15 | 2726/7066 | 3 | 2200 | 2400 | 0.122 | 0.147 | Powertrain/Safety |
| DFEG7030D-1R0M | 1 | 2726/7066 | 3 | 9100 | 9000 | 0.0082 | 0.0099 | Powertrain/Safety |
| DFEG7030D-1R5M | 1.5 | 2726/7066 | 3 | 7600 | 7300 | 0.012 | 0.015 | Powertrain/Safety |
| DFEG7030D-220M | 22 | 2726/7066 | 3 | 1900 | 2000 | 0.17 | 0.198 | Powertrain/Safety |
| DFEG7030D-2R2M | 2.2 | 2726/7066 | 3 | 7100 | 6900 | 0.015 | 0.018 | Powertrain/Safety |
| DFEG7030D-3R3M | 3.3 | 2726/7066 | 3 | 5400 | 5300 | 0.024 | 0.029 | Powertrain/Safety |
| DFEG7030D-4R7M | 4.7 | 2726/7066 | 3 | 4200 | 4200 | 0.034 | 0.041 | Powertrain/Safety |
| DFEG7030D-5R6M | 5.6 | 2726/7066 | 3 | 3800 | 4100 | 0.045 | 0.054 | Powertrain/Safety |
| DFEG7030D-6R8M | 6.8 | 2726/7066 | 3 | 3500 | 3900 | 0.049 | 0.059 | Powertrain/Safety |
| DFEG7030D-8R2M | 8.2 | 2726/7066 | 3 | 3100 | 3200 | 0.065 | 0.078 | Powertrain/Safety |
| DFEH10040D-100M | 10 | 4339/109100 | 4 | 5700 | 5500 | 0.027 | 0.033 | Powertrain/Safety |
| DFEH10040D-150M | 15 | 4339/109100 | 4 | 5200 | 4400 | 0.039 | 0.047 | Powertrain/Safety |
| DFEH10040D-1R0M | 1 | 4339/109100 | 4 | 17000 | 18000 | 0.0029 | 0.0035 | Powertrain/Safety |
| DFEH10040D-1R5M | 1.5 | 4339/109100 | 4 | 14000 | 14000 | 0.0041 | 0.005 | Powertrain/Safety |
| DFEH10040D-220M | 22 | 4339/109100 | 4 | 3800 | 4000 | 0.058 | 0.07 | Powertrain/Safety |
| DFEH10040D-2R2M | 2.2 | 4339/109100 | 4 | 12000 | 11000 | 0.0062 | 0.0075 | Powertrain/Safety |
| DFEH10040D-330M | 33 | 4339/109100 | 4 | 3300 | 3000 | 0.089 | 0.107 | Powertrain/Safety |
| DFEH10040D-3R3M | 3.3 | 4339/109100 | 4 | 10000 | 10000 | 0.0092 | 0.012 | Powertrain/Safety |
| DFEH10040D-470M | 47 | 4339/109100 | 4 | 2500 | 2900 | 0.137 | 0.164 | Powertrain/Safety |
| DFEH10040D-4R7M | 4.7 | 4339/109100 | 4 | 8800 | 7300 | 0.013 | 0.016 | Powertrain/Safety |
| DFEH10040D-5R6M | 5.6 | 4339/109100 | 4 | 8000 | 6900 | 0.015 | 0.018 | Powertrain/Safety |
| DFEH10040D-6R8M | 6.8 | 4339/109100 | 4 | 6400 | 6500 | 0.019 | 0.023 | Powertrain/Safety |
| DFEH10040D-8R2M | 8.2 | 4339/109100 | 4 | 5900 | 5600 | 0.024 | 0.029 | Powertrain/Safety |
| DFEH12060D-100M | 10 | 5150/130126 | 6 | 7900 | 6600 | 0.016 | 0.02 | Powertrain/Safety |
| DFEH12060D-150M | 15 | 5150/130126 | 6 | 6600 | 5600 | 0.023 | 0.028 | Powertrain/Safety |
| DFEH12060D-1R0M | 1 | 5150/130126 | 6 | 20000 | 19000 | 0.0024 | 0.0029 | Powertrain/Safety |
| DFEH12060D-1R5M | 1.5 | 5150/130126 | 6 | 17000 | 17000 | 0.003 | 0.0036 | Powertrain/Safety |
| DFEH12060D-220M | 22 | 5150/130126 | 6 | 6000 | 4900 | 0.029 | 0.035 | Powertrain/Safety |
| DFEH12060D-2R2M | 2.2 | 5150/130126 | 6 | 16000 | 16000 | 0.0036 | 0.0044 | Powertrain/Safety |
| DFEH12060D-330M | 33 | 5150/130126 | 6 | 4200 | 3400 | 0.045 | 0.054 | Powertrain/Safety |
| DFEH12060D-3R3M | 3.3 | 5150/130126 | 6 | 13000 | 14000 | 0.0052 | 0.0063 | Powertrain/Safety |
| DFEH12060D-470M | 47 | 5150/130126 | 6 | 3600 | 3000 | 0.066 | 0.079 | Powertrain/Safety |
| DFEH12060D-4R7M | 4.7 | 5150/130126 | 6 | 10000 | 11000 | 0.0086 | 0.011 | Powertrain/Safety |
| DFEH12060D-5R6M | 5.6 | 5150/130126 | 6 | 10000 | 10000 | 0.0089 | 0.011 | Powertrain/Safety |
| DFEH12060D-6R8M | 6.8 | 5150/130126 | 6 | 9000 | 8300 | 0.011 | 0.014 | Powertrain/Safety |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I_temp. (mA) | I_saturation (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|-----------------|-----------------|---------------------|------------------|--------------|-------------------|----------------|----------------|-------------------|
| DFEH12060D-8R2M | 8.2 | 5150/130126 | 6 | 8000 | 8300 | 0.014 | 0.017 | Powertrain/Safety |
| DFEH7030D-100M | 10 | 2726/7066 | 3 | 3000 | 3200 | 0.068 | 0.082 | Powertrain/Safety |
| DFEH7030D-150M | 15 | 2726/7066 | 3 | 2200 | 2400 | 0.122 | 0.147 | Powertrain/Safety |
| DFEH7030D-1R0M | 1 | 2726/7066 | 3 | 9100 | 9000 | 0.0082 | 0.0099 | Powertrain/Safety |
| DFEH7030D-1R5M | 1.5 | 2726/7066 | 3 | 7600 | 7300 | 0.012 | 0.015 | Powertrain/Safety |
| DFEH7030D-220M | 22 | 2726/7066 | 3 | 1900 | 2000 | 0.17 | 0.198 | Powertrain/Safety |
| DFEH7030D-2R2M | 2.2 | 2726/7066 | 3 | 7100 | 6900 | 0.015 | 0.018 | Powertrain/Safety |
| DFEH7030D-3R3M | 3.3 | 2726/7066 | 3 | 5400 | 5300 | 0.024 | 0.029 | Powertrain/Safety |
| DFEH7030D-4R7M | 4.7 | 2726/7066 | 3 | 4200 | 4200 | 0.034 | 0.041 | Powertrain/Safety |
| DFEH7030D-5R6M | 5.6 | 2726/7066 | 3 | 3800 | 4100 | 0.045 | 0.054 | Powertrain/Safety |
| DFEH7030D-6R8M | 6.8 | 2726/7066 | 3 | 3500 | 3900 | 0.049 | 0.059 | Powertrain/Safety |
| DFEH7030D-8R2M | 8.2 | 2726/7066 | 3 | 3100 | 3200 | 0.065 | 0.078 | Powertrain/Safety |
| LQH2HPZ100MDR | 10 | 1008/2520 | 0.6 | 430 | 420 | 1.2 | 1.44 | Infotainment |
| LQH2HPZ100MGR | 10 | 1008/2520 | 1 | 710 | 700 | 0.56 | 0.672 | Infotainment |
| LQH2HPZ100MJR | 10 | 1008/2520 | 1.2 | 830 | 830 | 0.38 | 0.456 | Infotainment |
| LQH2HPZ150MDR | 15 | 1008/2520 | 0.6 | 290 | 340 | 2.5 | 3 | Infotainment |
| LQH2HPZ150MGR | 15 | 1008/2520 | 1 | 560 | 570 | 0.925 | 1.11 | Infotainment |
| LQH2HPZ150MJR | 15 | 1008/2520 | 1.2 | 710 | 690 | 0.55 | 0.66 | Infotainment |
| LQH2HPZ1R0MDR | 1 | 1008/2520 | 0.6 | 960 | 1370 | 0.24 | 0.288 | Infotainment |
| LQH2HPZ1R0MGR | 1 | 1008/2520 | 1 | 2100 | 2130 | 0.068 | 0.0816 | Infotainment |
| LQH2HPZ1R0NJR | 1 | 1008/2520 | 1.2 | 2400 | 2600 | 0.048 | 0.0576 | Infotainment |
| LQH2HPZ1R2NJR | 1.2 | 1008/2520 | 1.2 | 2070 | 2450 | 0.055 | 0.066 | Infotainment |
| LQH2HPZ1R5MDR | 1.5 | 1008/2520 | 0.6 | 900 | 1120 | 0.29 | 0.348 | Infotainment |
| LQH2HPZ1R5MGR | 1.5 | 1008/2520 | 1 | 1850 | 1700 | 0.087 | 0.1044 | Infotainment |
| LQH2HPZ1R5NJR | 1.5 | 1008/2520 | 1.2 | 1810 | 2200 | 0.075 | 0.09 | Infotainment |
| LQH2HPZ220MDR | 22 | 1008/2520 | 0.6 | 270 | 260 | 3 | 3.6 | Infotainment |
| LQH2HPZ220MGR | 22 | 1008/2520 | 1 | 430 | 460 | 1.36 | 1.632 | Infotainment |
| LQH2HPZ220MJR | 22 | 1008/2520 | 1.2 | 540 | 530 | 0.84 | 1.008 | Infotainment |
| LQH2HPZ2R2MDR | 2.2 | 1008/2520 | 0.6 | 820 | 850 | 0.34 | 0.408 | Infotainment |
| LQH2HPZ2R2MGR | 2.2 | 1008/2520 | 1 | 1470 | 1550 | 0.134 | 0.1608 | Infotainment |
| LQH2HPZ2R2MJR | 2.2 | 1008/2520 | 1.2 | 1650 | 1700 | 0.092 | 0.1104 | Infotainment |
| LQH2HPZ3R3MDR | 3.3 | 1008/2520 | 0.6 | 730 | 750 | 0.45 | 0.54 | Infotainment |
| LQH2HPZ3R3MGR | 3.3 | 1008/2520 | 1 | 1100 | 1230 | 0.225 | 0.27 | Infotainment |
| LQH2HPZ3R3MJR | 3.3 | 1008/2520 | 1.2 | 1420 | 1450 | 0.13 | 0.156 | Infotainment |
| LQH2HPZ4R7MDR | 4.7 | 1008/2520 | 0.6 | 650 | 650 | 0.56 | 0.672 | Infotainment |
| LQH2HPZ4R7MGR | 4.7 | 1008/2520 | 1 | 1000 | 1090 | 0.3 | 0.36 | Infotainment |
| LQH2HPZ4R7MJR | 4.7 | 1008/2520 | 1.2 | 1290 | 1230 | 0.17 | 0.204 | Infotainment |
| LQH2HPZ6R8MDR | 6.8 | 1008/2520 | 0.6 | 490 | 550 | 1 | 1.2 | Infotainment |
| LQH2HPZ6R8MGR | 6.8 | 1008/2520 | 1 | 860 | 830 | 0.395 | 0.474 | Infotainment |
| LQH2HPZ6R8MJR | 6.8 | 1008/2520 | 1.2 | 1000 | 1050 | 0.26 | 0.312 | Infotainment |
| LQH2HPZR47MDR | 0.47 | 1008/2520 | 0.6 | 1250 | 1670 | 0.14 | 0.168 | Infotainment |
| LQH2HPZR47MGR | 0.47 | 1008/2520 | 1 | 2520 | 2900 | 0.045 | 0.054 | Infotainment |
| LQH2HPZR47NJR | 0.47 | 1008/2520 | 1.2 | 2750 | 3500 | 0.031 | 0.0372 | Infotainment |
| LQH2HPZR68MGR | 0.68 | 1008/2520 | 1 | 2330 | 2430 | 0.055 | 0.066 | Infotainment |
| LQH2MPZ100MGR | 10 | 0806/2016 | 0.95 | 480 | 610 | 0.88 | 1.056 | Infotainment |
| LQH2MPZ150MGR | 15 | 0806/2016 | 0.95 | 340 | 490 | 1.7 | 2.04 | Infotainment |
| LQH2MPZ1R0NGR | 1 | 0806/2016 | 0.95 | 900 | 1550 | 0.25 | 0.3 | Infotainment |
| LQH2MPZ1R5NGR | 1.5 | 0806/2016 | 0.95 | 790 | 1330 | 0.32 | 0.384 | Infotainment |
| LQH2MPZ220MGR | 22 | 0806/2016 | 0.95 | 290 | 410 | 2.1 | 2.52 | Infotainment |
| LQH2MPZ2R2MGR | 2.2 | 0806/2016 | 0.95 | 680 | 1180 | 0.39 | 0.468 | Infotainment |
| LQH2MPZ330MGR | 33 | 0806/2016 | 0.95 | 200 | 310 | 4.3 | 5.16 | Infotainment |
| LQH2MPZ3R3MGR | 3.3 | 0806/2016 | 0.95 | 640 | 1020 | 0.47 | 0.564 | Infotainment |
| LQH2MPZ470MGR | 47 | 0806/2016 | 0.95 | 180 | 270 | 5.3 | 6.36 | Infotainment |
| LQH2MPZ4R7MGR | 4.7 | 0806/2016 | 0.95 | 580 | 870 | 0.6 | 0.72 | Infotainment |
| LQH2MPZ680MGR | 68 | 0806/2016 | 0.95 | 160 | 230 | 6.7 | 8.04 | Infotainment |
| LQH2MPZ6R8MGR | 6.8 | 0806/2016 | 0.95 | 530 | 730 | 0.72 | 0.864 | Infotainment |
| LQH2MPZ820MGR | 82 | 0806/2016 | 0.95 | 150 | 210 | 7.3 | 8.76 | Infotainment |
| LQH2MPZR33NGR | 0.33 | 0806/2016 | 0.95 | 1130 | 2200 | 0.15 | 0.18 | Infotainment |
| LQH2MPZR47NGR | 0.47 | 0806/2016 | 0.95 | 1060 | 1950 | 0.18 | 0.216 | Infotainment |
| LQH32PH100MN0 | 10 | 1210/3225 | 1.7 | 700 | 750 | 0.38 | 0.456 | Powertrain/Safety |
| LQH32PH100MNC | 10 | 1210/3225 | 1.7 | 900 | 1000 | 0.295 | 0.354 | Powertrain/Safety |
| LQH32PH150MNC | 15 | 1210/3225 | 1.7 | 700 | 800 | 0.475 | 0.57 | Powertrain/Safety |
| LQH32PH1R0NN0 | 1 | 1210/3225 | 1.7 | 2050 | 2300 | 0.045 | 0.054 | Powertrain/Safety |
| LQH32PH1R0NNC | 1 | 1210/3225 | 1.7 | 2500 | 3000 | 0.036 | 0.0432 | Powertrain/Safety |
| LQH32PH1R5NN0 | 1.5 | 1210/3225 | 1.7 | 1750 | 1750 | 0.057 | 0.0684 | Powertrain/Safety |
| LQH32PH1R5NNC | 1.5 | 1210/3225 | 1.7 | 2100 | 2600 | 0.053 | 0.0636 | Powertrain/Safety |
| LQH32PH220MNC | 22 | 1210/3225 | 1.7 | 550 | 650 | 0.685 | 0.822 | Powertrain/Safety |
| LQH32PH2R2NN0 | 2.2 | 1210/3225 | 1.7 | 1600 | 1550 | 0.076 | 0.0912 | Powertrain/Safety |
| LQH32PH2R2NNC | 2.2 | 1210/3225 | 1.7 | 1850 | 2000 | 0.064 | 0.0768 | Powertrain/Safety |
| LQH32PH3R3NN0 | 3.3 | 1210/3225 | 1.7 | 1200 | 1250 | 0.12 | 0.144 | Powertrain/Safety |
| LQH32PH3R3NNC | 3.3 | 1210/3225 | 1.7 | 1550 | 1900 | 0.1 | 0.12 | Powertrain/Safety |
| LQH32PH4R7NN0 | 4.7 | 1210/3225 | 1.7 | 1000 | 1000 | 0.18 | 0.216 | Powertrain/Safety |
| LQH32PH4R7NNC | 4.7 | 1210/3225 | 1.7 | 1200 | 1600 | 0.155 | 0.186 | Powertrain/Safety |
| LQH32PH6R8NN0 | 6.8 | 1210/3225 | 1.7 | 850 | 850 | 0.24 | 0.288 | Powertrain/Safety |
| LQH32PH6R8NNC | 6.8 | 1210/3225 | 1.7 | 1100 | 1300 | 0.22 | 0.264 | Powertrain/Safety |
| LQH32PHR47NN0 | 0.47 | 1210/3225 | 1.7 | 2550 | 3400 | 0.03 | 0.036 | Powertrain/Safety |
| LQH32PHR47NNC | 0.47 | 1210/3225 | 1.7 | 2900 | 4400 | 0.024 | 0.0288 | Powertrain/Safety |
| LQH32PZ100MN0 | 10 | 1210/3225 | 1.7 | 700 | 750 | 0.38 | 0.456 | Infotainment |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I_temp. (mA) | I_saturation (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|--------------|-------------------|----------------|----------------|-------------------|
| LQH32PZ100MNC | 10 | 1210/3225 | 1.7 | 900 | 1000 | 0.295 | 0.354 | Infotainment |
| LQH32PZ101MN0 | 100 | 1210/3225 | 1.7 | 250 | 180 | 2.7 | 3.24 | Infotainment |
| LQH32PZ121MN0 | 120 | 1210/3225 | 1.7 | 200 | 170 | 4.38 | 5.26 | Infotainment |
| LQH32PZ150MN0 | 15 | 1210/3225 | 1.7 | 520 | 600 | 0.57 | 0.684 | Infotainment |
| LQH32PZ150MNC | 15 | 1210/3225 | 1.7 | 700 | 800 | 0.475 | 0.57 | Infotainment |
| LQH32PZ1R0NN0 | 1 | 1210/3225 | 1.7 | 2050 | 2300 | 0.045 | 0.054 | Infotainment |
| LQH32PZ1R0NNC | 1 | 1210/3225 | 1.7 | 2500 | 3000 | 0.036 | 0.0432 | Infotainment |
| LQH32PZ1R5NN0 | 1.5 | 1210/3225 | 1.7 | 1750 | 1750 | 0.057 | 0.0684 | Infotainment |
| LQH32PZ1R5NNC | 1.5 | 1210/3225 | 1.7 | 2100 | 2600 | 0.053 | 0.0636 | Infotainment |
| LQH32PZ220MN0 | 22 | 1210/3225 | 1.7 | 450 | 500 | 0.81 | 0.972 | Infotainment |
| LQH32PZ220MNC | 22 | 1210/3225 | 1.7 | 550 | 650 | 0.685 | 0.822 | Infotainment |
| LQH32PZ2R2NN0 | 2.2 | 1210/3225 | 1.7 | 1600 | 1550 | 0.076 | 0.0912 | Infotainment |
| LQH32PZ2R2NNC | 2.2 | 1210/3225 | 1.7 | 1850 | 2000 | 0.064 | 0.0768 | Infotainment |
| LQH32PZ330MN0 | 33 | 1210/3225 | 1.7 | 390 | 380 | 1.15 | 1.38 | Infotainment |
| LQH32PZ3R3NN0 | 3.3 | 1210/3225 | 1.7 | 1200 | 1250 | 0.12 | 0.144 | Infotainment |
| LQH32PZ3R3NNC | 3.3 | 1210/3225 | 1.7 | 1550 | 1900 | 0.1 | 0.12 | Infotainment |
| LQH32PZ470MN0 | 47 | 1210/3225 | 1.7 | 310 | 330 | 1.78 | 2.14 | Infotainment |
| LQH32PZ4R7NN0 | 4.7 | 1210/3225 | 1.7 | 1000 | 1000 | 0.18 | 0.216 | Infotainment |
| LQH32PZ4R7NNC | 4.7 | 1210/3225 | 1.7 | 1200 | 1600 | 0.155 | 0.186 | Infotainment |
| LQH32PZ680MN0 | 68 | 1210/3225 | 1.7 | 275 | 280 | 2.28 | 2.74 | Infotainment |
| LQH32PZ6R8NN0 | 6.8 | 1210/3225 | 1.7 | 850 | 850 | 0.24 | 0.288 | Infotainment |
| LQH32PZ6R8NNC | 6.8 | 1210/3225 | 1.7 | 1100 | 1300 | 0.22 | 0.264 | Infotainment |
| LQH32PZR47NN0 | 0.47 | 1210/3225 | 1.7 | 2550 | 3400 | 0.03 | 0.036 | Infotainment |
| LQH32PZR47NNC | 0.47 | 1210/3225 | 1.7 | 2900 | 4400 | 0.024 | 0.0288 | Infotainment |
| LQH3NPZ100MGR | 10 | 1212/3030 | 1 | 1120 | 570 | 0.28 | 0.336 | Infotainment |
| LQH3NPZ100MJR | 10 | 1212/3030 | 1.2 | 1200 | 810 | 0.24 | 0.288 | Infotainment |
| LQH3NPZ100MME | 10 | 1212/3030 | 1.5 | 1280 | 810 | 0.19 | 0.228 | Infotainment |
| LQH3NPZ101MME | 100 | 1212/3030 | 1.5 | 430 | 260 | 1.59 | 1.908 | Infotainment |
| LQH3NPZ150MGR | 15 | 1212/3030 | 1 | 900 | 480 | 0.39 | 0.468 | Infotainment |
| LQH3NPZ150MJR | 15 | 1212/3030 | 1.2 | 870 | 650 | 0.38 | 0.456 | Infotainment |
| LQH3NPZ150MME | 15 | 1212/3030 | 1.5 | 1020 | 660 | 0.29 | 0.348 | Infotainment |
| LQH3NPZ1R0MGR | 1 | 1212/3030 | 1 | 2080 | 1700 | 0.062 | 0.0744 | Infotainment |
| LQH3NPZ1R0MJR | 1 | 1212/3030 | 1.2 | 2780 | 2250 | 0.04 | 0.048 | Infotainment |
| LQH3NPZ1R0MME | 1 | 1212/3030 | 1.5 | 3000 | 2350 | 0.025 | 0.03 | Infotainment |
| LQH3NPZ1R5MGR | 1.5 | 1212/3030 | 1 | 2040 | 1400 | 0.074 | 0.0888 | Infotainment |
| LQH3NPZ1R5MJR | 1.5 | 1212/3030 | 1.2 | 2510 | 1950 | 0.049 | 0.0588 | Infotainment |
| LQH3NPZ220MGR | 22 | 1212/3030 | 1 | 750 | 390 | 0.53 | 0.636 | Infotainment |
| LQH3NPZ220MJR | 22 | 1212/3030 | 1.2 | 800 | 520 | 0.5 | 0.6 | Infotainment |
| LQH3NPZ220MME | 22 | 1212/3030 | 1.5 | 860 | 570 | 0.4 | 0.48 | Infotainment |
| LQH3NPZ2R2MGR | 2.2 | 1212/3030 | 1 | 1730 | 1180 | 0.087 | 0.1044 | Infotainment |
| LQH3NPZ2R2MJR | 2.2 | 1212/3030 | 1.2 | 2200 | 1800 | 0.068 | 0.0816 | Infotainment |
| LQH3NPZ2R2MME | 2.2 | 1212/3030 | 1.5 | 2100 | 1800 | 0.065 | 0.078 | Infotainment |
| LQH3NPZ330MGR | 33 | 1212/3030 | 1 | 600 | 320 | 0.86 | 1.032 | Infotainment |
| LQH3NPZ330MJR | 33 | 1212/3030 | 1.2 | 630 | 420 | 0.79 | 0.948 | Infotainment |
| LQH3NPZ330MME | 33 | 1212/3030 | 1.5 | 760 | 440 | 0.55 | 0.66 | Infotainment |
| LQH3NPZ3R3MGR | 3.3 | 1212/3030 | 1 | 1580 | 1050 | 0.12 | 0.144 | Infotainment |
| LQH3NPZ3R3MJR | 3.3 | 1212/3030 | 1.2 | 1700 | 1350 | 0.095 | 0.114 | Infotainment |
| LQH3NPZ3R3MME | 3.3 | 1212/3030 | 1.5 | 1900 | 1520 | 0.084 | 0.1008 | Infotainment |
| LQH3NPZ470MGR | 47 | 1212/3030 | 1 | 460 | 260 | 1.4 | 1.68 | Infotainment |
| LQH3NPZ470MJR | 47 | 1212/3030 | 1.2 | 570 | 360 | 1 | 1.2 | Infotainment |
| LQH3NPZ470MME | 47 | 1212/3030 | 1.5 | 610 | 380 | 0.82 | 0.984 | Infotainment |
| LQH3NPZ4R7MGR | 4.7 | 1212/3030 | 1 | 1520 | 850 | 0.14 | 0.168 | Infotainment |
| LQH3NPZ4R7MJR | 4.7 | 1212/3030 | 1.2 | 1580 | 1180 | 0.12 | 0.144 | Infotainment |
| LQH3NPZ4R7MME | 4.7 | 1212/3030 | 1.5 | 1700 | 1300 | 0.1 | 0.12 | Infotainment |
| LQH3NPZ560MME | 56 | 1212/3030 | 1.5 | 500 | 350 | 1 | 1.2 | Infotainment |
| LQH3NPZ680MME | 68 | 1212/3030 | 1.5 | 470 | 310 | 1.15 | 1.38 | Infotainment |
| LQH3NPZ6R8MGR | 6.8 | 1212/3030 | 1 | 1140 | 720 | 0.23 | 0.276 | Infotainment |
| LQH3NPZ6R8MJR | 6.8 | 1212/3030 | 1.2 | 1360 | 970 | 0.18 | 0.216 | Infotainment |
| LQH3NPZ6R8MME | 6.8 | 1212/3030 | 1.5 | 1450 | 1040 | 0.14 | 0.168 | Infotainment |
| LQH3NPZR47NGR | 0.47 | 1212/3030 | 1 | 2540 | 2820 | 0.047 | 0.0564 | Infotainment |
| LQH3NPZR68NJR | 0.68 | 1212/3030 | 1.2 | 2860 | 2700 | 0.032 | 0.0384 | Infotainment |
| LQH43PH100M26 | 10 | 1812/4532 | 2.8 | 1170 | 1050 | 0.147 | 0.1764 | Powertrain/Safety |
| LQH43PH101M26 | 100 | 1812/4532 | 2.8 | 320 | 320 | 1.538 | 1.8456 | Powertrain/Safety |
| LQH43PH151M26 | 150 | 1812/4532 | 2.8 | 260 | 280 | 2.362 | 2.8344 | Powertrain/Safety |
| LQH43PH1R0N26 | 1 | 1812/4532 | 2.8 | 3300 | 3400 | 0.026 | 0.0312 | Powertrain/Safety |
| LQH43PH220M26 | 22 | 1812/4532 | 2.8 | 780 | 700 | 0.327 | 0.3924 | Powertrain/Safety |
| LQH43PH221M26 | 220 | 1812/4532 | 2.8 | 240 | 220 | 2.9 | 3.48 | Powertrain/Safety |
| LQH43PH2R2M26 | 2.2 | 1812/4532 | 2.8 | 2500 | 2300 | 0.042 | 0.0504 | Powertrain/Safety |
| LQH43PH3R3M26 | 3.3 | 1812/4532 | 2.8 | 2100 | 1800 | 0.052 | 0.0624 | Powertrain/Safety |
| LQH43PH470M26 | 47 | 1812/4532 | 2.8 | 520 | 470 | 0.718 | 0.8616 | Powertrain/Safety |
| LQH43PH4R7M26 | 4.7 | 1812/4532 | 2.8 | 1600 | 1400 | 0.075 | 0.09 | Powertrain/Safety |
| LQH43PH6R8M26 | 6.8 | 1812/4532 | 2.8 | 1400 | 1200 | 0.098 | 0.1176 | Powertrain/Safety |
| LQH43PH8R2M26 | 8.2 | 1812/4532 | 2.8 | 1300 | 1100 | 0.128 | 0.1536 | Powertrain/Safety |
| LQH43PZ100M26 | 10 | 1812/4532 | 2.8 | 1170 | 1050 | 0.147 | 0.1764 | Infotainment |
| LQH43PZ101M26 | 100 | 1812/4532 | 2.8 | 320 | 320 | 1.538 | 1.8456 | Infotainment |
| LQH43PZ151M26 | 150 | 1812/4532 | 2.8 | 260 | 280 | 2.362 | 2.8344 | Infotainment |
| LQH43PZ1R0N26 | 1 | 1812/4532 | 2.8 | 3300 | 3400 | 0.026 | 0.0312 | Infotainment |
| LQH43PZ220M26 | 22 | 1812/4532 | 2.8 | 780 | 700 | 0.327 | 0.3924 | Infotainment |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I_temp. (mA) | I_saturation (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|---------------|-----------------|---------------------|------------------|--------------|-------------------|----------------|----------------|-------------------|
| LQH43PZ221M26 | 220 | 1812/4532 | 2.8 | 240 | 220 | 2.9 | 3.48 | Infotainment |
| LQH43PZ2R2M26 | 2.2 | 1812/4532 | 2.8 | 2500 | 2300 | 0.042 | 0.0504 | Infotainment |
| LQH43PZ3R3M26 | 3.3 | 1812/4532 | 2.8 | 2100 | 1800 | 0.052 | 0.0624 | Infotainment |
| LQH43PZ470M26 | 47 | 1812/4532 | 2.8 | 520 | 470 | 0.718 | 0.8616 | Infotainment |
| LQH43PZ4R7M26 | 4.7 | 1812/4532 | 2.8 | 1600 | 1400 | 0.075 | 0.09 | Infotainment |
| LQH43PZ6R8M26 | 6.8 | 1812/4532 | 2.8 | 1400 | 1200 | 0.098 | 0.1176 | Infotainment |
| LQH43PZ8R2M26 | 8.2 | 1812/4532 | 2.8 | 1300 | 1100 | 0.128 | 0.1536 | Infotainment |
| LQH44PZ100MGR | 10 | 1515/4040 | 1 | 1100 | 800 | 0.27 | 0.324 | Infotainment |
| LQH44PZ150MGR | 15 | 1515/4040 | 1 | 900 | 640 | 0.42 | 0.504 | Infotainment |
| LQH44PZ220MGR | 22 | 1515/4040 | 1 | 750 | 500 | 0.57 | 0.684 | Infotainment |
| LQH44PZ2R2NGR | 2.2 | 1515/4040 | 1 | 2000 | 1600 | 0.074 | 0.0888 | Infotainment |
| LQH44PZ330MGR | 33 | 1515/4040 | 1 | 480 | 400 | 1.4 | 1.68 | Infotainment |
| LQH44PZ3R3NGR | 3.3 | 1515/4040 | 1 | 1700 | 1500 | 0.11 | 0.132 | Infotainment |
| LQH44PZ470MGR | 47 | 1515/4040 | 1 | 410 | 360 | 1.7 | 2.04 | Infotainment |
| LQH44PZ4R7MGR | 4.7 | 1515/4040 | 1 | 1600 | 1200 | 0.13 | 0.156 | Infotainment |
| LQH44PZ6R8MGR | 6.8 | 1515/4040 | 1 | 1400 | 850 | 0.17 | 0.204 | Infotainment |
| LQH44PZR68NGR | 0.68 | 1515/4040 | 1 | 2500 | 2400 | 0.043 | 0.0516 | Infotainment |
| LQH5BPZ100MT0 | 10 | 2020/5050 | 2.2 | 1600 | 2000 | 0.106 | 0.1272 | Infotainment |
| LQH5BPZ150MT0 | 15 | 2020/5050 | 2.2 | 1200 | 1600 | 0.187 | 0.2244 | Infotainment |
| LQH5BPZ1R0NT0 | 1 | 2020/5050 | 2.2 | 3100 | 5800 | 0.019 | 0.0228 | Infotainment |
| LQH5BPZ1R2NT0 | 1.2 | 2020/5050 | 2.2 | 3100 | 5400 | 0.019 | 0.0228 | Infotainment |
| LQH5BPZ1R5NT0 | 1.5 | 2020/5050 | 2.2 | 3000 | 5000 | 0.024 | 0.0288 | Infotainment |
| LQH5BPZ220MT0 | 22 | 2020/5050 | 2.2 | 1050 | 1400 | 0.259 | 0.3108 | Infotainment |
| LQH5BPZ2R2NT0 | 2.2 | 2020/5050 | 2.2 | 2600 | 4000 | 0.03 | 0.036 | Infotainment |
| LQH5BPZ2R7NT0 | 2.7 | 2020/5050 | 2.2 | 2500 | 3800 | 0.035 | 0.042 | Infotainment |
| LQH5BPZ3R3NT0 | 3.3 | 2020/5050 | 2.2 | 2300 | 3500 | 0.044 | 0.0528 | Infotainment |
| LQH5BPZ4R7NT0 | 4.7 | 2020/5050 | 2.2 | 2000 | 3000 | 0.058 | 0.0696 | Infotainment |
| LQH5BPZ6R8NT0 | 6.8 | 2020/5050 | 2.2 | 1650 | 2500 | 0.083 | 0.0996 | Infotainment |
| LQH5BPZR47NT0 | 0.47 | 2020/5050 | 2.2 | 4000 | 7700 | 0.012 | 0.0144 | Infotainment |
| LQM18PZ1R0MCH | 1 | 0603/1608 | 0.65 | 950 | 600 | 0.23 | 0.29 | Infotainment |
| LQM18PZ2R2MCH | 2.2 | 0603/1608 | 0.65 | 750 | 200 | 0.38 | 0.48 | Infotainment |
| LQM18PZ2R2MDH | 2.2 | 0603/1608 | 0.75 | 650 | 250 | 0.38 | 0.47 | Infotainment |
| LQM18PZ2R2MFH | 2.2 | 0603/1608 | 0.95 | 700 | 300 | 0.38 | 0.47 | Infotainment |
| LQM18PZ2R5NCH | 2.5 | 0603/1608 | 0.6 | 900 | 100 | 0.24 | 0.3 | Infotainment |
| LQM21PH2R2MGC | 2.2 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | Powertrain/Safety |
| LQM21PH2R2NGC | 2.2 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | Powertrain/Safety |
| LQM21PZ1R0MC0 | 1 | 0805/2012 | 0.55 | 800 | | 0.19 | 0.238 | Infotainment |
| LQM21PZ1R0NGC | 1 | 0805/2012 | 1 | 900 | | 0.1 | 0.125 | Infotainment |
| LQM21PZ1R0NGR | 1 | 0805/2012 | 1 | 1300 | | 0.066 | 0.0825 | Infotainment |
| LQM21PZ1R5MC0 | 1.5 | 0805/2012 | 0.55 | 700 | | 0.26 | 0.325 | Infotainment |
| LQM21PZ2R2MC0 | 2.2 | 0805/2012 | 0.55 | 600 | | 0.34 | 0.425 | Infotainment |
| LQM21PZ2R2NGC | 2.2 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | Infotainment |
| LQM21PZ3R3MG0 | 3.3 | 0805/2012 | 1 | 800 | | 0.165 | 0.207 | Infotainment |
| LQM21PZ3R3MGR | 3.3 | 0805/2012 | 1 | 1000 | | 0.15 | 0.188 | Infotainment |
| LQM21PZ3R3NG0 | 3.3 | 0805/2012 | 1 | 800 | | 0.165 | 0.207 | Infotainment |
| LQM21PZ3R3NGR | 3.3 | 0805/2012 | 1 | 1000 | | 0.15 | 0.188 | Infotainment |
| LQM21PZ4R7MGR | 4.7 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | Infotainment |
| LQM21PZ4R7NGR | 4.7 | 0805/2012 | 1 | 800 | | 0.23 | 0.288 | Infotainment |
| LQM21PZR47MC0 | 0.47 | 0805/2012 | 0.55 | 1100 | | 0.12 | 0.15 | Infotainment |
| LQM21PZR47MG0 | 0.47 | 0805/2012 | 1 | 1300 | | 0.075 | 0.094 | Infotainment |
| LQM21PZR54MG0 | 0.54 | 0805/2012 | 1 | 1300 | | 0.075 | 0.094 | Infotainment |
| LQM2HPZ1R0MG0 | 1 | 1008/2520 | 1 | 1600 | | 0.055 | 0.069 | Infotainment |
| LQM2HPZ1R0MGC | 1 | 1008/2520 | 1 | 1500 | | 0.08 | 0.1 | Infotainment |
| LQM2HPZ1R0MJ0 | 1 | 1008/2520 | 1.2 | 1500 | | 0.09 | 0.113 | Infotainment |
| LQM2HPZ1R0MJC | 1 | 1008/2520 | 1.2 | 1500 | | 0.086 | 0.108 | Infotainment |
| LQM2HPZ1R5MG0 | 1.5 | 1008/2520 | 1 | 1500 | | 0.07 | 0.088 | Infotainment |
| LQM2HPZ2R2MG0 | 2.2 | 1008/2520 | 1 | 1300 | | 0.08 | 0.1 | Infotainment |
| LQM2HPZ2R2MGS | 2.2 | 1008/2520 | 1 | 1100 | | 0.18 | 0.225 | Infotainment |
| LQM2HPZ2R2MJ0 | 2.2 | 1008/2520 | 1.2 | 1000 | | 0.12 | 0.15 | Infotainment |
| LQM2HPZ2R2NJC | 2.2 | 1008/2520 | 1.2 | 1000 | | 0.175 | 0.219 | Infotainment |
| LQM2HPZ3R3MG0 | 3.3 | 1008/2520 | 1 | 1200 | | 0.1 | 0.125 | Infotainment |
| LQM2HPZ3R3MGC | 3.3 | 1008/2520 | 1 | 1000 | | 0.16 | 0.2 | Infotainment |
| LQM2HPZ3R3MGS | 3.3 | 1008/2520 | 1 | 1050 | | 0.21 | 0.263 | Infotainment |
| LQM2HPZ3R3MJ0 | 3.3 | 1008/2520 | 1.2 | 1000 | | 0.12 | 0.15 | Infotainment |
| LQM2HPZ4R7MG0 | 4.7 | 1008/2520 | 1 | 1100 | | 0.11 | 0.138 | Infotainment |
| LQM2HPZ4R7MGC | 4.7 | 1008/2520 | 1 | 800 | | 0.18 | 0.225 | Infotainment |
| LQM2HPZ4R7MGS | 4.7 | 1008/2520 | 1 | 1000 | | 0.25 | 0.313 | Infotainment |
| LQM2HPZR47MG0 | 0.47 | 1008/2520 | 1 | 1800 | | 0.04 | 0.05 | Infotainment |
| LQM2HPZR56ME0 | 0.56 | 1008/2520 | 0.8 | 1500 | | 0.06 | 0.075 | Infotainment |
| LQM2MPZ1R0NG0 | 1 | 0806/2016 | 1 | 1400 | | 0.085 | 0.107 | Infotainment |
| LQM2MPZ1R5MG0 | 1.5 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | Infotainment |
| LQM2MPZ1R5NG0 | 1.5 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | Infotainment |
| LQM2MPZ2R2MG0 | 2.2 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | Infotainment |
| LQM2MPZ2R2NG0 | 2.2 | 0806/2016 | 1 | 1200 | | 0.11 | 0.138 | Infotainment |
| LQM2MPZ3R3NG0 | 3.3 | 0806/2016 | 1 | 1200 | | 0.12 | 0.15 | Infotainment |
| LQM2MPZ4R7MG0 | 4.7 | 0806/2016 | 1 | 1100 | | 0.14 | 0.175 | Infotainment |
| LQM2MPZ4R7NG0 | 4.7 | 0806/2016 | 1 | 1100 | | 0.14 | 0.175 | Infotainment |
| LQM2MPZR10MJH | 0.1 | 0806/2016 | 1.2 | 4000 | 4000 | 0.38 | 0.019 | Infotainment |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|-----------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------------|
| LQM2MPZR47MG0 | 0.47 | 0806/2016 | 1 | 1600 | | 0.06 | 0.075 | Infotainment |
| LQM2MPZR47NG0 | 0.47 | 0806/2016 | 1 | 1600 | | 0.06 | 0.075 | Infotainment |
| MBH10145C-100MA | 10 | 4141/104104 | 4.8 | 3300 | 3100 | 0.037 | 0.0444 | Powertrain/Safety |
| MBH10145C-150MA | 15 | 4141/104104 | 4.8 | 2500 | 2600 | 0.048 | 0.0576 | Powertrain/Safety |
| MBH10145C-220MA | 22 | 4141/104104 | 4.8 | 2300 | 2200 | 0.06 | 0.072 | Powertrain/Safety |
| MBH10145C-3R3NA | 3.3 | 4141/104104 | 4.8 | 4300 | 4900 | 0.016 | 0.0204 | Powertrain/Safety |
| MBH10145C-5R6NA | 5.6 | 4141/104104 | 4.8 | 3700 | 4100 | 0.022 | 0.0264 | Powertrain/Safety |
| MBH12282C-100MA | 10 | 4949/125125 | 8.5 | 5300 | 5700 | 0.018 | 0.0216 | Powertrain/Safety |
| MBH12282C-150MA | 15 | 4949/125125 | 8.5 | 4700 | 4400 | 0.021 | 0.0252 | Powertrain/Safety |
| MBH12282C-220MA | 22 | 4949/125125 | 8.5 | 4000 | 4800 | 0.029 | 0.0348 | Powertrain/Safety |
| MBH12282C-4R7NA | 4.7 | 4949/125125 | 8.5 | 5900 | 7900 | 0.013 | 0.0156 | Powertrain/Safety |
| MBH12282C-6R8NA | 6.8 | 4949/125125 | 8.5 | 5700 | 7000 | 0.015 | 0.018 | Powertrain/Safety |
| MBH12575C-100MA | 10 | 5050/128128 | 6.8 | 5200 | 4900 | 0.016 | 0.0192 | Powertrain/Safety |
| MBH12575C-150MA | 15 | 5050/128128 | 6.8 | 4700 | 3800 | 0.019 | 0.0228 | Powertrain/Safety |
| MBH12575C-220MA | 22 | 5050/128128 | 6.8 | 4000 | 3100 | 0.027 | 0.0324 | Powertrain/Safety |
| MBH12575C-5R6NA | 5.6 | 5050/128128 | 6.8 | 6000 | 7000 | 0.012 | 0.0144 | Powertrain/Safety |
| MBH12575C-6R8NA | 6.8 | 5050/128128 | 6.8 | 5600 | 5900 | 0.014 | 0.0168 | Powertrain/Safety |
| MBH6045C-100MA | 10 | 2424/6262 | 4.8 | 2000 | 2300 | 0.063 | 0.0756 | Powertrain/Safety |
| MBH6045C-100MB | 10 | 2424/6262 | 4.8 | 2500 | 1200 | 0.038 | 0.0456 | Powertrain/Safety |
| MBH6045C-101MA | 100 | 2424/6262 | 4.8 | 700 | 710 | 0.487 | 0.5844 | Powertrain/Safety |
| MBH6045C-101MB | 100 | 2424/6262 | 4.8 | 830 | 400 | 0.34 | 0.408 | Powertrain/Safety |
| MBH6045C-150MA | 15 | 2424/6262 | 4.8 | 1500 | 1800 | 0.099 | 0.1188 | Powertrain/Safety |
| MBH6045C-150MB | 15 | 2424/6262 | 4.8 | 2100 | 900 | 0.055 | 0.066 | Powertrain/Safety |
| MBH6045C-151MA | 150 | 2424/6262 | 4.8 | 510 | 580 | 0.772 | 0.9264 | Powertrain/Safety |
| MBH6045C-151MB | 150 | 2424/6262 | 4.8 | 710 | 320 | 0.48 | 0.576 | Powertrain/Safety |
| MBH6045C-1R5NA | 1.5 | 2424/6262 | 4.8 | 4300 | 6300 | 0.017 | 0.0221 | Powertrain/Safety |
| MBH6045C-1R5NB | 1.5 | 2424/6262 | 4.8 | 4400 | 3500 | 0.015 | 0.0195 | Powertrain/Safety |
| MBH6045C-220MA | 22 | 2424/6262 | 4.8 | 1200 | 1500 | 0.139 | 0.1668 | Powertrain/Safety |
| MBH6045C-220MB | 22 | 2424/6262 | 4.8 | 1700 | 900 | 0.078 | 0.0936 | Powertrain/Safety |
| MBH6045C-221MA | 220 | 2424/6262 | 4.8 | 480 | 470 | 1.08 | 1.296 | Powertrain/Safety |
| MBH6045C-221MB | 220 | 2424/6262 | 4.8 | 560 | 260 | 0.78 | 0.936 | Powertrain/Safety |
| MBH6045C-330MA | 33 | 2424/6262 | 4.8 | 1100 | 1200 | 0.178 | 0.2136 | Powertrain/Safety |
| MBH6045C-330MB | 33 | 2424/6262 | 4.8 | 1500 | 700 | 0.103 | 0.1235 | Powertrain/Safety |
| MBH6045C-331MB | 330 | 2424/6262 | 4.8 | 480 | 230 | 0.97 | 1.164 | Powertrain/Safety |
| MBH6045C-3R3NA | 3.3 | 2424/6262 | 4.8 | 3400 | 4100 | 0.024 | 0.0312 | Powertrain/Safety |
| MBH6045C-3R3NB | 3.3 | 2424/6262 | 4.8 | 3500 | 2300 | 0.019 | 0.0247 | Powertrain/Safety |
| MBH6045C-470MA | 47 | 2424/6262 | 4.8 | 1000 | 1100 | 0.256 | 0.3072 | Powertrain/Safety |
| MBH6045C-470MB | 47 | 2424/6262 | 4.8 | 1100 | 560 | 0.13 | 0.156 | Powertrain/Safety |
| MBH6045C-471MB | 470 | 2424/6262 | 4.8 | 410 | 180 | 1.42 | 1.704 | Powertrain/Safety |
| MBH6045C-4R7NA | 4.7 | 2424/6262 | 4.8 | 2800 | 3300 | 0.029 | 0.0377 | Powertrain/Safety |
| MBH6045C-4R7NB | 4.7 | 2424/6262 | 4.8 | 3200 | 2000 | 0.023 | 0.0299 | Powertrain/Safety |
| MBH6045C-680MA | 68 | 2424/6262 | 4.8 | 840 | 900 | 0.347 | 0.4164 | Powertrain/Safety |
| MBH6045C-680MB | 68 | 2424/6262 | 4.8 | 940 | 480 | 0.215 | 0.258 | Powertrain/Safety |
| MBH6045C-6R8NA | 6.8 | 2424/6262 | 4.8 | 2100 | 2700 | 0.051 | 0.0663 | Powertrain/Safety |
| MBH6045C-6R8NB | 6.8 | 2424/6262 | 4.8 | 2600 | 1600 | 0.027 | 0.0351 | Powertrain/Safety |
| MBH7045C-100MA | 10 | 2828/7272 | 4.8 | 2500 | 1300 | 0.036 | 0.0432 | Powertrain/Safety |
| MBH7045C-100MB | 10 | 2828/7272 | 4.8 | 2700 | 2000 | 0.038 | 0.0456 | Powertrain/Safety |
| MBH7045C-101MA | 100 | 2828/7272 | 4.8 | 1000 | 480 | 0.25 | 0.3 | Powertrain/Safety |
| MBH7045C-101MB | 100 | 2828/7272 | 4.8 | 840 | 630 | 0.31 | 0.372 | Powertrain/Safety |
| MBH7045C-102MA | 1000 | 2828/7272 | 4.8 | 310 | 140 | 2.28 | 2.736 | Powertrain/Safety |
| MBH7045C-150MA | 15 | 2828/7272 | 4.8 | 2100 | 1100 | 0.052 | 0.0624 | Powertrain/Safety |
| MBH7045C-150MB | 15 | 2828/7272 | 4.8 | 2100 | 1600 | 0.054 | 0.0648 | Powertrain/Safety |
| MBH7045C-151MA | 150 | 2828/7272 | 4.8 | 790 | 390 | 0.34 | 0.408 | Powertrain/Safety |
| MBH7045C-151MB | 150 | 2828/7272 | 4.8 | 670 | 510 | 0.46 | 0.552 | Powertrain/Safety |
| MBH7045C-220MA | 22 | 2828/7272 | 4.8 | 1900 | 1000 | 0.061 | 0.0732 | Powertrain/Safety |
| MBH7045C-220MB | 22 | 2828/7272 | 4.8 | 1800 | 1400 | 0.07 | 0.084 | Powertrain/Safety |
| MBH7045C-221MA | 220 | 2828/7272 | 4.8 | 650 | 340 | 0.52 | 0.624 | Powertrain/Safety |
| MBH7045C-330MA | 33 | 2828/7272 | 4.8 | 1400 | 800 | 0.096 | 0.1152 | Powertrain/Safety |
| MBH7045C-330MB | 33 | 2828/7272 | 4.8 | 1500 | 1100 | 0.105 | 0.126 | Powertrain/Safety |
| MBH7045C-331MA | 330 | 2828/7272 | 4.8 | 540 | 250 | 0.74 | 0.888 | Powertrain/Safety |
| MBH7045C-3R3NA | 3.3 | 2828/7272 | 4.8 | 3500 | 2500 | 0.019 | 0.0228 | Powertrain/Safety |
| MBH7045C-3R3NB | 3.3 | 2828/7272 | 4.8 | 3400 | 3300 | 0.021 | 0.0252 | Powertrain/Safety |
| MBH7045C-470MA | 47 | 2828/7272 | 4.8 | 1300 | 700 | 0.125 | 0.15 | Powertrain/Safety |
| MBH7045C-470MB | 47 | 2828/7272 | 4.8 | 1100 | 900 | 0.15 | 0.18 | Powertrain/Safety |
| MBH7045C-471MA | 470 | 2828/7272 | 4.8 | 430 | 220 | 1.05 | 1.26 | Powertrain/Safety |
| MBH7045C-4R7NA | 4.7 | 2828/7272 | 4.8 | 3200 | 2000 | 0.023 | 0.0276 | Powertrain/Safety |
| MBH7045C-4R7NB | 4.7 | 2828/7272 | 4.8 | 2900 | 3000 | 0.024 | 0.0288 | Powertrain/Safety |
| MBH7045C-680MA | 68 | 2828/7272 | 4.8 | 1100 | 590 | 0.175 | 0.21 | Powertrain/Safety |
| MBH7045C-680MB | 68 | 2828/7272 | 4.8 | 1000 | 750 | 0.21 | 0.252 | Powertrain/Safety |
| MBH7045C-681MA | 680 | 2828/7272 | 4.8 | 360 | 200 | 1.48 | 1.776 | Powertrain/Safety |
| MBH7045C-6R8NA | 6.8 | 2828/7272 | 4.8 | 2700 | 1700 | 0.028 | 0.0336 | Powertrain/Safety |
| MBH7045C-6R8NB | 6.8 | 2828/7272 | 4.8 | 2800 | 2400 | 0.029 | 0.0348 | Powertrain/Safety |
| MDH10060C-100MA | 10 | 4039/101100 | 6.3 | 3800 | 4100 | 0.017 | 0.0221 | Powertrain/Safety |
| MDH10060C-100MB | 10 | 4039/101100 | 6.3 | 3400 | 4800 | 0.019 | 0.0247 | Powertrain/Safety |
| MDH10060C-101MA | 100 | 4039/101100 | 6.3 | 1300 | 1300 | 0.15 | 0.195 | Powertrain/Safety |
| MDH10060C-101MB | 100 | 4039/101100 | 6.3 | 1200 | 1500 | 0.16 | 0.208 | Powertrain/Safety |
| MDH10060C-150MA | 15 | 4039/101100 | 6.3 | 3100 | 3400 | 0.027 | 0.0351 | Powertrain/Safety |
| MDH10060C-150MB | 15 | 4039/101100 | 6.3 | 2800 | 3900 | 0.027 | 0.0351 | Powertrain/Safety |

| Part Number | Inductance (uH) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|-----------------|-----------------|---------------------|------------------|-------------------------|------------------------------|----------------|----------------|-------------------|
| MDH10060C-151MA | 150 | 4039/101100 | 6.3 | 1000 | 1000 | 0.24 | 0.312 | Powertrain/Safety |
| MDH10060C-151MB | 150 | 4039/101100 | 6.3 | 1000 | 1200 | 0.24 | 0.312 | Powertrain/Safety |
| MDH10060C-1R5NB | 1.5 | 4039/101100 | 6.3 | 6100 | 13000 | 0.0053 | 0.00689 | Powertrain/Safety |
| MDH10060C-220MA | 22 | 4039/101100 | 6.3 | 2700 | 2800 | 0.04 | 0.052 | Powertrain/Safety |
| MDH10060C-220MB | 22 | 4039/101100 | 6.3 | 2600 | 3300 | 0.04 | 0.052 | Powertrain/Safety |
| MDH10060C-221MA | 220 | 4039/101100 | 6.3 | 880 | 880 | 0.35 | 0.455 | Powertrain/Safety |
| MDH10060C-221MB | 220 | 4039/101100 | 6.3 | 800 | 1000 | 0.345 | 0.4485 | Powertrain/Safety |
| MDH10060C-2R2NB | 2.2 | 4039/101100 | 6.3 | 5600 | 11000 | 0.0063 | 0.00819 | Powertrain/Safety |
| MDH10060C-330MA | 33 | 4039/101100 | 6.3 | 2200 | 2200 | 0.061 | 0.0793 | Powertrain/Safety |
| MDH10060C-330MB | 33 | 4039/101100 | 6.3 | 2100 | 2600 | 0.061 | 0.0793 | Powertrain/Safety |
| MDH10060C-331MA | 330 | 4039/101100 | 6.3 | 720 | 720 | 0.48 | 0.624 | Powertrain/Safety |
| MDH10060C-331MB | 330 | 4039/101100 | 6.3 | 680 | 840 | 0.49 | 0.637 | Powertrain/Safety |
| MDH10060C-3R3NB | 3.3 | 4039/101100 | 6.3 | 5300 | 8700 | 0.0085 | 0.01105 | Powertrain/Safety |
| MDH10060C-470MA | 47 | 4039/101100 | 6.3 | 2000 | 1900 | 0.074 | 0.0962 | Powertrain/Safety |
| MDH10060C-470MB | 47 | 4039/101100 | 6.3 | 1800 | 2200 | 0.074 | 0.0962 | Powertrain/Safety |
| MDH10060C-471MA | 470 | 4039/101100 | 6.3 | 560 | 560 | 0.75 | 0.975 | Powertrain/Safety |
| MDH10060C-471MB | 470 | 4039/101100 | 6.3 | 560 | 700 | 0.79 | 1.027 | Powertrain/Safety |
| MDH10060C-4R7NA | 4.7 | 4039/101100 | 6.3 | 4900 | 5900 | 0.01 | 0.013 | Powertrain/Safety |
| MDH10060C-4R7NB | 4.7 | 4039/101100 | 6.3 | 4800 | 7100 | 0.011 | 0.0143 | Powertrain/Safety |
| MDH10060C-680MA | 68 | 4039/101100 | 6.3 | 1700 | 1600 | 0.091 | 0.1183 | Powertrain/Safety |
| MDH10060C-680MB | 68 | 4039/101100 | 6.3 | 1500 | 1800 | 0.099 | 0.1287 | Powertrain/Safety |
| MDH10060C-6R8NA | 6.8 | 4039/101100 | 6.3 | 4300 | 5000 | 0.013 | 0.0169 | Powertrain/Safety |
| MDH10060C-6R8NB | 6.8 | 4039/101100 | 6.3 | 3800 | 6000 | 0.014 | 0.0182 | Powertrain/Safety |
| MDH12577C-100MA | 10 | 5049/128125 | 8 | 4700 | 7700 | 0.014 | 0.0182 | Powertrain/Safety |
| MDH12577C-101MA | 100 | 5049/128125 | 8 | 1600 | 2300 | 0.108 | 0.1404 | Powertrain/Safety |
| MDH12577C-150MA | 15 | 5049/128125 | 8 | 3600 | 5700 | 0.022 | 0.0286 | Powertrain/Safety |
| MDH12577C-151MA | 150 | 5049/128125 | 8 | 1400 | 1900 | 0.17 | 0.221 | Powertrain/Safety |
| MDH12577C-220MA | 22 | 5049/128125 | 8 | 3000 | 4900 | 0.033 | 0.0429 | Powertrain/Safety |
| MDH12577C-221MA | 220 | 5049/128125 | 8 | 1100 | 1500 | 0.25 | 0.325 | Powertrain/Safety |
| MDH12577C-330MA | 33 | 5049/128125 | 8 | 2700 | 4000 | 0.039 | 0.0507 | Powertrain/Safety |
| MDH12577C-331MA | 330 | 5049/128125 | 8 | 900 | 1300 | 0.41 | 0.533 | Powertrain/Safety |
| MDH12577C-470MA | 47 | 5049/128125 | 8 | 2100 | 3400 | 0.066 | 0.0858 | Powertrain/Safety |
| MDH12577C-471MA | 470 | 5049/128125 | 8 | 700 | 1000 | 0.54 | 0.702 | Powertrain/Safety |
| MDH12577C-4R7NA | 4.7 | 5049/128125 | 8 | 5400 | 11000 | 0.009 | 0.0117 | Powertrain/Safety |
| MDH12577C-680MA | 68 | 5049/128125 | 8 | 1800 | 2800 | 0.09 | 0.117 | Powertrain/Safety |
| MDH12577C-6R8NA | 6.8 | 5049/128125 | 8 | 4800 | 8600 | 0.012 | 0.0156 | Powertrain/Safety |
| MDH6045C-100MA | 10 | 2524/6360 | 4.8 | 1900 | 2000 | 0.04 | 0.052 | Powertrain/Safety |
| MDH6045C-100MB | 10 | 2524/6360 | 4.8 | 2000 | 1800 | 0.038 | 0.0494 | Powertrain/Safety |
| MDH6045C-101MA | 100 | 2524/6360 | 4.8 | 640 | 600 | 0.34 | 0.442 | Powertrain/Safety |
| MDH6045C-101MB | 100 | 2524/6360 | 4.8 | 680 | 560 | 0.34 | 0.442 | Powertrain/Safety |
| MDH6045C-150MA | 15 | 2524/6360 | 4.8 | 1700 | 1600 | 0.06 | 0.078 | Powertrain/Safety |
| MDH6045C-150MB | 15 | 2524/6360 | 4.8 | 1800 | 1400 | 0.055 | 0.0715 | Powertrain/Safety |
| MDH6045C-151MA | 150 | 2524/6360 | 4.8 | 540 | 520 | 0.52 | 0.676 | Powertrain/Safety |
| MDH6045C-151MB | 150 | 2524/6360 | 4.8 | 580 | 440 | 0.5 | 0.65 | Powertrain/Safety |
| MDH6045C-1R0NA | 1 | 2524/6360 | 4.8 | 3900 | 5800 | 0.011 | 0.0143 | Powertrain/Safety |
| MDH6045C-1R2NB | 1.2 | 2524/6360 | 4.8 | 3800 | 5500 | 0.011 | 0.0143 | Powertrain/Safety |
| MDH6045C-1R5NA | 1.5 | 2524/6360 | 4.8 | 3600 | 5000 | 0.013 | 0.0169 | Powertrain/Safety |
| MDH6045C-220MA | 22 | 2524/6360 | 4.8 | 1400 | 1400 | 0.082 | 0.1066 | Powertrain/Safety |
| MDH6045C-220MB | 22 | 2524/6360 | 4.8 | 1400 | 1200 | 0.08 | 0.104 | Powertrain/Safety |
| MDH6045C-221MA | 220 | 2524/6360 | 4.8 | 440 | 400 | 0.72 | 0.936 | Powertrain/Safety |
| MDH6045C-221MB | 220 | 2524/6360 | 4.8 | 480 | 360 | 0.7 | 0.91 | Powertrain/Safety |
| MDH6045C-2R2NA | 2.2 | 2524/6360 | 4.8 | 3400 | 4200 | 0.015 | 0.0195 | Powertrain/Safety |
| MDH6045C-330MA | 33 | 2524/6360 | 4.8 | 1200 | 1000 | 0.13 | 0.169 | Powertrain/Safety |
| MDH6045C-330MB | 33 | 2524/6360 | 4.8 | 1300 | 960 | 0.105 | 0.1365 | Powertrain/Safety |
| MDH6045C-331MB | 330 | 2524/6360 | 4.8 | 380 | 300 | 0.97 | 1.261 | Powertrain/Safety |
| MDH6045C-3R3NA | 3.3 | 2524/6360 | 4.8 | 3000 | 3600 | 0.019 | 0.0247 | Powertrain/Safety |
| MDH6045C-470MA | 47 | 2524/6360 | 4.8 | 1000 | 880 | 0.16 | 0.208 | Powertrain/Safety |
| MDH6045C-470MB | 47 | 2524/6360 | 4.8 | 1100 | 760 | 0.13 | 0.169 | Powertrain/Safety |
| MDH6045C-471MB | 470 | 2524/6360 | 4.8 | 340 | 240 | 1.45 | 1.885 | Powertrain/Safety |
| MDH6045C-4R7NA | 4.7 | 2524/6360 | 4.8 | 2700 | 2900 | 0.023 | 0.0299 | Powertrain/Safety |
| MDH6045C-680MA | 68 | 2524/6360 | 4.8 | 800 | 720 | 0.22 | 0.286 | Powertrain/Safety |
| MDH6045C-680MB | 68 | 2524/6360 | 4.8 | 840 | 680 | 0.2 | 0.26 | Powertrain/Safety |
| MDH6045C-6R8NA | 6.8 | 2524/6360 | 4.8 | 2500 | 2500 | 0.027 | 0.0351 | Powertrain/Safety |
| MDH7045C-100MA | 10 | 2928/7470 | 4.8 | 2600 | 2500 | 0.033 | 0.0429 | Powertrain/Safety |
| MDH7045C-101MA | 100 | 2928/7470 | 4.8 | 800 | 750 | 0.29 | 0.377 | Powertrain/Safety |
| MDH7045C-150MA | 15 | 2928/7470 | 4.8 | 1800 | 2000 | 0.055 | 0.0715 | Powertrain/Safety |
| MDH7045C-151MA | 150 | 2928/7470 | 4.8 | 600 | 640 | 0.43 | 0.559 | Powertrain/Safety |
| MDH7045C-1R0NB | 1 | 2928/7470 | 4.8 | 4700 | 8800 | 0.009 | 0.0117 | Powertrain/Safety |
| MDH7045C-1R5NB | 1.5 | 2928/7470 | 4.8 | 4300 | 7100 | 0.01 | 0.013 | Powertrain/Safety |
| MDH7045C-220MA | 22 | 2928/7470 | 4.8 | 1700 | 1600 | 0.069 | 0.0897 | Powertrain/Safety |
| MDH7045C-221MA | 220 | 2928/7470 | 4.8 | 510 | 530 | 0.55 | 0.715 | Powertrain/Safety |
| MDH7045C-2R2NB | 2.2 | 2928/7470 | 4.8 | 4100 | 5800 | 0.013 | 0.0169 | Powertrain/Safety |
| MDH7045C-330MA | 33 | 2928/7470 | 4.8 | 1300 | 1400 | 0.097 | 0.1261 | Powertrain/Safety |
| MDH7045C-331MA | 330 | 2928/7470 | 4.8 | 490 | 420 | 0.8 | 1.04 | Powertrain/Safety |
| MDH7045C-3R3NB | 3.3 | 2928/7470 | 4.8 | 3400 | 5000 | 0.016 | 0.0208 | Powertrain/Safety |
| MDH7045C-470MA | 47 | 2928/7470 | 4.8 | 1100 | 1100 | 0.13 | 0.169 | Powertrain/Safety |
| MDH7045C-471MA | 470 | 2928/7470 | 4.8 | 350 | 360 | 1.2 | 1.56 | Powertrain/Safety |
| MDH7045C-4R7NB | 4.7 | 2928/7470 | 4.8 | 3000 | 4200 | 0.018 | 0.0234 | Powertrain/Safety |

| Part Number | Inductance (μ H) | Size code (inch/mm) | T size (mm Max.) | I _{temp.} (mA) | I _{saturation} (mA) | DCR (ohm Typ.) | DCR (ohm Max.) | Application |
|----------------|--------------------------|------------------------|---------------------|----------------------------|---------------------------------|-------------------|-------------------|-------------------|
| MDH7045C-680MA | 68 | 2928/7470 | 4.8 | 880 | 960 | 0.2 | 0.26 | Powertrain/Safety |
| MDH7045C-6R8NB | 6.8 | 2928/7470 | 4.8 | 2800 | 3400 | 0.022 | 0.0286 | Powertrain/Safety |