

# Datasheet of SAW Device

# SAW Duplexer

for Band12 / Unbalanced / LR /1814

# Murata PN: SAYEY707MBA0F0A



- ≻ LTE-A
- High Power Durability
- ➢ Good 3f Linearity



Note : Murata SAW Component is applicable for Cellular /Cordless phone (Terminal) relevant market only. Please also read caution at the end of this document.



Revision Number	Date	Description
SAYEY707MBA0F0A_rev. A	Mar-05-2014	∎ Initial Release
SAYEY707MBA0F0A_rev. B	Mar-31-2014	■ Updated by new version
SAYEY707MBA0F0A_rev. C	Jul-04-2014	■ Updated for MP
SAYEY707MBA0F0A_rev. D	Sep-03-2015	■ Updated for Feature
SAYEY707MBA0F0A_rev. E	Sep-08-2015	■ Updated for Feature
SAYEY707MBA0F0A_rev. F	Jun-24-2016	■ Updated for SPEC
SAYEY707MBA0F0A_rev. G	Sep-06-2016	Updated General Information
SAYEY707MBA0F0A_rev. H	Aug-31-2017	Updated General Information
SAYEY707MBA0F0A_rev. I	Nov-13-2017	■ Updated SPEC

- Operating temperature
- : -20 to +85 deg.C
- Storage temperature
- : -40 to +85 deg.C


- Input Power

- : +30.0 dBm 5000 h +50 deg.C
- D.C. Volatage between the terminals
- : 3V (25+/-2 deg.C)
- Minimum Resistance between the terminals  $\pm$  10M ohm : Yes
- RoHS compliance

- ESD (ElectroStatic Discharge) sensitive device









# Electrical Characteristic < TX→ANT. >

T.	$X \rightarrow ANT.$			( -20	to +85 d		Unit	Note	
				min.	typ.*	max.			
Center Frequency					707.5		MHz		
Insertion Loss	699.25 to	715.75			1.9	2.4	dB		
	701.5 to	713.5	MHz		1.5	2.2	dB <sub>INT</sub>	Any 4.5MHz	
Ripple Deviation	699.25 to	715.75			0.8	2.0	dB		
VSWR	699.25 to	715.75			1.6	2.0		ANT.	
	699.25 to	715.75			1.7	2.0		TX	
Absolute Attenuation	10. to	685.	MHz	30	40		dB		
	722. to	729.	MHz	2.0	10.0		dB	Ch56	
	729.25 to			45	57		dB	RX	
	746. to	768.	MHz	30	42		dB		
	768. to	805.	MHz	25	41		dB		
	824. to	849.	MHz	30	41		dB	B5 TX	
	869. to	894.	MHz	36	41		dB		
	1398. to	1432.	MHz	30	41		dB	2f	
	1559. to	1563.	MHz	35	38		dB	COMPASS	
	1565.42 to	1573.37		35	38		dB	Lower GPS	
	1573.37 to	1577.47		35	38		dB	Regular GPS	
	1577.47 to	1585.42		35	38		dB	Upper GPS	
	1597.55 to			35	38		dB	GLONASS	
	1710. to		MHz	30	36		dB	B4 TX	
	1805. to	1880.	MHz	30	35		dB	DCS RX	
	1930. to		MHz	29	34		dB		
	2097. to		MHz	29	34		dB	3f, B1 RX	
	2155. to		MHz	29	34		dB	B1 RX	
	2400. to	2484.	MHz	25	35		dB	ISM2.4	
	2816. to		MHz	12	21		dB	4f	
	4900. to	5950.	MHz	5.0	10.0		dB	ISM 5G	
								1	
				ļ					
				ļ	<u> </u>				
								1	
				ļ				1	
				<u> </u>	<u> </u>				
								1	
								1	
				ļ				l	
				<u> </u>	<u> </u>				
								* Typical value at 25+2deg (	

\* Typical value at 25±2deg.C



## Electrical Characteristic $\langle ANT. \rightarrow RX \rangle$

A	NT. $\rightarrow RX$			Cha (-20	racteri to +85 d	stics eg.C)	Unit	Note		
				min.	typ.*	max.				
Center Frequency					737.5		MHz			
Insertion Loss	729.25	to 745.75	5 MHz		1.8	2.4	dB			
		to 743.5			1.7	2.2	dB <sub>INT</sub>	Any 4.5MHz		
Ripple Deviation	729.25				0.5	2.0	dB			
VSWR	729.25	to 745.75			1.7	2.0		ANT.		
	729.25	to 745.75			1.7	2.0		RX		
Absolute Attenuation		to 699.	MHz	40	55		dB	Out-of-band rejection		
		to 30.	MHz	50	106		dB	RX-TX		
	699.25	to 715.75		45	56		dB	TX		
		to 722.	MHz	0.5	16.0		dB	Average attenuation		
		to 793.	MHz	24	29		dB	Upper 700 MHz Tx jammer		
		to 805.	MHz	35	55		dB	PS mobile transmitters		
			MHz	40	56		dB	BC0 TX jammer		
		1.	MHz	40	50		dB	B4 TX		
				40	49		dB			
			MHz	40	49 47		dB dB	B2 TX		
			MHz	40	47 45		dB dB	3f		
		to 2500.	MHz					ISM2.4		
		to 5950.	MHz	36	41		dB	ISM 5G		
		to 6714.	MHz	30	49		dB	9f		
		to 7460.	MHz	25	37		dB	10f		
		to 8206.	MHz	15	28		dB	11f		
		to 8952.	MHz	10	25		dB	12f		
	9477.	to 9698.	MHz	5.0	22.0		dB	13f		
		to 10444.	MHz	5.0	15.0		dB	14f		
	10935.	to 11190.	MHz	5.0	11.0		dB	15f		
	11664.	to 11936.	MHz	5.0	12.0		dB	16f		
	12393.	to 12682.	MHz	5.0	15.0		dB	17f		
				ļ						
	ļ									
	L									
	ľ									
	[									
				1						
				1						

\* Typical value at 25±2deg.C




# Electrical Characteristic $< TX \rightarrow RX. >$


		.10 4		stics				
T.	$X \rightarrow RX$			(-20	to +85 d typ.*	eg.C)	Unit	Note
Isolation	699.25 to	715.75	MHz	57	60	max.	dB	
	701.5 to	713.5	MHz	58	62		dB <sub>INT</sub>	Any 4.5MHz
	729.25 to	745.75	MHz	55	61		dB	
	731.5 to	743.5	MHz	56	65		dB <sub>INT</sub>	Any 4.5MHz
	1398. to		MHz	30	62		dB	2f
	2097. to		MHz	30	55		dB	3f
	2792. to	2864.	MHz	30	52		dB	4f
				ļ	ļ	ļ		
				<u> </u>	<u> </u>			
				1	1			
				ļ		ļ		
				<u> </u>	<u> </u>			
				<u> </u>	<u> </u>			
				<u> </u>	<u> </u>	<u> </u>		
	ļ			I	I	ı	I	* Typical value at 25+2deg.C


\* Typical value at 25±2deg.C



# **Electrical Characteristic**











# **Electrical Characteristic**





< ANT.→RX >






# **Electrical Characteristic**











Dimensions of Tape & Reel unit: mm


#### **Carrier** Tape



Tape



Reel





#### Marking Code

Table A: Month Code

<u> </u>	01071												
ſ	2013	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
	2017 2021	Α	В	С	D	Е	F	G	н	J	ĸ	L	м
ſ	2014	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
	2018 2022	N	Ρ	Q	R	S	Т	U	V	W	х	Y	Z
[	2015	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
	2019 2023	а	р	ю	d	e	f	g	h	j	k	l	m
[	2016	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
	2020 2024	n	p	ġ	r	4	t	u	v	ω	ĸ	y	8

#### Table B: Date Code

date	1st	2nd	3rd	4th	5th	6th	7th	8th	9th	10th	
code	А	В	С	D	E	F	G	Η	J	К	
date	11th	12th	13th	14th	15th	16th	17th	18th	19th	20th	
code	L	М	Ν	Р	Q	R	S	Т	U	V	
date	21st	22nd	23rd	24th	25th	26th	27th	28th	29th	30th	31st
code	W	Х	Y	Z	а	b	ō	d	е	f	g

#### Important Notice (1/2)

PLEASE READ THIS NOTICE BEFORE USING OUR PRODUCTS.

Please make sure that your product has been evaluated and confirmed from the aspect of the fitness for the specifications of our product when our product is mounted to your product. All the items and parameters in this product specification/datasheet/catalog have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment specified in this specification. You are requested not to use our product deviating from the condition and the environment specified in this specification.

Please note that the only warranty that we provide regarding the products is its conformance to the specifications provided herein. Accordingly, we shall not be responsible for any defects in products or equipment incorporating such products, which are caused under the conditions other than those specified in this specification.

WE HEREBY DISCLAIMS ALL OTHER WARRANTIES REGARDING THE PRODUCTS, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, THAT THEY ARE DEFECT-FREE, OR AGAINST INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

The product shall not be used in any application listed below which requires especially high reliability for the prevention of such defect as may directly cause damage to the third party's life, body or property. You acknowledge and agree that, if you use our products in such applications, we will not be responsible for any failure to meet such requirements.

Furthermore, YOU AGREE TO INDEMNIFY AND DEFEND US AND OUR AFFILIATES AGAINST ALL CLAIMS, DAMAGES, COSTS, AND EXPENSES THAT MAY BE INCURRED, INCLUDING WITHOUT LIMITATION, ATTORNEY FEES AND COSTS, DUE TO THE USE OF OUR PRODUCTS IN SUCH APPLICATIONS.



### Important Notice (2/2)

- Aircraft equipment.
- Aerospace equipment
- Undersea equipment.
- Power plant control equipment Medical equipment.
- Transportation equipment (vehicles, trains, ships, elevator, etc.).
- Traffic signal equipment.
- Disaster prevention / crime prevention equipment.
- Burning / explosion control equipment
- Application of similar complexity and/ or reliability requirements to the applications listed in the above.

We expressly prohibit you from analyzing, breaking, Reverse-Engineering, remodeling altering, and reproducing our product. Our product cannot be used for the product which is prohibited from being manufactured, used, and sold by the regulations and laws in the world.

Please do not use the product in molding condition.

This product is ESD (ElectroStatic Discharge) sensitive device. When you install or measure this, you should be careful not to add antistatic electricity or high voltage. Please be advised that you had better check anti serge voltage.

We do not warrant or represent that any license, either express or implied, is granted under any our patent right, copyright, mask work right, or our other intellectual property right relating to any combination, machine, or process in which our products or services are used. Information provided by us regarding third-party products or services does not constitute a license from us to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from us under our patents or other intellectual property.

Please do not use our products, our technical information and other data provided by us for the purpose of developing of mass-destruction weapons and the purpose of military use. Moreover, you must comply with "foreign exchange and foreign trade law", the "U.S. export administration regulations", etc.

Please note that we may discontinue the manufacture of our products, due to reasons such as end of supply of materials and/or components from our suppliers.

Customer acknowledges that Murata will, if requested by you, conduct a failure analysis for defect or alleged defect of Products only at the level required for consumer grade Products, and thus such analysis may not always be available or be in accordance with your request (for example, in cases where the defect was caused by components in Products supplied to Murata from a third party).

The product shall not be used in any other application/model than that of claimed to Murata.

Customer acknowledges that engineering samples may deviate from specifications and may contain defects due to their development status.

We reject any liability or product warranty for engineering samples.

In particular we disclaim liability for damages caused by

•the use of the engineering sample other than for evaluation purposes, particularly the installation or integration in the product to be sold by you,

·deviation or lapse in function of engineering sample,

·improper use of engineering samples.

We disclaim any liability for consequential and incidental damages.

If you can't agree the above contents, you should inquire our sales.