



PRODUCT SUMMARY

$V_{(BR)DSS}$	$R_{DS(ON)}$	I_D
-30	20mΩ	-9A



4 :GATE
5,6,7,8 :DRAIN
1,2,3 :SOURCE

ABSOLUTE MAXIMUM RATINGS ($T_C = 25\text{ °C}$ Unless Otherwise Noted)

100% UIS tested

PARAMETERS/TEST CONDITIONS		SYMBOL	LIMITS	UNITS
Drain-Source Voltage		V_{DS}	-30	V
Gate-Source Voltage		V_{GS}	±25	V
Continuous Drain Current	$T_C = 25\text{ °C}$	I_D	-9	A
	$T_C = 70\text{ °C}$		-7	
Pulsed Drain Current ¹		I_{DM}	-50	
Avalanche Current		I_{AS}	-26	
Avalanche Energy	L = 0.1mH	E_{AS}	34	mJ
Power Dissipation	$T_C = 25\text{ °C}$	P_D	2.5	W
	$T_C = 70\text{ °C}$		1.6	
Operating Junction & Storage Temperature Range		T_j, T_{stg}	-55 to 150	°C

THERMAL RESISTANCE RATINGS

THERMAL RESISTANCE	SYMBOL	TYPICAL	MAXIMUM	UNITS
Junction-to-Case	$R_{\theta JC}$		25	°C / W
Junction-to-Ambient	$R_{\theta JA}$		50	°C / W

¹Pulse width limited by maximum junction temperature.

ELECTRICAL CHARACTERISTICS ($T_C = 25\text{ °C}$, Unless Otherwise Noted)







PARAMETER	SYMBOL	TEST CONDITIONS	LIMITS			UNIT
			MIN	TYP	MAX	
STATIC						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = -250\mu A$	-30			V
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\mu A$	-1	-1.5	-3	
Gate-Body Leakage	I_{GSS}	$V_{DS} = 0V, V_{GS} = \pm 25V$			±100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = -24V, V_{GS} = 0V$			-1	μA
		$V_{DS} = -20V, V_{GS} = 0V, T_J = 125\text{ °C}$			-10	
On-State Drain Current ¹	$I_{D(ON)}$	$V_{DS} = -5V, V_{GS} = -10V$	9			A
Drain-Source On-State Resistance ¹	$R_{DS(ON)}$	$V_{GS} = -4.5V, I_D = -7A$		25	35	mΩ
		$V_{GS} = -10V, I_D = -9A$		15	20	






Forward Transconductance ¹	g_{fs}	$V_{DS} = -10V, I_D = -9A$		24		S
DYNAMIC						
Input Capacitance	C_{iss}	$V_{GS} = 0V, V_{DS} = -15V, f = 1MHz$		1610		pF
Output Capacitance	C_{oss}			410		
Reverse Transfer Capacitance	C_{rss}			200		
Gate Resistance	R_g	$V_{GS} = 15mV, V_{DS} = 0V, f = 1MHz$		3.7		Ω
Total Gate Charge ²	Q_g	$V_{DS} = 0.5V_{(BR)DSS}, V_{GS} = -10V, I_D = -9A$		31.4		nC
Gate-Source Charge ²	Q_{gs}			4.5		
Gate-Drain Charge ²	Q_{gd}			8.2		
Turn-On Delay Time ²	$t_{d(on)}$	$V_{DS} = -15V, R_L = 1\Omega, I_D \cong -1A, V_{GS} = -10V, R_{GS} = 6\Omega$		5.7		nS
Rise Time ²	t_r			10		
Turn-Off Delay Time ²	$t_{d(off)}$			18		
Fall Time ²	t_f			5		
SOURCE-DRAIN DIODE RATINGS AND CHARACTERISTICS ($T_C = 25^\circ C$)						
Continuous Current	I_S				-2.1	A
Forward Voltage ¹	V_{SD}	$I_F = -1A, V_{GS} = 0V$			-1.2	V

¹Pulse test : Pulse Width $\leq 300 \mu sec$, Duty Cycle $\leq 2\%$.

²Independent of operating temperature.

REMARK: THE PRODUCT MARKED WITH "P2003EVG", DATE CODE or LOT #





SOIC-8(D) MECHANICAL DATA

Dimension	mm			Dimension	mm		
	Min.	Typ.	Max.		Min.	Typ.	Max.
A	4.8	4.9	5.0	H	0.4	0.715	0.83
B	3.8	3.9	4.0	I	0.19	0.22	0.25
C	5.8	6.0	6.2	J	0.25	0.375	0.5
D	0.33	0.445	0.51	K	0°	4°	8°
E		1.27		L			
F	1.25	1.375	1.62	M			
G	0.1	0.175	0.25	N			

