

Schottky Barrier Rectifiers

Using the Schottky Barrier principle with a Refractory metal capable of high temperature operation metal. The proprietary barrier technology allows for reliable operation up to 175°C junction temperature. Typical application are in switching Mode Power Supplies such as adaptors, DC/DC converters, freewheeling and polarity protection diodes.

Features

- *Low Forward Voltage.
- *Low Switching noise.
- *High Current Capacity
- * Guarantee Reverse Avalanche.
- *Guard-Ring for Stress Protection.
- *Low Power Loss & High efficiency.
- *175°C Operating Junction Temperature
- *Low Stored Charge Majority Carrier Conduction.
- *Plastic Material used Carries Underwriters Laboratory Flammability Classification 94V-O



* In compliance with EU RoHs 2002/95/EC directives

MAXIMUM RATINGS

Characteristic		MBR30100CT	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	$egin{array}{c} V_{RRM} \ V_{RWM} \ V_{R} \ \end{array}$	100	V
RMS Reverse Voltage	$V_{R(RMS)}$	70	٧
Average Rectifier Forward Current (per diode) Total Device (Rated V _R), T _C =100°C		15 30	Α
Peak Repetitive Forward Current (Rate V _R , Square Wave, 20kHz)		30	А
Non-Repetitive Peak Surge Current (Surge applied at rate load conditions halfware, single phase, 60Hz)		250	Α
Junction Operating Temperature Range Storage Temperature (1)		-65 to +175 20~35 °C ⋅ 30%~60% RH	$^{\circ}$

(1)expired date: 1 year

THERMAL RESISTANCES


Typical Thermal Resistance junction to case	$R_{\theta jc}$	3.0	°C/w
---	-----------------	-----	------


ELECTRICAL CHARACTERISTICS

Characteristic	Symbol	MBR30100CT	Unit	
Maximum Instantaneous Forward Voltage (per diode)				
(I _F =15 Amp T _C = 25°C)	V_{F}	0.85	V	
(I _F =15 Amp T _C = 125℃)		0.78		
Maximum Instantaneous Reverse Current				
(Rated DC Voltage, T _C = 25°ℂ)		0.01	mA	
(Rated DC Voltage, T _C = 125℃)		15		


SCHOTTKY BARRIER RECTIFIERS

30 AMPERES 100 VOLTS






DIM	MILLIM	ETERS
וווט	MIN	MAX
Α	14.68	15.32
В	9.78	10.42
С	5.02	6.52
D	13.06	14.62
E	3.57	4.07
F	2.42	2.66
G	1.20	1.47
Н	0.72	0.96
- 1	4.22	4.98
J	1.14	1.38
K	2.20	2.98
L	0.33	0.55
M	2.48	2.98
0	3.70	3.90



MBR30100CT



CASE TEMPERATURE (℃)

