



# **SPECIFICATION**

Customer:		
		Receipt
Item:	CRYSTAL OSCILLATOR	
Type:	NT2016SF	
Nominal frequency:	38.4 MHz	
Customer's Spec. No.:		
NDK Spec. No.:	ENG5141A	

	Revision Record									
Rev.	Date	Items Contents Approved Che		Checked	ecked Drawn					
	Jul. 26. 2017	Issue		K.Moriya	S.Kawahara	H.Kawabata				

# 1. Type NT2016SF

2. Maximum Rating

	Item	Rating	unit
1	Supply Voltage (V <sub>CC</sub> )	-0.6 to +4.6	٧
2	Storage temp. range	-40 to +85	<b>→</b> C

3. Electrical specification

	Parameters		Electric	cal Spec.		Notes
		Min.	Тур.	Max.	Units	
1	Nominal frequency		38.4		MHz	
2	Supply voltage (Vcc)		+2.8		<b>V</b>	(-Earth)
3	Current consumption			1.7	mA	
4	Output voltage	0.8			Vp-p	Clipped sine wave (DC-Coupling)
5	Operating temp. range	-40		+85	<b>→</b> C	
6	Load impedance (resistance part)	9	10	11	k,	
7	Load impedance (parallel capacitance)	9	10	11	pF	
8	DC-cut capacitor					DC-cut capacitor of output is not put in TCXO. Please add DC-cut capacitor (1000 pF) in output line.
	Frequency stability					
	Frequency     /Temperature characteristics	-0.5		+0.5	ppm	-40 to +85 →C Based on frequency at +25+/-2 →C
	2. Frequency/Voltage coefficient	-0.2		+0.2	ppm	+2.8 +/-5 ^
9	3. Frequency/Load coefficient	-0.2		+0.2	ppm	(10 k_//10 pF) +/-10 <sup>&lt;</sup>
	4. Frequency tolerance	-2.0		+2.0	ppm	+25+/-2 →C, before reflow soldering, based on nominal frequency
	5. Long-term frequency stability	-1.0		+1.0	ppm	year (at +25+/-2→C)

# 4. Reflow soldering

After 2 times reflow soldering, frequency deviation shall meet within max +/-1.0 ppm.

Based on frequency before the reflow soldering.

Conditions of temperature profile (Refer to Fig.1)

Soldering peak temp. +260 →C

# 5. Marking

- (1) Lot No.
- (2) Manufacture Name (NDK symbol mark)
- (3) Nominal frequency (MHz)
- (4) Trace code

## 6. Inspection parameters

Para 3.1, 3.3, 3.4, 3.9.1, 5, 10.2 are inspected.

The other parameters are guaranteed to be within specified characteristics by NDK design. Inspection data is not submitted for mass production lot. But only if requested, a copy of first lot production data will be submitted.

### 7. Precaution in the storage

Please keep the oscillator in the ordinary temperature and humidity that are suggested as below table.

	After taking out of dry bag			
Temperature	+30 →C max.			
Humidity	60 % max.			
Period	1 year *			
(table)				

(table)

#### 8. Frequency establishment condition

When output frequency is set, we suppose to have the ground pattern under the oscillator.

#### 9. Washing

Not available for washing.

#### 10. Application drawing

10.1 Reliability assurance item

ETS30B-00399

10.2 Dimension of External

ETD14B-01892

10.3 Packing

ETK17B-00463

10.4 Land pattern

ETD15B-00020A

10.5 Marking

ETH11B-00443B

<sup>\*</sup>It is desirable for the oscillator to be used within 1 year after taking out of dry bag.

Please pack the oscillator into used dry bag with a desiccant and seal it up by heat sealer etc.

In case the heat sealer is not available, sealing up with cellophane tape or a vinyl tape will do.

#### 11. Notice

- 11.1 Order items are manufactured according to specification. As to conditions, which are not indicated in this specification and unpredictable such as applied condition and oscillation margin, please check them beforehand.
- 11.2 Unless we receive request for modification within 3 weeks from the issue date of this NDK specification sheet, we will supply products according to this specification. Also, if you'd like to modify specification of order, which has been placed with delivery request within 3 weeks from the issue data of this specification sheet, we would like to discuss with you separately.
- 11.3 Where any change to the process condition is made due to the change(s) in the production line, inform personnel of the specifications.
- 11.4 Should this specification data give rise to any disputes relating to any intellectual property rights or any other rights of a third person, the company shall not indemnify anyone for any damage.

  Their disclosure must not be construed as the grant of a license to use any of the intellectual property rights owned by the company.
- 11.5 If you intend to use products listed on this specification for applications that may result in loss of life or assets (controls relating to safety, medical equipment, aeronautical equipment, space equipment, etc.), please do not fail to advise us of your intention beforehand.
- 11.6 In the company's production process whatever amount of ozone depleting substances (ODS) as specified in the Montreal protocol is not used.
- 11.7 Information contained in this specification must not be quoted, reproduced or used for other purposes including processing either in part or in full without obtaining prior approval from the company.
- 11.8 In no event shall the company be liable for any product failure resulting from an inappropriate handling or operation of the product beyond the scope of its guarantee.
- 11.9 The appearance color and so on have a different case by purchasing it more than 2 suppliers of the component, but characteristic and reliability are guaranteed.
- 11.10 If you use resin for fixing components during manufacturing, please keep resin from adhering to the oscillator.

#### 12. Prohibited items

Be sure to use the product under the following conditions. Otherwise, the characteristics deterioration or destruction of the product may result.


(1) Reflow soldering heat resistance

Peak temperature: +265 →C

Heating: +225 →C or higher, 90 sec

(2) Manual soldering heat resistance

Pressing a soldering iron of +410 →C on the terminal electrode for five seconds.



# Reliability assurance item

(page: 1/1)


No.	Test Item	Test Methods	Specification Code
1	Vibration	5 to 26Hz: 1.52mm (total amplitude) 26 to 500Hz: 19.6m/s <sup>2</sup> 20 minutes per 1 cycle. 2 hours for each 3 planes.	А
2	Shock	Half sine wave 6ms, 980 m/s <sup>2</sup> . 3 times for each 3 planes.	Α
3	Drop Test	Drop freely on the concrete from the height of 150cm With jig(150g). 3time for each 6 planes.	А
4	Humidity	+60→C, 95 <sup>\(\sigma\)</sup> RH for 48H. And normal temperature, with normal humidity for 24H.	А

Specification code	Specification			
Α	After the test, shall meet electrical specification.			


1000pF 


#2

77/177




	Date of Revise		Charge	Approved	Reason			
		Date	Name	Third Angle Project	ction	Tolerance	Sc	ale
Drav	wn	25.Aug.2015	M.Fukunaga	Dimension:mn	n	+/- 0.2		/1
Desi	igned	25.Aug.2015	M.Fukunaga	Title		Drawing No.		Rev.
Che	cked	25.Aug.2015	K.Koyama	Dimension	f = 1,40 mm	ETD44	D 04000	
App	roved	25.Aug.2015	K.Moriya	Dimension of	Extern	iai EID14	B-01892	-






	Embossed carrier tape	Top cover tape
Materials	PS	PET + PE + Adhesive layer
Disposition	Antistatic	Antistatic


Da	te of Revise	Charge	harge Approved Reason				
	Date	Name	Third Angle Proje	ction	Tolerance	Sca	ale
Drawn	9. Nov. 2016	E.Hoshi	Dimension:mr	n		3/	′1
Designed	9. Nov. 2016	E.Hoshi	Title		Drawing No.		Rev.
Checked	9. Nov. 2016	M.Fukunaga	Booki		ETI(47D 00	100 (4/2)	
Approved	9. Nov. 2016	M.Fukunaga	Packi	ng	ETK17B-004	163 (1/3)	-






Da	te of Revise	Charge	Approved	Reason			
	Date	Name	Third Angle Proje	ection	Tolerance	Sc	ale
Drawn	9. Nov. 2016	E.Hoshi	Dimension:mm				- <b>-</b>
Designed	9. Nov. 2016	E.Hoshi	Title		Drawing No.		Rev.
Checked	9. Nov. 2016	M.Fukunaga	Dools	!	ETI(4=D 00	(2.12)	
Approved	9. Nov. 2016	M.Fukunaga	Packi	ing	ETK17B-004	163 (2/3)	-

-3000pcs.Max./Reel -5 Reels Max./Carton




D	ate of Revise	Charge	Approved	Reason			
	Date	Name	Third Angle Projection		Tolerance	Tolerance Sc	
Drawn	9. Nov. 2016	E.Hoshi	Dimension:mr	m			
Designed	9. Nov. 2016	E.Hoshi	Title		Drawing No.		Rev.
Checked	9. Nov. 2016	M.Fukunaga	Dool:		ETI(170 001	00 (0.0)	
Approved	9. Nov. 2016	M.Fukunaga	Packi	ng	ETK17B-004	63 (3/3)	-



Note) Please reserve a large ground pattern on the PCB where the oscillator is installed.


	Date of Revise Charge Approved Reason								
Α	8.Jul.2011 Y.Kanehira A.		A.Konda	Change Note					
		Date	Name	Third Angle Proje	ction 7		olerance	Scale	
Drawn		19.Mar.2007	H.Harima	Dimension:m	n		30 / 1		
Designed		19.Mar.2007	H.Harima	Title			Drawing No.		Rev.
Checked		19.Mar.2007	K.Moriya	Land pattern		ETD15B-00020		00000	Λ
Approved		19.Mar.2007	H.Mizumura					00020	Α

NIHON DEMPA KOGYO CO., LTD.



Terminal land connections: Please refer to "Dimension of External".

# (Marking Contents)



### \*2 Trace code

Trace code indicates production date and production line number.

# \*3 Nominal Frequency

- A unit (MHz) is not written.
- A decimal point omits.

(Example : (2digits) 26MHz  $\rightarrow$  26 , (3digits) 19.2MHz  $\rightarrow$  192, (4more digits) 16.368MHz  $\rightarrow$  163)

Marking Method: Laser Trimming

	Date of Revise		Charge	Approved	Reason					
B 4. Mar. 2015		Mar. 2015	E.Hoshi	A.Konda	Clerical error Correction					
		Date	Name	Third Angle Projection		Tolerance		Sc	Scale	
Drawn		16. Apr. 2013	R.Yoshizaki	Dimension:mr	n					
Desi	igned	16. Apr. 2013	R.Yoshizaki	Title			Drawing No.		Rev.	
Checked		16. Apr. 2013	M.Kashiwamura	Marking		ETU44D		00442	D	
App	roved	16. Apr. 2013	K.Moriya	Marking		ETH11B-00443		В		