

Sales

Engineer

RoHS Compliant
Directive 2011/65/EU

## **SPECIFICATION**

Customer:		
		Receipt
Item:	Crystal Unit	Neceipt
Type:	NX2520SA	
Nominal frequency	16.000 MHz	
Customer's Spec. No.:		
NDK Spec. No.:	STD-CSW-5	
Charge:		

Tel: 886-2-2555-0232

Tel: (81)-4-2900-6653

Mail: matsuo@ndk.com

Mail: sherise@tp.ndk.com

NDK-TP

Sherise Peng

Engineering Dept. 1 Matsuo

	Revision Record						
Rev. Rev. Date Items Contents Rem							
	21.May.2014	Issue					

Customer Specifications Number

2. NDK Specification Number : STD-CSW-5

3. Type : NX2520SA

#### 4. Electrical Characteristics

	Floatrian Characteristics Itama	Cumbal	Electric	cal Cha	racterist	tics Spec.	Notes	
	Electrical Characteristics Items	Symbol	MIN	TYP	MAX	Unit	Notes	
1	Nominal frequency	fnom		16.000		MHz		
2	Overtone order	-	Fu	ndamer	ntal	-		
3	Frequency tolerance	-	-15	-	+15	ppm	at +25°C	
4	Frequency versus Temperature Chacteristic	-	-25	-	+25	ppm	at -40 to +85°C	
5	Equivalent resistance	-	-	-	80	ohm	IEC $\pi$ -network / Series	
6	Load capacitance	CL	-	8	-	рF	IEC $\pi$ -network	
7	Level of drive	1	-	10	200	μW		
8	Insulation resistance	-	500	-	,	Mohm	Terminal to terminal insulation resistance also terminal to cover insulation resistance must be $500 M\Omega \ (\text{min}) \ \text{when}$ DC100V $\pm 15 \text{V}$ is applied.	
9	Operating Temperature range	-	-40	-	+85	°C		
10	Storage temperature range	-	-40	-	+85	°C		
11	Air-tightness	-	-	-	1.1 x10 <sup>-9</sup>	Pa m <sup>3</sup> /s	Helium leak detector	

#### 5. Examination results document

Since a performance is guaranteed, an examination results document does not submit.

#### 6. Application drawing

6.1 External dimension : EXD14B-00420
6.2 Taping and reel figure : EXK17B-00161
6.3 Holder marking : EXH11B-00317
6.4 Reliability assurance Item : EXS30B-00249

#### 7. Notice

- 7.1 Order items are manufactured according to specification. As to conditions, which are not indicated in this specification and unpredictable such as applied condition and oscillation margin, please check them beforehand.
- 7.2 Unless we receive request for modification within 3 weeks from the issue date of this NDK specification sheet, we will supply products according to this specification. Also, if you'd like to modify specification of order, which has been placed with delivery request within 3 weeks from the issue data of this specification sheet, we would like to discuss with you separately.
- 7.3 In no event shall the company be liable for any product failure resulting from an inappropriate handling or operation of the product beyond the scope of its guarantee.
- 7.4 Where any change to the process condition is made due to the change(s) in the production line, inform personnel of the specifications.
- 7.5 Should this specification data give rise to any disputes relating to any intellectual property rights or any other rights of a third person, the company shall not indemnify anyone for any damage. Their disclosure must not be construed as the grant of a license to use any of the intellectual property rights owned by the company.
- 7.6 If you intend to use products listed on this specification for applications that may result in loss of life or assets (controls relating to safety, medical equipment, aeronautical equipment, space equipment, etc.), please do not fail to advise us of your intention beforehand.
- 7.7 In the company's production process whatever amount of ozone depleting substances (ODS) as specified in the Montreal protocol is not used.
- 7.8 Information contained in this specification must not be quoted, reproduced or used for other purposes including processing either in part or in full without obtaining prior approval from the company.
- 7.9 Crystal units will be damaged by ultrasonic welding process due to resonance of crystal wafer itself. NDK does not recommend using ultrasonic welding. If Ultra Sonic welding used, NDK strongly recommend verifying crystal unit damage by ultrasonic weld.
- 7.10 The appearance color has a different case by purchasing it more than 2 suppliers of the component, but characteristic and reliability are guaranteed.

#### 8. Prohibited items

Be sure to use the product under the following conditions. Otherwise, the characteristics deterioration or destruction of the product may result.


(1) Reflow soldering heat resistance

Peak temperature: 265°C, 10 sec Heating: 230°C or higher, 40 sec Preheating: 150°C to 180°C, 120 sec

Reflow passage times: twice

(2) Manual soldering heat resistance


Pressing a soldering iron of 400°C on the terminal electrode for four seconds (twice).




Da	te of Revise	Charge	Approved	Reason			
	Date	Name	Third Angle Projection		Tolerance	Sc	ale
Drawn	30.Oct.2007	K.Sato	Dimension:mr	Dimension:mm		- /	/ <b>-</b>
Designed	30.Oct.2007	K.Sato	Title		Drawing No.		Rev.
Checked			NX252	NX2520SA		00420	
Approved	30.Oct.2007	K.Kubota	Dimension Drawing		EXD14B-00420		

NIHON DEMPA KOGYO CO., LTD.

#### Document No. EXS10B-21611 5/7



	Dat	e of Revise	Charge	Approved	Reaso	on			
В	14.	Mar. 2008	Wada	Kubota	Changed drawing title				
		Date	Name	Third Angle Projection T		To	Tolerance S		ale
Drav	wn	19.Jun.2003	H.Yagishita	Dimension: m	nm		- ,	/ -	
Des	signed	19.Jun.2003	H.Yagishita	Title			Drawing No.		Rev.
Che	ecked	19.Jun.2003	K.Kubota	NX2520 Series			EXK17B-	.00161	В
App	roved	19.Jun.2003	T.Ishii	Taping and Reel Spec.		pec.	LANII D-00101		ם



#### **NOTE**

### 1. Frequency Code

Marking Frequency is consist of five digits, first five digits of Nominal Frequency

## Example

Nominal Frequency	28.636363 MHz
Frequency Code	28.636

#### 2. Month Code Table

Month	1	2	3	4	5	6	7	8	9	10	11	12
	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Month Code	1	2	3	4	5	6	7	8	9	Х	Υ	Z

<sup>\*</sup>Marking digits are not include a decimal point and dot mark.

	Dat	e of Revise	Charge	Approved	Reason				
В	10	.July.2008	Miyahara	K.Kubota	Delete application period.				
		Date	Name	Third Angle Projection Tolera		Tolerance Sc		ale	
Drav	wn	16.Jan.2006	I.Miyahara	Dimension:mr	Dimension:mm			/	1
Des	signed	16.Jan.2006	I.Miyahara	Title			Drawing No.		Rev.
Che	ecked	16.Jan.2006		Crystal Hald	ar Marki	ina	EXH11B-	00247	Б
App	roved	16.Jan.2006	K.Okamoto	Crystal Holde	ei iviaiki	iiig	EVUIID.	-00317	В

# Reliability assurance item

(page: 1/1)

			(page: 1/1)
No.	Test Item	Test Methods	Specification Code
1	High Temperature Storage *1	+85±3°C 720h	А
2	Low Temperature Storage	-40±3°C 500h	А
3	Temperature Humidity	+60±3°C 90~95%RH 500h	А
4	Temperature Cycling *1	-40±3°C / +85±3°C It is 500 cycles using 30 minutes each as 1 cycle.	А
5	Vibration	Frequency Range: 10~55Hz Amplitude: 1.52mm 1 cycle: 1 minutes Test time: Three mutually perpendicular axes each 2 hours.	А
6	Shock	Devices are shocked to half sine wave (981m/s²) three mutually perpendicular axis each 3 times.	А
7	Drop	Devices are dropped from the height 75cm onto wooden block. (more than 30mm thickness.) Execution 3 times random drops	А
8	Solderability	Pre-heat temperature: +150±10°C Pre-heat time: 60~120s When the temperature of the specimen is reached at +215±3°C, it shall be left for 30±1sec. Peak temperature 240±5°C Material: Pb-free (Sn-3.0Ag-0.5Cu) Flux: Rosin resin methyl alcohol solvent (1:4)	В
9	Reflow resistance	Pre-heat temperature: +150~180°C Pre-heat time: 90±30s Heat temperature: more than +230°C Heat time: 30s±10s Peak temperature: +260±5°C Peak time: less than 10s	А

### \*1. High Temperature Storage and Temperature Cycling

In case of customer spec on High temperature exceed +85°C, Low temperature exceed -40°C, above test according to customer spec high or low temperature will be perform and guarantee.

Specification code	Specification
А	$\Delta f/f \le \pm 5$ ppm $\Delta CI/CI \le \pm 15$ % or 5 $\Omega$ make use larger value
В	The electrodes should be covered by a new solder at least 90% of immersed area.