

# **SPECIFICATION**

| Customer:             |              |             |  |
|-----------------------|--------------|-------------|--|
|                       |              |             |  |
|                       |              | Receipt     |  |
| Item:                 | Crystal Unit |             |  |
|                       |              |             |  |
| Type:                 | NX3225SA     |             |  |
| Nominal Frequency:    | 26 MHz       |             |  |
| Nominal Frequency.    | 20 MHZ       | <del></del> |  |
| Customer's Spec. No.: |              |             |  |
| NDK Spec. No.:        | W-168-491-1  |             |  |
|                       |              |             |  |
|                       |              |             |  |
|                       |              |             |  |

Charge:

| Sales    | Sales Dept.<br>T. Takeuchi              | Tel.<br>81-03-5453-6783 | Approved       | Y. Sakunma               |
|----------|---|-------------------------|----------------|--------------------------|
| Engineer | 1 <sup>ST</sup> Eng. Dept.<br>Y. Takaki | Tel.<br>81-04-2900-6631 | Checked  Drawn | I. Miyahara<br>Y. Takaki |

|      | Revision Record |       |          |         |  |  |  |
|------|-----------------|-------|----------|---------|--|--|--|
| Rev. | Rev. Date       | Items | Contents | Remarks |  |  |  |
|      | 15. Oct. 2012   | Issue |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |
|      |                 |       |          |         |  |  |  |

1. Customer specifications number : ---

2. NDK specification number : W-168-491-1

3. Type : NX2520SA

4. Electrical characteristics

4.1. Nominal Frequency (F<sub>0</sub>) : 26 MHz4.2. Overtone Order : Fundamental

4.3. Adjustment Tolerance  $: \pm 10 \times 10^{-6} \,\text{Max.} \, (at + 25 \,^{\circ}\text{C})$ 4.4. Frequency stability over temperature  $: \pm 10 \times 10^{-6} \,\text{Max.} \, (at - 20 \, to + 85 \,^{\circ}\text{C})$ 

The reference temp. shall be +25 °C

4.5. Equivalent Resistance ( $R_R$ ) : 50  $\Omega$  Max.

4.6. Shunt Capacitance ( C0 )  $\phantom{0}$  : 1.22 pF  $\pm$ 10% (Grounded) 4.7. Motional Capacitance ( C1 )  $\phantom{0}$  : 4.92 fF  $\pm$ 15% (Grounded)

4.8. Drive Level : 100uW max.

4.9. Insulation Resistance : Terminal to terminal insulation resistance also

terminal to cover insulation resistance must be  $500M\Omega$  (Min.) when DC100V  $\pm15V$  is applied.

5. Measurement circuit

5.1. Frequency measurement

Measuring Instrument : π-network
 Load Capacitance (C<sub>L</sub>) : 7.36 pF
 Level of Drive : 10 μW

5.2. Equivalent resistance measurement

 $\begin{array}{lll} \cdot \mbox{ Measuring Instrument} & : \pi\mbox{-network} \\ \cdot \mbox{ Load Capacitance (C_L)} & : \mbox{ Series} \\ \cdot \mbox{ Level of Drive} & : 10 \ \mu\mbox{W} \\ \end{array}$ 

6. Other performances

6.1. Air-tightness : Less than 1.1×10<sup>-9</sup> Pa m³/s (Helium leak detector)

6.2. Operating Temperature range : - 20 to +85 °C 6.3. Storage Temperature range : - 40 to +85 °C

7. Examination results document

Since a performance is guaranteed, an examination results document does not submit.

8. Application drawing

8.1. Dimension Drawing : EXD14B-00370
8.2. Taping and Reel figure : EXK17B-00247
8.3. Holder Marking : EXH11B-00489
8.4. Reliability assurance Item : EXS30B-00250

#### 9. Notice

- 9.1. Order items are manufactured according to specification. As to conditions, which are not indicated in this specification and unpredictable such as applied condition and oscillation margin, please check them beforehand.
- 9.2. Unless we receive request for modification within 3 weeks from the issue date of this NDK specification sheet, we will supply products according to this specification. Also, if you'd like to modify specification of order, which has been placed with delivery request within 3 weeks from the issue data of this specification sheet, we would like to discuss with you separately.
- 9.3. In no event shall the company be liable for any product failure resulting from an inappropriate handling or operation of the product beyond the scope of its guarantee.
- 9.4. Where any change to the process condition is made due to the change(s) in the production line, inform personnel of the specifications.
- 9.5. Should this specification data give rise to any disputes relating to any intellectual property rights or any other rights of a third person, the company shall not indemnify anyone for any damage. Their disclosure must not be construed as the grant of a license to use any of the intellectual property rights owned by the company.
- 9.6. If you intend to use products listed on this specification for applications that may result in loss of life or assets (controls relating to safety, medical equipment, aeronautical equipment, space equipment, etc.), please do not fail to advise us of your intention beforehand.
- 9.7. In the company's production process whatever amount of ozone depleting substances (ODS) as specified in the Montreal protocol is not used.
- 9.8. Information contained in this specification must not be quoted, reproduced or used for other purposes including processing either in part or in full without obtaining prior approval from the company.

#### 10. Prohibited items

Be sure to use the product under the following conditions. Otherwise, the characteristics deterioration or destruction of the product may result.


(1) Reflow soldering heat resistance

Peak temperature: 265°C, 10 sec Heating: 230°C or higher, 40 sec Preheating: 150°C to 180°C, 120 sec


Reflow passage times: Three

(2) Manual soldering heat resistance


Pressing a soldering iron of 400°C on the terminal electrode for four seconds (twice).



## LAND PATTERN (TYPICAL)



### PIN CONNECTION (TOP VIEW)




**\*** #1,#3 : Xtal


#2,#4: GND (CONNECTION COVER)


|      | Da     | te of Revise | Charge     | Approved               | ed Reason      |           |              |       |      |
|------|--------|--------------|------------|------------------------|----------------|-----------|--------------|-------|------|
| Α    | 4.     | Sep.2007     | R.Shariman | K.Kubota               | Add Tolerance. |           |              |       |      |
|      |        | Date         | Name       | Third Angle Projection |                | Tolerance | Scale        |       |      |
| Drav | wn     | 25.Oct.2005  | S.Mizusawa | Dimension:mm           |                | ±0.1      | -/-          |       |      |
| Des  | signed | 25.Oct.2005  | S.Mizusawa | Title                  |                |           | Drawing No.  |       | Rev. |
| Che  | ecked  |              |            | NX322                  | 5SA            |           | EVD44B       | 00270 | Α.   |
| App  | roved  | 25.Oct.2005  | S.Mizusawa | Dimension Drawing      |                | g         | EXD14B-00370 |       | Α    |

NIHON DEMPA KOGYO CO., LTD.

#### Document No. EXS10B-18131 5/7








|      | Dat   | e of Revise | Charge      | Approved              | Reason |             |        |      |
|------|-------|-------------|-------------|-----------------------|--------|-------------|--------|------|
| Α    |       |             |             |                       |        |             |        |      |
|      |       | Date        | Name        | Third Angle Proje     | ction  | Tolerance   | Sc     | ale  |
| Drav | wn    | 30.Jun.2006 | H.Yagishita | Dimension:mm          |        |             | -      | / -  |
| Desi | igned | 30.Jun.2006 | H.Yagishita | Title                 |        | Drawing No. |        | Rev. |
| Che  | cked  | 30.Jun.2006 | K.Kubota    | NX3225 S              | Series | EXK17B      | 00247  |      |
| App  | roved | 30.Jun.2006 | T.Ishii     | Taping and Reel Spec. |        | C. EARITE   | -00247 |      |

NIHON DEMPA KOGYO CO., LTD.



### NOTE

## 1. Frequency Code

Marking Frequency is consist of five digits, first five digits of Nominal Frequency

## Example

| Nominal Frequency | 28.636363 MHz |
|-------------------|---------------|
| Frequency Code    | 28.636        |

### 2. Month Code Table

| Month      | 1    | 2    | 3    | 4    | 5    | 6    | 7    | 8    | 9    | 10   | 11   | 12   |
|------------|------|------|------|------|------|------|------|------|------|------|------|------|
|            | Jan. | Feb. | Mar. | Apr. | May. | Jun. | Jul. | Aug. | Sep. | Oct. | Nov. | Dec. |
| Month Code | 1    | 2    | 3    | 4    | 5    | 6    | 7    | 8    | 9    | Х    | Υ    | Z    |

<sup>\*</sup>Marking digits are not include a decimal point and dot mark.

|         | Date of Revise | Charge   | Approved Reason           |           |           |        |      |
|---------|----------------|----------|---------------------------|-----------|-----------|--------|------|
|         |                |          |                           |           |           |        |      |
|         | Date           | Name     | Third Angle Projection To |           | Tolerance | Sc     | ale  |
| Drawn   | 29.Jun.2012    | H.Ouchi  | Dimension:mm              |           |           | ,      | 1    |
| Designe | ed 29.Jun.2012 | H.Ouchi  | Title                     | Title     |           |        | Rev. |
| Checke  | ed             |          | Crystal Halday            | . Markina | EXH11B    | 00400  |      |
| Approv  | ed 29.Jun.2012 | M.Kubota | Crystal Holder            | warking   | EVULLE    | -00469 |      |

# Reliability assurance item

(page: 1/1)

| No. | Test Item                   | Test Methods   | Specification<br>Code |
|-----|-----------------------------|--|-----------------------|
| 1   | High Temperature<br>Storage | +85±3°C 720h   | А                     |
| 2   | Low Temperature<br>Storage  | -40±3°C 500h   | А                     |
| 3   | Temperature<br>Humidity     | +85±3°C 80~85%RH 500h  | А                     |
| 4   | Temperature<br>Cycling      | -40±3°C / +85±3°C<br>It is 1000 cycles using 30 minutes each as 1 cycle.   | А                     |
| 5   | Vibration                   | Frequency Range: 10~2000Hz  Amplitude or Acceleration: 1.52mm or 196m/s² 1 cycle: 20 minutes Test time: Three mutually perpendicular axes each 4 hours.  | А                     |
| 6   | Shock                       | Devices are shocked to half sine wave (29418m/s², 0.3msec) six mutually perpendicular axis each 1 times.   | А                     |
| 7   | Drop                        | Preparation: Test pieces should be fixed on the dummy load with 200g weight. Condition: Height 1.5m onto concrete Drop times: 10 times in 6 mutually perpendicular axes  | А                     |
| 8   | Solderability               | Pre-heat temperature: +150±10°C Pre-heat time: 60~120s When the temperature of the specimen is reached at +215±3°C, it shall be left for 30±1sec. Peak temperature 240±5°C Material: Pb-free (Sn-3.0Ag-0.5Cu) Flux: Rosin resin methyl alcohol solvent (1:4) | В                     |
| 9   | Reflow resistance           | Pre-heat temperature: +150~180°C Pre-heat time: 90±30s Heat temperature: more than +230°C Pre-heat time: less than 30s Peak temperature: +260±5°C Peak time: less than 10s   | А                     |

| Specification code | Specification  |
|--------------------|--|
| А                  | $\Delta f/f \le \pm 3$ ppm $\Delta CI/CI \le \pm 15$ % or 5 $\Omega$ make use larger value |
| В                  | The electrodes should be covered by a new solder at least 90% of immersed area.            |