Chip Type, Wide Temperature Range







UWZ

• Chip type operating over wide temperature range of to −55 to +105°C.


• Designed for surface mounting on high density PC board.


• Applicable to automatic mounting machine fed with carrier tape.

• Compliant to the RoHS directive (2011/65/EU).

• AEC-Q200 compliant. Please contact us for details.

Values marked with an \* in the dimension table are scheduled to be discontinued and are not recommended for new designs.







#### ■ Specifications

Item	Performance Characteristics												
Category Temperature Range	-55 to +105°C												
Rated Voltage Range	4 to 50V												
Rated Capacitance Range	1 to 1500μF	to 1500µF											
Capacitance Tolerance	±20% at 120Hz, 20	±20% at 120Hz, 20°C											
Leakage Current	After 2 minutes' ap	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01CV or 3 (µA), whichever is greater.											
								Measurem				,	
Tangent of loss angle (tan $\delta$ )	Rated voltage (V)	4	6.3		10	16		25	3	-	50		
	tan δ (MAX.)	0.40	0.30	(	).24	0.20	)	0.16	0.	14	0.14	j	
	Measurement frequency : 120Hz												
O1-1-77	Rated voltage (V)			4	6.3	3 1	10	16	25	35	50		
Stability at Low Temperature	Impedance ratio	Z-25°C /	Z+20°C	7	4		3	2	2	2	2		
	ZT / Z20 (MAX.)	Z-40°C /	Z+20°C	15	8		8	4	4	3	3		
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for					tance		Within ±20%	of the initia	ial capacitance value for capacitors of \$43mm unit, and 16V or less. initial capacitance value for capacitors of 25V or more. the initial specified value			
	1000 hours at 105°		· [	tan δ Leakag	age current Less than or equal to the initial specified value								
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.												
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 se is maintained at 250°C. The capacitors shall me characteristic requirements listed at right when removed from the plate and restored to 20°C.				neet the		1	Capacitance tan δ Leakage cur		Within ±10% of the initial capacitance value Less than or equal to the initial specified value Less than or equal to the initial specified value			
Marking	Black print on the case top.												


# ■Chip Type





<sup>%1.</sup> Voltage mark for 6.3V is 「6V」. In case of marking for \$\phi\$ units, "V" for rated

# Type numbering system (Example: 16V 10µF)



									(mm)
φD×L	* 3 × 5.4	4 × 5.4	5 × 5.4	6.3 × 5.4	6.3 × 5.8	6.3 × 7.7	8 × 5.4	8 × 10	10 × 10
Α	1.5	1.8	2.1	2.4	2.4	2.4	3.3	2.9	3.2
В	3.3	4.3	5.3	6.6	6.6	6.6	8.3	8.3	10.3
С	3.3	4.3	5.3	6.6	6.6	6.6	8.3	8.3	10.3
E	0.8	1.0	1.3	2.2	2.2	2.2	2.3	3.1	4.5
L	5.4	5.4	5.4	5.4	5.8	7.7	5.4	10	10
Н	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.5 to 0.8	0.8 to 1.1	0.8 to 1.1

<sup>※2.</sup> In case of marking for φ3 units. Lot No is expressed by a digit (month code).



#### ■ Dimensions

V		4		6.3		10		16		25		35		50	
Cap. (µF) Code		0G		0J		1A		1C		1E		1V		1H	
1	010						]   							4 × 5.4 (*3)	6.3(5.9)
2.2	2R2						! !					<b>%</b> 3×5.4	7.5	4 × 5.4 (*3)	11 (9)
3.3	3R3				i							*3 × 5.4	9	4 × 5.4	14
4.7	4R7						 			4 × 5.4 (*3)	13 (10)	4 × 5.4	15	5 × 5.4	19
10	100				!		1	4 × 5.4 (*3)	18 (14)	5 × 5.4	23	5 × 5.4	25	6.3 × 5.4	30
22	220	4 × 5.4	22	4 × 5.4	22	5 × 5.4	27	5 × 5.4	30	6.3 × 5.4	38	$6.3 \times 5.4$	42	•8 × 5.4	51 (45)
33	330	5 × 5.4	30	5 × 5.4	30	5 × 5.4	35	6.3 × 5.4	40	6.3 × 5.4	48	• 8 × 5.4	59 (52)	6.3 × 7.7	60
47	470	5 × 5.4	36	5 × 5.4	36	$6.3 \times 5.4$	46	6.3 × 5.4	50	●8×5.4	66 (59)	$6.3 \times 5.8$	63	6.3 × 7.7	63
100	101	$6.3 \times 5.4$	60	$6.3 \times 5.4$	60	$6.3 \times 5.4$	60	$6.3 \times 5.4$	60	6.3 × 7.7	91	$6.3 \times 7.7$	84	8 × 10	140
150	151	$6.3 \times 5.8$	86	$6.3 \times 5.8$	86	$6.3 \times 5.8$	86	6.3×7.7	95	8 × 10	140	8 × 10	155	10 × 10	180
220	221	• 8 × 5.4	102 (91)	• 8 × 5.4	102 (91)	6.3×7.7	105	6.3×7.7	105	8 × 10	155	8 × 10	190	10 × 10	220
330	331	6.3 × 7.7	105	6.3 × 7.7	105	8 × 10	195	8 × 10	195	8 × 10	190	10 × 10	300		
470	471	8 × 10	210	8 × 10	210	8 × 10	210	8 × 10	230	10×10	300		! !		
680	681	8 × 10	210	8 × 10	210	10 × 10	310	10 × 10	310						
1000	102	8 × 10	230	8 × 10	230	10 × 10	310						İ	Case size	Rated
1500	152	10 × 10	310	10 × 10	310	·							l I	φD×L(mm)	ripple

 $(*3):_{\varphi 3}$  In such a case, 2 will be put at 12th digit of type numbering system.

Rated ripple current (mArms) at 105°C 120Hz

Size  $\phi$ 6.3 × 5.8 is available for capacitors marked. " • " In such a case, 6 will be put at 12th digit of type numbering system.

# • Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more	
Coefficient	0.70	1.00	1.17	1.36	1.50	

- Taping specifications are given in page 23.
- Recommended land size, soldering by reflow are given in page 18, 19.
- Please select UUX(p.158), UUJ(p.164) series if high C/V products are reqired.
- Please refer to page 3 for the minimum order quantity.

 $<sup>\</sup>ensuremath{\text{\#}}$  However,  $\phi 3$  which are scheduled to be discontinued. Not recommended for new designs.