DB2G42900L1

For rectification

■ Features

- Low forward voltage VF
- Forward current (Average) IF(AV) ≦ 1.0 A rectification is possible
- RoHS compliant (EU RoHS / MSL:Level 1 compliant)


■ Marking Symbol: D5

Packaging

Embossed type (Thermo-compression sealing): 1 000 pcs / reel (standard)

■ Absolute Maximum Ratings

Parameter	Symbol	Min	Max	Unit
Reverse Voltage *1	VR	-	40	V
Maximum Peak Reverse Voltage *1	VRM	-	40	V
Average Forward Current *2,3	IF(AV)	-	1.0	Α
Average Forward Current *2,4	IF(AV)	-	1.0	Α
Non-repetitive Peak Surge Forward Current *1,5	IFSM	-	15	Α
Operating Junction Temperature *6	Tj	-	150	°C
Ambient Temperature	Та	-40	+150	°C
Storage Temperature	Tstg	-55	+150	°C



Note) *1: Ta = Tj = 25°C

*2: Squre wave : $\sigma = 0.5$

*3: Ta ≤ 91°C, when device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick), copper wiring (620.0mm² area, 36µm thick).

- *4: Tsp ≦ 137°C
- *5: Squre wave : Tp = 5 ms
- *6: Power derating is necessary so that Tj < 150°C.

(Waveform definition)	IF ↑ ← Tp
Duty Cycle : $\sigma = \frac{Tp}{T}$	Time
	Time


■ Electrical Characteristics Ta = 25 °C ± 3 °C

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Forward Voltage	VF	IF = 1.0 A	-	0.43	0.52	V
Reverse Current	IR	VR = 40 V	-	50	150	μA
Terminal Capacitance	Ct	VR = 10 V, f = 1 MHz	-	28	-	pF
Reverse Recovery Time *1	trr	IF = IR = 100 mA, Irr = 10 mA	-	8.8	-	ns


- Note) 1. Measuring methods are based on JAPANESE INDUSTRIAL STANDARD JIS C 7031 measuring methods for diodes.
 - 2. This product is sensitive to electric shock (static electricity, etc.).

Due attention must be paid on the charge of a human body and the leakage of current from the operating equipment.

3. *1: Measurement circuit, input pulse, output pulse for Reverse recovery time




- (1) Bias Insertion Unit (N-50BU)
- (2) Pulse Generator (PG-10N), RS = 50Ω
- (3) Wave Form Analyzer (SAS-8130), Ri = 50 Ω



 $tp = 2 \mu s$ tr = 0.35 ns

tr = 0.35 ns $\sigma = 0.05$





IR = 100 mA

Irr = 10 mA


Page 1 of 8

Electrical Characteristics Technical Data (Reference)





IR - VR / Typical Data



(Graph legends)

(1)	Ta =	150	°C
(2)	Ta =	125	°C
(3)	Ta =	85	°C
(4)	Ta =	25	°C
(5)	Ta =	-40	°C

Page 2 of 8

Electrical Characteristics Technical Data (Reference)

PF(AV) - IF(AV) / Typical Data 1.00 Average Forward Power Dissipation : PF(AV) [W] Tj = 25°C (Waveform definition) (1) (2) (3)Duty Cycle : $\sigma = \frac{Tp}{T}$ (4) (Graph legends) σ= 1.0 σ= 0.8 (3) σ = 0.5 $\sigma = 0.3$ 0.00 0.4 1.6

Average Forward Current : IF(AV) [A]

PR(AV) - VR / Typical Data 0.0030 Average Reverse Power Dissipation: PR(AV) [W] Tj = 25°C (Waveform definition) 0.0025 (1) 0.0020 Duty Cycle : $\sigma = \frac{Tp}{T}$ 0.0015 (2) (3) 0.0010 (Graph legends) σ= 1.0 σ= 0.7 0.0005 (4) σ= 0.5 (3)(4) σ = 0.2 0.0000 10 30 40

Reverse Voltage: VR [V]

Page 3 of 8

Established : 2015-10-13 Revised : ###-##-##


DB2G42900L1

Panasonic

Electrical Characteristics Technical Data (Reference)

PF(AV) - IF(AV) / Typical Data 1.00 Average Forward Power Dissipation : PF(AV) [W] (Waveform definition) Tj = 150°C (1) (2) (3)Duty Cycle : $\sigma = \frac{Tp}{T}$ (4) (Graph legends) σ= 1.0 σ= 0.8 (3) σ = 0.5 $\sigma = 0.3$ 0.00 0.4 0.6 1.6

Average Forward Current : IF(AV) [A]



Page 4 of 8

Established : 2015-10-13 Revised : ###-##-##

Schottky Barrier Diode


DB2G42900L1

Panasonic


■ Thermal Characteristics

Parameter	Symbol	Conditions	Min	Тур	Max	Unit
Thermal Resistance, Junction to Solder Point	$R_{th(j-sp)}$	Ta = 25°C, in free air	-	20	1	°C/W
Thermal Resistance, Junction to Ambient *1	R _{th(j-a)}	Ta = 25°C, in free air	-	92	-	°C/W
Thermal Resistance, Junction to Ambient *2	R _{th(j-a)}	Ta = 25°C, in free air	-	170	-	°C/W


- Note) *1: Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick), copper wiring (620.0mm² area, 36µm thick).
 - *2: Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick), copper wiring (108.6mm² area, 36µm thick).



Thermal Characteristics Technical Data (Reference)



Note) *1: Single pulse measurement (Waveform definition)




(Graph legends)


		- 3 /
(1)		Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick),
(1)	(1)	copper wiring (108.6mm ² area, 36µm thick).
(2)		Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick),
(2)	copper wiring (620.0mm ² area, 36µm thick).	

DB2G42900L1

Panasonic


Thermal Characteristics Technical Data (Reference)





Note) *1: Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick), copper wiring (108.6mm² area, 36µm thick). *2: Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick), copper wiring (620.0mm² area, 36µm thick).

Power Derating Technical Data (Reference)




IF(AV) - Ta *2 / Typical Data 1.6 Tj =150°C (1) 1.4 Average Forward Current: IF(AV) [A] (2) 1.2 (3) 1.0 (4) 8.0 0.6 0.4 0.2 0.0 25 50 75 150 100 125 Ambient Temperature: Ta [°C]

IF(AV) - Tsp / Typical Data 1.6 Tj =150°C (1) 1.4 Average Forward Current: IF(AV) [A] (2) 1.2 (3) 1.0 (4) 8.0 0.6 0.4 0.2 0.0 25 50 75 100 125 150

Solder Point Temperature: Tsp [°C]

(Grap	h legends)	(
(1)	σ = 1.0	
(2)	$\sigma = 0.8$	
(3)	$\sigma = 0.5$	
(4)	$\sigma = 0.3$	



Note)

*1: Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick), copper wiring (108.6mm² area, 36µm thick).

(Evaluation board outline)



*2: Device mounted on a FR4 PCB (25.4mm×25.4mm, 1mm thick), copper wiring (620.0mm² area, 36µm thick).

(Evaluation board outline)




Page 7 of 8

Schottky Barrier Diode

DB2G42900L1


DCSP1006010-N1

Unit: mm



■ Land Pattern (Reference)

Unit: mm



Page 8 of 8

Established : 2015-10-13 Revised : ###-##-##

Request for your special attention and precautions in using the technical information and semiconductors described in this book

- (1) If any of the products or technical information described in this book is to be exported or provided to non-residents, the laws and regulations of the exporting country, especially, those with regard to security export control, must be observed.
- (2) The technical information described in this book is intended only to show the main characteristics and application circuit examples of the products. No license is granted in and to any intellectual property right or other right owned by Panasonic Corporation or any other company. Therefore, no responsibility is assumed by our company as to the infringement upon any such right owned by any other company which may arise as a result of the use of technical information described in this book.
- (3) The products described in this book are intended to be used for general applications (such as office equipment, communications equipment, measuring instruments and household appliances), or for specific applications as expressly stated in this book.

 Consult our sales staff in advance for information on the following applications:
 - Special applications (such as for airplanes, aerospace, automotive equipment, traffic signaling equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 - It is to be understood that our company shall not be held responsible for any damage incurred as a result of or in connection with your using the products described in this book for any special application, unless our company agrees to your using the products in this book for any special application.
- (4) The products and product specifications described in this book are subject to change without notice for modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the range of absolute maximum rating and the guaranteed operating conditions (operating power supply voltage and operating environment etc.). Especially, please be careful not to exceed the range of absolute maximum rating on the transient state, such as power-on, power-off and mode-switching. Otherwise, we will not be liable for any defect which may arise later in your equipment.
 - Even when the products are used within the guaranteed values, take into the consideration of incidence of break down and failure mode, possible to occur to semiconductor products. Measures on the systems such as redundant design, arresting the spread of fire or preventing glitch are recommended in order to prevent physical injury, fire, social damages, for example, by using the products.
- (6) Comply with the instructions for use in order to prevent breakdown and characteristics change due to external factors (ESD, EOS, thermal stress and mechanical stress) at the time of handling, mounting or at customer's process. When using products for which damp-proof packing is required, satisfy the conditions, such as shelf life and the elapsed time since first opening the packages.
- (7) This book may be not reprinted or reproduced whether wholly or partially, without the prior written permission of our company.

20100202