



BAS70TS

SURFACE MOUNT SCHOTTKY DIODES

VOLTAGE 70 Volts **CURRENT** 0.2 Amperes

SOD-523


Unit: inch (mm)

FEATURES

- Fast switching speed
- Surface mount package ideally suited for automatic insertion
- High conductor
- In compliance with EU RoHS 2002/95/EC directives

MECHANICAL DATA

- Case: SOD-523, Plastic
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 0.002 gram
- Marking: 70



ABSOLUTE RATINGS

PARAMETER	Symbol	Value	Units
Reverse Voltage	V_R	70	V
Peak Reverse Voltage	V_{RRM}	70	V
Average Rectified Current at Temp=25°C	$I_{F(AV)}$	0.2	A
Non-repetitive Peak Forward Surge Current at t=1.0 s	I_{FSM}	0.6	A

ELECTRICAL AND THERMAL CHARACTERISTICS

PARAMETER	Symbol	Test Condition	MIN.	TYP.	MAX.	Units
Power Dissipation	P_{TOT}	150	-	-	-	mW
Thermal Resistance , Junction to Ambient	$R_{\theta JA}$	667	-	-	-	°C/W
Junction Temperature	T_J	150	-	-	-	°C
Storage Temperature at Temp=25°C	T_{STG}	-55 to 150	-	-	-	°C
Reverse Breakdown Voltage	$V_{(BR)}$	$I_R=10\mu A$	70	-	-	V
Reverse Current	I_R	$V_R=70V$ $V_R=50V$	-	-	1.0 0.1	μA
Forward Voltage	V_F	$I_F=1.0mA$ $I_F=10mA$	-	-	0.41 0.75 1.00	V
Maximum Junction Capacitance	C_J	$V_R=0V, f=1.0MHz$	-	-	2.0	pF



BAS70TS

ELECTRICAL CHARACTERISTICS CURVE




FIG. 1-TYPICAL FORWARD CHARACTERISTIC




FIG. 2-TYPICAL REVERSE CHARACTERISTICS




FIG. 3 TYPICAL JUNCTION CAPACITANCE




FIG. 4 FORWARD CURRENT DERATING




BAS70TS

MOUNTING PAD LAYOUT

SOD-523

Unit: inch (mm)



ORDER INFORMATION

- Packing information
 - T/R - 12K per 13" plastic Reel
 - T/R - 5K per 7" plastic Reel

LEGAL STATEMENT

Copyright PanJit International, Inc 2009

The information presented in this document is believed to be accurate and reliable. The specifications and information herein are subject to change without notice. Pan Jit makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose. Pan Jit products are not authorized for use in life support devices or systems. Pan Jit does not convey any license under its patent rights or rights of others.