

## 30V N-Channel Enhancement Mode MOSFET



**V<sub>DSS</sub>= 30V****R<sub>D(on)</sub>, V<sub>GS</sub>@10V, I<sub>DS</sub>@5.8A < 38m****R<sub>D(on)</sub>, V<sub>GS</sub>@4.5V, I<sub>DS</sub>@5.0A < 52m**

## Features

Advanced trench process technology

High Density Cell Design For Ultra Low On-Resistance

## Package Dimensions



REF.	Millimeter		REF.	Millimeter	
	Min.	Max.		Min.	Max.
A	2.70	3.10	G	1.90	REF.
B	2.40	2.80	H	1.00	1.30
C	1.40	1.60	K	0.10	0.20
D	0.35	0.50	J	0.40	-
E	0	0.10	L	0.85	1.15
F	0.45	0.55	M	0°	10°







**ABSOULTE MAXIMUM RATINGS (Ta = 25 Unless otherwise noted )**

Parameter	Symbol	Typical	Unit
Drain-Source Voltage	V <sub>DSS</sub>	30	V
Gate-Source Voltage	V <sub>GSS</sub>	±20	V
Continuous Drain Current (T <sub>J</sub> =150 ) T <sub>A</sub> =25 T <sub>A</sub> =70	I <sub>D</sub>	5.8 4.9	A
Pulsed Drain Current	I <sub>DM</sub>	30	A
Power Dissipation T <sub>A</sub> =25 T <sub>A</sub> =70	P <sub>D</sub>	1.4 1.0	W
Maximum Body-Diode Continuous Current		2.5	A
Operation Junction Temperature	T <sub>J</sub>	-55	C
Storage Temperature Range	T <sub>STG</sub>	-55/150	C
Thermal Resistance-Junction to Ambient	R <sub>JA</sub>	150	W

**ELECTRICAL CHARACTERISTICS ( Ta = 25 Unless otherwise noted )**

Parameter	Symbol	Condition	Min	Typ	Max	Unit
<b>Static</b>						
Drain-Source Breakdown Voltage	V(BR)DSS	V <sub>GS</sub> =0V, I <sub>D</sub> =250uA	30			V
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250uA	1.1		3.0	V
Gate Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> =0V, V <sub>GS</sub> =±20V			±100	nA
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =30V, V <sub>GS</sub> =0V			1	uA
On-State Drain Current	I <sub>D(on)</sub>	V <sub>DS</sub> 5V, V <sub>GS</sub> =4.5V	10			A
Drain-source On-Resistance	R <sub>DSS(on)</sub>	V <sub>GS</sub> =10V, I <sub>D</sub> =5.8A V <sub>GS</sub> =4.5V, I <sub>D</sub> =5.0A		33 37	38 52	m
Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> =1.0A, V <sub>GS</sub> =0V		0.7	1.1	V
<b>Dynamic</b>						
Total Gate Charge	Q <sub>g</sub>	V <sub>DS</sub> =15V, V <sub>GS</sub> =4.5V I <sub>D</sub> 5.8A		9.7	12	nC
Gate-Source Charge	Q <sub>gs</sub>			1.6		
Gate-Drain Charge	Q <sub>gd</sub>			3.1		
Turn-On Time	t <sub>d(on)</sub> t <sub>r</sub>	V <sub>GS</sub> =10V, V <sub>DS</sub> =10V, R <sub>L</sub> =2.7 , V <sub>GEN</sub> =4.5V		3.3	5	nS
Turn-Off Time	t <sub>d(off)</sub> t <sub>f</sub>			4.8	7	
				26.3	40	
				4.1	6	

## TYPICAL CHARACTERISTICS



## TYPICAL CHARACTERISTICS




Figure 7: Gate-Charge Characteristics




Figure 8: Capacitance Characteristics




Figure 9: Maximum Forward Biased Safe Operating Area (Note E)




Figure 10: Single Pulse Power Rating Junction-to-Ambient (Note E)




Figure 11: Normalized Maximum Transient Thermal Impedance