## **HCJ Series** Surface Mount High Current Jumper Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

#### Features:

- Chip size from 0402 to 2512
  - Max. resistance value less than 3 milliohm for 0402, less than 0.5 milliohm for all other sizes
  - Qualified to AEC-Q200
  - RoHS compliant, lead-free and halogen-free

### Applications: • Switching power supply

- Voltage regulation module
- DC-DC converter, adaptor, battery pack, charger
- PDA and cell phone
- Power and battery management applications



Electrical Specifications								
Type / Code	Power Rating (W) @ 70 °C	Current Rating (A)	Max Overload Current (A)	Operating Temperature Range	Ohmic Range ( $\Omega$ )			
HCJ0402	0.125	6.5	14.2		≤ 0.003			
HCJ0603	0.25	22.4	56		≤ 0.0005			
HCJ0805	0.5	31.6	79	-55°C to +155°C	≤ 0.0005			
HCJ1206	0.75	38.7	96.7		≤ 0.0005			
HCJ2512	2	63.2	158		≤ 0.0005			

Power rating: P=I<sup>2</sup>\*R



Type / Code	L	VV	t	A	Unit
110 10 10 2	$0.039 \pm 0.004$	$0.020 \pm 0.002$	0.016 ± 0.002	$0.012 \pm 0.004$	inches
11050402	$1.00 \pm 0.10$	$0.50 \pm 0.05$	$0.40 \pm 0.05$	$0.30 \pm 0.10$	mm
	0.063 ± 0.010	$0.031 \pm 0.010$	$0.020 \pm 0.008$	$0.016 \pm 0.008$	inches
11050003	$1.60 \pm 0.25$	$0.80 \pm 0.25$	$0.50 \pm 0.20$	$0.40 \pm 0.20$	mm
	0.079 ± 0.010	$0.047 \pm 0.010$	$0.026 \pm 0.008$	$0.022 \pm 0.008$	inches
11050805	$2.00 \pm 0.25$	$1.20 \pm 0.25$	$0.65 \pm 0.20$	$0.55 \pm 0.20$	mm
HC 11206	0.126 ± 0.010	$0.063 \pm 0.010$	$0.026 \pm 0.008$	$0.031 \pm 0.008$	inches
11031200	$3.20 \pm 0.25$	$1.60 \pm 0.25$	$0.65 \pm 0.20$	$0.80 \pm 0.20$	mm
HC 12512	$0.256 \pm 0.008$	0.126 ± 0.008	$0.030 \pm 0.004$	0.033 ± 0.010	inches
11032312	$6.50 \pm 0.20$	$3.20 \pm 0.20$	0.75 ± 0.10	$0.85 \pm 0.25$	mm

### Power Derating Curve:



# Stackpole Electronics, Inc.

### HCJ Series Surface Mount High Current Jumper Chip Resistor

**Resistive Product Solutions** 

Performance Characteristics								
Test	Test Method	Test Specification	Test Condition					
Short Time Overload	JIS C-5201-1 clause 4.13		2.5 times of rated current Rating power duration: 5 seconds					
High Temperature Exposure	JIS C-5201-1 clause 4.23.2		1000 hours at 155 °C ± 2 °C					
Low Temperature Storage	JIS C 5201-1 clause 4.23.4		1000 hours at -55 °C ± 2 °C					
Resistance to Solder Heat	JIS C-5201-1 clause 4.18		The part shall be immersed into the flux specified in the solder bath 260 °C ± 5 °C for 10 ± 1 seconds					
Moisture Load Life	JIS C-5201-1 clause 4.24		Specimens shall be placed in a chamber and subject to a relative humidity of 90~95% and to a temperature of 40 °C ± 2 °C. Load with rated current 1.5 hours "ON", 0.5 hours "OFF", for the period of 1000 hours.					
Temperature cycling JIS C-520 clause 4.			-55 °C to +155 °C, 100 cycles					
Load Life	JIS C-5201-1 clause 4.25	For size 0402, max. 0.003 $\Omega$ All other sizes, max. 0.0005 $\Omega$	Apply rated power at 70 °C ± 2 °C for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF"					
Mechanical Shock	JIS C-5202 clause 6.7		a = 50G, t = 11 ms, 5 times shock					
Substrate Bending	JIS C-5201-1 clause 4.33		Span between fulcrums: 90mm Bend width: 2mm					
Solderability	JIS C-5201-1 clause 4 17	Solder shall cover 95% or more of the electrode area	$245 \pm 5$ °C for $3 \pm 0.5$ seconds					



Resistive Product Solutions





Type / Code	а	b	С	Unit
	0.016	0.020	0.024	inches
HCJ0402	0.40	0.50	0.60	mm
HCJ0603	0.024	0.051	0.039	inches
	0.60	1.30	1.00	mm
110 10005	0.031	0.055	0.055	inches
HC30803	0.80	1.40	1.40	mm
HCJ1206	0.047	0.071	0.071	inches
	1.20	1.80	1.80	mm
HCJ2512	0.150	0.083	0.134	inches
	3.80	2.10	3.40	mm

# HCJ Series

Surface Mount High Current Jumper Chip Resistor

Stackpole Electronics, Inc.

**Resistive Product Solutions** 



	Taping Specifications – Paper Tape								
Type / Code	А	В	E	F	W	Unit			
HCJ0402	$0.028 \pm 0.002$	$0.047 \pm 0.002$	$0.069 \pm 0.004$	$0.138 \pm 0.002$	$0.315 \pm 0.008$	inches			
	$0.70 \pm 0.05$	1.20 ± 0.05	1.75 ± 0.10	$3.50 \pm 0.05$	$8.00 \pm 0.20$	mm			
HCJ0603	$0.046 \pm 0.008$	$0.078 \pm 0.008$	$0.069 \pm 0.004$	$0.138 \pm 0.004$	$0.315 \pm 0.012$	inches			
	1.18 ± 0.20	$1.98 \pm 0.20$	1.75 ± 0.10	$3.50 \pm 0.10$	8.00 ± 0.30	mm			
HCJ0805	$0.066 \pm 0.008$	$0.094 \pm 0.008$	$0.069 \pm 0.004$	$0.138 \pm 0.004$	$0.315 \pm 0.012$	inches			
	$1.68 \pm 0.20$	2.38 ± 0.20	1.75 ± 0.10	$3.50 \pm 0.10$	8.00 ± 0.30	mm			
HCJ1206	$0.081 \pm 0.008$	$0.144 \pm 0.008$	$0.069 \pm 0.004$	$0.138 \pm 0.004$	$0.315 \pm 0.012$	inches			
	2.05 ± 0.20	$3.65 \pm 0.20$	1.75 ± 0.10	$3.50 \pm 0.10$	8.00 ± 0.30	mm			
Type / Code	G	Р	Н	D	Т	Unit			
HCJ0402	$\begin{array}{r} 0.157 \pm 0.004 \\ 4.00 \ \pm \ 0.10 \end{array}$	$0.079 \pm 0.004$ 2.00 \pm 0.10	$0.079 \pm 0.004$ 2.00 \pm 0.10	0.059 +0.004/-0.00 1.50 +0.10/-0.00	$0.018 \pm 0.004$ $0.45 \pm 0.10$	inches mm			
HCJ0603	$0.157 \pm 0.004$	$0.157 \pm 0.004$	$0.079 \pm 0.004$	0.059 +0.004/-0.00	$0.030 \pm 0.008$	inches			
	$4.00 \pm 0.10$	$4.00 \pm 0.10$	2.00 ± 0.10	1.50 +0.10/-0.00	$0.75 \pm 0.20$	mm			
HCJ0805	$0.157 \pm 0.004$	$0.157 \pm 0.004$	$0.079 \pm 0.004$	0.059 +0.004/-0.00	$0.034 \pm 0.008$	inches			
	$4.00 \pm 0.10$	$4.00 \pm 0.10$	2.00 ± 0.10	1.50 +0.10/-0.00	$0.87 \pm 0.20$	mm			
HCJ1206	$0.157 \pm 0.004$	$0.157 \pm 0.004$	$0.079 \pm 0.004$	0.059 +0.004/-0.00	$0.034 \pm 0.008$	inches			
	$4.00 \pm 0.10$	$4.00 \pm 0.10$	2.00 ± 0.10	1.50 +0.10/-0.00	$0.87 \pm 0.20$	mm			

**Resistive Product Solutions** 

Taping Specifications – Embossed Plastic Tape										
		Top Tape Top Tape Embossed Resistor Tape		F W						
Type / Code	А	В	E	F	W	Unit				
	0.138 ± 0.004 0.268 ± 0.004 0.069 ± 0.004 0.217 ± 0.002 0.472 ± 0.008 inches 3.50 ± 0.10 6.80 ± 0.10 1.75 ± 0.10 5.50 ± 0.05 12.00 ± 0.20 mm									
HCJ2512	HCJ2512 P0 P1 P2 D0 T Unit									
	$0.157 \pm 0.002$	$0.157 \pm 0.004$	$0.079 \pm 0.002$	$0.059 \pm 0.004$	$0.039 \pm 0.008$ 1 00 ± 0.20	inches				
	4.00 £ 0.05	4.00 £ 0.10	2.00 £ 0.05	1.00 ± 0.10	1.00 ± 0.20					

### **RoHS** Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union's directive regarding "Restrictions on Hazardous Substances" (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

	RoHS Compliance Status									
Standard Product Series	Description	Package / Termination Type	Standard Series RoHS Compliant	Lead-Free Termination Composition	Lead-Free Mfg. Effective Date (Std Product Series)	Lead-Free Effective Date Code (YY/WW)				
HCJ	Molded Metal Plate Sensing Resistor	SMD	YES	100% Matte Sn over Ni	Always	Always				

### "Conflict Metals" Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the "conflict region" of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.

### Compliance to "REACH"

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, "The Registration, Evaluation, Authorization and Restriction of Chemicals", otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

### **Environmental Policy**

It is the policy of Stackpole Electronics, Inc. (SEI) to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.

How to Order												
1	2	3	4	Ę	5	6	7	8	9	10	11	12 13
н	С	J	0	(	6	0	3	Z	Т	0	R	0 0
Product Series		Size		To	erance				Pac	kaging		Resistance Value
HCJ	Size 0402 0603	Rating Current 6.5A 22.4A	Code	Tol	Size 0402 0603	Value (Ω) <0.003	Code	Description Paper Tape		Size 0402 0603, 0805, 1206	Quantity 10,000 5.000	Four characters with the multiplier used as the decimal holder.
	0805 1206 2512	31.6A 38.7A 63.2A	Z	Zero Ohm	0805 1206 2512	<0.0005		Embossed Plasti	с	2512	4,000	0 ohm = 0R00