# LOW CAPACITANCE MINIATURE TVS ARRAY



## DESCRIPTION

The PRSB6.8C is a transient voltage suppressor array (TVS) designed to protect applications such as wireless telecommunication devices, SMART phones and portable electronics. The PRSB6.8C is available in a bidirectional configuration with a working voltage of 4.7V and a minimum breakdown voltage of 5.7V. This device is rated for 10 Watt peak pulse power using the 10/1000µs waveform and 50 Watts at 8/20µs, which is sufficient protection for tertiary type lightning threats at key interface locations.

The PRSB6.8C is also suited to protect data lines against ESD and EFT. This device meets the IEC 61000-4-2 and IEC 61000-4 requirements. At higher operating frequencies or faster edge rates, insertion loss and signal integrity are a major concern. This device in conjunction with passive components integrated into a TVS/filter network can be used for EMI/RFI protection.

## **FEATURES**

# • Compatible with IEC 61000-4-2 (ESD): Air ±15kV, Contact ±8kV

- Compatible with IEC 61000-4-4 (EFT)
- 10 Watts Peak Pulse Power per Line (tp =10/1000μs)
- 50 Watts Peak Pulse Power per Line ( $tp = 8/20\mu s$ )
- Bidirectional Configuration
- Protects 1 Data Line
- Low Clamping Voltage
- Easy Placement for Manufacturing
- Low Capacitance
- RoHS Compliant
- REACH Compliant

# **MECHANICAL CHARACTERISTICS**

- Molded JEDEC DFN-2-0402 Package
- Approximate Weight: 0.8 milligrams
- Lead-Free Nickel Paladium Gold Plating
- Solder Reflow Temperature 260-270°C
- 8mm Tape and Reel Per EIA Standard 481
- Flammability Rating UL 94V-0

# APPLICATIONS

- Noise Suppression for Data Lines
- SMART Phones
- Portable Electronics

# **PIN CONFIGURATION**




# TYPICAL DEVICE CHARACTERISTICS

05224

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified								
PARAMETER	SYMBOL	VALUE	UNITS					
Operating Temperature	T <sub>opr</sub>	-55 to 150	°C					
Storage Temperature	T <sub>stg</sub>	-55 to 150	°C					
Junction Temperature	T <sub>A</sub>	150	°C					
Peak Pulse Power (tp = 10/1000μs) - See Figure 1	P <sub>pp</sub>	10	Watts					
Peak Pulse Power (tp = 8/20µs) - See Figure 1	P <sub>pp</sub>	50	Watts					
Power Dissipation	Р	150	mW					


ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified								
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE	MINIMUM BREAKDOWN VOLTAGE	MAXIMUM CLAMPING VOLTAGE (Fig. 2)	MAXIMUM CLAMPING VOLTAGE (Fig. 2)	MAXIMUM LEAKAGE CURRENT	TYPICAL CAPACITANCE	
		V <sub>wm</sub> VOLTS	@ 1mA V <sub>(BR)</sub> VOLTS	@ IP = 1A V <sub>c</sub> VOLTS	@ 8/20μs V <sub>c</sub> @ Ι <sub>թթ</sub>	@ 3.5V Ι <sub>υ</sub> μΑ	@0V, 1MHz C pF	
PRSB6.8C	А	4.7	5.7	13.0	17.5V @ 3.0A	0.5	15	




05224.R18 7/18

# 


## **TYPICAL DEVICE CHARACTERISTICS**





# 

## **TYPICAL DEVICE CHARACTERISTICS**



05224.R18 7/18

## **DFN-2-0402 PACKAGE INFORMATION**


<b>OPTION 1 - OUTLINE DIMENSIONS</b>								
		IETERS	INCHES					
DIIVI	MIN	MAX	MIN	MAX				
А	0.99	1.04	0.039	0.041				
В	0.58	0.64	0.023	0.025				
С	0.43	0.48	0.017	0.019				
н	0.13	0.18	0.005	0.007				
L1	0.28	0.33	0.011	0.013				
L2	0.23	0.28	0.009	0.011				
L3	0.23	0.28	0.009	0.011				
L4	0.18	0.23	0.007	0.009				
NOTES								


#### NOTES

05224

1. Dimensioning and tolerances per ANSI Y14.M, 1985.


2. Controlling dimension: inches.






OPTION 1 - PAD LAYOUT DIMENSIONS								
DIM	MILLIN	IETERS	INCHES					
	MIN	MAX	MIN	MAX				
А	0.737	0.787	0.029	0.031				
В	0.331	0.381	0.013	0.015				
С	0.356	0.406	0.014	0.016				
E	1.423	1.523	0.056	0.060				
F	0.534	0.584	0.021	0.023				
NOTES								

1. Controlling dimension: inches.






05224.R18 7/18

## TAPE AND REEL

05222



SPECIFICATIONS												
REEL DIA.	TAPE WIDTH	A0	В0	ко	D	E	F	W	PO	P2	Р	tmax
178mm (7")	8mm	0.70 ± 0.05	1.15 ± 0.05	0.60 ± 0.003	1.55 ± 0.10	1.75 ± 0.10	3.50 ± 0.05	8.00 ± 0.30	4.00 ± 0.10	2.00 ± 0.05	2.00 ± 0.05	0.25
NOTES 1. Dimensions are in millimeters. 2. Surface mount product is taped and reeled in accordance with FIA-481												

Surface mount product is taped and reeled in accordance with EIA-481.
 Suffix - T710 = 7" Reel - 10,000 pieces per 8mm tape.

4. Marking on Part - marking code (see page 2).

ORDERING INFORMATION								
BASE PART NUMBER         LEADFREE SUFFIX         TAPE SUFFIX         QTY/REL         REEL SIZE         TUBE QTY								
PRSB6.8C	-LF	-T710	10,000	7″	n/a			
This device is only available in a Lead-Free configuration.								

## COMPANY INFORMATION

## **COMPANY PROFILE**

In business more than 20 years, ProTek Devices<sup>™</sup> is a privately held semiconductor company. The company offers a product line of overvoltage protection and overcurrent protection components. These include transient voltage suppressor array (TVS arrays) avalanche breakdown diode, steering diode TVS array and electronics SMD chip fuses. These components deliver circuit protection in electronic systems from numerous overvoltage and overcurrent events. They include lightning; electrostatic discharge (ESD); nuclear electromagnetic pulses (NEMP); inductive switching; and electromagnetic interference (EMI) / radio frequency interference (RFI). ProTek Devices also offers LED wafer die for ESD protection and related high frequency products.

## CONTACT US

## **Corporate Headquarters**

2929 South Fair Lane Tempe, Arizona 85282 USA

## By Telephone

General: 602-431-8101 Sales: & Marketing: 602-414-5109 Customer Service: 602-414-5114 Product Technical Support: 602-414-5107

#### By Fax

General: 602-431-2288

### By E-mail:

Asia Sales: <u>asiasales@protekdevices.com</u> Europe Sales: <u>europesales@protekdevices.com</u> U.S. Sales: <u>ussales@protekdevices.com</u> Distributor Sales: <u>distysales@protekdevices.com</u> Customer Service: <u>service@protekdevices.com</u> Technical Support: <u>support@protekdevices.com</u>

## ProTek Devices (Asia Pacific) Pte. Ltd.

8 Ubi Road 2, #06-19 Zervex Singapore - 408538 Tel: +65-67488312 Fax: +65-67488313

#### Web

www.protekdevices.com

COPYRIGHT © ProTek Devices 2007 - This literature is subject to all applicable copyright laws and is not for resale in any manner.

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice.

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance. ProTek assumes no responsibility with respect to the selection or specifications of such products. ProTek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ProTek assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability without limitation special, consequential or incidental damages.

LIFE SUPPORT POLICY: ProTek Devices products are not authorized for use in life support systems without written consent from the factory.