

SEMF3V3LC

Low Capacitance Quad Array for ESD Protection Description

Revision:A

General Description

This integrated transient voltage suppressor device (TVS) is designed for applications requiring transient overvoltage protection, printers, business machines, communication systems, medical equipment, and other applications. Its integrated design provides very effective and reliable protection for separate lines using only one package. These devices are ideal for situations where board space is at a premium.

Applications

- Serial and Parallel Ports
- Microprocessor Based Equipment
- Notebooks, Desktops, Servers
- Cellular and Portable Equipment

Features

- Four Separate Unidirectional Configurations for Protection
- Low Leakage Current < 1 μ A @ 3Volts
- Power Dissipation: 380mW
- Small SOT-353 SMT Package
- Low Capacitance
- Complies to USB 1.1 Low Speed & Speed Specifications
- These are Pb-Free Devices

Complies with the following standards IEC61000-4-2

Level 4 15 kV (air discharge)


8 kV(contact discharge)

MIL STD 883E - Method 3015-7 Class 3
25 kV HBM (Human Body Model)

Functional diagram








Maximum Ratings (1 _A =25°C)									
Symbol	Parameter	Value	Units						
P_{PK}	Peak Power Dissipation(8×20 μ s@T _A =25°C)	30	W						
P_D	Steady State Power-1 Diode	380	mW						
R _{® JA}	Thermal Resistance, Junction-to-Ambient	327	°C/W						
	Above 25℃, Derate	3.05	Mw/℃						
T_{Jmax}	Maximum Junction Temperature	150	$^{\circ}$						
$T_J T_{stg}$	Operation Junction and Storage Temperature Range	-55 to +150	$^{\circ}$						
T_L	Lead Solder Temperature(10 seconds duration)	260	$^{\circ}$						

Electrical Parameter

Symbol	Parameter					
I _{PP}	Maximum Reverse Peak Pulse Current					
V _C	Clamping Voltage @ I _{PP}					
V_{RWM}	Working Peak Reverse Voltage					
I _R	Maximum Reverse Leakage Current @ V _{RWM}					
I _T	Test Current					
V_{BR}	Breakdown Voltage @ I _T					
I _F	Forward Current					
V_{F}	Forward Voltage @ I _F					




Electrical Characteristics

Part Numbers	V_{BR}					V _F		С	
	Min.	Тур.	Max.	I _T	V_{RWM}	I _R	Max.	I _F	Typ. 0v bias
	V	V	V	mA	V	μA	V	mA	pF
MSEMF3V3LC	5.3	5.6	5.88	1	3.3	1.0	1.25	200	28

- 1. Non-repetitive current per Figure 1.
- 2. Only 1 diode under power. For 4 diodes under power
- Capacitance of one diode at f=1MHz,T_A=25[°]C

Typical Characteristics







Figure 1 Pulse Width

Figure 2 Power Derating Curve



SOT-353 Mechanical Data

