

ALUMINUM ELECTROLYTIC CAPACITORS SPECIFICATION SHEET

RoHS Compliant Part

CUSTOMER PART No.		
Rubycon PART No.	330 FW 102 A OLY C 11×30	
DRAWING No.	REE - 073981	ISSUE No. 1
ISSUE DATE	5 February 2019	



RUBYCON CORPORATION

ENGINEERING DIVISION
ELECTROLYTIC CAPACITOR DESIGN DEPT.

1938-1, NISIMINOWA, INA-SHI, NAGANO-KEN, JAPAN

TEL No. 0265-72-7116


FAX No. 0265-73-3380

DESIGN	KOICHI WADA
	<i>K. Wada</i>
CHECK	
APPROVAL	HIROKAZU HORIKAWA
	<i>H. Horikawa</i>

Fixed aluminium electrolytic capacitors
with non-solid electrolyte
for use in electronic flash equipment

Style	CE 04
Customer Part Number	
Operating Temperature Range	-20°C ~ +60°C
The General Standard	JEITA RC-2365B

1. Dimensions (UNIT : mm)



NAME	SLEEVE	CASE	SEAL	LEAD WIRE
MATERIAL	PET	A α	Rubber	CP Wire
APPEARANCE	Black			Tin plating

2. Electrical Performance


RUBYCON CATALOGUE NUMBER	NOMINAL CAPACITANCE (MFD)	CAPACITANCE TOLERANCE (%)	RATED VOLTAGE (V d.c.)	SURGE VOLTAGE (V d.c.)	LEAKAGE CURRENT (μ A/330V.5min.) MAX.	D.F. (%) MAX
330 FW 102	102	-10 ~ +20	330	350	102	6

Condition : Measuring Temperature . . . 25°C \pm 2°C
Measuring Frequency 120Hz

3. Marking : Unless otherwise specified, capacitor shall be clearly marked on its body.

- (1) Brand **Rubycon**
- (2) Application PHOTO-FLASH
- (3) Rated Voltage 330V
- (4) Nominal Capacitance 102 μ F
- (5) Polarity
- (6) Lot. No.
- (7) Sleeve Material PET

4. Charge/Discharge Life Test Ambient Temperature: 5°C ~ 35°C



	1 cycle/30sec.	After 5,000 cycles
Capacitance Change		Within \pm 10% of the initial value.
D.F.		Not more than 150% of the specified value.
Leakage Current		Not more than 150% of the specified value.

5. Note (on the use of aluminium electrolytic capacitors)

Guide to application expect the above are described in our catalog and EIAJ RCR-2367C.
EIAJ RCR-2367C : "Safety Application Guide for fixed aluminum electrolytic capacitors for use in electronic equipment." Published by Japan Electronics and Information Technology Industries Association.

Rubycon
RUBYCON CORPORATION

DRAWING No.

REE - 073981

ISSUE No.

1