



RoHS

MESSRS: _____

APPROVAL NO

710 - 045

DATE

2014.11.20

ALUMINUM ELECTROLYTIC

CAPACITOR

APPROVAL SHEET

CATALOG TYPE	SHL-BP SERIES
USER PART NO.	
适用机种	
特记事项	Halogen-Free

QINGDAO SAMYOUNG ELECTRONICS CO.,LTD.

MANAGER OF DEVELOPMENT DEPARTMENT

GONG JANG SUG



USER APPROVAL:

APPROVAL NO.: _____

SamYoung(Korea) : 47,SAGIMAKGOL-RO,JUNGWON-GU,SEONGNAM-SI,GYEONGGI-DO,KOREA

SamYoung(China) : No.5 CHANGJIANG ROAD,PINGDU-CITY,SHANDONG-PROVINCE,CHINA

样式: H-1001-011

A4 (210×297)



SamYoung Electronics Co., Ltd.

APPROVAL NO. 710 - 045	ALUMINUM ELECTROLYTIC CAPACITOR	PAGE: 1 OF 5 DATE: 2014.11.20
---	--	--

Specifications of SHL-BP Series

Item	Characteristics								
Rated Voltage Range	6.3 ~ 100 VDC				160 ~ 250 VDC				
Operating Temperature Range	- 40 ~ + 85 °C				- 25 ~ + 85 °C				
Capacitance Tolerance	±20% (M) (at 20°C 120HZ)								
Leakage Current (in both directions)	After 5 minutes: $I = 0.03CV$ (μA) or $3 \mu A$, whichever is greater, Where, I: Max. Leakage current (μA) C: Nominal capacitance (μF) V: Rated Voltage (V_{DC}) (at 20°C)								
Dissipation Factor (TAN δ) (20°C , 120Hz)	Rated voltage(V_{DC})	6.3	10	16~25	35	50	63~100	160	200~250
	TAN δ (Max)	0.25	0.24	0.20	0.16	0.14	0.12	0.15	0.20
When the capacitance exceeds 1000 μF , 0.02 shall be added every 1000 μF increase.									
Temperature Characteristic (Impedance ratio at 120Hz)	Rated voltage(V_{DC})	6.3	10	16	25-100	160	160-2500		
	Z-25°C/Z+20°C	4	3	2	2	4	6		
	Z-40°C/Z+20°C	10	8	6	4	-	-		
Load Life	<p>The following specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied for 2,000 hours at 85°C. During this test , the raged voltage shall be reversed on the capacitor every 250 Hrs.</p> <p>Capacitance change : $\leq \pm 20\%$ of the initial Value (where $WV \leq 16V_{DC}, \pm 25\%$)</p> <p>TAN$\delta$: $\leq 200\%$ of the initial specified value</p> <p>Leakage current : \leq The initial specified value</p>								
Shelf Life	<p>The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them at 85°C for a half assurance load life time without voltage applied.</p> <p>The rated voltage shall be applied to the capacitors for a minimum of 30 minutes, at least 24 hours and not more than 48 hours before the measurements.</p> <p>Capacitance change : $\leq \pm 20\%$ of the initial Value (where $WV \leq 16V_{DC}, \pm 25\%$)</p> <p>TAN$\delta$: $\leq 200\%$ of the initial specified value</p> <p>Leakage current : $\leq 200\%$ of the initial specified value</p>								
Others	Satisfied characteristics KS C IEC 60384-4								

	← 	← 	← 
--	---	--	--

ALUMINUM ELECTROLYTIC CAPACITORS


APPROVAL NO.
710 - 045

RATINGS OF SHL-BP Series

ØDXL(mm)

WV CAP	6.3	10	16	25	35	50	63	80	100	160	200	250
0.47						5×11 11			5×11 14			
1						5×11 17			5×11 21			
2.2						5×11 25		5×11 29	6.3×11 34			
3.3						5×11 27	5×11 28	6.3×11 39	6.3×11 39	10×16 49	10×16 42	10×20 46
4.7					5×11 34	5×11 34	6.3×11 39	6.3×11 47	6.3×11 47	10×16 59	10×20 55	12.5×20 65
6.8									8×11.5 58			
10			5×11 27	5×11 42	5×11 43	6.3×11 52	6.3×11 57	8×11.5 65	8×11.5 71	12.5×20 109	12.5×20 95	12.5×25 103
22		5×11 37	5×11 40	6.3×11 65	6.3×11 73	8×11.5 89	8×11.5 95	10×16 125	10×16 135	12.5×25 177	16×25 170	16×31.5 186
33	5×11 64	5×11 45	5×11 49	6.3×11 80	8×11.5 100	8×11.5 105	10×12.5 135	10×16 150	12.5×20 220	16×25 240	16×35.5 239	18×35.5 256
47	5×11 76	5×11 54	6.3×11 67	6.3×11 95	8×11.5 120	8×11.5 124	10×16 180	10×20 195	12.5×20 240	16×35.5 329	18×40 321	
100	6.3×11 125	6.3×11 90	8×11.5 110	8×11.5 160	10×16 230	10×20 265	12.5×20 320	12.5×25 350	16×25 425	18×35.5 425		
220	8×11.5 215	8×11.5 150	10×12.5 195	10×16 305	12.5×20 410	12.5×25 480	16×25 575	16×31.5 615	18×35.5 720			
330	8×11.5 265	10×16 240	10×16 265	12.5×20 450	12.5×20 505	16×25 650	16×31.5 655	18×35.5 755				
470	10×12.5 370	10×16 290	10×20 345	12.5×20 540	12.5×20 655	16×31.5 835	18×35.5 965					
1000	10×20 650	12.5×20 510	12.5×25 605	16×25 950	16×31.5 1140							
2200	12.5×25 1160	16×25 940	16×31.5 1070	18×35.5 1620								
3300	16×25 1570	16×31.5 1200	18×35.5 1400	← Case Size ØD X L (mm)								
4700	16×31.5 2020	18×35.5 2160		← Permissible Ripple Current (mA rms) at 85°C, 120Hz								
6800	18×35.5 2607											

DIMENSIONS OF SHL-BP Series



Marking:


BLACK SLEEVE, WHITE INK

When $\Phi D \leq 8$, $\Phi D' \leq D + 0.5$, and $L' \leq L + 1.5$

When $\Phi D > 8$, $\Phi D' \leq D + 0.5$, and $L' \leq L + 2.0$

ΦD	5	6.3	8	10	12.5	16	18
F	2	2.5	3.5	5	5	7.5	7.5
Φd	0.5	0.5	0.6	0.6	0.6	0.8	0.8



ALUMINUM ELECTROLYTIC CAPACITORS**APPROVAL NO.
710 - 045****STRUCTURE AND MATERIALS**

CE04 TYPE

MINIATURE SIZED TYPE CAPACITORS COMPONENT

PART NAME	MATERIALS	VENDER
LEAD WIRE	TINNED COPPER - PLY WIRE(Pb-FREE)	KISTRON (KOREA/CHINA) KOHOKU (JAPAN/CHINA) NANTONG HONG YANG (CHINA)
AL LEAD	ALUMINUM 99.92 % OVER	KANG WON AUTO FITTING NAN TONG HUI FENG (CHINA) NANTONG HONG YANG KOHOKU (JAPAN/CHINA) KISTRON (KOREA/CHINA)
PACKING PAD	SYNTHETIC RUBBER	SUNG NAM (KOREA/CHINA) CCW/ZHE JIANG TIAN TAI (CHINA) ZHE JIANG TIAN HUA
SLEEVE	P.E.T(Poly Ethylene Terephthalate Resin)	MOO DEUNG (KOREA/CHINA) SUZHOU QILIAN (CHINA) YUN LIN PLASTIC
AL CASE	ALUMINUM 99.0 % OVER	ZHANG JIA GANG LIAN YI LIN AN AO XING (CHINA) NANTONG CHUANGJIA DONG NAM (KOREA/CHINA) D.N TECH/HA NAM
AL FOIL ⊕	FORMED ALUMINUM 99.9 % OVER	K.D.K/JCC/MATSUSHITA (JAPAN) SAM YOUNG (KOREA) BECROMAL (ITALY) SATMA (FRANCE) HEC XINJIANG JOINWORLD (CHINA) HUAFENG / HISTAR / RAOIO LUXON/LITON (TAIWAN)
AL FOIL ⊖	ETCHED ALUMINUM 98.0 % OVER	K-JCC (KOREA) K.D.K (JAPAN) AFT/INCULCU/SHENGHONG (CHINA) ELECON/WU JIANG FEILO
SEPARATOR	INSULATION PAPER	KAN/LUNAN (CHINA) SPO (GERMANY) N.K.K (JAPAN)
ADHESIVE TAPE	POLY PROPYLENE OR POLY IMIDE FILM	NITTO/NICHIBAN (JAPAN) DAEIL/SWECO (KOREA)



When using aluminum electrolytic capacitors, pay strict attention to the following:

1. Electrolytic capacitors for DC application require polarization.

Confirm the polarity. If used in reversed polarity, the circuit life may be shortened or the capacitor may be damaged. For use on circuits whose polarity is occasionally reversed, or whose polarity is unknown, use bi-polarized capacitors (BP-series). Also, note that the electrolytic capacitor cannot be used for AC application.

2. Do not apply a voltage exceeding the capacitor's voltage rating.

If a voltage exceeding the capacitor's voltage rating is applied, the capacitor may be damaged as leakage current increases. When using the capacitor with AC voltage superimposed on DC voltage, care must be exercised that the peak value of AC voltage does not exceed the rated voltage.

3. Do not allow excessive ripple current to pass.

Use the electrolytic capacitor at current values within the permissible ripple range. If the ripple current exceeds the specified value, request capacitors for high ripple current applications.

4. Ascertain the operating temperature range.

Use the electrolytic capacitors according to the specified operating temperature range. Usage at room temperature will ensure longer life.

5. The electrolytic capacitor is not suitable for circuits in which charge and discharge are frequently repeated.

If used in circuits in which charge and discharge are frequently repeated, the capacitance value may drop, or the capacitor may be damaged. Please consult our engineering department for assistance in these applications.

6. Apply voltage treatment to the electrolytic capacitor which has been allowed to stand for a long time.

If the electrolytic capacitor is allowed to stand for a long time, its withstand voltage is liable to drop, resulting in increased leakage current. If the rated voltage is applied to such a product, a large leakage current occurs and this generates internal heat, which damaged the capacitor. If the electrolytic capacitor is allowed to stand for a long time, therefore, use it after giving voltage treatment (Note 1). (However, no voltage treatment is required if the electrolytic capacitor is allowed to stand for less than 2 or 3 years at normal temperature.)

7. Be careful of temperature and time when soldering.

When soldering a printed circuit board with various components, care must be taken that the soldering temperature is not too high and that the dipping time is not too long. Otherwise, there will be adverse effects on the electrical characteristics and insulation sleeve of electrolytic capacitors in the case of small-sized electrolytic capacitors, nothing abnormal will occur if dipping is performed at less than 260°C for less than 10 seconds.

8. Do not place a soldering iron on the body of the capacitor.

The electrolytic capacitor is covered with a vinyl sleeve. If the soldering iron comes in contact with the electrolytic capacitor body during wiring, damage to the vinyl sleeve and/or case may result in defective insulation, or improper protection of the capacitor element.

9. Cleaning circuit boards after soldering.

Some solvents have adverse effects on capacitors.

Please refer to the next page.

10. Do not apply excessive force to the lead wires or terminals.

If excessive force is applied to the lead wires and terminals, they may be broken or their connections with the internal elements may be affected. (For strength of terminals, refer to KS C IEC 60384-4 (JIS C5101-1, JIS C5101-4))

11. Care should be used in selecting a storage area.

If electrolytic capacitors are exposed to high temperatures caused by such things as direct sunlight, the life of the capacitor may be adversely affected. Storage in a high humidity atmosphere may affect the solderability of lead wires and terminals.

12. Surge voltage.

The surge voltage rating is the maximum DC over-voltage to which the capacitor may be subjected for short periods not exceeding approximately 30 seconds at infrequent intervals of not more than six minutes. According to KS C IEC 60384-4, the test shall be conducted 1000 cycles at room temperature for the capacitors of characteristic KS C IEC 60384-4 or at the maximum operating temperature for the capacitors of characteristics B and C of KS C IEC 60384-4 with voltage applied through a series resistance of 1000 ohms without discharge. The electrical characteristics of the capacitor after the test are specified in KS C IEC 60384-4. Unless otherwise specified, the rated surge voltage are as follows:

Rated Voltage(V)	2	4	6.3	10	16	25	35	50	63	80	100	160	200	250	315	350	400	450	500
Rated Surge Voltage(V)	2.5	5	8	13	20	32	44	63	79	100	125	200	250	300	365	400	450	500	550

Note 1 Voltage treatment ... Voltage treatment shall be performed by increasing voltage up to the capacitor's voltage rating gradually while lowering the leakage current. In this case, the impressed voltage shall be in the range where the leakage current of the electrolytic capacitor is less than specified value. Meanwhile, the voltage treatment time may be effectively shortened if the ambient temperature is increased (within the operating temperature range).

Note 2 For methods of testing, refer to KS C IEC 60384-4, (JIS C 5101-1, JIS C 5101-4)



CLEANING CONDITIONS

Aluminum electrolytic capacitors that have been exposed to halogenated hydrocarbon cleaning and defluxing solvents are susceptible to attack by these solvents. This exposure can result in solvent penetration into the capacitors, leading to internal corrosion and potential failure.

Common type of halogenated cleaning agents are listed below.

Chemical Name	Structural Formula	Representative Brand Name
Trichlorotrifluoroethane	C ₂ Cl ₃ F ₃	Freon TF, Daiflon S-3
Fluorotrichloromethane	CCl ₃ F	Freon-11, Daiflon S-1
1,1,1-Trichloroethane	F ₂ H ₃ Cl ₃	Chloroethane
Trichloroethylene	C ₂ HCl ₃	Trichiene
Methyl Chloride	CH ₃ Cl	MC

We would like to recommend you the below cleaning materials for your stable cleaning condition taking the place of previous materials.

◎ Isopropyl Alcohol (IPA) or Water

Cleaning method: One of immersion, ultrasonic or vapor cleaning.

Maximum cleaning time: 5 minutes (Chip type: 2 minutes)

※ Do not use AK225AES

Aluminum electrolytic capacitors are easily affected by halogen ions, particularly by chloride ions. Excessive amounts of halogen ions, if happened to enter the inside of the capacitors, will give corrosion accidents-rapid capacitance drop and vent open. The extent of corrosion accidents varies with kinds of electrolytes and seal-materials. Therefore, the prevention of halogen ion contamination is the most important check point for quality control in our production lines. At present, halogenated hydrocarbon-contained organic solvents such as Trichloroethylene, 1,1,1-Trichloroethane, and Freon are used to remove flux from circuit boards.


If electrolytic capacitors are cleaned with such solvents, they may gradually penetrate the seal portion and cause the erosion. When using latex-based adhesive on the capacitors rubber end seal for adhesion to a PCB, corrosion may occur depending on the kind of solvent in the adhesive. Select an adhesive as an organic solvent with dissolved polymer that is not halogenated hydrocarbon. Hot air drying is required for eliminating the solvent between the product and the PCB at 50°C~80°C after coating.

Followings are the penetration path of the halogenated solvent.


- ① Penetration between the rubber and the aluminum case
- ② Penetration between the rubber and the lead wire
- ③ Penetration through the rubber

The inside of the capacitors, the mechanism of corrosion of aluminum electrolytic capacitors by halogen ions can be explained as follows:

Halides (RX) are absorbed and diffused into the seal portion. The halides then enter the inside of the capacitors and contact with the electrolyte of the capacitors. Where by halogen ions are made free by a hydrolysis with water in the electrolyte:



The halogen ions (X⁻) react with the dielectric substance (Al₂O₃) of aluminum electrolytic capacitors:



AlX₃ is dissociated with water:



※ MANUFACTURING SITE

- SamYoung Electronics Co., Ltd. (Korea/China)

