

1N5400 - 1N5408

AXIAL LEADED SILICON RECTIFIER DIODES

VOLTAGE RANGE: 50 - 1000V CURRENT: 3.0 A

Features

- High Current Capability and Low Forward Voltage Drop
- Low Reverse Leakage Current
- Plastic Material: UL Flammability Classification Rating 94V-0

Mechanical Data

Case: DO-201AD

Terminals: Plated Leads Solderable per


MIL-STD-202, Method 208Polarity: Cathode Band

Mounting Position: AnyMarking: Type Number

Weight: 1.1 grams (approx.)







DO-201AD							
Dim	Min	Max					
Α	25.40	_					
В	7.20	9.50					
С	1.20	1.30					
D	4.80	5.30					
All Dimensions in mm							

Maximum Ratings and Electrical Characteristics @ TA = 25°C unless otherwise specified


Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.


Characteristic	Symbol	1N 5400	1N 5401	1N 5402	1N 5404	1N 5406	1N 5407	1N 5408	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	50	100	200	400	600	800	1000	>
RMS Reverse Voltage	V _{R(RMS)}	35	70	140	280	420	560	700	V
Average Rectified Output Current @ T _A = 105°C (Note 1)	I _O	3.0					Α		
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	200							Α
Forward Voltage @ I _F = 3.0A	V _{FM}	1.0						٧	
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	I _{RM}	10 100					μΑ		
Typical Junction Capacitance (Note 2)	C _j	50 25			pF				
Typical Thermal Resistance Junction to Ambient		15						K/W	
Operating and Storage Temperature Range		-65 to +150						°C	

Notes: 1. Valid provided that leads are kept at ambient temperature at a distance of 9.5mm from the case.


2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.







V_F, INSTANTANEOUS FORWARD VOLTAGE (V) Fig. 2 Typical Forward Characteristics



1.0 10 100 100 100

NUMBER OF CYCLES AT 60Hz Fig. 3 Maximum Non-Repetitive Surge Current

V_R, REVERSE VOLTAGE (V) Fig. 4 Typical Junction Capacitance