	Specifications No.	
Messrs.		
(first · revised) Delivery	/ Specificatio	ons
Product No : Quartz Crystal Unit S	P-T2A-F	
Item code : Q-SPT2S0327620C5I	DJ	
Product form : 32.768kHz ± 20 × 10	0 ⁻⁶ / 12.5pF	
The number of copies : copies (copies ret	urn to us)	
Date of Registrantion :		
NOTICE		
Advance agreement will be needed before char		
2. Provided that the information herein is subject t3. When the product described herein includes Reetc, they may not be exported without authorization.	egulated Products subject The	Wassenaar Arrangement
 The contents of this specification including all fi (copyright or know-how) of Seiko Instruments Ir specifications to third parties without permission 	nc. It is strictly prohibited to cor	
 In the case that the products described herein a influence any one of the human body, human life medical equipment or vehicles, please let us known. 	e and property, such as physic	
Seiko Instruments Inc.	Dept. of Issue	Dept. of Control
Quartz Crystal Division Network Components Business	Sales Section	Quality Assurance Section
1-8, Nakase, Mihamaku, Chiba shi, Chiba 261-8507 Japan		

Delivery Specifications

1.Scope

These specifications apply to QUARTZ CRYSTAL RESONATORS (hereinafter referred to as RESONATORS) to be manufactured by Seiko Instruments Inc. (hereinafter referred to as SII) to

2.Designation

RESONATORS are designated "SP-T2A-F"(32.768kHz).

3.Shape and dimensions

As per the SP-T2A-F drawing shown on page 5.

4.Electrical characteristics

Specified on page 2 through 3.

5. Shipment and packaging

- 5.1 (3,000) pcs are the standard lot size to which the lot number shall be allotted
- 5.2 The packaging shall conform to the resonator packaging standards.

6.Outgoing inspection

- 6.1 When mutually agreed, the outgoing inspection shall be conducted as per the standard on page 4.
- 6.2 The outgoing inspection slip is not basically affixed to each packaging.

7.Warranty

In the event that any defective RESONAT	TORS or defective lot is found at
incoming inspection at	and that
any defect resulting from failures in proces	ss-control at SII after incoming
inspection is found, good RESONATORS	shall be supplied to
free of cha	arge as a replacement
In the event that any trouble or problems	rising directly from RESONATORS
occurs, it will be amicably settled between	both parties, provided that
warranty shall be done within the score of	replacement of good RESONATORS.

8. Amendment or abolition of the specifications

Amendment or abolition of the sp	pecifications shall be made upon mutual consent
between	and SII. If any problem arises ,
it shall be amicably settled betwe	en both parties.

9.Effectiveness of the specifications

These specifications are effective after receipt of returned copies with your approved sign.

10.Ohters

RoHS compliant

These products use Pb in high melting temperature type solders exempted by RoHS directive.

[1] The maximum rating

	<u>- </u>			
	Item	Symbol	Rating	Note
1	Storage temperature range	T_stg	-55 ~ +125	
2	Maximum drive level	DL max.	1.0 μW max.	

[2] Recommended Operating Condition

	Item	Symbol	Rating	Note
1	Operating temperature range	T_use	-40 ~ +85	
2	Drive level	DL	0.1 μW typ.	

[3] Electrical -Characteristics

Measurement temperature: 25±2

_[3	Electrical -Character	Measurement temperature 1 25±2		
	Item	Symbol	Specifications	Conditions
1	Nominal frequency	f_nom	32.768 kHz	
2	Frequency tolerance	f_tol	± 20 × 10 ⁻⁶	
3	Load capacitance	C_L	12.5 pF	
4	Motional resistance	R ₁	50 kΩ max.	Measured with ATI 4192A Impedance analyzer. OSC LEVEL = 0.1V
5	Q-value	Q	40 × 10 ³ min.	calculated with the following equation: Q=(2π·Fr·L ₁)/R ₁
6	Motional capacitance	C ₁	2.2 fF typ.	
7	Shunt capacitance	C ₀	1.0 pF typ.	Measured with ATI 4192A Impedance analyzer. OSC LEVEL = 0.1V
8	Turnover temperature	Ti	25 ± 5	Measure this coefficient at 3 points of 10 、25 、and 40 using
9	Parabolic coefficient	В	(-3.5±0.8)×10 ⁻⁸ /	C-MOS circuit.
10	Frequency ageing	f_age	± 5 × 10 ⁻⁶ / year	25±3 、 First year
11	Insulation resistance	IR	500 MΩ min.	Measured with ATI 4329A Insulation Resistance Meter. Apply DC100V.

[4] Environment-proof · Mechanical property

	-			
No	Item	Specifications	Conditions	
1	High temperature storage	$f/f = \pm 5 \times 10^{-6}$	After storage under 85 for 500 hrs,	*1
			measure at room temperature.	
2	Low temperature storage	$f/f = \pm 5 \times 10^{-6}$	After storage under -40 for 500	*1
			hrs, measure at room temperature.	
3	High temperature and	$f/f = \pm 5 \times 10^{-6}$	After storage under 60 ±2 , 90 to	*1
	high humidity storage		95% RH for 500 hrs, measure at room	
			temperature.	
4	Thermal shock resistance	$f/f = \pm 5 \times 10^{-6}$	Measured at room temperature after	*1
			20 cycles.	
			-25 +80 for 30 minutes.	
5	Mechanical shock resistance	$f/f = \pm 5 \times 10^{-6}$	Measure after free drop of the	*2
			RESONATOR three times from the	
			height of 75cm onto a wooden board.	
6	Vibration resistance	$f/f = \pm 5 \times 10^{-6}$	Amplitude 1.5mm and 10 ~ 60Hz with	*2
			cycle time 2 ~ 3 minutes in 3 direction	
			(X,Y,and Z axis)each for 2 hrs.	
7	IR Reflow	$f/f = \pm 10 \times 10^{-6}$	Measure after 1 time reflow under	*1
			reflow profile specified in page 10	

Note:

- 1. The adove tests no. 1 to 7 must be conducted independently (not series tests)
- 2. *1: Measure after 24 hours soak at room temperature .
- 3. *2: Measure after 2 hours soak at room temperature .
- 4. R1 is $70k\Omega$ max. after the each above tests.

[5] Precautions

(1) Recommended mounting conditions

Reflow profile As per reflow profile shown in page 10.

Manual soldering 350 max. for 4 sec. max.

(2) Cleaning

The crystal resonator may be destroyed by ultrasonic cleaning.

We don't guarantee the quality of the product with that cleaning method because such conditions as type of the washing machine, power, time, position in the bath, etc. can not be specified.

Please confirm ultrasonic cleaning is not giving any damage to the product before use when that cleaning method must be used.

[6] Outgoing inspection standard


·The outgoing inspection shall be conducted as per the following standard .

·The sampling shall be performed according to the ANSI/ASQCZ1.4-1996 .


No	Item	Sampling level	AQL(%)
1	Frequency tolerance		1.0
2	Equivalent series resistance		1.0
3	Outer appearance		1.5
4	Others characteristics	Periodical quality insp	ection

[7] Out Line Drawing

1 . Mechanical dimensions




2 . Marking




- *1 Frequency
- *2 Specification
- *3 Mfg. Year Last digit of year
- *4 Mfg. Month

 Jan. ~ Dec. : A ~ M


 (excluding I)






3 . Lead connection
Do not connect Terminals #2, #3 to the outside electrode. These are dummy terminals.

4. Recommendation soldering pattern figure.





Materials	42 Alloy	Remarks	Unit
	Sn (100%)		1 = 1 mm

[8] Taping specification

1. Drawing of tape dimensions


Carrier tape see Drawing No. 8/11 Reel for carrier tape see Drawing No. 9/11

2. Material

Carrier tape : Polystyrene Reel for carrier tape : HIPS

3. Taping method

(1) Taping shall be placed in tapes in such manner as to assure that marking of the components is visible as per Fig. 1




(2) Reel

On the side of reel there shall be more than 20 blocks of "No components". The beginning of Carrier Tape shall be bent vertically and hooked on groove of reel.


(3) Leader

On the side of leader, there shall be more than 20 blocks of "No components " The length of Leader shall be over 400 mm.


The Length of Stick Tape for Cover Tape shall be about 100 mm and Stick Tape shall never be detached.



(4) Gap between Carrier Tape and Cover Tape Cover Tape protrudes from Carrier Tape by 0.5mm max.



Holes of Carrier Tape are covered with Cover Tape by 0.75mm max.




(5) Peel strength

The method of testing is done as shown below.


The value of force is at the beginning of desealing.

The Cover Tape peel forth shall be 0.1 ~ 1.3N at a peel speed of 300±10mm/min.



Carrier tape


- (1) Conforms with EIA-481(2) Tolerance ± 0.2




Unit=mm

Taping reel

- (1) Conforms with EIAJ ET-7200B
- (2) Quantity per reel: 3,000pcs./ for a reel




[9]Reflow Profile



Note: The temperature used herein means the temperature on the circuit board.


Reflow: 2 times max.

[10] Outside box packing specification



Outside Box	K2	K1	G2M	T1
Maximum reels	4	10	15	20

(4) An outer case packing structure (the sectional plan)



[Figure 3]

- (5) Storage quantity
 - ·It makes N=3,000 pieces/Lot
- [6] Sample of the label display (display department, please refer to [Figure 1] [Figure 2])

	PART	SP-T2A-F
Product bar code	Lot No.	
	Quantity	3,000 pcs
Item bar code *	Calibre	32.768kHz
		12.5 pF/ $\pm 20 \times 10^{-6}$
Quantity Lot. No. bar code	Remar	ks
3,000 XXXX		

PART : Our company product name

Lot No. : Lot No. display

Quantity: Quantity

Calibre: Frequency, CL value, F0 deviation

Remarks: Marking etc. : Item code

(7) Storage environment

A product avoids the direct ray and please store with the normal temperature and humidity . (Conformance in JIS Z8703 Standard Atmospheric Conditions for Testing.)

* Normal temperature range: 5 to 35

* Normal relative humidity range: 45 to 85%