



0.8A SURFACE MOUNT GLASS PASSIVATED BRIDGE RECTIFIER

FEATURES:


- Glass Passivated Chip Junction
- Reverse Voltage - 100 to 1000 V
- Average Rectified Output Current- 0.8 A
- High Surge Current Capability
- Designed for Surface Mount Application

PINNING

PIN	DESCRIPTION
1	Input Pin (~)
2	Input Pin (~)
3	Output Anode (+)
4	Output Cathode (-)

MECHANICAL DATA

- Case: UMB
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 68mg 0.0022oz



Maximum Ratings and Electrical characteristics






Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	UM1B	UM2B	UM4B	UM6B	UM8B	UM10B	Units
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	100	200	400	600	800	1000	V
Average Rectified Output Current at $T_A = 40^\circ C$	I_o	0.8						A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)	I_{FSM}	25						A
Forward Voltage per element $@I_F = 0.4A$ $@I_F = 0.8A$	V_F	1.0 1.1						V
Maximum DC Reverse Current $@T_A = 25^\circ C$ $@T_A = 125^\circ C$	I_R	5.0 100						μA
Typical Junction Capacitance (Note1)	C_J	13						pF
Typical Thermal Resistance (Note2)	$R_{\theta JA}$	180						$^\circ C/W$
Operating and Storage Temperature Range	T_j, T_{stg}	-55 ~ +150						$^\circ C$

Note: 1. Measured at 1MHz and applied reverse voltage of 4 V D.C.

2. P.C.B. mounted with 4x0.1x0.1"(4x2.54x2.54mm) copper pad areas.






PACKAGE OUTLINE

Plastic surface mounted package; 4 leads


UMB



UMB mechanical data

UNIT		A	C	D	E	H _E	d	e	∠
mm	max	1.1	0.22	3.5	3.5	4.0	2.6	0.5	7°
	min	0.96	0.15	3.3	3.3	3.6	2.4	0.4	
mil	max	44	8.7	137	137	276	103	20	7°
	min	38	5.9	130	130	252	94	15	

The recommended mounting pad size



Marking

Type number	Marking code
UM1B	UM1B
UM2B	UM2B
UM4B	UM4B
UM6B	UM6B
UM8B	UM8B
UM10B	UM10B