

深圳市金航标电子有限公司

客戶名稱 CUSTOMER:

客戶料號

CUSTOMER'S P/N:

料號

PART NUMBER : KH-3216F245W36

規格

DESCRIPTION : Chip Antenna 3216 M-Ant 2.45G Type 36

版本

VERSION: V2.2

日期

ISSUE DATE : 2018/01/30

客戶承認	
CUSTOMER APPROVED	


	工 程 部 R&D CENTER	
承 認 APPROVAL	確認 CHECKED	製 作 DRAWN
Ray	James	Thor





3216 Chip antenna

For Bluetooth / WLAN Applications



P/N: KH3216F245W36

	Dimension (mm)			
L	3.23 ± 0.20			
W	1.66 ± 0.20			
Т	1.23 ± 0.20			



Part Number Information

KH 3216 F 245 W 36

A	Product Series	Antenna
В	Dimension L x W	3.2X1.6mm (+-0.2mm)
C	Material	High K material
D	Working Frequency	2.4 ~ 2.5GHz
E	Feeding mode	Monopole & Single Feeding
F	Antenna type	Type=36

1. Electrical Specification


Specification						
Part Number	KH3216F245W36					
Central Frequency	2450	MHz				
Bandwidth	100 (Min.)	MHz				
Return Loss	-6.5 (Max)	dB				
Peak Gain	2.71	dBi				
Impedance	50	Ohm				
Operating Temperature	-40∼+85	$^{\circ}\!\mathbb{C}$				
Maximum Power	4	W				
Resistance to Soldering Heats	10 (@ 260°C)	sec.				
Polarization	Linear					
Azimuth Beamwidth Omni-directional						
Termination	Cu / Sn (Leadless)					

Remark : Bandwidth & Peak Gain was measured under evaluation board of next page




2. Recommended PCB Pattern

1.Evaluation Board Dimension



2. Evaluation Board Dimension

(若淨空區夠大,建議使用此 Layout,效能較佳)



Unit: mm








Suggested Matching

Feed Line TOP Copper VIA


重要資訊:

匹配元件建議使用精準度±1%以下的電感、電容、電阻






1.Layout Dimensions in Clearance area(Size=5.2*5.0mm)




Matching Circuit

2.Layout Dimensions in Clearance area(Size=8.2*5.0mm)

(若淨空區夠大,建議使用此 Layout,效能較佳)









3. Measurement Results

Return Loss






Radiation Pattern



	Efficiency	Peak Gain	Directivity
2400MHz	55.21 %	1.45 dBi	5.32 dBi
2450MHz	66.45 %	2.71 dBi	5.21 dBi
2500MHz	57.53 %	1.98 dBi	5.29 dBi

Chamber Coordinate System







ITEM		Test Condic	-	TEST CONDITION
ITEMREQUIREMENTSSolderability1. Wetting shall exceed 90% cover			coverage	Pre-heating temperature:150°C /60sec.
Solderability		ole mechanical dam		
	2. NO VISIL	ne mechanical dan	lage	Solder temperature:230±5°C
	Т	EMP (°C)		Duration:4±1sec.
				Solder:Sn-Ag3.0-Cu0.5
	2	230°C	4±1 sec.	Flux for lead free: rosin
			/ \	
		150℃	\longrightarrow	
		/	→ \	
		60s	sec \	
Solder heat		ole mechanical dam		Pre-heating temperature:150°C /60sec.
Resistance	2. Central	Freq. change :with	in ± 6%	Solder temperature:260±5°℃
	Ι τ	EMP (°C)		Duration:10±0.5sec.
			 1	Solder:Sn-Ag3.0-Cu0.5
		260°C	10±0.5 sec.	Flux for lead free: rosin
			/ \	
	1	150℃	 /	
		/ 	<u>→</u> \	
		/ 60	sec \	
	4			
Component Adhesion	1. No visib	ole mechanical dam	nage	The device should be reflow
(Push test)				soldered(230±5°C for 10sec.) to a tinned
(Fusii lest)				copper substrate A dynometer force gauge should be applied the side of the
				component. The device must with-ST-F
				0.5 Kg without failure of the termination
				attached to component.
Component	1. No visib	ole mechanical dam	nage	Insert 10cm wire into the remaining open
Adhesion			-	eye bend ,the ends of even wire lengths
(Pull test)				upward and wind together.
(. a 1881)				Terminal shall not be remarkably
				damaged.
Thermal shock	1 No vioih	ole mechanical dam	2000	+85°C =>30±3min
momar oncox			•	-40°C=>30±3min
	2. Central	Freq. change :with	In ±6%	Test cycle:10 cycles
	Phase	Temperature(°C)	Time(min)	The chip shall be stabilized at normal
	1 1	+85±5°C	30±3	condition for 2~3 hours before
	2	Room	Within	measuring.
	2	Temperature	3sec	measuring.
	3	-40±2℃	30±3	
		Room	Within	
	4	Temperature	3sec	
			<u>'</u>	
Resistance to	1. No visib	ole mechanical dam	nage	Temperature: 85±5°C
High		Freq. change :with	•	Duration: 1000±12hrs
Temperature		· =		The chip shall be stabilized at normal
	3. No disc	onnection or short	circuit.	condition for 2~3 hours before
				measuring.
Resistance to	1 No vicih	olo mochanical dam	2220	Temperature:-40±5°C
Low		ole mechanical dam	_	Duration: 1000±12hrs
Temperature		Freq. change :with		The chip shall be stabilized at normal
Tomporature	3. No disc	onnection or short	circuit.	condition for 2~3 hours before
				measuring.
Lumidit:				Temperature: 40±2°C
Humidity		ole mechanical dam	=	
	2. Central	Freq. change :with	in ±6%	Humidity: 90% to 95% RH
	3. No disc	onnection or short	circuit.	Duration: 1000±12hrs
				The chip shall be stabilized at normal
				condition for 2~3 hours before
				measuring.



5. Soldering and Mounting

Mildly activated rosin fluxes are preferred. The minimum amount of solder can lead to damage from the stresses caused by the difference in coefficients of expansion between solder, chip and substrate. The terminations are suitable for all wave and re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.





Recommended temperature profiles for re-flow soldering in Figure 1.


Products attachment with a soldering iron is discouraged due to the inherent process control limitations. In the event that a soldering iron must be employed the following precautions are recommended.

- Preheat circuit and products to 150°C
- Never contact the ceramic with the iron tip
- Use a 20 watt soldering iron with tip diameter of 1.0mm
- 280°C tip temperature (max)
- 1.0mm tip diameter (max)
- · Limit soldering time to 3 sec.




6.Packaging Information

♦ Tape Specification:



W	Ao	Во	Ко	Р	F	E	D	D1	Ро	P2	t
8.0	1.80	3.51	1.59	4.00	3.50	1.75	1.50	0.00	4.00	2.00	0.25
±0.30	±0.05	±0.10	±0.10	±0.05	±0.05	±0.10	±0.10	±0.10	±0.10	±0.05	±0.05

Reel Specification: (7", Φ180 mm)



7" x 8 mm

Tape Width(mm)	A(mm)	B(mm)	C(mm)	D(mm)	Chip/Reel(pcs)
8	9.0±0.5	60±2	13.5±0.5	178±2	3000



7. Storage and Transportation Information

Storage Conditions

To maintain the solderability of terminal electrodes:

- 1. Temperature and humidity conditions: -10~ 40°C and 30~70% RH.
- 2. Recommended products should be used within 6 months from the time of delivery.
- 3. The packaging material should be kept where no chlorine or sulfur exists in the air.

Transportation Conditions

- 1. Products should be handled with care to avoid damage or contamination from perspiration and skin oils.
- 2. The use of tweezers or vacuum pick up is strongly recommended for individual components.
- 3. Bulk handling should ensure that abrasion and mechanical shock are minimized.