




SHAPE & DIMENSION (UNIT:mm)

PAD LAYOUT(MM):

Recommended land pattern


ELECTRICAL SCHEMATIC:

ELECTRICAL SPECIFICATION


MEAS. ITEM	SPEC.				TEST FREQ.	CONDITIONS
L	3.3	μH	±	20%	100KHz//0.25V	Ta=25°C, Idc=0A
DCR	169	mΩ	Max.			Ta=25°C
Isat	2.4	A	Max.		100KHz//0.25V	ΔL/L ≤ 30%
Irms	2.0	A	Max.		100KHz//0.25V	ΔT ≤ 40°C

GENERAL SPECIFICATION

Electrical specifications :	at 25°C
Operation Temperature:	-40~+125°C
Storage Temperature:	-40~+125°C
(1)WIRE TYPE: H ∅ 0.13mm	
(2)WINDING: 13.5Ts(REF)	

Isat(飽和電流):電感瞬間的突波電流


TME(秒)	Lsat(A)	L(UH)	$\Delta L/L(\%)$
1	0.0	3.29	0.00
1	0.3	3.28	0.30
1	0.6	3.26	0.91
1	0.9	3.23	1.82
1	1.2	3.19	3.03
1	1.5	3.14	4.55
1	1.8	3.08	6.38
1	2.1	3.01	8.51
1	2.4	2.94	10.6
1	2.7	2.87	12.7
1	3.0	2.48	24.6



單點溫昇

TIME(S)	I _{rms} (A)	L(uH)	ΔL/L(%)	Temp(°C)	ΔT(°C)
0	0.0	3.29	0.00	28.0	0.0
30	0.3	3.28	0.30	28.2	0.2
30	0.6	3.26	0.91	29.6	1.6
30	0.9	3.23	1.82	32.8	4.8
30	1.2	3.19	3.03	36.3	8.3
30	1.5	3.14	4.55	40.1	12.1
30	1.8	3.08	6.38	49.7	21.7
30	2.1	3.01	8.51	58.7	30.7
30	2.4	2.94	10.6	73.0	45.0
30	2.7	2.87	12.7	88.2	60.2
30	3.0	2.48	24.6	118.4	90.4

※DC bias current characteristics in the ambient temperature 25°C Frequency 100KHz/0.25V




TEST DATA FOR PREPRODUCTION SAMPLE

TEST RESOLUTION					DIMENSION (Unit: mm)		
MEAS.							
ITEM	μH	$\text{m}\Omega$			长	宽	高
SPEC.	3.3	169			3.0±0.2	3.0±0.2	1.5MAX
	±	max					
TEST FREQ.	100KHz/0.25V		Isat 2.4A	$\Delta L/L \leq 30\%$	mm	mm	mm
	1	3.32	124	2.93	12.2	3.02	3.02
2	3.30	125	2.85	11.4	3.02	3.07	1.42
3	3.26	126	3.00	11.7	3.01	3.03	1.37
4	3.26	125	2.89	11.6	3.02	3.03	1.43
5	3.37	129	2.98	11.0	3.03	3.06	1.39
6							
7							
8							
9							
10							
AVG.	3.28	125	2.93	11.5	3.02	3.04	1.40
R	0.11	5.0	0.15	1.20	0.02	0.05	0.06

PACKAGING

包装



Packaging Quantity: **2,000** pcs/reel

Reel dimensions

UNIT:mm

