

REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD
1	▲	Finish change	16/JUN/17	VANDY	FRANK
2	▲	Add the "TXGA" logo	29/OCT/18	KATE	ANDY

SPECIFICATIONS:






Electrical

- Current Rating: 0.5A AC(rms)/DC
- Voltage Rating: 125V AC(rms)/DC
- Contact Resistance: 100 mΩ Max
- Insulation Resistance: 1000 MΩ Min
- Withstanding Voltage: 500V AC r.m.s
- Temperature Range-Operating: -20°C~+60°C


Material and Plating

- Housing: Thermoplastic UL 94V-0 Black
- ▲ Contact: Copper Alloy/gold in contact area, tin on tail
- Shell: Stainless Steel/tin plated
- Durability: 5000~10000 Times

Pin No.	Pin Assignment
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



Recommended P.C.Board Layout
General Tolerances: ±0.05mm



 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY	DATE	PART NO.	ITEM NO.	 Leader Of Industry
	X.±.012(0.30)	X.'±5'	FRANK	12/SEP/16	FCD708-7M	FCD708	
DESIGN UNITS Inch (metric)	X.X±.008(0.20)	.X'±2'	CHECKED BY	DATE	TITLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
SCALE 5:1	X.XX±.006(0.15)	.XX±1'	CHERRY	12/SEP/16	SIM card connector(H:1.35mm)		
SIZE A4	X.XXX±.004(0.10)	.XXX±0.5'	DRAWN BY	DATE			REV 2
			VERNON	12/SEP/16			SHEET NO. 1/1