

High Value Multilayer Ceramic Capacitors (High dielectric type)

LMK316ABJ226ML-T



■ Features

- Item Summary
22uF±20%, 10V,
X5R/B, 1206/3216 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 2000pcs

■ Products characteristics table

Capacitance	22 uF ± 20 %
Case Size (EIA/JIS)	1206/3216
Rated Voltage	10 V
tan δ (max)	10 %
Temperature Characteristic (EIA)	X5R
Operating Temp. Range (EIA)	-55 to +85 °C
Temperature Characteristic (JIS)	B
Operating Temp. Range (JIS)	-25 to +85 °C
High Temperature Loading (% Rated Voltage)	150 %
Insulation Resistance (min)	100 MΩ · μF
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	3.2 ±0.20 mm
Dimension W	1.6 ±0.20 mm
Dimension T	1.6 ±0.20 mm
Dimension e	0.50 +0.35/-0.25 mm






2016.12.30

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.

○ LMK316ABJ226ML

10V 3216 B/X5R 22 μ F +/- 20% t=1.8mmMAX

10V 1206 B/X5R 22 μ F +/- 20% t=0.071inchMAX



部品特性は設置環境、測定条件等により変化する場合があります。本データをご使用される際は実際の製品特性に対する参考データとしてご利用ください。また、本データは予告無く追加・削除及び変更を行う場合があります。ご注文の際は、納入仕様書のご確認をお願いします。

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.

TAIYO YUDEN reserves the right to make change to the data at any time without notice.

Before making final selection, please check product specification.