Spec Sheet

Wire-wound Chip Inductors (LB series)

LBC2518T470K



Features

- Item Summary 47uH±10%, 0.165A, 1007/2518 (EIA/JIS)
- Lifecycle Stage
 - Mass Production
- Standard packaging quantity (minimum)
 Taping Embossed 2000pcs

Products characteristics table

| Inductance | 47 uH ± 10 % |
|--|--|
| Case Size (EIA/JIS) | 1007/2518 |
| Rated Current (max) | 0.165 A |
| DC Resistance (max) | 2.47 Ω |
| DC Resistance (typ) | 1.9 Ω |
| LQ Measuring Frequency | 2.52 MHz |
| Self Resonant Frequency (min) | 12 MHz |
| Operating Temp. Range | -40 to +105 ℃ (Including-self-generated heat) |
| Temperature characteristic (Inductance change) | ± 25 % |
| RoHS2 Compliance (10 subst.) | Yes |
| REACH Compliance (168 subst.) | Yes |
| Soldering | Reflow |

■ External Dimensions

| Dimension L | 2.5 ±0.2 mm |
|-------------|-------------|
| Dimension W | 1.8 ±0.2 mm |
| Dimension T | 1.8 ±0.2 mm |
| Dimension e | 0.5 ±0.2 mm |

The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the Date at any time without notice.

Before making final selection, please check product specification.



Wire-wound Chip Inductors (LB series)

LBC2518T470K



Dimension unit: mm unit: inch

Length: 2.5 + / - 0.2 (0.098 + / - 0.008)

Width: 1.8 + / - 0.2 (0.071 + / - 0.008)

Height: 1.8 + / - 0.2 (0.071 + / - 0.008)

Inductance: 47 uH (test freq at 2.52MHz)
DC Resistance: 1.9 / 2.47 ohm (typ / max)

Rated Current: 165 mA

Rated current typical: 10% reduction from initial L value.

and Temperature will rise by 20 deg C





