



## Features

- N-Channel, 5V Logic Level Control
- Enhancement mode
- Very low on-resistance  $R_{DS(on)}$  @  $V_{GS}=4.5V$
- 100% Avalanche test
- Pb-free lead plating; RoHS compliant



Part ID	Package Type	Marking	Tape and reel information
VS40200AT	TO-220AB	40200AT	50pcs/Tube

$V_{DS}$	40	V
$R_{DS(on),TYP} @ V_{GS}=10V$	2.5	m $\Omega$
$R_{DS(on),TYP} @ V_{GS}=4.5V$	3.5	m $\Omega$
$I_D$	200	A

**TO-220AB**


## Maximum ratings, at $T_j=25^{\circ}C$ , unless otherwise specified


Symbol	Parameter	Rating	Unit
$V_{(BR)DSS}$	Drain-Source breakdown voltage	40	V
$I_S$	Diode continuous forward current	$T_C=25^{\circ}C$ 200	A
$I_D$	Continuous drain current @ $V_{GS}=-10V$	$T_C=25^{\circ}C$ 200	A
		$T_C=100^{\circ}C$ 142	A
$I_{DM}$	Pulse drain current tested ①	$T_C=25^{\circ}C$ 800	A
EAS	Avalanche energy, single pulsed ②	390	mJ
$P_D$	Maximum power dissipation	$T_C=25^{\circ}C$ 150	W
$V_{GS}$	Gate-Source voltage	$\pm 20$	V
$T_{STG} T_J$	Storage and operating temperature range	-55 to 175	$^{\circ}C$
<b>Thermal Characteristics</b>			
$R_{\theta JC}$	Thermal Resistance-Junction to Case	1.0	$^{\circ}C/W$
$R_{\theta JA}$	Thermal Resistance-Junction to Ambient	62.5	$^{\circ}C/W$

Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
<b>Static Electrical Characteristics @ <math>T_j = 25^\circ\text{C}</math> (unless otherwise stated)</b>						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	40	--	--	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=40V, V_{GS}=0V$	--	--	1	$\mu A$
	Zero Gate Voltage Drain Current( $T_j=125^\circ\text{C}$ )	$V_{DS}=40V, V_{GS}=0V$	--	--	100	$\mu A$
$I_{GSS}$	Gate-Body Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	--	--	$\pm 100$	nA
$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	1.2	1.8	2.4	V
$R_{DS(ON)}$	Drain-Source On-State Resistance <sup>③</sup>	$V_{GS}=10V, I_D=60A$	--	2.5	4	m $\Omega$
$R_{DS(ON)}$	Drain-Source On-State Resistance <sup>③</sup>	$V_{GS}=4.5V, I_D=30A$	--	3.5	6	m $\Omega$
<b>Dynamic Electrical Characteristics @ <math>T_j = 25^\circ\text{C}</math> (unless otherwise stated)</b>						
$C_{iss}$	Input Capacitance	$V_{DS}=20V, V_{GS}=0V,$ $f=1\text{MHz}$	5600	6605	7600	pF
$C_{oss}$	Output Capacitance		400	550	700	pF
$C_{rss}$	Reverse Transfer Capacitance		320	440	560	pF
$R_g$	Gate Resistance	$f=1\text{MHz}$	--	1.9	--	$\Omega$
$Q_g$	Total Gate Charge	$V_{DS}=20V, I_D=30A,$ $V_{GS}=10V$	--	109	--	nC
$Q_{gs}$	Gate-Source Charge		--	30.5	--	nC
$Q_{gd}$	Gate-Drain Charge		--	42	--	nC
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-on Delay Time	$V_{DD}=20V,$ $I_D=30A,$ $R_G=3\Omega,$ $V_{GS}=10V$	--	30	--	nS
$t_r$	Turn-on Rise Time		--	24	--	nS
$t_{d(off)}$	Turn-Off Delay Time		--	45.5	--	nS
$t_f$	Turn-Off Fall Time		--	16.5	--	nS
<b>Source- Drain Diode Characteristics @ <math>T_j = 25^\circ\text{C}</math> (unless otherwise stated)</b>						
$V_{SD}$	Forward on voltage	$I_{SD}=30A, V_{GS}=0V$	--	0.9	1.2	V
$t_{rr}$	Reverse Recovery Time	$T_j=25^\circ\text{C}, I_{sd}=30A,$ $V_{GS}=0V$ $di/dt=500A/\mu s$	--	29	--	nS
$Q_{rr}$	Reverse Recovery Charge		179	--	--	nC


**NOTE:**

- ① Repetitive rating; pulse width limited by max. junction temperature.
- ② Limited by  $T_{jmax}$ , starting  $T_j = 25^\circ\text{C}$ ,  $L = 0.5\text{mH}, R_G = 25\Omega, I_{AS} = 29A, V_{GS} = 10V$ . Part not recommended for use above this value
- ③ Pulse width  $\leq 300\mu s$ ; duty cycle  $\leq 2\%$ .


**Typical Characteristics**




**Fig1.** Typical Output Characteristics




**Fig2.**  $V_{GS(TH)}$  Gate-Source Voltage Vs.  $T_j$




**Fig3.** Typical Transfer Characteristics



**Fig4.** Normalized On-Resistance Vs.  $T_j$



**Fig5.** Typical Source-Drain Diode Forward Voltage



**Fig6.** Maximum Safe Operating Area

Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance




Fig10. Unclamped Inductive Test Circuit and waveforms





Fig11. Switching Time Test Circuit and waveforms

## TO-220AB Package Outline Data



Symbol	Dimensions (unit: mm)		
	Min	Typ	Max
<b>A</b>	4.30	4.52	4.70
<b>A1</b>	1.15	1.30	1.40
<b>A2</b>	2.20	2.40	2.60
<b>b</b>	0.70	0.80	1.00
<b>b2</b>	1.17	1.32	1.50
<b>c</b>	0.45	0.50	0.61
<b>D</b>	15.30	15.65	15.90
<b>D1</b>	9.00	9.20	9.40
<b>DEP</b>	0.05	0.10	0.25
<b>E</b>	9.66	9.90	10.28
<b>E1</b>	-	8.70	-
<b>E2</b>	9.80	10.00	10.20
$\phi P1$	1.40	1.50	1.60
<b>e</b>	2.54 BSC		
<b>e1</b>	5.08 BSC		
<b>H1</b>	6.40	6.50	6.80
<b>L</b>	12.70	-	14.27
<b>L1</b>	-	-	3.95
<b>L2</b>	2.40	2.50	2.60
$\phi P$	3.53	3.60	3.70
<b>Q</b>	2.70	2.80	2.90
$\theta1$	5 °	7 °	9 °
$\theta2$	1 °	3 °	5 °

### Notes:

1. Refer to JEDEC TO-220 variation AB
2. Dimension "D" and "E" do NOT include mold flash. Mold flash shall not exceed 0.127mm per side.

## Customer Service

### Sales and Service:

[sales@vgsemi.com](mailto:sales@vgsemi.com)

Vanguard Semiconductor CO., LTD

TEL: (86-755) -26902410

FAX: (86-755) -26907027

WEB: [www.vgsemi.com](http://www.vgsemi.com)