

## Features


- Enhancement mode
- Low on-resistance  $R_{DS(on)}$  @  $V_{GS}=4.5\text{ V}$
- Fast Switching and High efficiency
- 100% Avalanche test
- Pb-free lead plating; RoHS compliant



Part ID	Package Type	Marking	Tape and reel information
VS4080AI	QIPAK	4080AI	75pcs/Tube

$V_{DS}$	40	V
$R_{DS(on),TYP}@ V_{GS}=10\text{ V}$	5	m $\Omega$
$R_{DS(on),TYP}@ V_{GS}=4.5\text{ V}$	6	m $\Omega$
$I_D$	80	A

### QIPAK



Drain Pin 2



Source Pin 3

### Maximum ratings, at $T_A=25^\circ\text{C}$ , unless otherwise specified

Symbol	Parameter	Rating	Unit
$V_{(BR)DSS}$	Drain-Source breakdown voltage	40	V
$V_{GS}$	Gate-Source voltage	$\pm 20$	V
$I_S$	Diode continuous forward current	$T_C=25^\circ\text{C}$	80 A
$I_D$	Continuous drain current @ $V_{GS}=10\text{V}$	$T_C=25^\circ\text{C}$	80 A
		$T_C=100^\circ\text{C}$	56 A
$I_{DM}$	Pulse drain current tested ①	$T_C=25^\circ\text{C}$	320 A
$I_{DSM}$	Continuous drain current @ $V_{GS}=10\text{V}$	$T_A=25^\circ\text{C}$	10 A
		$T_A=70^\circ\text{C}$	8 A
EAS	Avalanche energy, single pulsed ②	240	mJ
$P_D$	Maximum power dissipation	$T_C=25^\circ\text{C}$	75 W
		$T_C=100^\circ\text{C}$	38 W
$P_{DSM}$	Maximum power dissipation ③	$T_A=25^\circ\text{C}$	1.3 W
		$T_A=70^\circ\text{C}$	0.8 W
$T_{STG}, T_J$	Storage and Junction Temperature Range	-55 to 175	$^\circ\text{C}$

### Thermal Characteristics

Symbol	Parameter	Typical	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	2	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	100	$^\circ\text{C/W}$

**Electrical Characteristics**

Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
<b>Static Electrical Characteristics @ T<sub>j</sub>=25°C (unless otherwise stated)</b>						
V <sub>(BR)DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	40	--	--	V
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =40V, V <sub>GS</sub> =0V	--	--	1	μA
	Zero Gate Voltage Drain Current (T <sub>j</sub> =125°C)	V <sub>DS</sub> =40V, V <sub>GS</sub> =0V	--	--	100	μA
I <sub>GSS</sub>	Gate-Body Leakage Current	V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V	--	--	±100	nA
V <sub>GS(TH)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	1.0	1.6	2.5	V
R <sub>DS(ON)</sub>	Drain-Source On-State Resistance ④	V <sub>GS</sub> =10V, I <sub>D</sub> =20A	--	5	7.5	mΩ
		T <sub>j</sub> =100°C	--	7	--	mΩ
R <sub>DS(ON)</sub>	Drain-Source On-State Resistance ④	V <sub>GS</sub> =4.5V, I <sub>D</sub> =15A	--	6	8.5	mΩ
<b>Dynamic Electrical Characteristics @ T<sub>j</sub> = 25°C (unless otherwise stated)</b>						
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> =20V, V <sub>GS</sub> =0V, f=1MHz	--	1400	--	pF
C <sub>oss</sub>	Output Capacitance		--	220	--	pF
C <sub>rss</sub>	Reverse Transfer Capacitance		--	150	--	pF
Q <sub>g</sub> (10V)	Total Gate Charge	V <sub>DS</sub> =20V, I <sub>D</sub> =10A, V <sub>GS</sub> =10V	--	37	--	nC
Q <sub>g</sub> (4.5V)	Total Gate Charge		--	26	--	nC
Q <sub>gs</sub>	Gate-Source Charge		--	7	--	nC
Q <sub>gd</sub>	Gate-Drain Charge		--	18	--	nC
<b>Switching Characteristics</b>						
t <sub>d(on)</sub>	Turn-on Delay Time	V <sub>DD</sub> =20V, I <sub>D</sub> =9A, R <sub>G</sub> =6.8Ω, V <sub>GS</sub> =10V	--	16	--	ns
t <sub>r</sub>	Turn-on Rise Time		--	15	--	ns
t <sub>d(off)</sub>	Turn-Off Delay Time		--	20	--	ns
t <sub>f</sub>	Turn-Off Fall Time		--	12	--	ns
<b>Source- Drain Diode Characteristics @ T<sub>j</sub> = 25°C (unless otherwise stated)</b>						
V <sub>SD</sub>	Forward on voltage	I <sub>SD</sub> =20A, V <sub>GS</sub> =0V	--	0.8	1.2	V
t <sub>rr</sub>	Reverse Recovery Time	T <sub>j</sub> =25°C, I <sub>SD</sub> =20A, V <sub>GS</sub> =0V	--	29	--	ns
Q <sub>rr</sub>	Reverse Recovery Charge	di/dt=100A/μs	--	16	--	nC

NOTE: ① Repetitive rating; pulse width limited by max junction temperature.

② Limited by T<sub>Jmax</sub>, starting T<sub>J</sub> = 25°C, L = 0.3mH, R<sub>G</sub> = 25Ω, I<sub>AS</sub> = 40A, V<sub>GS</sub> = 10V. Part not recommended for use above this value

③ The power dissipation P<sub>DSM</sub> is based on R<sub>θJA</sub> and the maximum allowed junction temperature of 150°C.

④ Pulse width ≤ 380μs; duty cycles ≤ 2%.

Typical Characteristics




Fig1. Typical Output Characteristics




Fig2. Maximum Drain Current Vs. Case Temperature  $T_c$ ,




Fig3. Typical Transfer Characteristics




Fig4. Normalized On-Resistance Vs.  $T_j$




Fig5. Typical Source-Drain Diode Forward Voltage




Fig6. Maximum Safe Operating Area

Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance




Fig10. Unclamped Inductive Test Circuit and waveforms





Fig11. Switching Time Test Circuit and waveforms



**Marking Information**



1st line: Vanguard Code (Vs)

2nd line: Part Number (4080AI)


3rd line: Date code (XXXYWW)

XXX: Wafer Lot Number Code, code changed with Lot Number

Y: Year Code (e.g. E=2017, F=2018, G=2019, H=2020, etc)

WW: Week Code (01 to 53)

**QIPAK Package Outline Data**



Symbol	Dimensions (unit: mm)		
	Min	Typ	Max
A	2.20	2.30	2.40
A2	0.97	1.07	1.17
B	0.25	0.40	0.55
b	0.68	0.78	0.90
b3	5.20	5.33	5.50
c	0.43	0.53	0.63
D	5.98	6.10	6.22
D1	5.30 REF		
D2	7.96	8.16	8.36
D3	0.85	1.05	1.25
E	6.40	6.60	6.80
E1	4.63	--	--
e	2.286 BSC		
H	16.22	16.52	16.82
L1	9.15	9.40	9.65
L3	0.88	1.02	1.28
L5	1.65	1.80	1.95

Note:

Dimension "D" and "E" do NOT include mold flash. Mold flash shall not exceed 0.127mm per side.

**Customer Service**

Sales and Service:

[sales@vgsemi.com](mailto:sales@vgsemi.com)

Vanguard Semiconductor CO., LTD

TEL: (86-755) -26902410

FAX: (86-755) -26907027

WEB: [www.vgsemi.com](http://www.vgsemi.com)