


## Features

- N-Channel, 5V Logic Level Control
- Enhancement mode
- Very low on-resistance  $R_{DS(on)}$  @  $V_{GS}=4.5$  V
- VitoMOS® Technology
- 100% Avalanche test
- Pb-free lead plating; RoHS compliant


**Halogen-Free**

$V_{DS}$	80	V
$R_{DS(on),TYP}$ @ $V_{GS}=10$ V	8	$m\Omega$
$R_{DS(on),TYP}$ @ $V_{GS}=4.5$ V	9	$m\Omega$
$I_D$	65	A

**PDFN5x6**


Part ID	Package Type	Marking	Tape and reel information
VSP007N07MS	PDFN5x6	007N07M	3000PCS/Reel

## Maximum ratings, at $T_A=25^\circ C$ , unless otherwise specified

Symbol	Parameter	Rating	Unit
$V_{(BR)DSS}$	Drain-Source breakdown voltage	80	V
$V_{GS}$	Gate-Source voltage	$\pm 20$	V
$I_S$	Diode continuous forward current	$T_C=25^\circ C$	A
$I_D$	Continuous drain current @ $V_{GS}=10V$	$T_C=25^\circ C$	A
		$T_C=100^\circ C$	A
$I_{DM}$	Pulse drain current tested ①	$T_C=25^\circ C$	A
EAS	Avalanche energy, single pulsed ②	$I_D=15A$	mJ
$P_D$	Maximum power dissipation	$T_C=25^\circ C$	W
$T_{STG}, T_J$	Storage and Junction Temperature Range	-55 to 150	°C

## Thermal Characteristics

Symbol	Parameter	Typical	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	2.5	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	60	°C/W



Symbol	Parameter	Condition	Min.	Typ.	Max.	Unit
<b>Static Electrical Characteristics @ T<sub>c</sub> = 25°C (unless otherwise stated)</b>						
V <sub>(BR)DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	80	--	--	V
I <sub>DSS</sub>	Zero Gate Voltage Drain Current(T <sub>c</sub> =25 °C)	V <sub>DS</sub> =64V, V <sub>GS</sub> =0V	--	--	0.1	μA
	Zero Gate Voltage Drain Current(T <sub>c</sub> =125 °C)	V <sub>DS</sub> =64V, V <sub>GS</sub> =0V	--	--	100	μA
I <sub>GSS</sub>	Gate-Body Leakage Current	V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V	--	--	±100	nA
V <sub>GS(TH)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	1.0	2.0	3.0	V
R <sub>DS(ON)</sub>	Drain-Source On-State Resistance <sup>③</sup>	V <sub>GS</sub> =10V, I <sub>D</sub> =20A	--	8	10	mΩ
R <sub>DS(ON)</sub>	Drain-Source On-State Resistance <sup>③</sup>	V <sub>GS</sub> =4.5V, I <sub>D</sub> =10A	--	9	11	mΩ
<b>Dynamic Electrical Characteristics @ T<sub>c</sub> = 25°C (unless otherwise stated)</b>						
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> =30V, V <sub>GS</sub> =0V, f=1MHz	--	3000	--	pF
C <sub>oss</sub>	Output Capacitance		--	250	--	pF
C <sub>rss</sub>	Reverse Transfer Capacitance		--	205	--	pF
R <sub>g</sub>	Gate Resistance	f=1MHz	--	1.5	--	Ω
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> =30V, I <sub>D</sub> =30A, V <sub>GS</sub> =10V	--	78	--	nC
Q <sub>gs</sub>	Gate-Source Charge		--	19	--	nC
Q <sub>gd</sub>	Gate-Drain Charge		--	10	--	nC
<b>Switching Characteristics</b>						
t <sub>d(on)</sub>	Turn-on Delay Time	V <sub>DD</sub> =30V, I <sub>D</sub> =10A, R <sub>G</sub> =6.8Ω, V <sub>GS</sub> =10V	--	13	--	ns
t <sub>r</sub>	Turn-on Rise Time		--	25	--	ns
t <sub>d(off)</sub>	Turn-Off Delay Time		--	98	--	ns
t <sub>f</sub>	Turn-Off Fall Time		--	43	--	ns
<b>Source- Drain Diode Characteristics@ T<sub>c</sub> = 25°C (unless otherwise stated)</b>						
V <sub>SD</sub>	Forward on voltage	I <sub>SD</sub> =20A, V <sub>GS</sub> =0V	--	0.78	1.2	V
t <sub>rr</sub>	Reverse Recovery Time	T <sub>j</sub> =25 °C, I <sub>sd</sub> =20A, V <sub>GS</sub> =0V di/dt=200A/μs	--	25	--	ns
Q <sub>rr</sub>	Reverse Recovery Charge		--	47	--	nC

NOTE:

- ① Repetitive rating; pulse width limited by max junction temperature.
- ② Limited by T<sub>Jmax</sub>, starting T<sub>J</sub> = 25°C, L = 0.5mH, R<sub>G</sub> = 25Ω, I<sub>AS</sub> = 15A, V<sub>GS</sub> = 10V. Part not recommended for use above this value
- ③ Pulse width ≤ 300μs; duty cycle≤ 2%.




Vanguard  
Semiconductor


**VSP007N07MS**

**80V/65A N-Channel Advanced Power MOSFET**


## Typical Characteristics




**Fig1.** Typical Output Characteristics




**Fig2.** Normalized Threshold Voltage Vs. Temperature




**Fig3.** Typical Transfer Characteristics



**Fig4.** Normalized On-Resistance Vs. Temperature




**Fig5.** Typical Source-Drain Diode Forward Voltage




**Fig6.** Maximum Safe Operating Area




## Typical Characteristics




**Fig7.** Typical Capacitance Vs.Drain-Source




**Fig8.** Typical Gate Charge Vs.Gate-Source



**Fig9.** Normalized Maximum Transient Thermal




**Fig10.** Unclamped Inductive Test Circuit and waveforms



**Fig11.** Switching Time Test Circuit and waveforms

**Marking Information**



1st line: Vanguard Code (Vs), Vanguard Logo

2nd line: Part Number (007N07M)

3rd line: Date code (XXXYWW)


XXX: Wafer Lot Number

Y: Year Code, e.g. E means 2017

WW: Week Code



### PDFN5x6 Package Outline Data



Symbol	DIMENSIONS ( unit : mm )		
	Min	Typ	Max
A	0.90	1.00	1.20
A1	0.00	--	0.05
b	0.30	0.40	0.51
c	0.20	0.25	0.33
D	4.80	4.90	5.40
D1	3.61	4.00	4.25
E	5.65	5.80	6.06
E1	5.90	6.10	6.35
E2	3.38	3.58	3.92
e	1.27 BSC		
L	0.51	0.61	0.71
L1	--	--	0.15
L2	0.41	0.51	0.61
θ	0°	--	12°

#### Notes:

1. Refer to JEDEC MO-240 variation AA.
2. Dimensions "D" and "E" do NOT include mold flash protrusions or gate burrs.
3. Dimensions "D" and "E" include interterminal flash or protrusion. Interterminal flash or protrusion shall not exceed 0.25mm per side.

### Customer Service

#### Sales and Service:

[sales@vgsemi.com](mailto:sales@vgsemi.com)

**Vanguard Semiconductor CO., LTD**

**TEL:** (86-755) -26902410

**FAX:** (86-755) -26907027

**WEB:** [www.vgsemi.com](http://www.vgsemi.com)