



General Purpose Rectifier



Features

- High efficiency
- High current capability
- High reliability
- High surge current capability
- Low power loss
- Glass passivated chip junction
- Solder dip 275 °C max. 7 s, per JESD 22-B106

Mechanical Data

- **Package:** DO-204AC(DO-15)
Molding compound meets UL 94 V-0 flammability rating, RoHS-compliant
- **Terminals:** Tin plated leads, solderable per J-STD-002 and JESD22-B102
- **Polarity:** Color band denotes cathode end

■ Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	RL201G	RL202G	RL203G	RL204G	RL205G	RL206G	RL207G
Device marking code			RL201G	RL202G	RL203G	RL204G	RL205G	RL206G	RL207G
Repetitive Peak Reverse Voltage	V_{RRM}	V	50	100	200	400	600	800	1000
Average Forward Current @60Hz sine wave, Resistance load, Ta =60°C	$I_{F(AV)}$	A	2.0						
Forward Surge Current (Non-repetitive) @60Hz Half-sine wave, 1 cycle, Ta=25°C	I_{FSM}	A	70						
Storage Temperature	Tstg	°C	-55 ~+150						
Junction Temperature	Tj	°C	-55~+150						

■ Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	TEST CONDITIONS	RL201G	RL202G	RL203G	RL204G	RL205G	RL206G	RL207G
Maximum instantaneous forward voltage drop per diode	V_{FM}	V	$I_{FM}=2.0A$	1.1						
Maximum DC reverse current at rated DC blocking voltage per diode	I_{RRM1}	μA	Ta=25°C	2.5						
	I_{RRM2}		Ta=100°C	50						
Typical junction capacitance	Cj	pF	Measured at 1MHZ and Applied Reverse Voltage of 4.0 V.D.C.	15						

■ Thermal Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	RL201G	RL202G	RL203G	RL204G	RL205G	RL206G	RL207G
Thermal Resistance(Typical)	$R_{\theta J-A}$	°C/W	50						



RL201G THRU RL207G

Ordering Information (Example)

PREFERRED P/N	PACKAGE CODE	UNIT WEIGHT(g)	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
RL201G~RL207G	D1	Approximate 0.38	3000	3000	30000	Tape
RL201G~RL207G	C1	Approximate 0.38	500	500	25000	Bulk

Characteristics (Typical)

FIG.1: Io-Ta Curve




FIG.2: Forward Surge Current Capability




FIG.3: Forward Voltage






FIG.4: Typical Reverse Characteristics





■ Outline Dimensions



DO-204AC(DO-15)		
Dim	Min	Max
A	5.80	7.60
B	2.60	3.60
C	25.4	/
D	0.70	0.90



RL201G THRU RL207G

Disclaimer

The information presented in this document is for reference only. Yangzhou Yangjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Yangjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.21yangjie.com](http://www.21yangjie.com) , or consult your nearest Yangjie's sales office for further assistance.