

ON Semiconductor®

FGH75T65SHDT 650 V, 75 A Field Stop Trench IGBT

Features

- Maximum Junction Temperature: T_J = 175°C
- Positive Temperature Co-efficient for Easy Parallel Operating
- **High Current Capability**
- Low Saturation Voltage: $V_{CE(sat)}$ = 1.6 V(Typ.) @ I_C = 75 A
- 100% of the Parts Tested for $I_{LM}(1)$
- · High Input Impedance
- · Fast Switching
- Tighten Parameter Distribution
- **RoHS Compliant**


General Description

Using novel field stop IGBT technology, ON Semiconductor's new series of field stop $3^{\rm rd}$ generation IGBTs offer the optimum performance for solar inverter, UPS, welder, telecom, ESS and PFC applica-tions where low conduction and switching losses are essential.

Applications

· Solar Inverter, UPS, Welder, Telecom, ESS, PFC





Absolute Maximum Ratings T_C = 25°C unless otherwise noted

Symbol	Description	scription FGH75T65SHDT-F1		Unit
V _{CES}	Collector to Emitter Voltage		650	V
.,	Gate to Emitter Voltage		± 20	V
V_{GES}	Transient Gate to Emitter Voltage		± 30	V
1	Collector Current	@ T _C = 25°C	150	А
IC	Collector Current	@ T _C = 100°C	75	А
I _{LM (1)}	Pulsed Collector Current	@ T _C = 25°C	225	Α
I _{CM (2)}	Pulsed Collector Current		225	Α
l _F	Diode Forward Current	@ T _C = 25°C	125	А
'F	Diode Forward Current	$@ T_C = 100^{\circ}C$	75	Α
I _{FM (2)}	Pulsed Diode Maximum Forward Curren	225	А	
P _D	Maximum Power Dissipation	@ T _C = 25°C	455	W
י ט	Maximum Power Dissipation	@ T _C = 100°C	227	W
T _J	Operating Junction Temperature		-55 to +175	οС
T _{stg}	Storage Temperature Range		-55 to +175	°C
T _L	Maximum Lead Temp. for soldering Purposes, 1/8" from case for 5 seconds		300	oC

- Notes: 1. V_{CC} = 400 V, V_{GE} = 15 V, I_{C} = 225 A, R_{G} = 20 $\Omega_{\rm }$ Inductive Load
- 2. Repetitive rating: Pulse width limited by max. junction temperature

Thermal Characteristics

Symbol	Parameter	FGH75T65SHDT-F155	Unit
$R_{\theta JC}(IGBT)$	Thermal Resistance, Junction to Case, Max.	0.33	°C/W
$R_{\theta JC}(Diode)$	Thermal Resistance, Junction to Case, Max.	0.65	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max.	40	°C/W

Package Marking and Ordering Information

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FGH75T65SHDT-155	FGH75T65SHDT	TO-247 G03	Tube	-	-	30

Electrical Characteristics of the IGBT T_C = 25°C unless otherwise noted

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
Off Charac	teristics					
BV _{CES}	Collector to Emitter Breakdown Voltage	V_{GE} = 0V, I_C = 1 mA	650	-	-	V
ΔBV _{CES} / ΔΤ _J	Temperature Coefficient of Breakdown Voltage	I _C = 1 mA, Reference to 25°C	-	0.6	-	V/°C
I _{CES}	Collector Cut-Off Current	$V_{CE} = V_{CES}$, $V_{GE} = 0 V$	-	-	250	μΑ
I _{GES}	G-E Leakage Current	V _{GE} = V _{GES} , V _{CE} = 0 V	-	-	±400	nA
On Charac	teristics					
V _{GE(th)}	G-E Threshold Voltage	I _C = 75 mA, V _{CE} = V _{GE}	4.0	5.5	7.5	V
- ()	j	I _C = 75 A, V _{GE} = 15 V	-	1.6	2.1	V
V _{CE(sat)}	Collector to Emitter Saturation Voltage	I _C = 75 A, V _{GE} = 15 V, T _C = 175°C	-	2.28	-	V
Dynamic C	haracteristics		-1	1	•	
C _{ies}	Input Capacitance		-	3680	-	pF
C _{oes}	Output Capacitance	V _{CE} = 30 V _, V _{GE} = 0 V, f = 1MHz	-	179	-	pF
C _{res}	Reverse Transfer Capacitance	1 - IIVINZ	-	43	-	pF
Switching	Characteristics					
t _{d(on)}	Turn-On Delay Time		-	28	_	ns
t _r	Rise Time		-	61	-	ns
t _{d(off)}	Turn-Off Delay Time	V _{CC} = 400 V, I _C = 75 A,	-	86	-	ns
t _f	Fall Time	$R_G = 3 \Omega$, $V_{GE} = 15 V$,	-	16	-	ns
E _{on}	Turn-On Switching Loss	Inductive Load, T _C = 25°C	-	3	-	mJ
E _{off}	Turn-Off Switching Loss		-	0.75	-	mJ
E _{ts}	Total Switching Loss		-	3.75	-	mJ
t _{d(on)}	Turn-On Delay Time		-	27	-	ns
t _r	Rise Time		-	62	-	ns
t _{d(off)}	Turn-Off Delay Time	V _{CC} = 400 V, I _C = 75 A,	-	93	-	ns
t _f	Fall Time	$R_G = 3 \Omega$, $V_{GE} = 15 V$,	-	16	-	ns
E _{on}	Turn-On Switching Loss	Inductive Load, T _C = 175°C	-	4.7	-	mJ
E _{off}	Turn-Off Switching Loss		-	1.03	-	mJ
E _{ts}	Total Switching Loss		-	5.73	-	mJ

Electrical Characteristics of the IGBT (Continued)

Symbol	Parameter	Test Conditions	Min.	Тур.	Max	Unit
Qg	Total Gate Charge	V _{CE} = 400 V, I _C = 75 A, V _{GE} = 15 V	-	123	-	nC
Q _{ge}	Gate to Emitter Charge		-	22.6	-	nC
Q _{gc}	Gate to Collector Charge		-	44.9	-	nC

Electrical Characteristics of the Diode T_C = 25°C unless otherwise noted

Symbol	Parameter	Test Conditions		Min.	Тур.	Max	Unit
V _{FM}	Diode Forward Voltage	I _F = 75 A	$T_{\rm C} = 25^{\rm o}{\rm C}$	-	1.8	2.1	V
FIVI	Diode i diwara veriage	F 7071	$T_{\rm C}$ = 175°C	-	1.7	-	•
E _{rec}	Reverse Recovery Energy		T _C = 175°C	-	160	-	uJ
t _{rr} Diode Reverse Rec	Diode Reverse Recovery Time	Time $I_F = 75 \text{ A}, dI_F/dt = 200 \text{ A/}\mu\text{s}$	T _C = 25°C	-	76	-	ns
	2.000 1.010.00 1.00010.9 1		$T_{\rm C}$ = 175°C	-	270	-	
Q _{rr}	Diode Reverse Recovery Charge		T _C = 25°C	-	206	-	nC
\$ 11	2.000 November 1.000 November 9		$T_{\rm C} = 175^{\rm o}{\rm C}$	-	2199	1	:

Figure 1. Typical Output Characteristics




Figure 3. Typical Saturation Voltage Characteristics




Figure 5. Saturation Voltage vs. V_{GE}




Figure 2. Typical Output Characteristics




Figure 4. Saturation Voltage vs. Case
Temperature at Variant Current Level




Figure 6. Saturation Voltage vs. V_{GE}




Figure 7. Capacitance Characteristics




Figure 9. Turn-on Characteristics vs.
Gate Resistance




Figure 11. Switching Loss vs.

Gate Resistance




Figure 8. Gate charge Characteristics




Figure 10. Turn-off Characteristics vs. Gate Resistance




Figure 12. Turn-on Characteristics vs. Collector Current




Figure 13. Turn-off Characteristics vs. Collector Current




Figure 15. Load Current vs. Frequency




Figure 17. Forward Characteristics




Figure 14. Switching Loss vs. Collector Current




Figure 16. SOA Characteristics




Figure 18. Reverse Recovery Current




Figure 19. Reverse Recovery Time




Figure 20. Stored Charge




Figure 21.Transient Thermal Impedance of IGBT





Figure 22. Transient Thermal Impedance of Diode



ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative