MOSFET - Small Signal, Complementary, SC-88 30 V/-20 V, +0.25/-0.88 A

Features

- Leading 20 V Trench for Low R_{DS(on)} Performance
- ESD Protected Gate
- SC-88 Package for Small Footprint (2 x 2 mm)
- NV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- DC-DC Conversion
- Load/Power Management
- Load Switch
- Cell Phones, MP3s, Digital Cameras, PDAs

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Pai	Symbol	Value	Unit			
Drain-to-Source Volt	N-Ch	V _{DSS}	30	V		
	P-Ch		-20			
Gate-to-Source Volta	N-Ch	V _{GS}	±20	V		
		P-Ch		±12		
N-Channel Continuous Drain	Steady	T _A = 25°C	I _D	0.25	Α	
Current (Note 1)	State	T _A = 85°C		0.18		
P-Channel Continuous Drain	Steady	T _A = 25°C		-0.88		
Current (Note 1)	State	T _A = 85°C		-0.63		
Power Dissipation (Note 1)	Steady State	T _A = 25°C	P _D	0.27	W	
Pulsed Drain Cur- N-C		t- 10	I _{DM}	0.5	Α	
rent	P-Ch	tp = 10 μs		-3.0		
Operating Junction and Storage Temperature			T _J , T _{stg}	–55 to 150	°C	
Source Current (Body	N-Ch	IS	0.25	Α		
	P-Ch		-0.48			
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			TL	260	°C	

THERMAL RESISTANCE RATINGS

Parameter	Symbol	Max	Unit
Junction-to-Ambient - Steady State (Note 1)	$R_{\theta JA}$	460	°C/W


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



ON Semiconductor®

www.onsemi.com

V _{(BR)DSS}	R _{DS(on)} Typ	I _D Max	
N-Ch	1.0 Ω @ 4.5 V	0.25 A	
30 V	1.5 Ω @ 2.5 V	0.23 A	
P-Ch	215 mΩ @ -4.5 V	-0.88 A	
-20 V	345 mΩ @ –2.5 V	-0.00 A	




(Top View)

MARKING DIAGRAM & PIN ASSIGNMENT



SC-88 (SOT-363) CASE 419B STYLE 26



XXX = Specific Device Code

M = Date Code ■ Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 7 of this data sheet.

1.	Surface mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [1 oz] including traces).

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Parameter	Symbol	N/P	Test Condition		Min	Тур	Max	Unit
OFF CHARACTERISTICS (Note 3)	,	,-				71	I	
Drain-to-Source	V/======	NI		I- 250 A	20	ī	I	\ \/
Breakdown Voltage	$V_{(BR)DSS}$	N P	$V_{GS} = 0 V$	I _D = 250 μA	30			V
9	\			$I_D = -250 \mu A$	-20			
Drain-to-Source Breakdown	V _{(BR)DSS} /	N				33		mV/ ∘C
Voltage Temperature Coefficient	TJ	Р		_		-9.0		
Zero Gate Voltage Drain Current	I _{DSS}	N	$V_{GS} = 0 \text{ V}, V_{DS} = 30 \text{ V}$	T _J = 25°C			1.0	μΑ
		Р	$V_{GS} = 0 \text{ V}, V_{DS} = -16 \text{ V}$	ů			1.0	
		N	V _{GS} = 0 V, V _{DS} = 30 V	T _{.1} = 125°C		0.5		
		Р	$V_{GS} = 0 \text{ V}, V_{DS} = -16 \text{ V}$	Ů		0.5		
Gate-to-Source Leakage Current	I _{GSS}	Ν	$V_{DS} = 0 V, V_{GS} =$	10 V			1.0	μΑ
		Р	$V_{DS} = 0 \text{ V}, V_{GS} = -$	4.5 V			1.0	
ON CHARACTERISTICS (Note 2)								
Gate Threshold Voltage	V _{GS(TH)}	N	., .,	I _D = 100 μA	0.8	1.2	1.5	V
S I	GO(111)	Р	$V_{GS} = V_{DS}$	$I_{D} = -250 \mu A$	-0.45	-0.61	-1.5	
Negative Gate Threshold	V _{GS(TH)} /	N				3.2		mV/
Temperature Coefficient	$T_{\rm J}$	P				-2.7		°C
Drain-to-Source On Resistance		N	V _{GS} = 4.5 V, I _D = 1	0 mΔ	1	1.0	1.5	Ω
Diam-to-Source Off Resistance	R _{DS(on)}	P	$V_{GS} = 4.5 \text{ V, } I_D = 1$ $V_{GS} = -4.5 \text{ V, } I_D = -4.5 \text{ V}$					52
						0.215	0.260	ł
		N	$V_{GS} = 2.5 \text{ V}, I_D = 1$			1.5	2.5	
		Р	$V_{GS} = -2.5 \text{ V}, I_D = -$			0.345	0.500	
Forward Transconductance	9FS	N	$V_{DS} = 3.0 \text{ V}, I_{D} = 1$			0.08		S
		Р	$V_{DS} = -10 \text{ V}, I_{D} = -10 \text{ V}$	0.88 A		3.0		
CHARGES, CAPACITANCES AND C	GATE RESIS	STANC	E					
Input Capacitance	C _{ISS}	N		V _{DS} = 5.0 V		20	33	pF
		Р		V _{DS} = -20 V		155	225	
Output Capacitance Reverse Transfer Capacitance	Coss	N		V _{DS} = 5.0 V		19	32	1
	C _{RSS}	Р	t = 1 MHz Voo = 0 V	V _{DS} = -20 V		25	40	
		N		V _{DS} = 5.0 V		7.25	12	1
, increse trainerer capacitaines	9400	P		$V_{DS} = -20 \text{ V}$		18	30	-
Total Gate Charge	Остот	N	V _{GS} = 5.0 V, V _{DS} = 24 V		1	0.9	1.5	nC
Total date onlinge	$Q_{G(TOT)}$	P	$V_{GS} = -4.5 \text{ V}, V_{DS} = -10 \text{ V}$			2.2	3.5	110
Threshold Cata Charge	0	-					3.5	
Threshold Gate Charge	Q _{G(TH)}	N	$V_{GS} = 5.0 \text{ V}, V_{DS} = 24 \text{ V}$			0.2		
		Р	$V_{GS} = -4.5 \text{ V}, V_{DS} = -10 \text{ V}$			0.2		
Gate-to-Source Charge	Q_{GS}	N	$V_{GS} = 5.0 \text{ V}, V_{DS} = 24 \text{ V}$			0.3		
		Р	$V_{GS} = -4.5 \text{ V}, V_{DS} = -10 \text{ V}$			0.5		
Gate-to-Drain Charge	Q_{GD}	N	$V_{GS} = 5.0 \text{ V}, V_{DS} = 24 \text{ V}$			0.2		
		Р	$V_{GS} = -4.5 \text{ V}, V_{DS} = -10 \text{ V}$, I _D = -0.88 A		0.65		
SWITCHING CHARACTERISTICS (N	Note 3)							
Turn-On Delay Time	t _{d(ON)}	N				15		ns
Rise Time	t _r	1	V _{GS} = 4.5 V, V _{DD} = 5.0 V,			66		1
Turn-Off Delay Time		1	$I_D = 250 \text{ mA}, R_G = 50 \Omega$			56		1
Turri-On Delay Time	t _{d(OFF)}		.b ===, ,g				 	1
Fall Time	t _{d(OFF)}		.p <u></u> ,			78		
Fall Time	t _f	P						
Fall Time Turn-On Delay Time	t _f t _{d(ON)}	Р		–10 V.		5.8		
Fall Time Turn-On Delay Time Rise Time	t _f t _{d(ON)} t _r	Р	V _{GS} = -4.5 V, V _{DD} =			5.8 6.5		
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time	t _f t _{d(ON)} t _r t _{d(OFF)}	Р				5.8 6.5 13.5		
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time	$\begin{array}{c} t_{\rm f} \\ t_{\rm d(ON)} \\ t_{\rm r} \\ \end{array}$	P	V _{GS} = -4.5 V, V _{DD} =			5.8 6.5		
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time DRAIN-SOURCE DIODE CHARACT	$\begin{array}{c} t_f \\ t_{d(ON)} \\ t_r \\ t_{d(OFF)} \\ t_f \end{array}$		V _{GS} = -4.5 V, V _{DD} =	20 Ω		5.8 6.5 13.5 3.5		
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time	$\begin{array}{c} t_{\rm f} \\ t_{\rm d(ON)} \\ t_{\rm r} \\ \end{array}$	N	$V_{GS} = -4.5 \text{ V}, V_{DD} = I_{D} = -0.5 \text{ A}, R_{G} = 3$	20 Ω I _S = 10 mA		5.8 6.5 13.5 3.5	0.7	V
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time DRAIN-SOURCE DIODE CHARACT	$\begin{array}{c} t_f \\ t_{d(ON)} \\ t_r \\ t_{d(OFF)} \\ t_f \end{array}$	N P	V _{GS} = -4.5 V, V _{DD} =	$I_S = 10 \text{ mA}$ $I_S = -0.48 \text{ A}$		5.8 6.5 13.5 3.5 0.65 -0.8	0.7 -1.2	V
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time DRAIN-SOURCE DIODE CHARACT	$\begin{array}{c} t_f \\ t_{d(ON)} \\ t_r \\ t_{d(OFF)} \\ t_f \end{array}$	N P N	$V_{GS} = -4.5 \text{ V}, V_{DD} = I_{D} = -0.5 \text{ A}, R_{G} = 20 \text{ V}$ $V_{GS} = 0 \text{ V}, T_{J} = 25^{\circ}\text{C}$	$I_S = 10 \text{ mA}$ $I_S = -0.48 \text{ A}$ $I_S = 10 \text{ mA}$		5.8 6.5 13.5 3.5		V
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time DRAIN-SOURCE DIODE CHARACT Forward Diode Voltage	$\begin{array}{c} t_f \\ t_{d(ON)} \\ t_r \\ t_{d(OFF)} \\ t_f \end{array}$	N P	$V_{GS} = -4.5 \text{ V}, V_{DD} = I_{D} = -0.5 \text{ A}, R_{G} = 3$	$I_S = 10 \text{ mA}$ $I_S = -0.48 \text{ A}$		5.8 6.5 13.5 3.5 0.65 -0.8		V
Fall Time Turn-On Delay Time Rise Time Turn-Off Delay Time Fall Time DRAIN-SOURCE DIODE CHARACT	$\begin{array}{c} t_f \\ t_{d(ON)} \\ t_r \\ t_{d(OFF)} \\ t_f \end{array}$	N P N	$V_{GS} = -4.5 \text{ V}, V_{DD} = I_{D} = -0.5 \text{ A}, R_{G} = 20 \text{ V}$ $V_{GS} = 0 \text{ V}, T_{J} = 25^{\circ}\text{C}$	$I_S = 10 \text{ mA}$ $I_S = -0.48 \text{ A}$ $I_S = 10 \text{ mA}$		5.8 6.5 13.5 3.5 0.65 -0.8 0.45		V

Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
 Switching characteristics are independent of operating junction temperatures.

TYPICAL N-CHANNEL PERFORMANCE CURVES (T_J = 25°C unless otherwise noted)





Figure 1. On-Region Characteristics



25°C

2.25

2.5

0.205

RDS(on), DRAIN-TO-SOURCE RESISTANCE (♥) 1.3 V_{GS} = 4.5 V $T_J = 125^{\circ}C$ 1.2 1.1 1.0 0.9 $T_J = 25^{\circ}C$ 8.0 0.7 0.6 $T_J = -55^{\circ}C$ 0.055 0.105 0.155 0.205 0.005 ID DRAIN CURRENT (AMPS)


Figure 3. On-Resistance vs. Drain Current and **Temperature**

Figure 4. On-Resistance vs. Drain Current and **Gate Voltage**

0.105

I_{D.} DRAIN CURRENT (AMPS)

0.155




0.005

0.055

Figure 5. On-Resistance Variation with **Temperature**

Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL N-CHANNEL PERFORMANCE CURVES (T_J = 25°C unless otherwise noted)



GATE-TO-SOURCE OR DRAIN-TO-SOURCE VOLTAGE (VOLTS)

Figure 7. Capacitance Variation




Figure 8. Gate-to-Source Voltage vs. Total Gate Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current

TYPICAL P-CHANNEL PERFORMANCE CURVES (T_J = 25°C unless otherwise noted)




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On–Resistance vs. Drain Current and Temperature




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On–Resistance Variation with Temperature





Figure 6. Drain-to-Source Leakage Current vs. Voltage

$\textbf{TYPICAL P-CHANNEL PERFORMANCE CURVES} \ \, (\textbf{T}_{J} = 25^{\circ} \text{C unless otherwise noted})$



GATE-TO-SOURCE OR DRAIN-TO-SOURCE VOLTAGE (VOLTS)






Figure 8. Gate-to-Source Voltage vs. Total
Gate Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current

ORDERING INFORMATION

Device	Marking	Package	Shipping [†]	
NTJD4158CT1G	TCD			
NTJD4158CT2G TCD		SC-88 (Pb-Free)	3000 / Tape & Reel	
NVJD4158CT1G*	VCD	,		


[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

^{*}NV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

PACKAGE DIMENSIONS

SC-88/SC70-6/SOT-363

CASE 419B-02 **ISSUE Y**



NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M. 1994.
- CONTROLLING DIMENSION: MILLIMETERS.
 DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH,
- DIMENSIONS D AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS. MOLD FLASH, PROTRUSIONS, OR GATE BURRS SHALL NOT EXCEED 0.20 PER END. DIMENSIONS D AND E1 AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY AND DATUM H.
 DATUMS A AND B ARE DETERMINED AT DATUM H.
 DIMENSIONS b AND C APPLY TO THE FLAT SECTION OF THE LEAD BETWEEN 0.08 AND 0.15 FROM THE TIP.

- DIMENSION 6 DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 TOTAL IN EXCESS OF DIMENSION 6 AT MAXIMUM MATERIAL CONDITION. THE DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OF THE FOOT.

	MIL	LIMETE	ERS	INCHES				
DIM	MIN	NOM	MAX	MIN	NOM	MAX		
Α			1.10			0.043		
A1	0.00		0.10	0.000		0.004		
A2	0.70	0.90	1.00	0.027	0.035	0.039		
b	0.15	0.20	0.25	0.006	0.008	0.010		
С	0.08	0.15	0.22	0.003	0.006	0.009		
D	1.80	2.00	2.20	0.070	0.078	0.086		
E	2.00	2.10	2.20	0.078	0.082	0.086		
E1	1.15	1.25	1.35	0.045	0.049	0.053		
е		0.65 BSC			0.026 BSC			
L	0.26	0.26 0.36 0.46			0.014	0.018		
L2		0.15 BSC			0.006 BSC			
aaa	0.15			0.006				
bbb	0.30			0.012				
ccc	0.10			0.004				
ddd		0.10		0.004				

STYLE 26: PIN 1. SOURCE 1


2. GATE 1

3 DRAIN 2 4. SOURCE 2 5. GATE 2 6. DRAIN 1

END VIEW RECOMMENDED **SOLDERING FOOTPRINT***

DETAIL A

C SEATING PLANE



Mounting Techniques Reference Manual, SOLDERRM/D.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and

ON Semiconductor and 🕠 are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. Coverage may be accessed at www.onsemi.com/site/par/-atent_-warking.pgr. On Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

6X | \triangle | CCC

SIDE VIEW

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Phone: 81-3-5817-1050