


Vishay General Semiconductor

Low V_F Single-Phase Single In-Line Bridge Rectifiers



PRIMARY CHARACTERISTICS				
Package	GSIB-5S			
I _{F(AV)}	25 A			
V _{RRM}	600 V			
I _{FSM}	550 A			
I _R	10 µA			
V_F at I_F = 12.5 A, T_A = 125 °C	0.76 V			
T _J max.	150 °C			
Diode variations	In-Line			

FEATURES

- UL recognition file number E54214, Vol. 1
- Thin single in-line package
- Oxide planar chip junction
- Low forward voltage drop
- High surge current capability
- High case dielectric strength of 2500 V_{RMS}
- Solder dip 275 °C max. 10 s, per JESD 22-B106
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

TYPICAL APPLICATIONS

General purpose use in AC/DC bridge full wave rectification for switching power supply, home appliances and white-goods applications specially for telecom power supply, high efficiency desktop PC and server SMPS.

MECHANICAL DATA

Case: GSIB-5S Epoxy meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 1A whisker test

Polarity: As marked on body

Mounting Torque: 10 cm-kg (8.8 in-lbs) maximum Recommended Torque: 5.7 cm-kg (5 in-lbs)

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER		SYMBOL	LVB2560	UNIT	
Maximum repetitive peak reverse voltage		V _{RRM}	600	V	
Maximum average forward rectified output current at	T _C = 105 °C	I _O ⁽¹⁾	25	^	
	T _A = 25 °C	I _O ⁽²⁾	3.6	A	
Non-repetiitive peak forward surge current 8.3 ms single sine-wave, $T_J = 25$ °C		I _{FSM}	550	А	
Rating for fusing (t < 8.3 ms)	$T_J = 25 \ ^\circ C$	l ² t	1255	A ² s	
Operating junction and storage temperature range		T _J , T _{STG}	- 55 to + 150	°C	

Notes

⁽¹⁾ Unit case mounted on aluminum plate heatsink

⁽²⁾ Units mounted on PCB without heatsink

Document Number: 89393

1

COMPLIANT

HALOGEN

FREE

LVB2560



Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)							
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT	
Instantaneous forward voltage	I _F = 12.5 A	T _A = 25 °C	V _F ⁽¹⁾	0.89	0.92	V	
		T _A = 125 °C		0.76	-		
Reverse current per diode	V _R = 600 V	T _A = 25 °C	I _R ⁽²⁾	0.2	10	μA	
		T _A = 125 °C		140	-		
Typical reverse recovery time	I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A		t _{rr}	1.8	-	μs	
Typical junction capacitance	4.0 V, 1 MHz		CJ	330	-	pF	

Notes

⁽¹⁾ Pulse test: 300 µs pulse width, 1 % duty cycle

⁽²⁾ Pulse test: pulse width \leq 40 ms

THERMAL CHARACTERISTICS ($T_A = 25 \text{ °C}$ unless otherwise noted)				
PARAMETER SYMBOL LVB2560		LVB2560	UNIT	
Maximum thermal resistance	R _{0JA} ⁽²⁾	25	°C/W	
	R _{0JC} ⁽¹⁾	1.0	0/11	

Notes

⁽¹⁾ With heatsink

⁽²⁾ Without heatsink, free air

EMC SURGE IMMUNITY TEST STANDARD ($T_A = 25 \text{ °C}$, unless otherwise noted)						
STANDARD	TEST TYPE	TEST CONDITIONS SY		CLASS	VALUE	
IEC 61000-4-5	Power supply coupling mode, line to line	1.2/50 μs waveform, R = 2 $\Omega,$ T_A = 25 °C $^{(1)}$	V _{PEAK}	-	6 kV maximum	

Note

(1) Immunity to IEC 61000-4-5 peak pulse voltage test, 1.2/50 µs, 2 Ω, 5 times each of positive and negative polarity test

ORDERING INFORMATION (Example)							
PREFERRED P/N	P/N UNIT WEIGHT (g) PREFERRED PACKAGE CODE BASE QUANTITY						
LVB2560-M3/45	7.1	45	20	Tube			

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Fig. 1 - Derating Curve Output Rectified Current




Fig. 2 - Forward Current Derating Curve

Revision: 26-Jun-13

2

Document Number: 89393

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

Vishay General Semiconductor







Fig. 3 - Forward Power Dissipation





PACKAGE OUTLINE DIMENSIONS in millimeters







Fig. 5 - Typical Reverse Characteristics Per Diode







Revision: 26-Jun-13 3 Document Number: 89393 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.