

APPROVAL SHEET

 Customer Name
 :

 Customer P/N
 :

 Frequency
 : 8.000000
 MHz

 AKER Approved P/N
 : 49M-008000-FD4D14

 AKER MPN
 : 49M-008000-FD4D14

 REVISION
 : A0

 ISSUED DATE
 : 2019/11/21

APPROVED	CHECKED	PREPARED
Evernest		Kiku
APPROVED BY CU	JSTOMER	

AKER TECHNOLOGY CO., LTD.

ADDRESS: No.11-3, Jianguo Rd., Tanzi Dist., Taichung City 427, Taiwan

TEL: 886-4-25335978 FAX: 886-4-25336011

Web: www.aker.com.tw

RoHS compliant



Customer P/N			
AKER Approved P/N	49M-008000-FD4D14		
APPROVED	Earnest	Earnest SHEET	
PREPARED	Kiku	REV.	A0

Revison	Date	Reviser	Revised contents
A0	2019/11/21	Kiku	Initial Released



Customer P/N			
AKER Approved P/N	49M-008000-		
APPROVED	Earnest SHEET		2 OF 6
PREPARED	Kiku	REV.	A0

HC-49US SMD CRYSTAL SPECIFICATION

1. ELECTRICAL CHARACTERISTICS

(1) Standard atmospheric conditions

Unless otherwise specified , the standard range of atmospheric conditions for making measurement and tests are as follow :

Ambient temperature: 25±5°C

Relative humidity : 40%~70%

If there is any doubt about the results, measurement shall be made within the following limits:

Ambient temperature: 25±3°C

Relative humidity : 40%~70%

(2) Measurement Equipment: SAUNDERS 350A (Measured FL)

(3) Cutting Model: AT CUT

(4) Oscillation Model: Fundamental


Parameters	Symbol	Ele	Electrical Specification			Notes
Farameters	Symbol	Min.	Тур.	Max.	Unit	Notes
Nominal Frequency	FL	8	3.000000)	MHz	
Load Capacitance	CL		20		pF	
Frequency Tolerance		-20	~	20	ppm	At $25^{\circ}\text{C} \pm 3^{\circ}\text{C}$
Frequency Stability		-20	~	20	ppm	Related to 25 °C
Drive Level	DL			100	uW	
Operating Temperature Range		-20	~	70	°C	
Storage Temperature Range		-55	~	125	°C	
Effective Series Resistance	RR			60	Ω	
Shunt Capacitance	C0			7	pF	
Motional Capacitance	C 1		N/A		fF	
Ratio Of Capacitance	r		N/A			C0/C1
Aging Rate		-3	~	3	ppm	First Year
Insulation Resistance		500			MOhms	At DC 100V

^{*}Please kindly be noted that AKER DO NOT guarantee parts quality which involves human security application.*




Customer P/N			
AKER Approved P/N	49M-008000-FD4D14		
APPROVED	Earnest	SHEET	3 OF 6
PREPARED	Kiku	REV.	A0

2. MARKING



Type and Date Code



Oscillation Mode Code

Code	Oscillation Mode			
F	AT Cut / Fundamental			
Т	AT Cut / 3rd Overtone			
В	BT Cut / Fundamental			

Load Capacitance Code

Code	CL	Code	CL
S	Series	P	4
A	16	Q	39
В	20	R	12.5
С	30	T	8
D	18	U	33
Е	32	V	7
F	12	W	6
G	22	X	17
Н	27	Y	8.5
I	10	Z	19.5
J	14	a	21.5
K	15	b	24
L	25	c	35
M	9	d	37
N	13		

Frquency Tolerance Code

Code	Tolerance	Code	Tolerance
1	±20 ppm	6	±50 ppm
2	±25 ppm	9	±10 ppm
3	±30 ppm	0	±100 ppm
5	±15 ppm		-


Date Code


Year	2017	2018	2019	2020
	2021	2022	2023	2024
	2025	2026	2027	2028
Month	2029	2030	2031	2032
JAN	A	N	a	n
FEB	В	P	b	p
MAR	C	Q	С	q
APR	D	R	d	r
MAY	Е	S	e	S
JUN	F	T	f	t
JUL	G	U	g	u
AUG	Н	V	h	V
SEP	J	W	j	W
OCT	K	X	k	X
NOV	L	Y	1	y
DEC	M	Z	m	Z





Customer P/N			
AKER Approved P/N	49M-008000		
APPROVED	Earnest	Earnest SHEET	
PREPARED	Kiku	REV.	A0

3. DIMENSIONS: (Unit:mm)











4. SUGGESTED LAND PATTERN: (Unit:mm)



5. SOLDERING REFLOW PROFILE




Please kindly be noted that AKER DO NOT guarantee parts quality which involves human security application.




Customer P/N			
AKER Approved P/N	49M-008000-FD4D14		
APPROVED	Earnest SHEET		5 OF 6
PREPARED	Kiku	REV.	A0

6.PACKING: (Unit:mm) 1000pcs/reel

6.1 TAPE SPECIFICATION



6.2 REEL SPECIFICATION



*Please kindly be noted that **AKER DO NOT** guarantee parts quality which involves human security application.*



Customer P/N			
AKER Approved P/N	49M-008000-FD4D14		
APPROVED	Earnest	SHEET	6 OF 6
PREPARED	Kiku	REV.	A0

7. RELIABILITY SPECIFICATION

No	Test Item	Test Methods	Performance	
1	Drop Test	Free drop from 50 cm height onto a hard wooden board	To satisfy the	
2	Mechanical Shock	for 3 times 1000 G, 0.5 msec, 3 times for each direction (X, Y, Z)		
3	Vibration	Frequency range: 20 ~ 2000 Hz Amplitude: 1.52 mm / 20G Sweep time: 20 minutes Test time for each direction: 2 Hours (Total 6 Hours)	electrical characteristics	
4	Gross Leak	Alcohol, Test Pressure : > -40cm-Hg	No bubbles stream	
5	Fine Leak	5 kgf /cm ² Helium bombing for 2 Hours	$\leq 10^{-8}$ atm.cc./sec	
6	Solderability	Temperature : 260° C ± 5° C	90% min. coverage	
		Immersion time : 5 ± 1 seconds	of new solder	
7	Resistance To Soldering Heat	Solder pot test Test temperature : $260^{\circ}\text{C} \pm 5^{\circ}\text{C}$ Test time : 10 ± 1 seconds		
8	High Temperature Storage	+ 125 $^{\circ}$ C ± 3 $^{\circ}$ C for 500 ± 12 Hours		
9	Low Temperature Storage	- 55 °C ± 3 °C for 500 ± 12 Hours		
10	Temperature Cycle	Total 100 cycles of the following temperature cycle 1 cycle 25° C ± 3° C -55° C ± 3° C 15 min.	To satisfy the electrical characteristics	
11	High Temperature And Humidity	85° C ± 5°C, RH 85% ± 5%, 500 ± 12 Hours		