




N-Channel 200-V (D-S) MOSFET

| PRODUCT SUMMARY | | | | |
|---------------------|----------------------------------|--------------------|--|--|
| V _{DS} (V) | $R_{DS(on)}(\Omega)$ | I _D (A) | | |
| 200 | 0.080 at V _{GS} = 10 V | 4.0 | | |
| | 0.090 at V _{GS} = 6.0 V | 3.8 | | |


FEATURES

- Halogen-free According to IEC 61249-2-21 Definition
- TrenchFET® Power MOSFETs
- Compliant to RoHS Directive 2002/95/EC





Ordering Information: Si4490DY-T1-E3 (Lead (Pb)-free) Si4490DY-T1-GE3 (Lead (Pb)-free and Halogen-free)



N-Channel MOSFET

| ABSOLUTE MAXIMUM RATINGS T _A = 25 °C, unless otherwise noted | | | | | |
|---|------------------------|-----------------------------------|--------------|------|----|
| Parameter | Symbol | 10 s | Steady State | Unit | |
| Drain-Source Voltage | | V _{DS} | 200 | | V |
| Gate-Source Voltage | | V _{GS} | ± 20 | | |
| Continuous Drain Current /T 150 °C\a | T _A = 25 °C | - I _D | 4.0 | 2.85 | |
| Continuous Drain Current (T _J = 150 °C) ^a | T _A = 70 °C | | 3.2 | 2.3 | 1 |
| Pulsed Drain Current | | I _{DM} | 40 | | Α |
| Avalanch Current | L = 0.1 mH | I _{AS} | 15 | | |
| Continuous Source Current (Diode Conduction) ^a | I _S | 2.6 | 1.3 | | |
| | T _A = 25 °C | P _D | 3.1 | 1.56 | W |
| Maximum Power Dissipation ^a | T _A = 70 °C | ' D | 2.0 | 1.0 | |
| Operating Junction and Storage Temperature Range | | T _J , T _{stg} | - 55 to 150 | | °C |

| THERMAL RESISTANCE RATINGS | | | | | |
|--|--------------|-------------------|---------|---------|------|
| Parameter | | Symbol | Typical | Maximum | Unit |
| Manifestor Location to Australia | t ≤ 10 s | R _{thJA} | 33 | 40 | |
| Maximum Junction-to-Ambient ^a | Steady State | ' ¹thJA | 65 | 80 | °C/W |
| Maximum Junction-to-Foot (Drain) | Steady State | R_{thJF} | 17 | 21 | |

Notes:

a. Surface Mounted on 1" x 1" FR4 board.


Vishay Siliconix




| SPECIFICATIONS $T_J = 25^{\circ}$ | Symbol | | | | Typ. Max. | Unit | |
|---|---------------------|--|--------|-------|-----------|------|--|
| | Symbol | rest Conditions | Willi. | Тур. | wax. | Unit | |
| Static | | | 1 | 1 | ı | | |
| Gate Threshold Voltage | V _{GS(th)} | $V_{DS} = V_{GS}, I_{D} = 250 \mu A$ | 2.0 | | | V | |
| Gate-Body Leakage | I _{GSS} | $V_{DS} = 0 V, V_{GS} = \pm 20 V$ | | | ± 100 | nA | |
| Zoro Cata Valtaga Drain Current | lass | $V_{DS} = 160 \text{ V}, V_{GS} = 0 \text{ V}$ | | | 1 | | |
| Zero Gate Voltage Drain Current | I _{DSS} | V _{DS} = 160 V, V _{GS} = 0 V, T _J = 55 °C | | | 5 | μΑ | |
| On-State Drain Current ^a | I _{D(on)} | $V_{DS} \ge 5 \text{ V}, V_{GS} = 10 \text{ V}$ | 40 | | | Α | |
| | В | V _{GS} = 10 V, I _D = 4.0 A | | 0.065 | 0.080 | | |
| Drain-Source On-State Resistance ^a | R _{DS(on)} | $V_{GS} = 6.0 \text{ V}, I_D = 4.0 \text{ A}$ | | 0.070 | 0.090 | Ω | |
| Forward Transconductance ^a | 9 _{fs} | V _{DS} = 15 V, I _D = 5 A | | 19 | | S | |
| Diode Forward Voltage ^a | V_{SD} | I _S = 2.8 A, V _{GS} = 0 V | | 0.75 | 1.2 | V | |
| Dynamic ^b | - | | | • | | | |
| Total Gate Charge | Q_g | | | 34 | 42 | | |
| Gate-Source Charge | Q_{gs} | $V_{DS} = 100 \text{ V}, V_{GS} = 10 \text{ V}, I_{D} = 4.0 \text{ A}$ | | 7.5 | | nC | |
| Gate-Drain Charge | Q_{gd} | | | 12.0 | | 1 | |
| Gate Resistance | R_{g} | | 0.2 | 0.85 | 1.3 | Ω | |
| Turn-On Delay Time | t _{d(on)} | | | 14 | 20 | | |
| Rise Time | t _r | V_{DD} = 100 V, R_L = 25 Ω | | 20 | 30 | | |
| Turn-Off Delay Time | t _{d(off)} | $I_D\cong 4.0$ A, $V_{GEN}=10$ V, $R_g=6$ Ω | | 32 | 50 | ns | |
| Fall Time | t _f | | | 25 | 35 | | |
| Source-Drain Reverse Recovery Time | t _{rr} | I _F = 2.8 A, dI/dt = 100 A/μs | | 70 | 100 | | |

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted






Notes: a. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %. b. Guaranteed by design, not subject to production testing.









TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




On-Resistance vs. Drain Current






2500
2000
C_{iss}
1500
1000
500
C_{rss}
C_{oss}
0
40
80
120
160
200

V_{DS} - Drain-to-Source Voltage (V) **Capacitance**



On-Resistance vs. Junction Temperature




On-Resistance vs. Gate-to-Source Voltage

Is - Source Current (A)

Vishay Siliconix

VISHAY.

TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?71341.



SOIC (NARROW): 8-LEAD JEDEC Part Number: MS-012







| | MILLIM | IETERS | INC | HES | |
|------------------------------|--------|--------|-----------|-------|--|
| DIM | Min | Max | Min | Max | |
| Α | 1.35 | 1.75 | 0.053 | 0.069 | |
| A ₁ | 0.10 | 0.20 | 0.004 | 0.008 | |
| В | 0.35 | 0.51 | 0.014 | 0.020 | |
| С | 0.19 | 0.25 | 0.0075 | 0.010 | |
| D | 4.80 | 5.00 | 0.189 | 0.196 | |
| Е | 3.80 | 4.00 | 0.150 | 0.157 | |
| е | 1.27 | BSC | 0.050 BSC | | |
| Н | 5.80 | 6.20 | 0.228 | 0.244 | |
| h | 0.25 | 0.50 | 0.010 | 0.020 | |
| L | 0.50 | 0.93 | 0.020 | 0.037 | |
| q | 0° | 8° | 0° | 8° | |
| S | 0.44 | 0.64 | 0.018 | 0.026 | |
| FCN: C-06527-Bey 11-Sen-06 | | | | | |

DWG: 5498

Document Number: 71192 www.vishay.com 11-Sep-06



RECOMMENDED MINIMUM PADS FOR SO-8



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index

Ш



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.