




P-Channel 100-V (D-S) MOSFET

PRODUCT SUMMARY						
V _{DS} (V)	$R_{DS(on)}$ (Ω)	I _D (A)	Q _g (Typ.)			
- 100	0.019 at V _{GS} = - 10 V	- 90	97 nC			
	0.021 at V _{GS} = - 4.5 V	- 85	97110			


FEATURES

- TrenchFET® Power MOSFET
- Compliant to RoHS Directive 2002/95/EC





Ordering Information: SUM90P10-19L-E3 (Lead (Pb)-free)



P-Channel MOSFET

Parameter	Symbol	Limit	Unit		
Drain-Source Voltage	V _{DS}	- 100	V		
Gate-Source Voltage		V _{GS}	± 20	v	
	T _C = 25 °C		- 90		
Continuous Drain Current (T _{.I} = 150 °C)	T _C = 125 °C	I _D	- 52		
Continuodo Brain Carrent (1) = 100 O)	T _A = 25 °C	.р	- 17.2 ^{b, c}		
	T _A = 125 °C		- 9.9 ^{b, c}	A	
Pulsed Drain Current		I _{DM}	- 90	7 ^	
Continuous Source-Drain Diode Current	T _C = 25 °C		- 250		
Continuous Source-Drain Diode Current	T _A = 25 °C	I _S	- 9 ^{b, c}		
Avalanche Current	L = 0.1 mH	I _{AS}	- 70		
Single-Pulse Avalanche Energy	L = 0.111111	E _{AS}	245	mJ	
	T _C = 25 °C		375		
Maximum Power Dissipation	T _C = 125 °C	P _D	125	w	
Maximum Fower Dissipation	T _A = 25 °C	' D	13.6 ^{b, c}	- vv	
	T _A = 125 °C		4.5 ^{b, c}		
Operating Junction and Storage Temperature R	T _J , T _{stg}	- 55 to 175	°C		

THERMAL RESISTANCE RATINGS						
Parameter		Symbol	Typical	Maximum	Unit	
Maximum Junction-to-Ambient ^{b, d}	t ≤ 10 s	R _{thJA}	8	11	°C/W	
Maximum Junction-to-Case (Drain)	Steady State	$R_{th,IC}$	0.33	0.4	O/ VV	

Notes:

- a. Package Limited.
- b. Surface Mounted on 1" x 1" FR4 board.
- c. t = 10 s
- d. Maximum under Steady State conditions is 40 $^{\circ}\text{C/W}.$

SUM90P10-19L

Vishay Siliconix



SPECIFICATIONS $T_J = 25$ Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = -250 \mu\text{A}$	- 100			V	
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$			- 125			
V _{GS(th)} Temperature Coefficient	$\Delta V_{GS(th)}/T_J$	I _D = - 250 μA		5.9		mV/°C	
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}$, $I_{D} = -250 \mu A$	- 1		- 3	V	
Gate-Source Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 100	nA	
7 0		V _{DS} = - 100 V, V _{GS} = 0 V			- 1	—— μA	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = - 100 V, V _{GS} = 0 V, T _J = 175 °C			- 500		
On-State Drain Current ^a	I _{D(on)}	$V_{DS} \ge 10 \text{ V}, V_{GS} = -10 \text{ V}$	- 90			Α	
	5	V _{GS} = - 10 V, I _D = - 20 A		0.0156	0.019	Ω	
Drain-Source On-State Resistance ^a	H _{DS(on)}	V _{GS} = - 4.5 V, I _D = - 15 A		0.0173	0.021		
Forward Transconductance ^a	9 _{fs}	V _{DS} = - 15 V, I _D = - 20 A		80		S	
Dynamic ^b							
Input Capacitance	C _{iss}			11100			
Output Capacitance	C _{oss}	V 50 V V 0 V f 1 M l=		700		pF	
Reverse Transfer Capacitance	C _{rss}	$V_{DS} = -50 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		1690			
		V _{DS} = - 50 V, V _{GS} = - 10 V, I _D = - 90 A		217	326	nC	
Total Gate Charge	Q_g			97	146		
Gate-Source Charge	Q_{gs}	$V_{DS} = -50 \text{ V}, V_{GS} = -4.5 \text{ V}, I_{D} = -90 \text{ A}$		42			
Gate-Drain Charge	Q_{gd}			51			
Gate Resistance	R_g	f = 1 MHz		3.5		Ω	
Turn-On Delay Time	t _{d(on)}			20	30		
Rise Time	t _r	V_{DD} = - 50 V, R_{L} = 0.56 Ω		510	855	ne	
Turn-Off Delay Time	t _{d(off)}	$I_D\cong$ - 90 A, V_{GEN} = - 10 V, R_g = 1 Ω		145	220	ns ns	
Fall Time	t _f			870	1300		
Drain-Source Body Diode Characte	ristics						
Continous Source-Drain Diode Current	I _S	$T_C = 25 ^{\circ}C$			- 90	А	
Pulse Diode Forward Current ^a	I _{SM}				- 250		
Body Diode Voltage	V_{SD}	I _S = - 20 A		- 0.8	- 1.5	V	
Body Diode Reverse Recovery Time	t _{rr}			80	120	ns	
Body Diode Reverse Recovery Charge	Q _{rr}	$I_F = -20 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, T_J = 25 ^{\circ}\text{C}$		220	330	nC	
Reverse Recovery Fall Time	t _a			56			
Reverse Recovery Rise Time t _b				24		ns	

Notes


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

a. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %.


b. Guaranteed by design, not subject to production testing.




TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted




Output Characteristics




On-Resistance vs. Drain Current






Transfer Characteristics





Capacitance




On-Resistance vs. Junction Temperature


Vishay Siliconix













Threshold Voltage

Single Pulse, Junction-to-Case (T_C = 25 °C)









Vishay Siliconix


TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted





Max Avalanche and Drain Current vs. Case Temperature







Normalized Thermal Transient Impedance, Junction-to-Case


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?73474.



TO-263 (D²PAK): 3-LEAD










DETAIL A (ROTATED 90°)



_	,	—b - -b	 			1
2	T			C	_ (<u>-</u>
	SE	^TIC	M	ا م		1

- 1. Plane B includes maximum features of heat sink tab and plastic.
- 2. No more than 25 % of L1 can fall above seating plane by max. 8 mils.
- 3. Pin-to-pin coplanarity max. 4 mils.
- 4. *: Thin lead is for SUB, SYB. Thick lead is for SUM, SYM, SQM.
- 5. Use inches as the primary measurement.

6 This feature is for thick lead.

		INC	HES	MILLIN	METERS	
	DIM.	MIN.	MAX.	MIN.	MAX.	
Α		0.160	0.190	4.064	4.826	
	b	0.020	0.039	0.508	0.990	
	b1	0.020	0.035	0.508	0.889	
	b2	0.045	0.055	1.143	1.397	
c*	Thin lead	0.013	0.018	0.330	0.457	
	Thick lead	0.023	0.028	0.584	0.711	
c1	Thin lead	0.013	0.017	0.330	0.431	
CI	Thick lead	0.023	0.027	0.584	0.685	
	c2	0.045	0.055	1.143	1.397	
	D	0.340	0.380	8.636	9.652	
	D1	0.220	0.240	5.588	6.096	
	D2	0.038	0.042	0.965	1.067	
	D3	0.045	0.055	1.143	1.397	
D4		0.044	0.052	1.118	1.321	
	Е	0.380	0.410	9.652	10.414	
	E1	0.245	-	6.223	-	
	E2	0.355	0.375	9.017	9.525	
	E3	0.072	0.078	1.829	1.981	
	е	0.100 BSC 2.54 B			BSC	
	K	0.045	0.055	1.143	1.397	
L		0.575	0.625	14.605	15.875	
L1		0.090	0.110	2.286	2.794	
	L2	0.040	0.055	1.016	1.397	
L3		0.050	0.070	1.270	1.778	
L4		0.010 BSC 0.25			BSC	
M		-	0.002	-	0.050	
ECN: T13-0707-Rev. K, 30-Sep-13						

DWG: 5843





RECOMMENDED MINIMUM PADS FOR D²PAK: 3-Lead



Recommended Minimum Pads Dimensions in Inches/(mm)

Return to Index



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.