

RF5515

4.9GHz TO 5.85GHZ LOW NOISE AMPLIFIER WITH ENABLE

Package Style: 2.2mm x 2.2mm x 0.5mm






Features

- 4.9GHz to 5.85GHz Operation
- 2.3V to 4.8V Single Supply
- 1.6dB Noise Figure
- 11dB Typical Gain

Applications

- High Band WiFi LNA/Driver
- General Purpose Amplifier for Portable Applications



Functional Block Diagram

Product Description

The RF5515 is a high performance Low Noise Amplifier design for 802.11a applications (4.9GHz to 5.85GHz) and other portable consumer electronics. This miniature LNA features a high dynamic range and high intercept point with low current consumption around 12mA. The LNA is DC blocked and internally matched to 50Ω at input and output pins. The IC is featured in a 2.2mm x 2.2mm x 0.5mm module compatible plastic package.

Ordering Information

RF5515 Standard 25 piece bag RF5515SR Standard 100 piece reel RF5515TR7 Standard 2500 piece reel

RF5515PCK-410 Fully assembled evaluation board and 5 piece loose samples

Optimum Technology Matching® Applied

| ☐ GaAs HBT | □ SiGe BiCMOS | GaAs pHEMT | ☐ GaN HEMT |
|---------------|---------------|------------|-------------|
| ☐ GaAs MESFET | ☐ Si BiCMOS | ☐ Si CMOS | ☐ BiFET HBT |
| ☐ InGaP HBT | ☐ SiGe HBT | ☐ Si BJT | ☐ LDMOS |

RF5515



Absolute Maximum Ratings

| Parameter | Rating | Unit |
|------------------------------------|-------------|------|
| DC Supply Voltage (No RF Applied) | 6.0 | V |
| DC Supply Voltage (RF Applied) | 5.25 | V |
| Maximum Input Power (No Damage) | 10 | dBm |
| Operating Temperature | -40 to +85 | °C |
| Storage Temperature | -40 to +150 | °C |



Caution! ESD sensitive device.

Exceeding any one or a combination of the Absolute Maximum Rating conditions may cause permanent damage to the device. Extended application of Absolute Maximum Rating conditions to the device may reduce device reliability. Specified typical performance or functional operation of the device under Absolute Maximum Rating conditions is not implied.

The information in this publication is believed to be accurate and reliable. However, no responsibility is assumed by RF Micro Devices, Inc. ("RFMD") for its use, nor for any infringement of patents, or other rights of third parties, resulting from its use. No license is granted by implication or otherwise under any patent or patent rights of RFMD. RFMD reserves the right to change component circuitry, recommended application circuitry and specifications at any time without prior notice.



RFMD Green: RoHS compliant per EU Directive 2002/95/EC, halogen free per IEC 61249-2-21, < 1000 ppm each of antimony trioxide in polymeric materials and red phosphorus as a flame retardant, and <2% antimony in solder.

| Davamatav | Specification | | | 0 1111 | | |
|---------------------------------------|---------------|------|------|--------|--|--|
| Parameter | Min. | Тур. | Max. | Unit | Condition | |
| Typical Conditions | | | | | Temp = 25 °C, V _{DD} = 3.3V, LNA_EN = 3.3V, Fre- | |
| | | | | | quency = 4.9GHz to 5.85GHz unless otherwise noted in the condition column. | |
| Frequency | 4.9 | | 5.85 | GHz | | |
| LNA Voltage Supply (V _{DD}) | 2.7 | 3.3 | 4.8 | V | | |
| LNA Enable Voltage (LNA_EN) | 2.5 | | 4.8 | VDD | LNA Enabled | |
| | | 0 | 0.2 | V | LNA Off | |
| LNA Current | | | | | | |
| LNA V _{DD} | 6 | 12 | 20 | mA | LNA in "On" state, over operating temperature range, Full V _{DD} range, full LNA_EN range, and full frequency band. | |
| | 0 | | 5 | μΑ | LNA in "Off" state | |
| LNA Enable | | | 200 | μΑ | | |
| Gain | | | | | | |
| LNA in "ON" State | 8 | 11 | 14 | dB | Over full operating temperature range, full V _{CC} range, Full LNA_EN range, and full frequency range. | |
| Noise Figure | | | | | | |
| LNA in "ON" State | 1.2 | 1.7 | 2.4 | dB | Over Full V _{DD} range, full LNA_EN range, Full frequency range, and over operating temperature range. | |
| Passband Ripple | -0.5 | | +0.5 | dB | Rx Mode, LNA ON | |
| Input P1dB | -4 | -1 | | dBm | Over operating temperature range, full voltage range, full LNA_EN range, and full frequency range. | |
| RF OUT Port Return Loss | | | -9.6 | dB | 4.9GHz to 5.85GHz | |
| RF IN Port Return Loss | | | -9.6 | dB | | |
| RF OUT Rx Port Impedance | | 50 | | Ω | No external matching | |




rfmd.com

| Pin | Function | Description |
|-------------|----------|--|
| 1 | RF IN | RF Input. Input is matched to 50Ω and DC block is provided internally. |
| 2 | NC | No Connect |
| 3 | LNA_EN | LNA Enable. Voltage which is a high impedance pin could require bypassing depending on the nature of the supply voltage and the layout. |
| 4 | NC | No Connect |
| 5 | RF OUT | RF Output. This pin is matched to 50Ω internally and it is a DC short to GND. See functional block diagram for more details. |
| 6 | NC | No Connect |
| 7 | VDD | Supply Voltage for the LNA circuit. It is recommended that bypass capacitors are placed on this voltage line as needed depending on the nature of the supply voltage and layout. |
| 8 | NC | No Connect |
| Pkg Base | GND | The center metal base of the QFN package provides DC and RF ground as well as heat sink for the amplifier. |

Package Drawing

2.2mm x 2.2mm x 0.5mm




1. SHADED LEAD IS PIN 1.

DIMENSION APPLIES TO METALLIZED PAD AND IS MEASURED BETWEEN 0.25 AND 0.30 MM FROM PAD TIP.




Evaluation Board Schematic










Evaluation Board Layout












Application Schematic - 4.9GHz to 5.85GHz





PCB Design Requirements

PCB Surface Finish


The PCB surface finish used for RFMD's qualification process is electroless nickel, immersion gold. Typical thickness is 3 microinch to 8 micro-inch gold over 180 micro-inch nickel.

PCB Land Pattern Recommendation *

PCB land patterns for RFMD components are based on IPC-7351 standards and RFMD empirical data. The pad pattern shown has been developed and tested for optimized assembly at RFMD. The PCB land pattern has been developed to accommodate lead and package tolerances. Since surface mount processes vary from company to company, careful process development is recommended.


PCB Metal Land Pattern

 $A = 0.280 \times 0.310 \text{ (mm) Typ}$ $B = 0.310 \times 0.280 \text{ (mm) Typ}$ C = 1.100 (mm) Sq



PCB Solder Mask Pattern

A = 0.42 x 0.45 (mm) Typ B = 0.45 x 0.42 (mm) Typ C = 1.24 (mm) Sq




RF5515



PCB Stencil Pattern

 $A = 0.25 \times 0.28$ (mm) Typ $B = 0.28 \times 0.25$ (mm) Typ C = 0.99 (mm) Sq



Note: Thermal vias for center slug "C" should be incorporated into the PCB design. The number and size of thermal vias will depend on the application. Example of the number and size of vias can be found on the RFMD evaluation board layout.





