# MOSFET – Power, Dual, P-Channel, ESD, μCool, UDFN, 1.6X1.6X0.55 mm -20 V, -2.1 A

#### **Features**

- UDFN Package with Exposed Drain Pads for Excellent Thermal Conduction
- Low Profile UDFN 1.6x1.6x0.55 mm for Board Space Saving
- ESD Protected
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

#### **Applications**

- High Side Load Switch
- PA Switch
- Optimized for Power Management Applications for Portable Products, such as Cell Phones, PMP, DSC, GPS, and others

#### MAXIMUM RATINGS (T<sub>J</sub> = 25°C unless otherwise stated)

Parameter		Symbol	Value	Units	
Drain-to-Source Voltage		V <sub>DSS</sub>	-20	V	
Gate-to-Source Vol	tage		$V_{GS}$	±8.0	V
Continuous Drain	Steady	T <sub>A</sub> = 25°C	I <sub>D</sub>	-1.7	Α
Current (Note 1)	State	T <sub>A</sub> = 85°C		-1.2	
	t ≤ 5 s	T <sub>A</sub> = 25°C	1	-2.1	
Power Dissipa- tion (Note 1)	Steady State	T <sub>A</sub> = 25°C	P <sub>D</sub>	0.8	W
	t ≤ 5 s	T <sub>A</sub> = 25°C	1	1.3	
Continuous Drain	Steady State	T <sub>A</sub> = 25°C	I <sub>D</sub>	-1.3	Α
Current (Note 2)	State	T <sub>A</sub> = 85°C	1	-0.9	
Power Dissipation (	Power Dissipation (Note 2) T <sub>A</sub> = 25°C		P <sub>D</sub>	0.5	W
Pulsed Drain Curre	Pulsed Drain Current tp = 10 μs		I <sub>DM</sub>	-8.0	Α
Operating Junction and Storage Temperature		T <sub>J</sub> , T <sub>STG</sub>	-55 to 150	°C	
Source Current (Body Diode) (Note 2)		I <sub>S</sub>	-0.6	Α	
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)		T <sub>L</sub>	260	°C	

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.


- Surface Mounted on FR4 Board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces).
- Surface-mounted on FR4 board using the minimum recommended pad size of 30 mm<sup>2</sup>, 2 oz. Cu.



#### ON Semiconductor®

#### http://onsemi.com

MOSFET				
V <sub>(BR)DSS</sub>	R <sub>DS(on)</sub> MAX	I <sub>D</sub> MAX		
	200 mΩ @ -4.5 V			
-20 V	290 mΩ @ -2.5 V	-2.1 A		
	390 mΩ @ –1.8 V	2.171		
	650 mΩ @ –1.5 V			



P-Channel MOSFET

#### MARKING DIAGRAM



UDFN6 CASE 517AT μCOOL™




AD = Specific Device Code

M = Date Code

= Pb-Free Package

(Note: Microdot may be in either location)

#### PIN CONNECTIONS



#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 5 of this data sheet.

#### THERMAL RESISTANCE RATINGS


Parameter	Symbol	Max	Units
Junction-to-Ambient – Steady State (Note 3)	$R_{\theta JA}$	155	°C/W
Junction-to-Ambient – $t \le 5$ s (Note 3)		100	
Junction-to-Ambient – Steady State min Pad (Note 4)		245	

Parameter	Symbol	Test Co	ondition	Min	Тур	Max	Units
OFF CHARACTERISTICS		•		- 1	1		
Drain-to-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	$V_{GS} = 0 \text{ V}, I_D = -250 \mu\text{A}$		-20			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V <sub>(BR)DSS</sub> /T <sub>J</sub>	I <sub>D</sub> = -250 μA, ref to 25°C			-10		mV/°C
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	$V_{GS} = 0 \text{ V},$ $T_J = 25^{\circ}\text{C}$				-1.0	μΑ
		V <sub>DS</sub> = -20 V	T <sub>J</sub> = 125°C			-10	
Gate-to-Source Leakage Current	$I_{GSS}$	V <sub>DS</sub> = 0 V, \	$I_{GS} = \pm 8.0 \text{ V}$			±10	μΑ
ON CHARACTERISTICS (Note 5)							
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS} = V_{DS}$ ,	I <sub>D</sub> = -250 μA	-0.4		-1.0	V
Negative Threshold Temp. Coefficient	V <sub>GS(TH)</sub> /T <sub>J</sub>				2.8		mV/°C
Drain-to-Source On Resistance	R <sub>DS(on)</sub>	$V_{GS} = -4.5^{\circ}$	V, I <sub>D</sub> = −2.0 A		160	200	mΩ
		V <sub>GS</sub> = -2.5	V, I <sub>D</sub> = −1.2 A		226	290	
		V <sub>GS</sub> = -1.8 \	/, I <sub>D</sub> = -0.24 A		300	390	
		V <sub>GS</sub> = -1.5 \	/, I <sub>D</sub> = -0.18 A		390	650	1
Forward Transconductance	9FS	V <sub>DS</sub> = -10 \	V, I <sub>D</sub> = -1.5 A		3.7		S
CHARGES, CAPACITANCES & GATE	RESISTANCE						
Input Capacitance	C <sub>ISS</sub>	$V_{GS} = 0 \text{ V, } f = 1 \text{ MHz,}$ $V_{DS} = -10 \text{ V}$			300		pF
Output Capacitance	C <sub>OSS</sub>				34		
Reverse Transfer Capacitance	C <sub>RSS</sub>				29		
Total Gate Charge	Q <sub>G(TOT)</sub>	$V_{GS} = -4.5 \text{ V}, V_{DS} = -10 \text{ V};$ $I_{D} = -1.7 \text{ A}$			4.2		nC
Threshold Gate Charge	Q <sub>G(TH)</sub>				0.3		
Gate-to-Source Charge	Q <sub>GS</sub>				0.7		
Gate-to-Drain Charge	$Q_{GD}$				1.1		
SWITCHING CHARACTERISTICS, VG	S = 4.5 V (Note 6)	•		•			
Turn-On Delay Time	t <sub>d(ON)</sub>				17.4		ns
Rise Time	t <sub>r</sub>	$V_{GS} = -4.5 \text{ V}, V_{DD} = -10 \text{ V},$ $I_{D} = -1.5 \text{ A}, R_{G} = 1 \Omega$			32.3		
Turn-Off Delay Time	t <sub>d(OFF)</sub>				149		
Fall Time	t <sub>f</sub>				74		
DRAIN-SOURCE DIODE CHARACTER	RISTICS	•					L
Forward Diode Voltage	VSD	$V_{GS} = 0 V,$ $I_{S} = -0.6 A$	T <sub>J</sub> = 25°C		0.8	1.2	V
-			T <sub>J</sub> = 125°C		0.68		1
Reverse Recovery Time	t <sub>RR</sub>	V <sub>GS</sub> = 0 V, dis/dt = 100 A/μs, I <sub>S</sub> = -1.0 A			10.6		ns
Charge Time	t <sub>a</sub>				8.7		
Discharge Time	t <sub>b</sub>				1.9		
Reverse Recovery Charge	Q <sub>RR</sub>				5.1		nC

- 3. Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces). 4. Surface-mounted on FR4 board using the minimum recommended pad size of 30 mm<sup>2</sup>, 2 oz. Cu. 5. Pulse Test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2%.

- 6. Switching characteristics are independent of operating junction temperatures.

#### **TYPICAL CHARACTERISTICS**






Figure 2. Transfer Characteristics




Figure 3. On–Resistance vs. Gate–to–Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On–Resistance Variation with Temperature





Figure 6. Drain-to-Source Leakage Current vs. Voltage






Figure 11. Threshold Voltage

Figure 12. Single Pulse Maximum Power Dissipation

#### **TYPICAL CHARACTERISTICS**




Figure 13. Maximum Rated Forward Biased Safe Operating Area





Figure 14. FET Thermal Response


#### **DEVICE ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
NTLUD3A260PZTAG	UDFN6 (Pb-Free)	3000 / Tape & Reel
NTLUD3A260PZTBG	UDFN6 (Pb-Free)	3000 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

#### PACKAGE DIMENSIONS





DETAIL B

SIDE VIEW

**BOTTOM VIEW** 


0.05 C


0.05 C

**DETAIL A** 

6X K

(A3)






#### NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: MILLIMETERS.
  3. DIMENSION b APPLIES TO PLATED TERMINAL
- DIMENSION b APPLIES TO PLATED TERMINA AND IS MEASURED BETWEEN 0.15 AND 0.30 mm FROM TERMINAL.
- COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

	MILLIMETERS		
DIM	MIN	MAX	
Α	0.45	0.55	
A1	0.00	0.05	
A3	0.13 REF		
b	0.20	0.30	
D	1.60 BSC		
Е	1.60 BSC		
е	0.50 BSC		
D1	1.14	1.34	
D2	0.38	0.58	
E1	0.54	0.74	
K	0.20		
L	0.15	0.35	
L1		0.10	

## D1 SOLDERMASK DEFINED MOUNTING FOOTPRINT\*



DIMENSIONS: MILLIMETERS

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

#### μCool is a trademark of Semiconductor Components Industries, LLC (SCILLC).

C A B

0.10

0.05 C NOTE 3

ON Semiconductor and IIII are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclains any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5773-3850 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative