

APPROVAL SHEET

RFBPF Series – 1608(0603)- RoHS Compliance

MULTILAYER CERAMIC Band PASS FILTER

Halogens Free Product

1805MHz ~ 2025MHz Band Working Frequency

P/N: RFBPF16081G9DS8T60

*Contents in this sheet are subject to change without prior notice.

FEATURES


- 1. Miniature footprint: 1.6 X 0.8 X 0.70 mm³.
- 2. Low Profile Thickness
- 3. Low Insertion loss
- 4. High attenuation on harmonic suppressed
- 5. LTCC process

APPLICATIONS

1. 1805 ~ 2025MHz working frequency.

CONSTRUCTION

Top view



PIN	PIN Connection		Connection
1	Input port	Input port 3 Output po	
2	GND	4	GND

DIMENSIONS


Figure	Symbol	Dimension (mm)	
<u> </u>	T -	L	1.60 ± 0.10
Top view ≥		W	0.80 ± 0.10
		Т	0.7 max.
	Side view	А	0.55 ± 0.10
Side view		В	0.60 ± 0.10
		С	0.25 ± 0.10
Bottom view		D	0.23 ± 0.10
		E	0.40 ± 0.10
F E D C		F	0.12 ± 0.10
		G	0.125 ± 0.10
		Н	0.21 ± 0.10



ELECTRICAL CHARACTERISTICS

RFBPF16081G9DS8T60	Specification
Frequency Range	1805 ~ 2025 MHz
Insertion Loss	1.6 dB max.
	30 dB min. @ 700 ~ 950 MHz
	15 dB min. @ 950 ~ 1050 MHz
	25 dB min. @ 2400 ~ 2500 MHz
Attenuation	35 dB min. @ 2700 ~ 5400 MHz
	35 dB min. @ 5500 ~ 6200 MHz
	35 dB min. @ 9350 ~ 10150 MHz
	20 dB min. @ 10500 ~ 12750 MHz
VSWR	2.0 max
Impedance	50 Ω
Operating Temperature Range	-40~ +85°C
Moisture sensitivity levels	MSL is LEVEL 1 (Refer to : IPC/JEDEC J-STD-020)
Typical I	Electrical Chart
S-Parameters (dB) -10 -20 -30 -40 -40 -70 -0.5 1.5 2.5 3.5 4.5	Insertion Loss Return Loss 5.5 6.5 7.5 8.5 9.5 10.5 11.5 12.5 13.5 freq, GHz

SOLDER LAND PATTERN





RELIABILITY TEST

Test item	Test condition / Test method	Specification
Solderability JIS C 0050-4.6 JESD22-B102D	*Solder bath temperature : $235 \pm 5^{\circ}$ C *Immersion time : 2 ± 0.5 sec Solder : Sn3Ag0.5Cu for lead-free	At least 95% of a surface of each terminal electrode must be covered by fresh solder.
Leaching (Resistance to dissolution of metallization) IEC 60068-2-58	*Solder bath temperature : $260 \pm 5^{\circ}\text{C}$ *Leaching immersion time : $30 \pm 0.5 \text{ sec}$ Solder : SN63A	Loss of metallization on the edges of each electrode shall not exceed 25%.
Resistance to soldering heat JIS C 0050-5.4	*Preheating temperature: 120~150°C, 1 minute. *Solder temperature: 270±5°C *Immersion time: 10±1 sec Solder: Sn3Ag0.5Cu for lead-free Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C. Loss of metallization on the edges of each electrode shall not exceed 25%.
Drop Test JIS C 0044 Customer's specification.	*Height: 75 cm *Test Surface: Rigid surface of concrete or steel. *Times: 6 surfaces for each units; 2 times for each side.	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Vibration JIS C 0040	*Frequency: 10Hz~55Hz~10Hz(1min) *Total amplitude: 1.5mm *Test times: 6hrs.(Two hrs each in three mutually perpendicular directions)	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Adhesive Strength of Termination JIS C 0051- 7.4.3	*Pressurizing force : 5N(≦0603) ; 10N(>0603) *Test time : 10±1 sec	No remarkable damage or removal of the termination.
Bending test JIS C 0051- 7.4.1	The middle part of substrate shall be pressurized by means of the pressurizing rod at a rate of about 1 mm/s per second until the deflection becomes 1mm/s and then pressure shall be maintained for 5±1 sec. Measurement to be made after keeping at room temperature for 24±2 hours	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.

Approvarance		
Temperature cycle JIS C 0025	 30±3 minutes at -40°C±3°C, 10~15 minutes at room temperature, 30±3 minutes at +85°C±3°C, 10~15 minutes at room temperature, Total 100 continuous cycles Measurement to be made after keeping at room temperature for 24±2 hrs 	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
High temperature JIS C 0021 Humidity	*Temperature: 85°C±2°C *Test duration: 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs *Humidity: 90% to 95% R.H.	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C. No mechanical damage.
(steady conditions) JIS C 0022	*Temperature: 40±2°C *Time: 1000+24/-0 hrs. Measurement to be made after keeping at room temperature for 24±2 hrs % 500hrs measuring the first data then 1000hrs data	Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Low temperature JIS C 0020	*Temperature : -40°C±2°C *Test duration : 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.

SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,





Fig 2. Infrared soldering profile

ORDERING CODE

RF	BPF	1608	1G9	D	S8T60
Walsin	Product Code	Dimension code	Central	Application	Specification
RF device	BPF:	Per 2 digits of	Frequency	D:GSM900/	Design Code
	Band Pass Filter	Length, Width:	1G9 :1.9 GHz	DCS1800	
		e.g. :			
		1608 =			
		Length 16,			
		Width 08			

Minimum Ordering Quantity: 4000 pcs per reel.

PACKAGING




Paper Tape specifications (unit :mm)

Index	Ao	Во	ΦD	Т	W
Dimension (mm)	0.975± 0.05	1.76 ±0.05	1.55 + 0.05	0.75± 0.10	8.0 ± 0.10
Index	E	F	Po	P1	P2
Dimension (mm)	1.75 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05



Reel dimensions



Index	А	В	С
Dimension (mm)	Ф178.0	Ф60.0	Ф13.0

Taping Quantity:4000 pieces per 7" reel

CAUTION OF HANDLING

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection, which can be confirmed.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.

■ Temperature : -10 to +40°C

Humidity: 30 to 70% relative humidity

- Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
- Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be storage under the airtight packaged condition.