

APPROVAL SHEET

MULTILAYER CERAMIC DIPLEXER

RFDIP Series - 1608(0603)- RoHS Compliance

Halogens Free Product

698~960 MHz /1710~2700 MHz Band RF Application

P/N: RFDIP1608070GM1T76

*Contents in this sheet are subject to change without prior notice.



FEATURES


- 1. Miniature footprint: 1.6 X 0.8 X 0.7 mm³
- 2. Low Insertion Loss
- 3. LTCC process

APPLICATIONS

1. 698~960 MHz /1710~2700 MHz working frequency

CONSTRUCTION

Top view



PIN	Connection	PIN	Connection
1	GND	4	Lower Freq. Port
2	Common Port	5	GND
3	GND	6	Higher Freq. Port

DIMENSIONS

	Figure	Symbol	Dimension (mm)
		L	1.60 ± 0.10
Top view	L T	W	0.80 ± 0.10
	→ → → →	Т	0.70 ± 0.10
		А	0.25 ± 0.15
Bottom view	A B C	В	0.35 ± 0.10
		С	0.22 ± 0.10
		D	0.225 ± 0.05
Side view	G H	E	0.22 ± 0.05
Side view		F	0.065 ± 0.065
		G	0.25 ± 0.15
		Н	0.32 ± 0.15



ELECTRICAL CHARACTERISTICS

RFDIP1608070GM1T76	Specification		
Frequency range	698~960 MHz	1710~2700 MHz	
Insertion Loss	0.80 dB max. (0.45 dB typ.) at 25°C	0.70 dB max. (0.50 dB typ.) at 25°C	
Insertion Loss	1.0 dB max. at -40°C ~ +85°C	0.9 dB max. at-40°C ~ +85°C	
Attonuation	25 dB min. (27dB typ.) @	20 dB min. (22dB typ.) @ 698~960 MHz	
Attenuation	1710~2700 MHz	20 dB min. (25dB typ.) @ 5150~5850 MHz	
Isolation	20 dB min. (22 dB typ.) @ 698~960 MHz		
เรอเลแอก	25 dB min. (27 dB typ.) @ 1710~2700 MHz		
VSWR	2.0 max.		
Impedance	50 Ω		
Moisture sensitivity levels	MSL is LEVEL 1 (Refer to : IPC/JEDEC J-STD-020)		

Operating & Storage Condition (Component)


Operation Temperature Range: -40°C ~ +85°C Storage Temperature Range: -40°C ~ +85°C

Storage Condition before Soldering (Included packaging material)


Storage Temperature Range: +5 ~ +40 ℃ Humidity: 30 to 70% relative humidity

TYPICAL ELECTRICAL PERFORMANCE





SOLDER LAND PATTERN





RELIABILITY TEST

Test item	Test condition / Test method	Specification
Solderability	*Solder bath temperature : 235 \pm 5°C	At least 95% of a surface of each terminal
JIS C 0050-4.6	*Immersion time : 2 ± 0.5 sec	electrode must be covered by fresh solder.
JESD22-B102D	Solder : Sn3Ag0.5Cu for lead-free	
Leaching (Resistance to	*Solder bath temperature : 260 ± 5°C	Loss of metallization on the edges of each
dissolution of	*Leaching immersion time : 30 ± 0.5 sec	electrode shall not exceed 25%.
metallization)	Solder : SN63A	
IEC 60068-2-58		
Resistance to soldering	*Preheating temperature: 120~150°C,	
heat	r reneating temperature : 120~130 G,	No mechanical damage.
JIS C 0050-5.4	1 minute.	Electrical specification shall satisfy the
	*Solder temperature: 270±5°C	descriptions in electrical characteristics under
	*Immersion time: 10±1 sec	the operational temperature range within -40
	Solder : Sn3Ag0.5Cu for lead-free	~ 85°C.
	Measurement to be made after keeping at	Loss of metallization on the edges of each
		electrode shall not exceed 25%.
	room temperature for 24±2 hrs	
Drop Test	*Height: 75 cm	No mechanical damage.
JIS C 0044	*Test Surface : Rigid surface of concrete or	Electrical specification shall satisfy the
Customer's specification.	steel.	descriptions in electrical characteristics under
	*Times: 6 surfaces for each units; 2 times	the operational temperature range within -40
	for each side.	~ 85°C.
Vibration	*Frequency: 10Hz~55Hz~10Hz(1min)	No mechanical damage.
JIS C 0040	*Total amplitude:1.5mm	Electrical specification shall satisfy the
	*Test times: 6hrs.(Two hrs each in three	descriptions in electrical characteristics under
	mutually perpendicular directions)	the operational temperature range within -40
Adhesive Strength		~ 85°C.
of Termination	*Pressurizing force :	No remarkable damage or removal of the
JIS C 0051- 7.4.3	5N(≦0603) ; 10N(>0603)	termination.
	*Test time: 10±1 sec	
Bending test	The middle part of substrate shall be	No mechanical damage.
JIS C 0051- 7.4.1	pressurized by means of the pressurizing rod	Electrical specification shall satisfy the
	at a rate of about 1 mm/s per second until the	descriptions in electrical characteristics under
	deflection becomes 1mm/s and then pressure	the operational temperature range within -40
	shall be maintained for 5±1 sec.	~ 85°C.
	Measurement to be made after keeping at	
	room temperature for 24±2 hours	

7 tppi o rai olioot		
Temperature cycle JIS C 0025	 30±3 minutes at -40°C±3°C, 10~15 minutes at room temperature, 30±3 minutes at +85°C±3°C, 10~15 minutes at room temperature, Total 100 continuous cycles Measurement to be made after keeping at room temperature for 24±2 hrs 	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
High temperature JIS C 0021	*Temperature: 85°C±2°C *Test duration: 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Humidity (steady conditions) JIS C 0022	*Humidity: 90% to 95% R.H. *Temperature: 40±2°C *Time: 1000+24/-0 hrs. Measurement to be made after keeping at room temperature for 24±2 hrs % 500hrs measuring the first data then 1000hrs data	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.
Low temperature JIS C 0020	*Temperature : -40°C±2°C *Test duration : 1000+24/-0 hours Measurement to be made after keeping at room temperature for 24±2 hrs	No mechanical damage. Electrical specification shall satisfy the descriptions in electrical characteristics under the operational temperature range within -40 ~ 85°C.

SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,





Fig 2. Infrared soldering profile

ORDERING CODE

RF	DIP	160807	0	G	M1T76
Walsin	Product	Dimension code	Unit of dimension	Application	Specification
RF	Code	Per 2 digits of Length, Width,	0 : 0.1 mm	G: GSM850/ PCS	Design code
device	DIP : Diplexer	Thickness :	1 : 1.0 mm	1900	
		e.g. :			
		160807 =			
		Length 16,			
		Width 08,			
		Thickness 07			

Minimum Ordering Quantity: 4000 pcs per reel.

PACKAGING




Paper Tape specifications (unit :mm)

Index	Ao	Во	ΦD	Т	W
Dimension (mm)	0.975± 0.10	1.76 ±0.10	1.55 + 0.05	0.75± 0.10	8.0 ± 0.10
Index	Е	F	Po	P1	P2
Dimension (mm)	1.75 ± 0.10	3.50 ± 0.05	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.05



Reel dimensions



Index	Α	В	С
Dimension (mm)	Ф178.0	Ф60.0	Ф13.0

Taping Quantity:4000 pieces per 7" reel

CAUTION OF HANDLING

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.

■ Temperature : +5 to +40°C

Humidity: 30 to 70% relative humidity

- Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
- Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
- Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
- Products should be storage under the airtight packaged condition.