

August 2010

USB1T11A — Universal Serial Bus Transceiver

Features

- Complies with Universal Serial Bus Specification 1.1
- Utilizes Digital Inputs and Outputs to Transmit and Receive USB Cable Data
- Supports 12Mbit/s "Full Speed" and 1.5Mbit/s "Low Speed" Serial Data Transmission
- Compatible with the VHDL "Serial Interface Engine" from USB Implementers' Forum
- Supports Single-ended Data Interface
- Single 3.3V Supply
- ESD Performance: Human Body Model >9.5kV on D-, D+ pins only >4kV on all other pins

Description

The USB1T11A is a one-chip, generic USB transceiver. It is designed to allow 5.0V or 3.3V programmable and standard logic to interface with the physical layer of the Universal Serial Bus. It is capable of transmitting and receiving serial data at both full-speed (12Mbit/s) and low-speed (1.5Mbit/s) data rates.

The input and output signals of the USB1T11A conform with the "Serial Interface Engine." Implementation of the serial interface engine allows designers to make USB-compatible devices with off-the-shelf logic to modify and update the application.

Ordering Information

Part Number	Operating Temperature Range	Package	Packing Method
USB1T11AM		14-Lead, Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150-Inch Narrow	Tube
USB1T11AMX	-40 to +85°C	14-Lead, Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150-Inch Narrow	Tape and Reel
USB1T11AMTC	-40 to +65 C	14-Lead, Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide	Tube
USB1T11AMTCX		14-Lead, Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide	Tape and Reel




Figure 1. Logic Diagram

Pin Configuration




Figure 2. TSSOP and SOIC Pin Assignments

Pin Descriptions

Pin Names	I/O	Description						
RCV	0	Receive Data. CMOS	Receive Data. CMOS level output for USB differential input.					
/OE	1		Output Enable. Active LOW, enables the transceiver to transmit data on the bus. When not active, the transceiver is in receive mode.					
Mode	1		Mode . When left unconnected, a weak pull-up transistor pulls it to V_{CC} and, in this GND, the V_{MO}/F_{SEO} pin takes the function of F_{SEO} (force SEO).					
		Inputs to differential d	river. (Outputs from	SIE.)				
		Mode	V_{PO}	V _{MO} /F _{SEO}	RESULT			
		0	0	0	Logic "0"			
		0	0	1	/SEO			
$V_{PO}, V_{MO}/F_{SEO}$		0	1	0	Logic "1"			
V PO, V MO/T SEO		0	1	1	/SEO			
		1	0	0	/SEO			
		1 0		1	Logic "0"			
		1	1	0	Logic "1"			
		1	1	1	Illegal Code			
		Buffered version of D- single ended zero (/SI	and D+. Outputs a EO), error condition	re logic "0" and logs, and interconnec	gic "1." Used to detect sted speed. (Input to SIE).			
		V _P		V _M	RESULT			
V_P,V_M	0	0		0	/SEO			
		0		1	Low Speed			
		1		0	Full Speed			
		0		1	Error			
D+, D-	AI/O	Data+, Data Differen	tial data bus confor	ming to the Univer	sal Serial Bus standard.			
SUSPND	1	Suspend . Enables a I suspend pin is active, STATE.	ow-power state whi it drives the RCV p	lle the USB bus is in to a logic "0" sta	inactive. While the tte. Both D+ and D- are 3-			
Speed	I	Edge Rate Control. Logic "1" operates at edge rates for "full speed." Logic "0" operates edge rates for "low speed."						
Vcc		3.0 to 3.6 power supp	ly.					
GND	<u> </u>	Ground reference.						

Functional Truth Table

	Input			I/	O		Outp	uts		
Mode	V_{PO}	V _{MO} /F _{SEO}	/OE	SUSPND	D+	D-	RCV	V _P	V _M	Result
0	0	0	0	0	0	1	0	0	1	Logic "0"
0	0	1	0	0	0	0	Undefined State	0	0	/SEO
0	1	0	0	0	1	0	1	1	0	Logic "1"
0	1	1	0	0	0	0	Undefined State	0	0	/SEO
1	0	0	0	0	0	0	Undefined State	0	0	/SEO
1	0	1	0	0	0	1	0	0	1	Logic "0"
1	1	0	0	0	1	0	1	1	0	Logic "1"
1	1	1	0	0	1	1	Undefined State	Undefined State	Undefined State	Illegal Code
Don't Care	Don't Care	Don't Care	1	0	3-State	3-State	Undefined State	Undefined State	Undefined State	D+/D- Hi-Z
Don't Care	Don't Care	Don't Care	1	1	3-State	3-State	Undefined State	Undefined State	Undefined State	D+/D- Hi-Z

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Paramet	Parameter			
V _{CC}	DC Supply Voltage		0.5	7.0	V
I _{IK}	DC Input Diode Current, V _{IN} <0V			-50	mA
V_{IN}	Input Voltage ⁽¹⁾	0.5	5.5	V	
V _{I/O}	Input Voltage	0.5	V _{CC} + 0.5	٧	
lok	Output Diode Current, Vo>Vcc or \		±50	mA	
Vo	Output Voltage		0.5	V _{CC} + 0.5	V
1-	Output Source or Sink Current	V _P , V _M , RCV Pins		±15	mA
lo	$(V_O = 0 \text{ to } V_{CC})$	D+/D- Pins		±50	IIIA
I _{CC} / I _{GND}	V _{CC} / GND Current			±100	mA
T _{STG}	Storage Temperature Range		-60	+150	°C

Note:

The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are
observed.

Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to Absolute Maximum Ratings.

Symbol	Parameter	Min.	Max.	Unit
Vcc	Power Supply Operating	3.0	3.6	V
V_{IN}	Input Voltage	0	5.5	V
V _{AI/O}	Input Range for AI/0	0	V_{CC}	V
Vo	Output Voltage	0	V _{CC}	V
T _A	Operating Ambient Temperature, Free Air	-40	+85	°C

DC Electrical Characteristics Digital Pins

Over recommended range of supply voltage and operating free air temperature unless otherwise noted. $V_{\rm CC}$ = 3.0V to 3.6V.

Cumbal	Doromotor	Conditions	T _A =-40 to +85°C			l lusit a	
Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units	
Input Leve	ls					•	
V _{IL}	Low-Level Input Voltage				0.8	V	
V _{IH}	High-Level Input Voltage		2			V	
Output Lev	rels						
	1 10 1 11/1	I _{OL} =4mA			0.4	V	
V _{OL}	Low-Level Output Voltage	I _{OL} =20µA			0.1	7 V	
	High Lavel Output Valtage	I _{OH} =4mA	2.5			V	
V _{OH}	High-Level Output Voltage	I _{OH} =20μA	V _{CC} -0.1			V	
Leakage C	urrent						
I _{IN}	Input Leakage Current	V _{CC} =3.0 to 3.6			±5	μΑ	
I _{CCFS}	Supply Current, Full Speed	V _{CC} =3.0 to 3.6			5	mA	
I _{CCLS}	Supply Current, Low Speed	V _{CC} =3.0 to 3.6			5	mA	
Iccq	Quiescent Supply Current	V _{CC} =3.0 to 3.6, V _{IN} =V _{CC} or GND			5	mA	
Iccs	Supply Current in Suspend	V _{CC} =3.0 to 3.6, Mode=V _{CC}		V	10	μΑ	

DC Electrical Characteristics D+/D- Pins

Over recommended range of supply voltage and operating free air temperature unless otherwise noted. $V_{CC} = 3.0 V$ to 3.6 V.

Symbol	Banamatan		T _A =			
	Parameter	Conditions	Min.	Тур.	Max.	Units
Input Leve	ls					
V_{DI}	Differential Input Sensitivity	(D+) - (D-)	0.2			V
V_{CM}	Differential Common-Mode Range	Includes V _{DI} Range	0.8	į.	2.5	V
V _{SE}	Single-Ended Receiver Threshold		0.8		2.0	V
Output Lev	vels					
V _{OL}	Static Output Low-Voltage				0.3	V
V _{OH}	Static Output High-Voltage	R_L of $1.5k\Omega$ to $3.6V$	2.8		3.6	V
V_{CR}	Differential Crossover	R_L of $1.5k\Omega$ to GND	1.3		2.0	V
Leakage C	urrent			7		
l _{OZ}	High Z-State Data Line Leakage Current	0V <v<sub>IN<3.3V</v<sub>			±5	μA
Capacitano	ce control of the con					
C _{IN} ⁽²⁾	Transceiver Capacitance	Pin to GND			10	pF
C _{IN} ,	Capacitance Match				10	%
Output Res	sistance				•	
¬ (3)	Driver Output Resistance	Steady-State Drive	4		20	Ω
$Z_{DRV}^{(3)}$	Resistance Match				10	%

Notes:

- 2. This specification is guaranteed by design and statistical process distribution.
- 3. Excludes external resistor. To comply with USB specification 1.1, external series resistors of 24W ±1% each on D+ and D- are recommended.

AC Electrical Characteristics D+/D- Pins, Full Speed

Over recommended range of supply voltage and operating free air temperature unless otherwise noted. V_{CC} = 3.0V to 3.6V, C_L = 50Pf; R_L = $k\Omega$ on D+ to V_{CC} .

Ols al	Doromotor	O a malitia ma	T _A =	11		
Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
Driver Cha	racteristics					•
t _R , t _F	Rise and Fall Time	10 and 90%, Figure 4	4		20	ns
t _{RFM}	Rise/Fall Time Matching	t _R / t _F	90		110	%
V _{CRS}	Output Signal Crossover Voltage		1.3		2.0	V
Driver Timi	ings					
t _{PLH}	Driver Propagation Delay (V _{PO} ,V _{MO} /F _{SEO} to D+/D-)	Figure 4			18	ns
t _{PHZ} , t _{PLZ}	Driver Disable Delay (/OE to D+/D-)	Figure 6			13	ns
t _{PZH} , t _{PZL}	Driver Enable Delay (/OE to D+/D-)	Figure 6			17	ns
Receiver T	imings					
t _{PLH}	Receiver Propagation Delay	Figure 5			16	ns
t _{PHL}	D+/D- to RVC	Figure 5			19	ns
t _{PLH} , t _{PHL}	Single-ended Receiver Delay (D+/D- to V _P , V _M)	Figure 5			8	ns


AC Electrical Characteristics D+/D- Pins, Low Speed

Over recommended range of supply voltage and operating free air temperature unless otherwise noted. V_{CC} = 3.0V to 3.6V, C_L = 200pF to 600pF; R_L = 1.5k Ω on D- to V_{CC} .

Cumbal	Doromotor	Conditions	T _A =	11		
Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units
Driver Cha	racteristics					
t _{LR} , t _{LF}	Rise and Fall Time	10 and 90%, Figure 4	75		300	ns
t _{RFM}	Rise/Fall Time Matching	t _R / t _F	80		120	%
V _{CRS}	Output Signal Crossover Voltage		1.3		2.0	V
Driver Tim	ings					
t _{PLH} , t _{PHL}	Driver Propagation Delay (V _{PO} ,V _{MO} /F _{SEO} to D+/D-)	Figure 4			300	ns
t _{PHZ} , t _{PLZ}	Driver Disable Delay (/OE to D+/D-)	Figure 6			13	ns
t _{PZH} , t _{PZL}	Driver Enable Delay (/OE to D+/D-)	Figure 6			205	ns
Receiver T	imings					D
t _{PLH} , t _{PHL}	Receiver Propagation Delay (D+/D- to RVC)	Figure 5			18	ns
t _{PLH} , t _{PHL}	Single-ended Receiver Delay (D+/D- to V _P , V _M)	Figure 5			28	ns

AC Loadings and Waveforms

V_{OL} and V_{OH} are the typical output voltage drops that occur with the output load. V_{CC} never goes below 3.0V.







Figure 3. Rise and Fall Times

Figure 4. V_{PO}, V_{MO}/F_{SEO} to D+/D-






Figure 5. D+/D- to RCV, V_P/V_M

Figure 6. /OE to D+/D-

Test Circuits and Waveforms





Figure 7. Load for V_M/V_P and RCV

Figure 8. Load for Enable and Disable Times



Test	S1
D-/LS	Close
D+/LS	Open
D-/FS	Open
D+/FS	Close

C_L=50pF, Full Speed

C_L=200pF, Full Speed (Minimum Timing)

C_L=600pF, Full Speed (Maximum Timing)

 $1.5k\Omega$ on D-(Low Speed) or D+ (Full Speed) only.

Figure 9. Load for D+/D-

Physical Dimensions





Figure 10. 14-Lead, Small Outline Integrated Circuit (SOIC) MO-012, 0.150-inch Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/packaging/.

DETAIL A

Physical Dimensions



- C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH,
- AND TIE BAR EXTRUSIONS D. DIMENSIONING AND TOLERANCES PER ANSI
- Y14.5M, 1982
- E. LANDPATTERN STANDARD: SOP65P640X110-14M
- F. DRAWING FILE NAME: MTC14REV6

Figure 11. 14-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: http://www.fairchildsemi.com/packaging/.





SYSTEM ®*
GENERAL

XS™

The Power Franchise®

TRADEMARKS

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

AccuPower™ Auto-SPM™ Build it Now™ CorePLUS™ CorePOWER™ CROSSVOLT™ CTL™ Current Transfer Logic™

DEUXPEED⁶ Dual Cool™ EcoSPARK® EfficientMa×™ ESBC™

Fairchild® Fairchild Semiconductor® FACT Quiet Series™ FACT® FastvCore™

FETBench™ FlashWriter®* F-PFS™ FRFET®

Global Power ResourceSM Green FPS™

Green FPS™ e-Series™ G*m*ax™ GTO™

IntelliMAX™ ISOPLANAR™ MegaBuck™ MICROCOUPLER™ MicroFET™

MicroPak™ MicroPak2™ MillerDrive™ MotionMa×™ Motion-SPM™ OptoHiT™ OPTOLOGIC® OPTOPLANAR®

PDP SPM™

Power-SPM™ PowerTrench® PowerXS™

Programmable Active Droop™

QFET QSTM

> Quiet Series™ RapidConfigure™

Saving our world, 1mW/W/kW at a time™

SignalWise™ SmartMax™ SMART START™ SPM®

STEALTH™ SuperFET™ SuperSOT™3 SuperSOT™-6 SuperSOT™-8

SupreMOS[®] SyncFET™ Sync-Lock™

TinyBoost™ TinyBuck™ TinyCalc™ TinyLogic[®] TINYOPTO** TinyPower** TinyPV⁄M™ TinyWire™ TriFault Detect™ TRUECURRENT"* μSerDes™ UHC Ultra FRFET™ UniFET™ VCX™ VisualMax™

* Trademarks of System General Corporation, used under license by Fairchild Semiconductor.

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN. WHICH COVERS THESE PRODUCTS

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- A critical component in any component of a life support, device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness

ANTI-COUNTERFEITING POLICY

Fairchild Semiconductor Corporation's Anti-Counterfeiting Policy. Fairchild's Anti-Counterfeiting Policy is also stated on our external website, www.fairchildsemi.com, under Sales Support

Counterfeiting of semiconductor parts is a growing problem in the industry. All manufacturers of semiconductor products are experiencing counterfeiting of their parts. Customers who inadvertently purchase counterfeit parts experience many problems such as loss of brand reputation, substandard performance, failed applications, and increased cost of production and manufacturing delays. Fairchild is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. Fairchild strongly encourages customers to purchase Fairchild parts either directly from Fairchild or from Authorized Fairchild Distributors who are listed by country on our web page cited above. Products customers buy either from Fairchild directly or from Authorized Fairchild Distributors are genuine parts, have full traceability, meet Fairchild's quality standards for handling and storage and provide access to Fairchild's full range of up-to-date technical and product information. Fairchild and our Authorized Distributors will stand behind all warranties and will appropriately address any warranty issues that may arise. Fairchild will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. Fairchild is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative / In Design	Datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	Datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	Datasheet contains specifications on a product that is discontinued by Fairchild Semiconductor. The datasheet is for reference information only.

Rev 149