

<u>To;</u>				SPEC No. ISSUE:	LH17204 Feb. 23. 2017		
		TARGET	TECHNICAL	LITERAT	URE		
	Product Ty	pe	Laser Diode				
	Model No.	Model NoGH05035A2G					
XThese specifications contain <u>4</u> pages including the cover and appendix. If you have any objections, please contact us before issuing purchasing order Output Description 1. The page is the cover and appendix. If you have any objections, please contact us before issuing purchasing order Output Description Outpu							
◆ This technical literature is subject to change without notice. ◆							
			Lightir Electro	oment Dept., I og Business Unit onic Components A CORPORATION	und Devices BU		



SPEC.No. **LH17204**PAGE **1/3**

Product name: LASER DIODE

Model No. : GH05035A2G

1. These specification sheets include materials protected under copyright of Sharp Corporation ("Sharp").

Please handle with great cares and do not reproduce or cause anyone to reproduce them without Sharp's consent.

2. When using this Sharp product, please observe the absolute maximum ratings, other conditions and instructions for use described in the specification sheets, as well as the precautions mentioned below.

Sharp assumes no responsibility for any damages resulting from use of the product which does not comply with absolute maximum ratings, other conditions and instructions for use included in the specification sheets, and the precautions mentioned below.

(Precautions)

- (1) In making catalogue or instruction manual based on the specification sheets, please verify the validity of the catalogue or instruction manuals after assembling Sharp products in customer's products at the responsibility of customer.
- (2) This Sharp product is designed for use in the following application areas;
 - Computers OA equipment Telecommunication equipment (Terminal) Measuring equipment
 - Tooling machines Audio visual equipment Home appliances

If the use of the Sharp product in the above application areas is for equipment listed in paragraphs (3) or (4), please be sure to observe the precautions given in those respective paragraphs.

- (3) Appropriate measures, such as fail-safe design and redundant design considering the safety design of the overall system and equipment, should be taken to ensure reliability and safety when Sharp product is used for equipment in responsibility of customer which demands high reliability and safety in function and precision, such as;
 - Transportation control and safety equipment (aircraft, train, automobile etc.)
 - Traffic signals Gas leakage sensor breakers Rescue and security equipment
 - Other safety equipment
- (4)Sharp product is designed for consumer goods and controlled as consumer goods in production and quality.

 Please do not use this product for equipment which require extremely high reliability and safety in function and precision, such as;
 - Space equipment Telecommunication equipment (for trunk lines)
 - Nuclear power control equipment Medical equipment
- (5) Please contact and consult with a Sharp sales representative if there are any question regarding interpretation of the above four paragraphs.

3. Disclaimer

The warranty period for Sharp product is one (1) year (or six (6) months in case of generalized product) after shipment. During the period, if there are any products problem, Sharp will repair (if applicable), replace or refund. Except the above, both parties will discuss to cope with the problems.

The failed Sharp product after the above one (1) year (or six (6) month for generalized product) period will be coped with by Sharp, provided that both parties shall discuss and determine on sharing responsibility based on the analysis results thereof subject to the above scope of warranty.

The warranty described herein is only for Sharp product itself which are purchased by or delivered to customer. Damages arising from Sharp product malfunction or failure shall be excepted.

Sharp will not be responsible for the Sharp product due to the malfunction or failures thereof which are caused by:

- (1) storage keep trouble during the inventory in the marketing channel.
- (2) intentional act, negligence or wrong/poor handling.
- (3) equipment which Sharp products are connected to or mounted in.
- (4) disassembling, reforming or changing Sharp products.
- (5) installation problem.
- (6) act of God or other disaster (natural disaster, fire, flood, etc.)
- (7) external factors (abnormal voltage, abnormal electromagnetic wave, fire, etc.)
- (8) special environment (factory, coastal areas, hotspring area, etc.)
- (9) phenomenon which cannot be foreseen based on the practical technologies at the time of shipment.
- (10) the factors not included in the product specification sheet.
- 4. Please contact and consult with a Sharp sales representative for any questions about Sharp product.



MODEL No.


GH05035A2G

PAGE

2/3


LH17204

4. Outline dimensions and Terminal connections



Enlarged drawing around the emission point $\begin{array}{c} X \\ Y \\ 0 \pm 0.08 \\ \end{array}$ Emission point 0 ± 0.08

Center of the imaginary circle which goes through the three point around the stem



Mass of the product : 0.31g (reference value)

Marking

Position : TBD

Printed contents : TBD

Note 1) Dimension of the bottom of leads.

Note 2) These dimensions are valid only in the range of 0 \sim 0.6mm below from the reference plane.

Note 3) Please don't connect the lead pin No. 2 to the driving circuit.

GENERAL TOLERANCES \pm O . 2 UNIT:mm

No.	Component	Material	Finish		
1	Laser Diode Chip	InAlGaN	-		
2	Stem	Fe/Cu	Gold-plated		
3	Cap	45Alloy	Nickel+Pd plated		
4	Window glass	Borosilicated glass	-		
(5)	Lead pins	Kovar	Gold-plated		



MODEL No.
GH05035A2G

PAGE

3/3 LH17204

5. Ratings and characteristics

Absolute Maximum Ratings

 $(Tc=25^{\circ}C(Note 1))$

Parameter		Symbol	Symbol Ratings	
Optical power output(CW) (Note 2)		Po	35	mW
Reverse voltage	Laser diode	Vrl	2	V
Operatings temperature(case temp.)		Top(c)	-10~+60	$^{\circ}$ C
Storage temperature(case temp.)		Tstg	-40~+85	${\mathbb C}$

(Note 1) Tc : Case temperature

(Note 2)CW: Continuous Wave Operation

Electro-optical Characteristics(Note 1) (Tc=25°C)

Electro optical Characteristics(Note 1) (1c=25 C)							
Parameter		Symbol	Conditions	min	typ	max	unit
Threshold current		Ith	-	-	70	-	mA
Operating current		Iop		-	125	-	mA
Operating voltage		Vop		-	6.0	-	V
Wavelength		λр		-	505	-	nm
Radiation Charcter- istics	Angle (Note 2) (Note 3)	θ //	Po=30mW	-	8.5	-	0
		θ⊥		-	23.0	-	0
Emission point accuracy	Angle (Note 3)	Δθ //		-3	0	3	0
		Δθ⊥		-3	0	3	0
Differential efficiecy		ηd	20mW I(30mW)-I(10mW)	-	0.5	-	mW/mA

⁽Note 1) Initial value, Continuous Wave Operation.

(Note 3) Paralel to the junction plane.(X-Z plane)

Perpendicular to the junction plane. (Y-Z plane)

⁽Note 2) Angle of 50% peak intensity.(Full angle at half-maximum)